

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331793-935

Luminaire Tested: **S122RDIW-S485D970U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331793-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4934.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32					32			
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28					28			
2	86	79	74	69	78	72	67	63	58	54	51	45	42	41	32	31	30	25					25			
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	21					21			
4	73	62	55	50	65	57	50	46	46	41	38	36	33	30	26	25	23	19					19			
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	20	17					17			
6	62	50	43	37	55	46	39	34	37	33	29	29	26	24	22	20	18	15					15			
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	16	14					14			
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12					12			
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11					11			
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.8
10°-20°	244.4	5.0
20°-30°	315.0	6.4
30°-40°	299.3	6.1
40°-50°	256.4	5.2
50°-60°	195.3	4.0
60°-70°	123.4	2.5
70°-80°	61.6	1.2
80°-90°	18.8	0.4
90°-100°	37.9	0.8
100°-110°	139.1	2.8
110°-120°	371.8	7.5
120°-130°	613.7	12.4
130°-140°	652.7	13.2
140°-150°	606.6	12.3
150°-160°	487.7	9.9
160°-170°	314.3	6.4
170°-180°	108.2	2.2
0°-30°	647.1	13.1
0°-40°	946.4	19.2
0°-60°	1398.1	28.3
0°-90°	1602.0	32.5
90°-120°	548.8	11.1
90°-150°	2421.8	49.1
90°-180°	3332.0	67.5
0°-180°	4934.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	22	1	22	1	22	10
95°	35	54	35	54	35	33
105°	62	250	62	250	62	65
115°	68	473	68	473	68	169
125°	703	669	703	669	703	609
135°	855	828	855	828	855	659
145°	975	960	975	960	975	610
155°	1058	1057	1058	1057	1058	488
165°	1112	1114	1112	1114	1112	314
175°	1133	1139	1133	1139	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	8.5	8.8	8.7	8.6	8.5	8.4	8.2	8.3	7.8	7.9	7.4
90°	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3	17.4	16.4	15.0
92.5°	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1	19.5	19.1	18.3
95°	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9	33.0	32.1	30.8
97.5°	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4	43.7	43.0	40.0
100°	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9	48.4	46.9	43.8
102.5°	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0	50.1	48.2	44.2
105°	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2	52.2	50.2	46.1
107.5°	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1	68.2	70.3	66.1
110°	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4	125.7	144.0	149.8



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7	296.4	363.2	376.2
115°	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3	422.9	507.6	503.1
117.5°	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2	541.7	562.2	559.1
120°	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4	605.3	603.0	599.8
122.5°	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5	643.2	641.9	638.3
125°	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8	696.5	695.2	691.7
127.5°	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0	745.1	743.2	740.6
130°	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2	776.2	774.2	772.1
132.5°	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6	806.8	805.1	803.1
135°	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9	850.1	848.3	846.5
137.5°	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1	890.4	888.6	886.7
140°	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2	916.5	914.9	912.8
142.5°	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2	940.7	939.2	936.9
145°	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9	974.6	973.3	970.2
147.5°	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1	1004.2	1003.2	1000.1
150°	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2	1022.1	1021.0	1018.0
152.5°	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7	1038.5	1037.4	1034.7
155°	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9	1060.8	1059.6	1057.5
157.5°	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6	1079.3	1078.1	1076.5
160°	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5	1090.4	1089.3	1088.2
162.5°	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6	1100.4	1099.2	1098.2
165°	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5	1110.9
167.5°	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4	1123.1	1121.9	1121.4
170°	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7	1128.4	1127.1	1126.8
172.5°	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6	1132.4	1131.1	1130.7
175°	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9	1136.6	1135.3	1135.0
177.5°	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4	1137.4	1136.3	1136.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	7.1	7.1	6.7	6.1	6.0	5.9	6.7	7.7	7.0	6.6	6.5
90°	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9	2.8	4.8	6.9
92.5°	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6	16.4	16.3	16.1
95°	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5	47.4	41.4	35.4
97.5°	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2	89.1	72.2	55.1
100°	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6	120.5	95.5	70.5
102.5°	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1	183.7	178.5	173.1
105°	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1	255.6	261.1	266.6
107.5°	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7	324.2	328.6	332.9
110°	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5	368.3	372.1	376.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6	410.0	413.4	416.8
115°	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0	476.1	479.3	482.4
117.5°	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4	536.0	539.4	542.9
120°	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9	578.7	581.3	584.1
122.5°	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8	615.6	618.5	621.4
125°	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8	671.2	673.6	676.0
127.5°	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7	722.4	725.0	727.6
130°	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0	754.9	757.9	760.7
132.5°	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9	787.4	789.9	792.3
135°	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7	830.6	833.5	836.5
137.5°	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9	873.0	875.0	877.1
140°	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2	900.7	902.2	903.6
142.5°	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9	924.2	925.6	926.9
145°	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1	959.9	959.8	959.6
147.5°	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6	991.8	991.1	990.4
150°	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6	1012.3	1011.0	1009.8
152.5°	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4	1029.9	1028.5	1027.1
155°	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2	1055.5	1053.9	1052.2
157.5°	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5	1076.1	1074.6	1073.2
160°	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1088.2	1087.1	1086.0
162.5°	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8	1098.7	1097.6	1096.5
165°	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0	1112.8	1111.7	1110.7
167.5°	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5	1123.3	1122.3	1121.2
170°	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4	1129.3	1128.3	1127.1
172.5°	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4	1133.2	1132.1	1131.1
175°	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4	1138.2	1136.9	1135.7
177.5°	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3	1139.3	1138.2	1137.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	6.6	6.7	6.5	6.8	7.1	7.1	7.3	7.2	7.4	7.7	7.5
90°	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3	19.2	20.1	20.8
92.5°	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1	20.5	21.0	21.4
95°	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9	34.9	35.7	36.1
97.5°	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4	45.1	45.9	46.3
100°	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9	51.3	52.8	53.6
102.5°	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0	53.9	55.8	57.0
105°	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2	56.2	58.2	59.6
107.5°	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1	64.1	62.1	61.4
110°	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4	89.1	70.9	62.1



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7	163.1	96.3	63.3
115°	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3	253.7	169.0	120.1
117.5°	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2	500.8	480.4	448.5
120°	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4	609.6	611.8	600.5
122.5°	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5	645.8	647.1	645.4
125°	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8	699.0	700.3	701.2
127.5°	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0	748.8	750.7	751.7
130°	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2	780.2	782.2	783.2
132.5°	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6	810.3	812.0	812.8
135°	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9	853.7	855.5	856.3
137.5°	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1	893.9	895.7	896.3
140°	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2	919.8	921.4	921.8
142.5°	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2	943.7	945.2	945.5
145°	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9	977.1	978.4	978.6
147.5°	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1	1006.1	1007.0	1007.1
150°	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2	1024.2	1025.4	1025.5
152.5°	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7	1040.7	1041.8	1041.8
155°	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9	1062.9	1064.0	1063.9
157.5°	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6	1081.8	1083.1	1083.0
160°	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5	1092.5	1093.6	1093.6
162.5°	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6	1102.9	1104.1	1104.0
165°	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6
167.5°	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4	1125.7	1127.0	1126.8
170°	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7	1130.9	1132.2	1132.0
172.5°	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6	1134.9	1136.2	1136.0
175°	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9	1139.2	1140.5	1140.2
177.5°	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4	1139.4	1140.4	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	7.6	7.4	7.7	7.5	7.7	7.4	7.6	7.5	7.7	7.4	7.2
90°	21.1	21.4	21.9	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3
92.5°	21.5	21.8	22.0	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1
95°	35.9	35.7	35.6	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9
97.5°	46.6	46.8	47.0	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4
100°	54.0	54.4	54.8	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9
102.5°	57.5	58.0	58.5	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0
105°	60.4	61.0	61.8	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2
107.5°	62.2	62.9	63.6	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1
110°	62.8	63.5	64.2	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.9	64.5	65.1	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7
115°	106.9	93.8	80.6	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3
117.5°	405.2	362.0	318.7	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2
120°	575.9	551.2	526.5	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4
122.5°	640.6	635.8	631.0	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5
125°	701.8	702.3	702.8	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8
127.5°	751.8	751.9	752.0	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0
130°	782.9	782.7	782.6	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2
132.5°	812.5	812.4	812.2	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6
135°	855.9	855.5	855.1	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9
137.5°	895.7	895.0	894.4	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1
140°	920.9	920.0	919.0	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2
142.5°	944.6	943.7	942.8	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2
145°	977.7	976.7	975.9	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9
147.5°	1006.3	1005.6	1004.8	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1
150°	1024.6	1023.6	1022.7	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2
152.5°	1040.6	1039.4	1038.2	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7
155°	1062.4	1060.9	1059.5	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9
157.5°	1081.5	1080.1	1078.7	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6
160°	1092.3	1091.0	1089.8	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5
162.5°	1102.3	1100.8	1099.2	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6
165°	1115.3	1114.0	1112.8	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0
167.5°	1125.2	1123.5	1121.9	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4
170°	1130.4	1128.8	1127.1	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7
172.5°	1134.4	1132.7	1131.1	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6
175°	1138.3	1136.5	1134.7	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9
177.5°	1138.9	1137.6	1136.3	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	7.3	7.1	7.1	6.8	6.5	6.7	6.6	6.5	6.6	7.0	7.7
90°	17.4	16.4	15.0	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9
92.5°	19.5	19.1	18.3	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6
95°	33.0	32.1	30.8	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5
97.5°	43.7	43.0	40.0	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2
100°	48.4	46.9	43.8	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6
102.5°	50.1	48.2	74.2	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1
105°	52.2	50.2	100.1	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1
107.5°	68.2	70.3	130.1	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7
110°	125.7	144.0	196.8	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	296.4	363.2	376.2	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6
115°	422.9	507.6	503.1	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0
117.5°	541.7	562.2	559.1	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4
120°	605.3	603.0	599.8	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9
122.5°	643.2	641.9	638.3	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8
125°	696.5	695.2	691.7	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8
127.5°	745.1	743.2	740.6	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7
130°	776.2	774.2	772.1	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0
132.5°	806.8	805.1	803.1	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9
135°	850.1	848.3	846.5	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7
137.5°	890.4	888.6	886.7	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9
140°	916.5	914.9	912.8	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2
142.5°	940.7	939.2	936.9	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9
145°	974.6	973.3	970.2	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1
147.5°	1004.2	1003.2	1000.1	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6
150°	1022.1	1021.0	1018.0	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6
152.5°	1038.5	1037.4	1034.7	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4
155°	1060.8	1059.6	1057.5	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2
157.5°	1079.3	1078.1	1076.5	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5
160°	1090.4	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3
162.5°	1100.4	1099.2	1098.2	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8
165°	1112.8	1111.5	1110.9	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0
167.5°	1123.1	1121.9	1121.4	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5
170°	1128.4	1127.1	1126.8	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4
172.5°	1132.4	1131.1	1130.7	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4
175°	1136.6	1135.3	1135.0	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4
177.5°	1137.4	1136.3	1136.2	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.7	5.9	6.0	6.1	6.7	7.1	7.1	7.4	7.9	7.8	8.3
90°	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3
92.5°	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1
95°	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9
97.5°	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4
100°	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9
102.5°	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0
105°	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2
107.5°	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1
110°	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7
115°	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3
117.5°	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2
120°	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4
122.5°	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5
125°	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8
127.5°	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0
130°	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2
132.5°	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6
135°	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9
137.5°	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1
140°	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2
142.5°	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2
145°	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9
147.5°	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1
150°	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2
152.5°	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7
155°	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9
157.5°	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6
160°	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5
162.5°	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6
165°	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0
167.5°	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4
170°	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7
172.5°	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6
175°	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9
177.5°	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	8.2	8.4	8.5	8.6	8.7	8.8	8.5
90°	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331793-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)