

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331804-930

Luminaire Tested: **S122RDIW-S485D1440U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331804-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5462.3 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.0	1.2
10°-20°	172.9	3.2
20°-30°	242.8	4.4
30°-40°	264.8	4.8
40°-50°	243.5	4.5
50°-60°	191.2	3.5
60°-70°	124.7	2.3
70°-80°	64.3	1.2
80°-90°	22.5	0.4
90°-100°	92.3	1.7
100°-110°	286.6	5.2
110°-120°	490.0	9.0
120°-130°	644.3	11.8
130°-140°	723.2	13.2
140°-150°	709.1	13.0
150°-160°	594.8	10.9
160°-170°	394.5	7.2
170°-180°	137.9	2.5
0°-30°	478.7	8.8
0°-40°	743.5	13.6
0°-60°	1178.2	21.6
0°-90°	1389.7	25.4
90°-120°	868.9	15.9
90°-150°	2945.5	53.9
90°-180°	4073.0	74.6
0°-180°	5462.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	1	17	43	41	42	4
95°	64	76	79	79	76	73
105°	264	268	270	273	273	279
115°	492	498	497	495	492	486
125°	715	726	723	719	718	639
135°	926	938	942	940	937	715
145°	1123	1132	1139	1140	1136	702
155°	1284	1288	1292	1297	1294	591
165°	1398	1396	1396	1404	1399	394
175°	1454	1450	1448	1456	1449	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	8.1	7.8	7.6	7.4	7.2	7.7	8.9	10.1	11.3	12.5	12.3
90°	1.2	4.5	7.7	11.1	14.3	19.0	25.0	31.0	37.0	43.0	42.5
92.5°	21.9	24.3	26.7	29.1	31.5	33.4	34.8	36.3	37.7	39.1	39.2
95°	63.9	66.6	69.4	72.1	74.8	76.5	77.0	77.5	78.1	78.7	78.7
97.5°	116.8	119.2	121.6	124.0	126.4	128.1	129.1	130.2	131.2	132.2	132.2
100°	156.1	158.2	160.5	162.7	164.9	166.3	167.1	168.0	168.8	169.6	169.6
102.5°	197.4	199.2	200.9	202.6	204.4	205.8	206.8	207.8	208.9	209.9	210.2
105°	264.2	265.1	265.9	266.7	267.5	268.2	268.8	269.3	269.9	270.4	270.9
107.5°	331.6	332.8	334.0	335.3	336.4	337.0	337.0	337.0	337.0	337.0	337.2
110°	374.9	376.5	378.1	379.8	381.4	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	423.7	425.3	427.0	428.6	429.3	429.1	428.9	428.7	428.4	427.8
115°	491.6	493.3	494.9	496.6	498.2	498.7	498.2	497.7	497.1	496.6	496.3
117.5°	561.0	563.1	565.3	567.5	569.7	570.1	568.5	567.0	565.4	563.9	563.3
120°	607.2	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	607.2
122.5°	649.5	652.1	654.7	657.3	660.0	660.5	659.0	657.5	655.9	654.4	653.7
125°	715.3	717.8	720.2	722.7	725.2	726.0	725.2	724.4	723.6	722.7	721.9
127.5°	779.5	782.6	785.7	788.9	792.0	793.0	792.1	791.1	790.1	789.1	788.1
130°	819.8	823.4	827.0	830.5	834.1	835.5	834.9	834.5	833.9	833.3	832.8
132.5°	865.0	868.0	870.8	873.8	876.6	878.2	878.2	878.3	878.5	878.6	877.3
135°	925.5	928.5	931.6	934.5	937.5	939.3	939.9	940.4	940.9	941.5	941.3
137.5°	989.2	991.6	994.1	996.5	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2
140°	1027.5	1030.0	1032.5	1034.9	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7
142.5°	1066.9	1069.3	1071.8	1074.2	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3
145°	1123.4	1125.4	1127.2	1129.1	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6
147.5°	1173.8	1176.1	1178.4	1180.7	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7
150°	1208.2	1209.8	1211.5	1213.2	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3
152.5°	1238.7	1240.3	1241.9	1243.6	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0
155°	1284.4	1285.2	1286.1	1286.9	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1
157.5°	1323.5	1324.0	1324.6	1325.2	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0
160°	1347.1	1347.7	1348.2	1348.7	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4
162.5°	1368.7	1368.9	1369.0	1369.1	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3
165°	1397.5	1397.3	1396.9	1396.7	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2
167.5°	1421.6	1420.7	1419.9	1419.1	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6
170°	1434.4	1433.5	1432.7	1431.9	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3
172.5°	1443.2	1442.4	1441.6	1440.8	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2
175°	1454.0	1453.2	1452.4	1451.6	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8
177.5°	1458.5	1457.8	1457.2	1456.5	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	12.1	11.8	11.7	11.6	11.6	11.7	11.7	11.7
90°	41.9	41.4	40.8	40.7	41.0	41.3	41.5	41.8
92.5°	39.3	39.4	39.5	39.6	39.6	39.7	39.8	39.8
95°	78.7	78.7	78.7	78.4	77.9	77.3	76.7	76.2
97.5°	132.2	132.2	132.2	132.2	132.2	132.1	132.1	132.0
100°	169.6	169.6	169.6	169.5	169.2	168.9	168.7	168.4
102.5°	210.3	210.6	210.8	210.8	210.5	210.3	209.9	209.7
105°	271.5	272.1	272.6	272.9	272.9	272.9	272.9	272.9
107.5°	337.5	337.7	337.9	337.4	336.1	334.8	333.6	332.3
110°	382.3	382.3	382.3	381.8	381.0	380.2	379.4	378.5



TEST NUMBER: P331804-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	427.1	426.5	425.8	425.2	424.6	424.0	423.4	422.8
115°	496.0	495.7	495.5	494.9	494.1	493.3	492.4	491.6
117.5°	562.6	562.0	561.3	560.5	559.7	558.9	558.1	557.3
120°	607.2	607.2	607.2	606.7	605.9	605.1	604.3	603.5
122.5°	653.1	652.4	651.8	651.1	650.5	650.0	649.3	648.7
125°	721.1	720.2	719.4	718.9	718.6	718.4	718.1	717.8
127.5°	787.1	786.1	785.1	784.2	783.3	782.4	781.6	780.7
130°	832.3	831.7	831.1	830.3	829.2	828.2	827.0	826.0
132.5°	876.2	875.0	873.8	872.7	871.9	871.0	870.1	869.2
135°	940.9	940.7	940.4	939.9	939.1	938.2	937.4	936.6
137.5°	1003.0	1002.8	1002.6	1001.9	1000.9	999.7	998.7	997.5
140°	1044.7	1044.7	1044.7	1044.2	1043.1	1042.0	1040.9	1039.8
142.5°	1082.6	1082.8	1083.0	1082.6	1081.5	1080.4	1079.3	1078.2
145°	1140.0	1140.2	1140.4	1140.0	1139.0	1137.9	1136.8	1135.7
147.5°	1190.3	1190.8	1191.5	1191.2	1190.2	1189.1	1188.1	1187.1
150°	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5
152.5°	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0
155°	1294.5	1295.9	1297.2	1297.5	1296.7	1295.9	1295.1	1294.3
157.5°	1331.9	1333.7	1335.6	1335.9	1334.6	1333.3	1332.0	1330.6
160°	1354.0	1355.7	1357.3	1357.6	1356.5	1355.4	1354.4	1353.2
162.5°	1374.2	1376.1	1377.9	1378.2	1376.9	1375.6	1374.3	1372.9
165°	1400.1	1402.0	1403.9	1404.2	1402.8	1401.5	1400.1	1398.7
167.5°	1421.5	1423.4	1425.3	1425.6	1424.2	1422.7	1421.3	1419.8
170°	1433.3	1435.2	1437.1	1437.2	1435.6	1433.9	1432.3	1430.7
172.5°	1442.1	1444.1	1445.9	1446.1	1444.5	1442.8	1441.2	1439.6
175°	1451.7	1453.6	1455.6	1455.7	1454.0	1452.4	1450.7	1449.1
177.5°	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5

(END OF REPORT)