

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331805-935

Luminaire Tested: **S122RDIW-S675D435U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331805-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D435U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3677.7 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	58	57	52
2	93	86	80	75	86	80	75	71	70	67	63	61	59	56	53	51	49	45
3	85	76	69	64	79	72	66	61	63	58	55	55	52	49	48	45	43	39
4	78	68	61	55	73	64	58	52	57	52	48	50	46	43	43	40	38	35
5	73	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34	31
6	67	56	48	42	63	53	46	41	47	41	37	42	37	34	36	33	30	28
7	63	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	28	25
8	58	46	39	34	55	44	37	33	40	34	30	35	31	28	31	28	25	23
9	55	43	35	31	51	41	34	29	37	31	27	33	28	25	29	26	23	21
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	20423	20423	20423	20423
5°	22809	20551	18220	20551
10°	25306	20407	15795	20407
15°	26551	20107	12445	20107
20°	23017	19663	10768	19663
25°	15096	19057	9615	19057
30°	10161	18321	8701	18321
35°	8229	17394	7849	17394
40°	7318	16387	7263	16387
45°	6624	15203	6485	15203
50°	6028	14031	6006	14031
55°	5666	12732	5590	12732
60°	4740	11538	4682	11538
65°	3996	10476	4531	10476
70°	3696	9356	4277	9356
75°	3456	8141	3949	8141
80°	3189	6704	3515	6704
85°	2927	5298	3094	5298



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.9	3.3
10°-20°	334.1	9.1
20°-30°	430.5	11.7
30°-40°	409.1	11.1
40°-50°	350.5	9.5
50°-60°	266.9	7.3
60°-70°	168.7	4.6
70°-80°	84.3	2.3
80°-90°	23.2	0.6
90°-100°	17.0	0.5
100°-110°	62.2	1.7
110°-120°	166.3	4.5
120°-130°	274.5	7.5
130°-140°	291.9	7.9
140°-150°	271.3	7.4
150°-160°	218.2	5.9
160°-170°	140.6	3.8
170°-180°	48.4	1.3
0°-30°	884.5	24.1
0°-40°	1293.7	35.2
0°-60°	1911.1	52.0
0°-90°	2187.2	59.5
90°-120°	245.5	6.7
90°-150°	1083.3	29.5
90°-180°	1490.0	40.5
0°-180°	3677.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1407	1268	1124	1268	1407	139
15°	1588	1203	744	1203	1588	428
25°	847	1070	540	1070	847	402
35°	418	882	398	882	418	267
45°	290	666	284	666	290	224
55°	201	452	199	452	201	177
65°	105	274	119	274	105	106
75°	55	130	63	130	55	59
85°	16	29	17	29	16	17
90°	10	0	10	0	10	5
95°	16	24	16	24	16	15
105°	28	112	28	112	28	29
115°	30	212	30	212	30	76
125°	315	299	315	299	315	272
135°	382	370	382	370	382	295
145°	436	430	436	430	436	273
155°	473	473	473	473	473	218
165°	497	498	497	498	497	140
175°	507	510	507	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1316.2	1317.2	1318.4	1315.9	1315.9	1313.7	1309.2	1305.7	1295.8	1294.4	1294.4
5°	1407.3	1406.4	1408.2	1402.5	1394.6	1392.8	1384.4	1373.5	1362.0	1349.3	1346.6
7.5°	1497.8	1496.5	1493.0	1492.0	1485.9	1472.7	1459.2	1444.9	1425.9	1407.4	1398.1
10°	1543.5	1558.1	1549.2	1533.9	1537.0	1516.3	1505.3	1486.4	1470.6	1442.9	1436.8
12.5°	1588.5	1594.2	1591.5	1582.7	1578.7	1564.4	1549.6	1533.2	1504.0	1479.1	1457.5
15°	1588.4	1596.7	1598.9	1596.3	1598.4	1597.6	1589.7	1576.1	1550.6	1523.3	1499.6
17.5°	1471.1	1476.9	1491.3	1501.1	1513.4	1539.4	1552.2	1557.2	1553.4	1537.9	1521.2
20°	1339.6	1329.9	1370.4	1391.0	1408.6	1452.5	1490.3	1504.9	1528.1	1527.7	1523.3
22.5°	1153.2	1155.5	1193.9	1218.4	1269.7	1313.6	1356.8	1411.4	1456.4	1486.2	1503.7
25°	847.4	864.1	902.3	935.7	992.8	1074.6	1148.8	1235.0	1316.3	1380.4	1441.6
27.5°	636.4	637.7	668.0	698.8	732.7	799.7	893.2	996.1	1112.0	1207.6	1317.7
30°	545.0	542.3	555.1	574.0	603.0	654.9	725.1	826.3	941.8	1086.0	1214.4
32.5°	480.3	480.4	490.1	504.0	528.1	563.1	611.2	693.4	802.6	944.3	1094.8
35°	417.5	417.1	424.1	434.2	444.4	466.7	499.7	542.8	617.9	750.2	904.0
37.5°	372.6	374.4	377.9	384.2	395.4	407.9	427.7	456.6	510.1	588.3	717.6
40°	347.2	348.1	352.9	358.2	364.8	374.4	390.7	414.0	453.1	515.6	610.0
42.5°	324.0	324.9	328.3	333.2	338.4	348.1	361.5	381.7	413.4	462.1	540.0
45°	290.1	290.1	293.2	295.3	301.1	309.9	320.8	337.5	359.6	395.5	447.4
47.5°	258.2	258.3	260.4	264.2	267.8	274.6	285.4	299.0	315.0	342.9	387.2
50°	240.0	240.4	241.7	244.8	247.0	253.1	261.5	273.4	290.1	311.6	348.5
52.5°	225.2	224.9	226.6	227.9	229.5	233.8	240.0	250.6	265.4	284.2	314.8
55°	201.3	199.5	202.2	204.4	205.7	207.4	210.9	217.6	230.3	246.2	269.0
57.5°	171.4	170.7	172.5	174.6	178.7	183.5	186.4	190.6	197.3	208.6	231.3
60°	146.8	146.8	150.8	152.1	156.9	163.1	169.2	172.7	179.3	186.8	203.5
62.5°	125.0	125.4	127.2	128.5	131.2	138.8	147.4	155.2	161.4	168.5	179.6
65°	104.6	105.5	105.5	106.3	108.1	109.9	113.4	119.5	130.5	140.6	149.0
67.5°	88.8	89.0	89.3	90.1	90.7	92.6	93.9	96.7	99.3	108.8	119.2
70°	78.3	79.6	79.1	80.0	80.4	81.3	83.1	84.4	88.3	90.6	96.7
72.5°	68.4	69.3	69.2	69.8	70.9	71.1	72.5	73.9	76.4	78.3	81.5
75°	55.4	54.9	55.4	56.2	56.7	57.2	57.2	58.9	60.2	62.0	64.1
77.5°	42.7	43.1	43.0	43.1	43.2	44.0	43.9	44.8	46.1	46.9	48.0
80°	34.3	34.7	34.3	34.7	35.1	35.6	35.1	35.6	36.9	37.8	37.8
82.5°	26.5	26.6	26.9	26.9	27.0	27.1	27.8	27.9	28.8	28.7	29.0
85°	15.8	15.4	15.4	15.4	15.8	16.3	15.8	15.8	16.3	16.3	16.3
87.5°	7.6	7.9	7.9	7.8	7.8	7.7	7.7	8.0	7.5	7.8	7.3
90°	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2	7.7	7.3	6.7
92.5°	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0	8.8	8.5	8.2
95°	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2	14.7	14.4	13.8
97.5°	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9	19.5	19.2	17.9
100°	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3	21.6	21.0	19.5
102.5°	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2	22.4	21.5	33.2
105°	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3	23.3	22.5	44.8
107.5°	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6	30.5	31.4	58.2
110°	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0	56.2	64.4	88.0



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8	132.6	162.5	168.2
115°	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4	189.2	227.0	225.0
117.5°	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2	242.4	251.5	250.1
120°	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7	270.7	269.8	268.3
122.5°	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3	287.7	287.1	285.5
125°	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1	311.5	311.0	309.4
127.5°	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2	333.3	332.4	331.3
130°	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1	347.2	346.3	345.4
132.5°	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7	360.9	360.2	359.2
135°	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1	380.2	379.4	378.7
137.5°	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1	398.2	397.4	396.6
140°	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7	409.9	409.2	408.3
142.5°	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5	420.8	420.1	419.0
145°	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5	435.9	435.3	433.9
147.5°	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6	449.2	448.8	447.4
150°	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7	457.2	456.7	455.4
152.5°	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0	464.5	464.1	462.8
155°	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0	474.5	474.0	473.0
157.5°	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4	482.8	482.2	481.6
160°	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2	487.8	487.2	486.7
162.5°	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8	492.2	491.6	491.2
165°	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1	497.0
167.5°	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0	502.4	501.8	501.6
170°	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3	504.7	504.2	504.0
172.5°	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0	506.5	505.9	505.8
175°	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0	508.4	507.8	507.6
177.5°	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2	508.8	508.2	508.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1295.1	1292.3	1289.9	1283.5	1280.4	1273.3	1272.3	1272.0	1262.7	1254.0	1251.5
5°	1339.6	1332.6	1322.0	1309.7	1296.9	1283.8	1275.0	1268.0	1250.3	1233.6	1224.0
7.5°	1384.4	1369.3	1351.1	1327.8	1308.4	1286.6	1270.4	1255.9	1231.0	1207.0	1190.9
10°	1417.8	1393.2	1369.1	1337.0	1311.9	1287.3	1264.5	1244.7	1216.5	1184.9	1162.4
12.5°	1438.6	1411.5	1378.2	1346.8	1314.4	1283.1	1252.5	1227.1	1194.0	1161.3	1134.7
15°	1466.6	1437.6	1397.1	1352.4	1310.6	1269.7	1234.6	1202.9	1159.9	1120.8	1088.2
17.5°	1489.5	1449.7	1406.2	1354.4	1306.1	1254.0	1208.8	1168.4	1120.4	1073.2	1034.9
20°	1496.9	1457.4	1407.3	1355.4	1298.3	1237.2	1188.4	1144.4	1093.0	1041.6	997.6
22.5°	1492.4	1461.6	1405.8	1343.8	1285.3	1221.3	1166.2	1115.3	1058.3	1005.7	954.8
25°	1461.4	1450.8	1398.1	1330.3	1263.6	1189.3	1125.6	1069.7	1004.7	948.5	893.0
27.5°	1389.0	1411.8	1379.1	1307.0	1232.7	1153.1	1081.4	1017.9	950.4	887.1	831.9
30°	1319.4	1371.7	1357.6	1290.8	1207.7	1129.5	1049.1	982.7	910.7	845.6	791.1
32.5°	1224.1	1310.5	1324.2	1268.3	1182.4	1096.5	1012.2	946.2	870.9	802.4	749.2
35°	1072.4	1201.6	1260.9	1225.3	1139.2	1046.5	959.4	882.5	806.9	739.3	686.5
37.5°	891.4	1067.4	1166.2	1168.8	1089.7	993.2	898.5	822.2	744.8	678.3	621.3
40°	774.0	964.7	1093.5	1122.1	1055.2	951.1	855.2	777.5	701.9	636.8	571.4
42.5°	668.5	858.5	1016.8	1066.5	1013.4	909.9	813.8	732.5	659.0	597.4	530.5
45°	540.6	706.7	881.2	970.0	940.6	844.7	743.2	665.8	596.8	543.6	479.5
47.5°	456.0	573.1	741.9	862.0	861.5	774.0	674.2	600.1	536.1	486.3	434.3
50°	407.9	509.8	652.6	788.9	800.3	726.9	632.0	558.6	498.9	446.5	404.8
52.5°	364.6	448.7	577.0	707.7	740.2	676.7	584.5	516.8	458.7	410.7	374.9
55°	308.1	373.2	470.7	592.9	642.1	597.3	515.6	452.3	405.2	364.8	334.0
57.5°	260.6	309.4	387.7	486.1	543.4	515.2	447.7	396.3	356.1	319.5	295.2
60°	230.7	270.7	337.1	419.3	482.6	462.8	405.2	357.3	323.0	291.4	268.5
62.5°	202.6	236.9	293.9	360.6	418.6	410.4	363.3	323.2	293.2	264.3	245.0
65°	163.1	188.1	232.5	284.8	331.4	335.4	301.5	274.2	247.5	224.5	207.4
67.5°	129.8	146.2	177.5	221.5	256.4	268.9	248.2	227.4	206.1	188.5	173.6
70°	109.4	122.6	145.5	181.1	213.2	226.4	214.5	198.2	179.8	165.2	152.5
72.5°	88.7	101.5	118.4	144.5	172.0	186.2	182.1	170.5	155.5	143.4	131.4
75°	66.8	70.8	82.2	99.8	121.3	133.6	136.7	130.5	118.6	109.4	102.4
77.5°	49.4	51.7	57.3	66.5	80.5	91.5	96.0	95.3	87.1	81.7	75.2
80°	39.5	40.9	43.5	47.4	58.0	69.0	72.1	72.1	66.4	64.1	57.6
82.5°	30.0	31.0	32.6	34.8	39.7	49.3	52.8	53.5	49.9	46.9	41.8
85°	17.1	16.7	17.6	18.9	19.8	22.4	27.7	28.6	27.7	24.2	22.8
87.5°	7.1	7.4	7.3	6.8	7.0	7.1	8.7	10.2	9.0	8.2	7.7
90°	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3	1.3	2.2	3.1
92.5°	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4	7.3	7.2	7.1
95°	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9	21.2	18.5	15.8
97.5°	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4	39.9	32.3	24.6
100°	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2	53.9	42.7	31.5
102.5°	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6	82.2	79.8	77.5
105°	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8	114.3	116.8	119.2
107.5°	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0	145.0	147.0	149.0
110°	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0	164.7	166.4	168.2





TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8	183.4	184.9	186.4
115°	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6	213.0	214.4	215.8
117.5°	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2	239.7	241.3	242.8
120°	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6	258.8	260.0	261.3
122.5°	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1	275.3	276.6	277.9
125°	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2	300.2	301.4	302.4
127.5°	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9	323.1	324.3	325.5
130°	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4	337.7	339.0	340.3
132.5°	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1	352.1	353.3	354.4
135°	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2	371.5	372.8	374.1
137.5°	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6	390.5	391.4	392.4
140°	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3	402.9	403.6	404.2
142.5°	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8	413.5	414.0	414.6
145°	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5	429.4	429.3	429.2
147.5°	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9	443.7	443.3	443.1
150°	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4	452.8	452.2	451.7
152.5°	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3	460.7	460.0	459.4
155°	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9	472.2	471.4	470.7
157.5°	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9	481.3	480.7	480.1
160°	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	486.7	486.3	485.8
162.5°	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0	491.5	490.9	490.5
165°	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3	497.8	497.3	496.8
167.5°	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0	502.5	502.0	501.5
170°	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7	505.1	504.6	504.2
172.5°	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4	507.0	506.4	505.9
175°	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7	509.1	508.5	508.0
177.5°	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1	509.6	509.1	508.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1247.0	1244.5	1239.9	1232.9	1228.6	1221.2	1216.3	1219.2	1219.9	1219.2	1218.5
5°	1213.5	1204.2	1191.5	1179.1	1167.8	1155.5	1148.4	1145.3	1139.2	1135.7	1133.9
7.5°	1172.9	1157.0	1139.0	1117.6	1099.3	1080.3	1070.6	1065.7	1053.1	1046.3	1040.3
10°	1142.7	1117.7	1099.7	1071.5	1054.4	1029.3	1012.2	1012.6	995.5	985.8	978.8
12.5°	1109.3	1081.8	1051.8	1026.5	1002.6	982.6	961.9	953.6	935.3	926.0	907.1
15°	1054.0	1021.8	990.2	955.9	931.8	900.5	870.6	834.1	804.7	779.2	772.2
17.5°	993.4	953.7	922.0	881.8	840.3	787.8	753.2	732.0	714.3	700.9	690.8
20°	951.9	911.5	877.7	817.0	761.2	725.7	700.2	683.9	665.4	650.9	643.0
22.5°	908.4	866.2	820.0	752.3	708.9	680.3	657.5	638.9	626.4	615.0	607.9
25°	846.4	800.3	724.3	677.7	642.6	612.7	596.8	585.4	572.2	556.8	549.8
27.5°	781.1	707.7	653.1	618.5	584.9	565.4	551.2	534.2	522.4	515.5	508.2
30°	732.2	658.8	616.2	578.4	554.7	533.1	516.4	506.8	495.3	483.5	478.6
32.5°	677.7	619.1	578.2	546.7	522.6	504.3	491.1	475.4	467.2	459.9	449.8
35°	610.0	565.7	528.3	502.8	479.9	465.0	449.6	440.4	425.4	419.3	415.3
37.5°	552.7	514.2	486.4	459.4	441.3	424.8	415.4	400.7	394.3	385.7	377.4
40°	520.4	482.6	455.7	433.8	413.5	401.2	389.4	377.5	367.8	363.9	353.8
42.5°	487.3	456.6	429.7	405.6	392.1	379.1	364.1	355.4	345.3	339.0	332.7
45°	441.7	414.5	391.6	371.8	356.9	343.3	333.6	319.1	313.4	300.6	295.3
47.5°	401.7	376.3	354.5	335.7	321.1	312.2	298.1	286.7	277.6	269.8	263.0
50°	373.2	352.1	331.0	314.3	301.1	288.3	273.8	268.1	254.0	250.0	246.2
52.5°	347.2	327.1	307.7	291.4	278.2	265.8	253.0	245.6	236.1	232.1	229.3
55°	310.7	291.4	272.9	258.4	245.2	232.5	224.5	215.3	210.9	207.8	204.4
57.5°	274.1	256.8	242.6	227.9	214.6	204.6	195.4	189.9	185.3	181.2	177.0
60°	251.0	234.3	221.5	207.8	194.2	185.9	178.9	172.3	167.0	160.8	159.1
62.5°	226.4	211.7	200.1	186.8	175.0	167.3	160.6	154.4	148.0	139.1	136.6
65°	192.5	181.1	168.8	157.8	147.2	139.7	130.1	123.0	120.5	119.5	119.1
67.5°	162.0	151.1	140.5	129.3	119.7	112.8	107.9	106.8	105.0	104.4	103.2
70°	141.5	131.4	120.9	110.3	101.1	99.8	98.0	96.3	94.0	93.2	92.3
72.5°	123.2	112.8	102.2	93.8	89.8	88.2	86.4	84.6	83.2	82.3	81.7
75°	94.5	84.8	77.8	74.7	72.5	71.2	68.5	67.2	66.4	65.0	64.6
77.5°	68.0	62.6	59.3	57.4	55.1	53.7	52.2	50.9	49.9	49.7	49.0
80°	51.8	49.2	47.0	44.4	43.5	41.8	41.3	40.0	40.5	39.1	39.1
82.5°	40.3	36.9	35.0	33.8	33.0	31.6	31.1	30.5	30.6	29.6	29.6
85°	20.7	19.8	18.9	18.0	18.0	16.7	17.1	16.7	16.7	15.8	15.4
87.5°	7.5	7.3	6.7	6.8	7.0	6.7	6.8	6.5	6.6	6.7	6.5
90°	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2	8.6	9.0	9.3
92.5°	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0	9.2	9.4	9.6
95°	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2	15.6	16.0	16.2
97.5°	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9	20.2	20.5	20.8
100°	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3	22.9	23.6	24.0
102.5°	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2	24.1	25.0	25.5
105°	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3	25.1	26.1	26.7
107.5°	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6	28.7	27.7	27.5
110°	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0	39.9	31.7	27.7



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8	72.9	43.1	28.3
115°	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4	113.5	75.6	53.7
117.5°	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2	224.0	214.8	200.6
120°	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7	272.7	273.7	268.6
122.5°	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3	288.9	289.5	288.7
125°	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1	312.7	313.2	313.7
127.5°	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2	334.9	335.8	336.2
130°	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1	349.0	349.9	350.3
132.5°	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7	362.4	363.2	363.5
135°	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1	381.9	382.7	383.0
137.5°	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1	399.8	400.6	400.9
140°	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7	411.5	412.2	412.3
142.5°	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5	422.1	422.8	422.9
145°	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5	437.0	437.6	437.7
147.5°	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6	450.0	450.5	450.5
150°	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7	458.1	458.7	458.7
152.5°	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0	465.5	466.1	466.0
155°	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0	475.4	476.0	475.9
157.5°	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4	483.9	484.5	484.4
160°	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2	488.7	489.2	489.1
162.5°	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8	493.4	493.9	493.8
165°	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3	498.9	499.5	499.5
167.5°	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0	503.5	504.1	504.0
170°	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3	505.9	506.4	506.4
172.5°	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0	507.6	508.2	508.2
175°	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0	509.5	510.1	510.1
177.5°	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2	509.6	510.1	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1214.6	1215.3	1214.3	1215.0	1214.3	1215.3	1214.6	1218.5	1219.2	1219.9	1219.2
5°	1131.7	1126.4	1125.6	1124.2	1125.6	1126.4	1131.7	1133.9	1135.7	1139.2	1145.3
7.5°	1032.8	1031.9	1029.8	1026.7	1029.8	1031.9	1032.8	1040.3	1046.3	1053.1	1065.7
10°	969.1	966.9	966.5	963.4	966.5	966.9	969.1	978.8	985.8	995.5	1012.6
12.5°	894.6	880.4	878.9	871.2	878.9	880.4	894.6	907.1	926.0	935.3	953.6
15°	761.6	759.1	750.2	744.5	750.2	759.1	761.6	772.2	779.2	804.7	834.1
17.5°	685.7	677.1	674.3	673.1	674.3	677.1	685.7	690.8	700.9	714.3	732.0
20°	636.8	629.0	627.6	626.7	627.6	629.0	636.8	643.0	650.9	665.4	683.9
22.5°	603.0	594.8	591.4	588.8	591.4	594.8	603.0	607.9	615.0	626.4	638.9
25°	545.4	542.3	540.6	539.7	540.6	542.3	545.4	549.8	556.8	572.2	585.4
27.5°	500.3	493.5	492.2	490.0	492.2	493.5	500.3	508.2	515.5	522.4	534.2
30°	474.7	472.4	469.4	466.7	469.4	472.4	474.7	478.6	483.5	495.3	506.8
32.5°	444.4	442.6	439.9	438.6	439.9	442.6	444.4	449.8	459.9	467.2	475.4
35°	411.0	404.8	402.2	398.2	402.2	404.8	411.0	415.3	419.3	425.4	440.4
37.5°	375.5	372.3	368.6	369.9	368.6	372.3	375.5	377.4	385.7	394.3	400.7
40°	348.1	345.9	345.0	344.6	345.0	345.9	348.1	353.8	363.9	367.8	377.5
42.5°	326.3	320.2	318.0	317.9	318.0	320.2	326.3	332.7	339.0	345.3	355.4
45°	293.2	287.4	283.4	284.0	283.4	287.4	293.2	295.3	300.6	313.4	319.1
47.5°	259.2	259.1	256.6	257.4	256.6	259.1	259.2	263.0	269.8	277.6	286.7
50°	243.1	240.4	238.7	239.1	238.7	240.4	243.1	246.2	250.0	254.0	268.1
52.5°	227.6	225.3	223.9	225.8	223.9	225.3	227.6	229.3	232.1	236.1	245.6
55°	202.2	199.5	199.1	198.6	199.1	199.5	202.2	204.4	207.8	210.9	215.3
57.5°	173.7	172.0	169.4	168.2	169.4	172.0	173.7	177.0	181.2	185.3	189.9
60°	153.3	149.9	145.5	145.0	145.5	149.9	153.3	159.1	160.8	167.0	172.3
62.5°	134.7	134.1	133.2	133.1	133.2	134.1	134.7	136.6	139.1	148.0	154.4
65°	118.2	117.8	118.2	118.6	118.2	117.8	118.2	119.1	119.5	120.5	123.0
67.5°	103.1	102.2	101.4	101.8	101.4	102.2	103.1	103.2	104.4	105.0	106.8
70°	91.4	91.0	90.6	90.6	90.6	91.0	91.4	92.3	93.2	94.0	96.3
72.5°	80.2	80.1	79.6	79.3	79.6	80.1	80.2	81.7	82.3	83.2	84.6
75°	64.1	63.3	63.3	63.3	63.3	63.3	64.1	64.6	65.0	66.4	67.2
77.5°	48.9	48.5	48.0	47.6	48.0	48.5	48.9	49.0	49.7	49.9	50.9
80°	38.7	38.2	37.8	37.8	37.8	38.2	38.7	39.1	39.1	40.5	40.0
82.5°	29.5	29.1	29.0	28.7	29.0	29.1	29.5	29.6	29.6	30.6	30.5
85°	15.8	16.3	15.8	16.7	15.8	16.3	15.8	15.4	15.8	16.7	16.7
87.5°	6.5	6.1	6.5	6.2	6.5	6.1	6.5	6.5	6.7	6.6	6.5
90°	9.5	9.6	9.8	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2
92.5°	9.6	9.7	9.8	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0
95°	16.1	16.0	15.9	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2
97.5°	20.8	20.9	21.0	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9
100°	24.2	24.4	24.5	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3
102.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2
105°	26.9	27.3	27.6	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3
107.5°	27.8	28.2	28.4	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6
110°	28.1	28.4	28.8	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	28.6	28.8	29.1	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8
115°	47.9	41.9	36.1	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4
117.5°	181.2	161.9	142.6	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2
120°	257.6	246.6	235.5	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7
122.5°	286.5	284.4	282.2	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3
125°	313.9	314.2	314.4	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1
127.5°	336.3	336.3	336.4	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2
130°	350.3	350.2	350.1	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1
132.5°	363.4	363.3	363.3	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7
135°	382.9	382.7	382.5	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1
137.5°	400.6	400.4	400.1	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1
140°	411.9	411.5	411.1	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7
142.5°	422.5	422.1	421.7	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5
145°	437.3	436.9	436.5	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5
147.5°	450.1	449.8	449.4	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6
150°	458.3	457.9	457.4	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7
152.5°	465.5	464.9	464.3	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0
155°	475.2	474.6	473.9	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0
157.5°	483.8	483.1	482.5	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4
160°	488.6	488.0	487.4	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2
162.5°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8
165°	498.9	498.3	497.7	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3
167.5°	503.3	502.6	501.8	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0
170°	505.7	504.9	504.2	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3
172.5°	507.4	506.7	505.9	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0
175°	509.2	508.4	507.6	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0
177.5°	509.5	508.9	508.2	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1216.3	1221.2	1228.6	1232.9	1239.9	1244.5	1247.0	1251.5	1254.0	1262.7	1272.0
5°	1148.4	1155.5	1167.8	1179.1	1191.5	1204.2	1213.5	1224.0	1233.6	1250.3	1268.0
7.5°	1070.6	1080.3	1099.3	1117.6	1139.0	1157.0	1172.9	1190.9	1207.0	1231.0	1255.9
10°	1012.2	1029.3	1054.4	1071.5	1099.7	1117.7	1142.7	1162.4	1184.9	1216.5	1244.7
12.5°	961.9	982.6	1002.6	1026.5	1051.8	1081.8	1109.3	1134.7	1161.3	1194.0	1227.1
15°	870.6	900.5	931.8	955.9	990.2	1021.8	1054.0	1088.2	1120.8	1159.9	1202.9
17.5°	753.2	787.8	840.3	881.8	922.0	953.7	993.4	1034.9	1073.2	1120.4	1168.4
20°	700.2	725.7	761.2	817.0	877.7	911.5	951.9	997.6	1041.6	1093.0	1144.4
22.5°	657.5	680.3	708.9	752.3	820.0	866.2	908.4	954.8	1005.7	1058.3	1115.3
25°	596.8	612.7	642.6	677.7	724.3	800.3	846.4	893.0	948.5	1004.7	1069.7
27.5°	551.2	565.4	584.9	618.5	653.1	707.7	781.1	831.9	887.1	950.4	1017.9
30°	516.4	533.1	554.7	578.4	616.2	658.8	732.2	791.1	845.6	910.7	982.7
32.5°	491.1	504.3	522.6	546.7	578.2	619.1	677.7	749.2	802.4	870.9	946.2
35°	449.6	465.0	479.9	502.8	528.3	565.7	610.0	686.5	739.3	806.9	882.5
37.5°	415.4	424.8	441.3	459.4	486.4	514.2	552.7	621.3	678.3	744.8	822.2
40°	389.4	401.2	413.5	433.8	455.7	482.6	520.4	571.4	636.8	701.9	777.5
42.5°	364.1	379.1	392.1	405.6	429.7	456.6	487.3	530.5	597.4	659.0	732.5
45°	333.6	343.3	356.9	371.8	391.6	414.5	441.7	479.5	543.6	596.8	665.8
47.5°	298.1	312.2	321.1	335.7	354.5	376.3	401.7	434.3	486.3	536.1	600.1
50°	273.8	288.3	301.1	314.3	331.0	352.1	373.2	404.8	446.5	498.9	558.6
52.5°	253.0	265.8	278.2	291.4	307.7	327.1	347.2	374.9	410.7	458.7	516.8
55°	224.5	232.5	245.2	258.4	272.9	291.4	310.7	334.0	364.8	405.2	452.3
57.5°	195.4	204.6	214.6	227.9	242.6	256.8	274.1	295.2	319.5	356.1	396.3
60°	178.9	185.9	194.2	207.8	221.5	234.3	251.0	268.5	291.4	323.0	357.3
62.5°	160.6	167.3	175.0	186.8	200.1	211.7	226.4	245.0	264.3	293.2	323.2
65°	130.1	139.7	147.2	157.8	168.8	181.1	192.5	207.4	224.5	247.5	274.2
67.5°	107.9	112.8	119.7	129.3	140.5	151.1	162.0	173.6	188.5	206.1	227.4
70°	98.0	99.8	101.1	110.3	120.9	131.4	141.5	152.5	165.2	179.8	198.2
72.5°	86.4	88.2	89.8	93.8	102.2	112.8	123.2	131.4	143.4	155.5	170.5
75°	68.5	71.2	72.5	74.7	77.8	84.8	94.5	102.4	109.4	118.6	130.5
77.5°	52.2	53.7	55.1	57.4	59.3	62.6	68.0	75.2	81.7	87.1	95.3
80°	41.3	41.8	43.5	44.4	47.0	49.2	51.8	57.6	64.1	66.4	72.1
82.5°	31.1	31.6	33.0	33.8	35.0	36.9	40.3	41.8	46.9	49.9	53.5
85°	17.1	16.7	18.0	18.0	18.9	19.8	20.7	22.8	24.2	27.7	28.6
87.5°	6.8	6.7	7.0	6.8	6.7	7.3	7.5	7.7	8.2	9.0	10.2
90°	7.7	7.3	6.7	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3
92.5°	8.8	8.5	8.2	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4
95°	14.7	14.4	13.8	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9
97.5°	19.5	19.2	17.9	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4
100°	21.6	21.0	19.5	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2
102.5°	22.4	21.5	33.2	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6
105°	23.3	22.5	44.8	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8
107.5°	30.5	31.4	58.2	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0
110°	56.2	64.4	88.0	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	132.6	162.5	168.2	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8
115°	189.2	227.0	225.0	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6
117.5°	242.4	251.5	250.1	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2
120°	270.7	269.8	268.3	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6
122.5°	287.7	287.1	285.5	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1
125°	311.5	311.0	309.4	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2
127.5°	333.3	332.4	331.3	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9
130°	347.2	346.3	345.4	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4
132.5°	360.9	360.2	359.2	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1
135°	380.2	379.4	378.7	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2
137.5°	398.2	397.4	396.6	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6
140°	409.9	409.2	408.3	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3
142.5°	420.8	420.1	419.0	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8
145°	435.9	435.3	433.9	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5
147.5°	449.2	448.8	447.4	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9
150°	457.2	456.7	455.4	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4
152.5°	464.5	464.1	462.8	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3
155°	474.5	474.0	473.0	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9
157.5°	482.8	482.2	481.6	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9
160°	487.8	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2
162.5°	492.2	491.6	491.2	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0
165°	497.7	497.1	497.0	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3
167.5°	502.4	501.8	501.6	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0
170°	504.7	504.2	504.0	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7
172.5°	506.5	505.9	505.8	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4
175°	508.4	507.8	507.6	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7
177.5°	508.8	508.2	508.2	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1272.3	1273.3	1280.4	1283.5	1289.9	1292.3	1295.1	1294.4	1294.4	1295.8	1305.7
5°	1275.0	1283.8	1296.9	1309.7	1322.0	1332.6	1339.6	1346.6	1349.3	1362.0	1373.5
7.5°	1270.4	1286.6	1308.4	1327.8	1351.1	1369.3	1384.4	1398.1	1407.4	1425.9	1444.9
10°	1264.5	1287.3	1311.9	1337.0	1369.1	1393.2	1417.8	1436.8	1442.9	1470.6	1486.4
12.5°	1252.5	1283.1	1314.4	1346.8	1378.2	1411.5	1438.6	1457.5	1479.1	1504.0	1533.2
15°	1234.6	1269.7	1310.6	1352.4	1397.1	1437.6	1466.6	1499.6	1523.3	1550.6	1576.1
17.5°	1208.8	1254.0	1306.1	1354.4	1406.2	1449.7	1489.5	1521.2	1537.9	1553.4	1557.2
20°	1188.4	1237.2	1298.3	1355.4	1407.3	1457.4	1496.9	1523.3	1527.7	1528.1	1504.9
22.5°	1166.2	1221.3	1285.3	1343.8	1405.8	1461.6	1492.4	1503.7	1486.2	1456.4	1411.4
25°	1125.6	1189.3	1263.6	1330.3	1398.1	1450.8	1461.4	1441.6	1380.4	1316.3	1235.0
27.5°	1081.4	1153.1	1232.7	1307.0	1379.1	1411.8	1389.0	1317.7	1207.6	1112.0	996.1
30°	1049.1	1129.5	1207.7	1290.8	1357.6	1371.7	1319.4	1214.4	1086.0	941.8	826.3
32.5°	1012.2	1096.5	1182.4	1268.3	1324.2	1310.5	1224.1	1094.8	944.3	802.6	693.4
35°	959.4	1046.5	1139.2	1225.3	1260.9	1201.6	1072.4	904.0	750.2	617.9	542.8
37.5°	898.5	993.2	1089.7	1168.8	1166.2	1067.4	891.4	717.6	588.3	510.1	456.6
40°	855.2	951.1	1055.2	1122.1	1093.5	964.7	774.0	610.0	515.6	453.1	414.0
42.5°	813.8	909.9	1013.4	1066.5	1016.8	858.5	668.5	540.0	462.1	413.4	381.7
45°	743.2	844.7	940.6	970.0	881.2	706.7	540.6	447.4	395.5	359.6	337.5
47.5°	674.2	774.0	861.5	862.0	741.9	573.1	456.0	387.2	342.9	315.0	299.0
50°	632.0	726.9	800.3	788.9	652.6	509.8	407.9	348.5	311.6	290.1	273.4
52.5°	584.5	676.7	740.2	707.7	577.0	448.7	364.6	314.8	284.2	265.4	250.6
55°	515.6	597.3	642.1	592.9	470.7	373.2	308.1	269.0	246.2	230.3	217.6
57.5°	447.7	515.2	543.4	486.1	387.7	309.4	260.6	231.3	208.6	197.3	190.6
60°	405.2	462.8	482.6	419.3	337.1	270.7	230.7	203.5	186.8	179.3	172.7
62.5°	363.3	410.4	418.6	360.6	293.9	236.9	202.6	179.6	168.5	161.4	155.2
65°	301.5	335.4	331.4	284.8	232.5	188.1	163.1	149.0	140.6	130.5	119.5
67.5°	248.2	268.9	256.4	221.5	177.5	146.2	129.8	119.2	108.8	99.3	96.7
70°	214.5	226.4	213.2	181.1	145.5	122.6	109.4	96.7	90.6	88.3	84.4
72.5°	182.1	186.2	172.0	144.5	118.4	101.5	88.7	81.5	78.3	76.4	73.9
75°	136.7	133.6	121.3	99.8	82.2	70.8	66.8	64.1	62.0	60.2	58.9
77.5°	96.0	91.5	80.5	66.5	57.3	51.7	49.4	48.0	46.9	46.1	44.8
80°	72.1	69.0	58.0	47.4	43.5	40.9	39.5	37.8	37.8	36.9	35.6
82.5°	52.8	49.3	39.7	34.8	32.6	31.0	30.0	29.0	28.7	28.8	27.9
85°	27.7	22.4	19.8	18.9	17.6	16.7	17.1	16.3	16.3	16.3	15.8
87.5°	8.7	7.1	7.0	6.8	7.3	7.4	7.1	7.3	7.8	7.5	8.0
90°	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2
92.5°	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0
95°	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2
97.5°	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9
100°	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3
102.5°	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2
105°	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3
107.5°	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6
110°	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0





TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8
115°	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4
117.5°	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2
120°	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7
122.5°	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3
125°	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1
127.5°	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2
130°	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1
132.5°	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7
135°	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1
137.5°	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1
140°	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7
142.5°	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5
145°	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5
147.5°	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6
150°	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7
152.5°	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0
155°	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0
157.5°	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4
160°	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2
162.5°	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8
165°	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3
167.5°	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0
170°	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3
172.5°	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0
175°	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0
177.5°	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1309.2	1313.7	1315.9	1315.9	1318.4	1317.2	1316.2
5°	1384.4	1392.8	1394.6	1402.5	1408.2	1406.4	1407.3
7.5°	1459.2	1472.7	1485.9	1492.0	1493.0	1496.5	1497.8
10°	1505.3	1516.3	1537.0	1533.9	1549.2	1558.1	1543.5
12.5°	1549.6	1564.4	1578.7	1582.7	1591.5	1594.2	1588.5
15°	1589.7	1597.6	1598.4	1596.3	1598.9	1596.7	1588.4
17.5°	1552.2	1539.4	1513.4	1501.1	1491.3	1476.9	1471.1
20°	1490.3	1452.5	1408.6	1391.0	1370.4	1329.9	1339.6
22.5°	1356.8	1313.6	1269.7	1218.4	1193.9	1155.5	1153.2
25°	1148.8	1074.6	992.8	935.7	902.3	864.1	847.4
27.5°	893.2	799.7	732.7	698.8	668.0	637.7	636.4
30°	725.1	654.9	603.0	574.0	555.1	542.3	545.0
32.5°	611.2	563.1	528.1	504.0	490.1	480.4	480.3
35°	499.7	466.7	444.4	434.2	424.1	417.1	417.5
37.5°	427.7	407.9	395.4	384.2	377.9	374.4	372.6
40°	390.7	374.4	364.8	358.2	352.9	348.1	347.2
42.5°	361.5	348.1	338.4	333.2	328.3	324.9	324.0
45°	320.8	309.9	301.1	295.3	293.2	290.1	290.1
47.5°	285.4	274.6	267.8	264.2	260.4	258.3	258.2
50°	261.5	253.1	247.0	244.8	241.7	240.4	240.0
52.5°	240.0	233.8	229.5	227.9	226.6	224.9	225.2
55°	210.9	207.4	205.7	204.4	202.2	199.5	201.3
57.5°	186.4	183.5	178.7	174.6	172.5	170.7	171.4
60°	169.2	163.1	156.9	152.1	150.8	146.8	146.8
62.5°	147.4	138.8	131.2	128.5	127.2	125.4	125.0
65°	113.4	109.9	108.1	106.3	105.5	105.5	104.6
67.5°	93.9	92.6	90.7	90.1	89.3	89.0	88.8
70°	83.1	81.3	80.4	80.0	79.1	79.6	78.3
72.5°	72.5	71.1	70.9	69.8	69.2	69.3	68.4
75°	57.2	57.2	56.7	56.2	55.4	54.9	55.4
77.5°	43.9	44.0	43.2	43.1	43.0	43.1	42.7
80°	35.1	35.6	35.1	34.7	34.3	34.7	34.3
82.5°	27.8	27.1	27.0	26.9	26.9	26.6	26.5
85°	15.8	16.3	15.8	15.4	15.4	15.4	15.8
87.5°	7.7	7.7	7.8	7.8	7.9	7.9	7.6
90°	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331805-935

CATALOG NUMBER: S122RDIW-S675D435U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)