

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331796-930

Luminaire Tested: **S122RDIW-S485D970U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331796-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D970U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4124.0 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	15
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.0	1.5
10°-20°	172.9	4.2
20°-30°	242.8	5.9
30°-40°	264.8	6.4
40°-50°	243.5	5.9
50°-60°	191.2	4.6
60°-70°	124.7	3.0
70°-80°	64.3	1.6
80°-90°	20.6	0.5
90°-100°	62.0	1.5
100°-110°	192.6	4.7
110°-120°	329.2	8.0
120°-130°	432.9	10.5
130°-140°	485.9	11.8
140°-150°	476.4	11.6
150°-160°	399.6	9.7
160°-170°	265.0	6.4
170°-180°	92.6	2.2
0°-30°	478.7	11.6
0°-40°	743.5	18.0
0°-60°	1178.2	28.6
0°-90°	1387.7	33.7
90°-120°	583.8	14.2
90°-150°	1979.0	48.0
90°-180°	2736.0	66.3
0°-180°	4124.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	1	11	29	27	28	3
95°	43	51	53	53	51	49
105°	178	180	182	183	183	188
115°	330	335	334	333	330	327
125°	481	488	486	483	482	429
135°	622	630	632	632	629	480
145°	755	760	766	766	763	471
155°	863	865	868	872	870	397
165°	939	938	938	943	940	265
175°	977	974	973	978	974	93
180°	978	978	978	978	978	



TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	8.0	7.5	7.1	6.7	6.3	6.4	7.3	8.1	8.9	9.7	9.5
90°	0.8	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5
92.5°	14.7	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3
95°	43.0	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8
97.5°	78.4	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9
100°	104.8	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0
102.5°	132.6	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2
105°	177.6	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1
107.5°	222.8	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6
110°	251.8	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	283.6	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4
115°	330.3	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5
117.5°	376.9	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5
120°	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0
122.5°	436.3	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2
125°	480.6	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0
127.5°	523.7	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5
130°	550.8	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5
132.5°	581.1	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5
135°	621.8	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3
137.5°	664.6	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0
140°	690.3	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9
142.5°	716.8	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2
145°	754.7	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6
147.5°	788.6	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2
150°	811.7	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5
152.5°	832.3	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8
155°	862.9	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8
157.5°	889.2	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6
160°	905.1	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7
162.5°	919.6	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0
165°	938.9	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4
167.5°	955.1	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7
170°	963.7	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6
172.5°	969.6	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6
175°	976.9	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0
177.5°	979.9	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	9.3	9.1	9.0	8.9	8.9	9.0	9.0	9.0
90°	28.1	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.4	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.4	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.4	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.7	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.8	256.6	256.0	255.4	254.9	254.4





TEST NUMBER: P331796-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	287.0	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.2	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	378.0	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.8	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	484.5	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.8	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	559.1	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	588.6	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.2	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.3	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	765.9	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	799.6	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	869.8	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	894.9	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	909.7	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	923.2	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	940.7	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	955.0	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	963.0	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	968.9	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	975.3	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)