

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331821-930

Luminaire Tested: **S122RDIW-S675D1440U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331821-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6770.1 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	86	79	73	69	77	71	67	62	57	54	51	43	41	39	31	30	29	23
3	79	70	63	58	70	63	57	53	51	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	30	25	24	22	18
5	66	55	48	42	60	50	44	39	41	36	32	32	28	26	23	21	20	16
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17	14
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16	13
8	53	41	34	29	47	37	31	27	31	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	15	13	11
10	46	34	28	23	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	1.7
10°-20°	316.4	4.7
20°-30°	407.7	6.0
30°-40°	387.4	5.7
40°-50°	331.9	4.9
50°-60°	252.7	3.7
60°-70°	159.8	2.4
70°-80°	79.8	1.2
80°-90°	24.7	0.4
90°-100°	53.5	0.8
100°-110°	196.0	2.9
110°-120°	524.0	7.7
120°-130°	865.0	12.8
130°-140°	919.9	13.6
140°-150°	855.0	12.6
150°-160°	687.4	10.2
160°-170°	443.0	6.5
170°-180°	152.5	2.3
0°-30°	837.6	12.4
0°-40°	1225.0	18.1
0°-60°	1809.6	26.7
0°-90°	2073.9	30.6
90°-120°	773.5	11.4
90°-150°	3413.3	50.4
90°-180°	4696.0	69.4
0°-180°	6770.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	17
90°	31	1	31	1	31	14
95°	50	75	50	75	50	47
105°	88	352	88	352	88	92
115°	95	667	95	667	95	238
125°	991	943	991	943	991	858
135°	1205	1166	1205	1166	1205	929
145°	1374	1353	1374	1353	1374	859
155°	1491	1490	1491	1490	1491	688
165°	1566	1570	1566	1570	1566	442
175°	1597	1606	1597	1606	1597	152
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	11.6	11.8	11.7	11.6	11.5	11.3	11.1	11.2	10.5	10.6	9.9
90°	31.3	30.8	30.2	29.8	29.3	28.4	27.1	25.8	24.5	23.2	21.1
92.5°	31.3	31.0	30.7	30.4	30.1	29.6	28.9	28.2	27.6	26.9	25.8
95°	49.9	50.1	50.4	50.6	50.9	50.4	49.1	47.8	46.5	45.2	43.5
97.5°	66.5	66.3	66.0	65.6	65.3	64.7	63.6	62.6	61.6	60.5	56.3
100°	77.7	77.2	76.6	76.1	75.7	74.4	72.3	70.2	68.2	66.1	61.7
102.5°	83.2	82.5	81.8	81.1	80.4	78.7	76.0	73.3	70.6	67.9	104.6
105°	88.1	87.1	86.1	85.0	84.0	82.1	79.2	76.4	73.5	70.8	141.0
107.5°	90.7	89.7	88.6	87.6	86.6	87.5	90.3	93.3	96.1	99.1	183.4
110°	91.6	90.6	89.5	88.5	87.5	99.9	125.6	151.4	177.2	202.9	277.4



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.5	91.7	90.9	90.1	89.2	135.8	229.8	323.8	417.8	511.8	530.2
115°	95.1	113.7	132.2	150.7	169.3	238.2	357.5	476.9	596.1	715.4	709.0
117.5°	388.2	449.1	510.1	571.1	632.1	677.0	705.9	734.7	763.6	792.5	788.0
120°	707.4	742.1	776.9	811.7	846.4	862.3	859.2	856.1	853.0	849.9	845.3
122.5°	882.6	889.4	896.2	902.9	909.6	912.1	910.3	908.4	906.5	904.7	899.6
125°	991.4	990.7	989.9	989.1	988.3	987.0	985.2	983.4	981.6	979.8	974.9
127.5°	1060.1	1059.9	1059.7	1059.6	1059.5	1058.0	1055.4	1052.8	1050.2	1047.6	1043.9
130°	1102.7	1103.0	1103.3	1103.5	1103.8	1102.4	1099.7	1096.8	1094.0	1091.1	1088.3
132.5°	1144.4	1144.8	1145.0	1145.3	1145.5	1144.4	1142.0	1139.5	1137.2	1134.7	1131.9
135°	1204.8	1205.3	1205.8	1206.3	1206.8	1205.8	1203.2	1200.6	1198.1	1195.5	1193.2
137.5°	1259.7	1260.6	1261.5	1262.3	1263.2	1262.4	1259.9	1257.4	1254.8	1252.3	1249.7
140°	1294.0	1295.3	1296.7	1298.0	1299.2	1298.7	1296.4	1294.0	1291.8	1289.4	1286.6
142.5°	1327.5	1328.8	1330.0	1331.3	1332.6	1332.2	1330.1	1328.0	1325.8	1323.7	1320.5
145°	1374.1	1375.3	1376.6	1377.9	1379.2	1379.0	1377.1	1375.3	1373.5	1371.7	1367.3
147.5°	1415.1	1416.2	1417.3	1418.4	1419.4	1419.4	1418.0	1416.7	1415.3	1414.0	1409.7
150°	1440.1	1441.4	1442.8	1444.1	1445.3	1445.2	1443.7	1442.1	1440.6	1439.0	1434.8
152.5°	1461.5	1463.2	1464.9	1466.6	1468.3	1468.4	1466.8	1465.3	1463.7	1462.2	1458.2
155°	1491.2	1493.2	1495.3	1497.4	1499.4	1499.7	1498.1	1496.6	1495.0	1493.5	1490.4
157.5°	1518.3	1520.3	1522.3	1524.4	1526.3	1526.5	1524.7	1523.0	1521.3	1519.5	1517.3
160°	1534.1	1535.9	1537.7	1539.5	1541.3	1541.4	1539.9	1538.3	1536.8	1535.2	1533.7
162.5°	1547.1	1549.3	1551.5	1553.7	1555.9	1556.2	1554.4	1552.7	1550.9	1549.2	1547.8
165°	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5	1565.8
167.5°	1578.8	1581.2	1583.5	1585.8	1588.1	1588.4	1586.6	1584.8	1583.0	1581.2	1580.5
170°	1586.2	1588.6	1590.9	1593.3	1595.5	1595.8	1594.0	1592.2	1590.4	1588.6	1588.0
172.5°	1591.8	1594.2	1596.4	1598.8	1601.1	1601.3	1599.5	1597.7	1595.9	1594.2	1593.7
175°	1596.7	1599.3	1601.8	1604.4	1607.0	1607.4	1605.6	1603.8	1602.0	1600.2	1599.7
177.5°	1599.7	1601.6	1603.4	1605.2	1607.1	1607.4	1605.9	1604.4	1603.0	1601.6	1601.3
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	9.5	9.4	9.0	8.2	7.9	7.7	8.8	9.9	9.1	8.7	8.6
90°	19.1	17.0	14.9	12.5	9.7	6.8	4.0	1.1	4.0	6.8	9.7
92.5°	24.9	23.8	22.7	22.4	22.7	22.9	23.2	23.4	23.2	22.9	22.7
95°	41.6	39.8	38.0	41.3	49.9	58.4	66.9	75.3	66.9	58.4	49.9
97.5°	52.2	48.0	43.9	53.7	77.7	101.7	125.6	149.6	125.6	101.7	77.7
100°	57.3	52.9	48.6	64.0	99.3	134.6	169.9	205.2	169.9	134.6	99.3
102.5°	141.2	177.9	214.5	236.6	244.0	251.5	259.0	266.4	259.0	251.5	244.0
105°	211.4	281.8	352.1	383.4	375.7	367.9	360.2	352.5	360.2	367.9	375.7
107.5°	267.7	352.1	436.5	475.6	469.3	463.1	456.8	450.6	456.8	463.1	469.3
110°	351.9	426.3	500.8	535.3	529.9	524.5	519.1	513.7	519.1	524.5	529.9



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	548.6	567.0	585.4	592.2	587.4	582.6	577.8	573.1	577.8	582.6	587.4
115°	702.5	696.1	689.7	684.3	679.9	675.5	671.2	666.8	671.2	675.5	679.9
117.5°	783.6	779.1	774.7	770.1	765.2	760.3	755.4	750.5	755.4	760.3	765.2
120°	840.7	836.0	831.4	827.1	823.3	819.4	815.5	811.7	815.5	819.4	823.3
122.5°	894.5	889.5	884.5	880.0	875.9	871.8	867.7	863.6	867.7	871.8	875.9
125°	970.0	965.2	960.3	956.1	952.8	949.4	946.1	942.7	946.1	949.4	952.8
127.5°	1040.2	1036.6	1032.9	1029.2	1025.5	1021.8	1018.1	1014.4	1018.1	1021.8	1025.5
130°	1085.5	1082.6	1079.8	1076.4	1072.2	1068.0	1064.0	1059.8	1064.0	1068.0	1072.2
132.5°	1129.0	1126.3	1123.4	1120.2	1116.7	1113.2	1109.7	1106.2	1109.7	1113.2	1116.7
135°	1190.8	1188.5	1186.2	1183.0	1178.8	1174.8	1170.6	1166.5	1170.6	1174.8	1178.8
137.5°	1247.1	1244.4	1241.8	1239.0	1236.2	1233.3	1230.4	1227.5	1230.4	1233.3	1236.2
140°	1283.8	1280.9	1278.1	1275.6	1273.6	1271.5	1269.4	1267.4	1269.4	1271.5	1273.6
142.5°	1317.3	1314.0	1310.8	1308.2	1306.4	1304.5	1302.6	1300.8	1302.6	1304.5	1306.4
145°	1363.0	1358.6	1354.2	1352.2	1352.4	1352.7	1352.9	1353.2	1352.9	1352.7	1352.4
147.5°	1405.3	1400.9	1396.6	1395.0	1396.0	1396.9	1397.9	1398.9	1397.9	1396.9	1396.0
150°	1430.8	1426.6	1422.5	1421.3	1423.2	1425.0	1426.8	1428.6	1426.8	1425.0	1423.2
152.5°	1454.3	1450.4	1446.5	1445.6	1447.6	1449.6	1451.6	1453.6	1451.6	1449.6	1447.6
155°	1487.4	1484.3	1481.2	1480.7	1483.0	1485.4	1487.7	1490.0	1487.7	1485.4	1483.0
157.5°	1515.2	1513.0	1510.8	1510.7	1512.7	1514.7	1516.6	1518.6	1516.6	1514.7	1512.7
160°	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1533.7	1532.2	1530.6
162.5°	1546.5	1545.2	1543.8	1543.9	1545.5	1547.0	1548.6	1550.0	1548.6	1547.0	1545.5
165°	1565.0	1564.2	1563.5	1563.8	1565.4	1566.9	1568.5	1570.0	1568.5	1566.9	1565.4
167.5°	1579.7	1579.0	1578.3	1578.7	1580.2	1581.8	1583.3	1584.9	1583.3	1581.8	1580.2
170°	1587.6	1587.1	1586.5	1587.1	1588.6	1590.2	1591.7	1593.3	1591.7	1590.2	1588.6
172.5°	1593.1	1592.6	1592.1	1592.6	1594.2	1595.7	1597.3	1598.8	1597.3	1595.7	1594.2
175°	1599.1	1598.6	1598.1	1598.8	1600.6	1602.4	1604.2	1606.0	1604.2	1602.4	1600.6
177.5°	1601.2	1600.9	1600.8	1601.3	1602.8	1604.3	1605.7	1607.1	1605.7	1604.3	1602.8
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	8.8	9.0	8.7	9.1	9.5	9.6	9.9	9.8	10.1	10.4	10.2
90°	12.5	14.9	17.0	19.1	21.1	23.2	24.5	25.8	27.1	28.4	29.3
92.5°	22.4	22.7	23.8	24.9	25.8	26.9	27.6	28.2	28.9	29.6	30.1
95°	41.3	38.0	39.8	41.6	43.5	45.2	46.5	47.8	49.1	50.4	50.9
97.5°	53.7	43.9	48.0	52.2	56.3	60.5	61.6	62.6	63.6	64.7	65.3
100°	64.0	48.6	52.9	57.3	61.7	66.1	68.2	70.2	72.3	74.4	75.7
102.5°	236.6	214.5	177.9	141.2	104.6	67.9	70.6	73.3	76.0	78.7	80.4
105°	383.4	352.1	281.8	211.4	141.0	70.8	73.5	76.4	79.2	82.1	84.0
107.5°	475.6	436.5	352.1	267.7	183.4	99.1	96.1	93.3	90.3	87.5	86.6
110°	535.3	500.8	426.3	351.9	277.4	202.9	177.2	151.4	125.6	99.9	87.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	592.2	585.4	567.0	548.6	530.2	511.8	417.8	323.8	229.8	135.8	89.2
115°	684.3	689.7	696.1	702.5	709.0	715.4	596.1	476.9	357.5	238.2	169.3
117.5°	770.1	774.7	779.1	783.6	788.0	792.5	763.6	734.7	705.9	677.0	632.1
120°	827.1	831.4	836.0	840.7	845.3	849.9	853.0	856.1	859.2	862.3	846.4
122.5°	880.0	884.5	889.5	894.5	899.6	904.7	906.5	908.4	910.3	912.1	909.6
125°	956.1	960.3	965.2	970.0	974.9	979.8	981.6	983.4	985.2	987.0	988.3
127.5°	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2	1052.8	1055.4	1058.0	1059.5
130°	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0	1096.8	1099.7	1102.4	1103.8
132.5°	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2	1139.5	1142.0	1144.4	1145.5
135°	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1	1200.6	1203.2	1205.8	1206.8
137.5°	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8	1257.4	1259.9	1262.4	1263.2
140°	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8	1294.0	1296.4	1298.7	1299.2
142.5°	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8	1328.0	1330.1	1332.2	1332.6
145°	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5	1375.3	1377.1	1379.0	1379.2
147.5°	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3	1416.7	1418.0	1419.4	1419.4
150°	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6	1442.1	1443.7	1445.2	1445.3
152.5°	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7	1465.3	1466.8	1468.4	1468.3
155°	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0	1496.6	1498.1	1499.7	1499.4
157.5°	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3	1523.0	1524.7	1526.5	1526.3
160°	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8	1538.3	1539.9	1541.4	1541.3
162.5°	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9	1552.7	1554.4	1556.2	1555.9
165°	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8
167.5°	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0	1584.8	1586.6	1588.4	1588.1
170°	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4	1592.2	1594.0	1595.8	1595.5
172.5°	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9	1597.7	1599.5	1601.3	1601.1
175°	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0	1603.8	1605.6	1607.4	1607.0
177.5°	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0	1604.4	1605.9	1607.4	1607.1
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	10.3	10.0	10.5	10.3	10.5	10.0	10.3	10.2	10.4	10.1	9.8
90°	29.8	30.2	30.8	31.3	30.8	30.2	29.8	29.3	28.4	27.1	25.8
92.5°	30.4	30.7	31.0	31.3	31.0	30.7	30.4	30.1	29.6	28.9	28.2
95°	50.6	50.4	50.1	49.9	50.1	50.4	50.6	50.9	50.4	49.1	47.8
97.5°	65.6	66.0	66.3	66.5	66.3	66.0	65.6	65.3	64.7	63.6	62.6
100°	76.1	76.6	77.2	77.7	77.2	76.6	76.1	75.7	74.4	72.3	70.2
102.5°	81.1	81.8	82.5	83.2	82.5	81.8	81.1	80.4	78.7	76.0	73.3
105°	85.0	86.1	87.1	88.1	87.1	86.1	85.0	84.0	82.1	79.2	76.4
107.5°	87.6	88.6	89.7	90.7	89.7	88.6	87.6	86.6	87.5	90.3	93.3
110°	88.5	89.5	90.6	91.6	90.6	89.5	88.5	87.5	99.9	125.6	151.4



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	90.1	90.9	91.7	92.5	91.7	90.9	90.1	89.2	135.8	229.8	323.8
115°	150.7	132.2	113.7	95.1	113.7	132.2	150.7	169.3	238.2	357.5	476.9
117.5°	571.1	510.1	449.1	388.2	449.1	510.1	571.1	632.1	677.0	705.9	734.7
120°	811.7	776.9	742.1	707.4	742.1	776.9	811.7	846.4	862.3	859.2	856.1
122.5°	902.9	896.2	889.4	882.6	889.4	896.2	902.9	909.6	912.1	910.3	908.4
125°	989.1	989.9	990.7	991.4	990.7	989.9	989.1	988.3	987.0	985.2	983.4
127.5°	1059.6	1059.7	1059.9	1060.1	1059.9	1059.7	1059.6	1059.5	1058.0	1055.4	1052.8
130°	1103.5	1103.3	1103.0	1102.7	1103.0	1103.3	1103.5	1103.8	1102.4	1099.7	1096.8
132.5°	1145.3	1145.0	1144.8	1144.4	1144.8	1145.0	1145.3	1145.5	1144.4	1142.0	1139.5
135°	1206.3	1205.8	1205.3	1204.8	1205.3	1205.8	1206.3	1206.8	1205.8	1203.2	1200.6
137.5°	1262.3	1261.5	1260.6	1259.7	1260.6	1261.5	1262.3	1263.2	1262.4	1259.9	1257.4
140°	1298.0	1296.7	1295.3	1294.0	1295.3	1296.7	1298.0	1299.2	1298.7	1296.4	1294.0
142.5°	1331.3	1330.0	1328.8	1327.5	1328.8	1330.0	1331.3	1332.6	1332.2	1330.1	1328.0
145°	1377.9	1376.6	1375.3	1374.1	1375.3	1376.6	1377.9	1379.2	1379.0	1377.1	1375.3
147.5°	1418.4	1417.3	1416.2	1415.1	1416.2	1417.3	1418.4	1419.4	1419.4	1418.0	1416.7
150°	1444.1	1442.8	1441.4	1440.1	1441.4	1442.8	1444.1	1445.3	1445.2	1443.7	1442.1
152.5°	1466.6	1464.9	1463.2	1461.5	1463.2	1464.9	1466.6	1468.3	1468.4	1466.8	1465.3
155°	1497.4	1495.3	1493.2	1491.2	1493.2	1495.3	1497.4	1499.4	1499.7	1498.1	1496.6
157.5°	1524.4	1522.3	1520.3	1518.3	1520.3	1522.3	1524.4	1526.3	1526.5	1524.7	1523.0
160°	1539.5	1537.7	1535.9	1534.1	1535.9	1537.7	1539.5	1541.3	1541.4	1539.9	1538.3
162.5°	1553.7	1551.5	1549.3	1547.1	1549.3	1551.5	1553.7	1555.9	1556.2	1554.4	1552.7
165°	1572.0	1570.2	1568.4	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2
167.5°	1585.8	1583.5	1581.2	1578.8	1581.2	1583.5	1585.8	1588.1	1588.4	1586.6	1584.8
170°	1593.3	1590.9	1588.6	1586.2	1588.6	1590.9	1593.3	1595.5	1595.8	1594.0	1592.2
172.5°	1598.8	1596.4	1594.2	1591.8	1594.2	1596.4	1598.8	1601.1	1601.3	1599.5	1597.7
175°	1604.4	1601.8	1599.3	1596.7	1599.3	1601.8	1604.4	1607.0	1607.4	1605.6	1603.8
177.5°	1605.2	1603.4	1601.6	1599.7	1601.6	1603.4	1605.2	1607.1	1607.4	1605.9	1604.4
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	9.9	9.6	9.5	9.1	8.7	9.0	8.8	8.6	8.7	9.1	9.9
90°	24.5	23.2	21.1	19.1	17.0	14.9	12.5	9.7	6.8	4.0	1.1
92.5°	27.6	26.9	25.8	24.9	23.8	22.7	22.4	22.7	22.9	23.2	23.4
95°	46.5	45.2	43.5	41.6	39.8	38.0	41.3	49.9	58.4	66.9	75.3
97.5°	61.6	60.5	56.3	52.2	48.0	43.9	53.7	77.7	101.7	125.6	149.6
100°	68.2	66.1	61.7	57.3	52.9	48.6	64.0	99.3	134.6	169.9	205.2
102.5°	70.6	67.9	104.6	141.2	177.9	214.5	236.6	244.0	251.5	259.0	266.4
105°	73.5	70.8	141.0	211.4	281.8	352.1	383.4	375.7	367.9	360.2	352.5
107.5°	96.1	99.1	183.4	267.7	352.1	436.5	475.6	469.3	463.1	456.8	450.6
110°	177.2	202.9	277.4	351.9	426.3	500.8	535.3	529.9	524.5	519.1	513.7



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	417.8	511.8	530.2	548.6	567.0	585.4	592.2	587.4	582.6	577.8	573.1
115°	596.1	715.4	709.0	702.5	696.1	689.7	684.3	679.9	675.5	671.2	666.8
117.5°	763.6	792.5	788.0	783.6	779.1	774.7	770.1	765.2	760.3	755.4	750.5
120°	853.0	849.9	845.3	840.7	836.0	831.4	827.1	823.3	819.4	815.5	811.7
122.5°	906.5	904.7	899.6	894.5	889.5	884.5	880.0	875.9	871.8	867.7	863.6
125°	981.6	979.8	974.9	970.0	965.2	960.3	956.1	952.8	949.4	946.1	942.7
127.5°	1050.2	1047.6	1043.9	1040.2	1036.6	1032.9	1029.2	1025.5	1021.8	1018.1	1014.4
130°	1094.0	1091.1	1088.3	1085.5	1082.6	1079.8	1076.4	1072.2	1068.0	1064.0	1059.8
132.5°	1137.2	1134.7	1131.9	1129.0	1126.3	1123.4	1120.2	1116.7	1113.2	1109.7	1106.2
135°	1198.1	1195.5	1193.2	1190.8	1188.5	1186.2	1183.0	1178.8	1174.8	1170.6	1166.5
137.5°	1254.8	1252.3	1249.7	1247.1	1244.4	1241.8	1239.0	1236.2	1233.3	1230.4	1227.5
140°	1291.8	1289.4	1286.6	1283.8	1280.9	1278.1	1275.6	1273.6	1271.5	1269.4	1267.4
142.5°	1325.8	1323.7	1320.5	1317.3	1314.0	1310.8	1308.2	1306.4	1304.5	1302.6	1300.8
145°	1373.5	1371.7	1367.3	1363.0	1358.6	1354.2	1352.2	1352.4	1352.7	1352.9	1353.2
147.5°	1415.3	1414.0	1409.7	1405.3	1400.9	1396.6	1395.0	1396.0	1396.9	1397.9	1398.9
150°	1440.6	1439.0	1434.8	1430.8	1426.6	1422.5	1421.3	1423.2	1425.0	1426.8	1428.6
152.5°	1463.7	1462.2	1458.2	1454.3	1450.4	1446.5	1445.6	1447.6	1449.6	1451.6	1453.6
155°	1495.0	1493.5	1490.4	1487.4	1484.3	1481.2	1480.7	1483.0	1485.4	1487.7	1490.0
157.5°	1521.3	1519.5	1517.3	1515.2	1513.0	1510.8	1510.7	1512.7	1514.7	1516.6	1518.6
160°	1536.8	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2
162.5°	1550.9	1549.2	1547.8	1546.5	1545.2	1543.8	1543.9	1545.5	1547.0	1548.6	1550.0
165°	1568.4	1566.5	1565.8	1565.0	1564.2	1563.5	1563.8	1565.4	1566.9	1568.5	1570.0
167.5°	1583.0	1581.2	1580.5	1579.7	1579.0	1578.3	1578.7	1580.2	1581.8	1583.3	1584.9
170°	1590.4	1588.6	1588.0	1587.6	1587.1	1586.5	1587.1	1588.6	1590.2	1591.7	1593.3
172.5°	1595.9	1594.2	1593.7	1593.1	1592.6	1592.1	1592.6	1594.2	1595.7	1597.3	1598.8
175°	1602.0	1600.2	1599.7	1599.1	1598.6	1598.1	1598.8	1600.6	1602.4	1604.2	1606.0
177.5°	1603.0	1601.6	1601.3	1601.2	1600.9	1600.8	1601.3	1602.8	1604.3	1605.7	1607.1
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.8	7.7	7.9	8.2	9.0	9.4	9.5	9.9	10.6	10.5	11.2
90°	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5	25.8
92.5°	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6	28.2
95°	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5	47.8
97.5°	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6	62.6
100°	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2	70.2
102.5°	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6	73.3
105°	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5	76.4
107.5°	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1	93.3
110°	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2	151.4



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8	323.8
115°	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1	476.9
117.5°	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6	734.7
120°	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0	856.1
122.5°	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5	908.4
125°	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6	983.4
127.5°	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2	1052.8
130°	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0	1096.8
132.5°	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2	1139.5
135°	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1	1200.6
137.5°	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8	1257.4
140°	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8	1294.0
142.5°	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8	1328.0
145°	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5	1375.3
147.5°	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3	1416.7
150°	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6	1442.1
152.5°	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7	1465.3
155°	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0	1496.6
157.5°	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3	1523.0
160°	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8	1538.3
162.5°	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9	1552.7
165°	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4	1570.2
167.5°	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0	1584.8
170°	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4	1592.2
172.5°	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9	1597.7
175°	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0	1603.8
177.5°	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0	1604.4
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	11.1	11.3	11.5	11.6	11.7	11.8	11.6
90°	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	125.6	99.9	87.5	88.5	89.5	90.6	91.6



TEST NUMBER: P331821-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)