

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331822-930

Luminaire Tested: **S122RDIW-S675D1440U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331822-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6148.4 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	26
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24	20
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17	14
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15	13
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14	12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	1.8
10°-20°	316.4	5.1
20°-30°	407.7	6.6
30°-40°	387.4	6.3
40°-50°	331.9	5.4
50°-60°	252.7	4.1
60°-70°	159.8	2.6
70°-80°	79.8	1.3
80°-90°	26.6	0.4
90°-100°	92.3	1.5
100°-110°	286.6	4.7
110°-120°	490.0	8.0
120°-130°	644.3	10.5
130°-140°	723.2	11.8
140°-150°	709.1	11.5
150°-160°	594.8	9.7
160°-170°	394.5	6.4
170°-180°	137.9	2.2
0°-30°	837.6	13.6
0°-40°	1225.0	19.9
0°-60°	1809.6	29.4
0°-90°	2075.8	33.8
90°-120°	868.9	14.1
90°-150°	2945.5	47.9
90°-180°	4073.0	66.2
0°-180°	6148.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	17
90°	42	1	42	1	42	19
95°	76	64	76	64	76	85
105°	273	264	273	264	273	287
115°	492	492	492	492	492	486
125°	718	715	718	715	718	640
135°	937	926	937	926	937	721
145°	1136	1123	1136	1123	1136	709
155°	1294	1284	1294	1284	1294	596
165°	1399	1398	1399	1398	1399	394
175°	1449	1454	1449	1454	1449	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	13.7	13.9	13.9	13.9	13.8	13.9	13.9	14.3	14.2	14.6	13.0
90°	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9	42.5	43.0	37.0
92.5°	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3	39.2	39.1	37.7
95°	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7	78.7	78.7	78.1
97.5°	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2	132.2	132.2	131.2
100°	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6	169.6	169.6	168.8
102.5°	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3	210.2	209.9	208.9
105°	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5	270.9	270.4	269.9
107.5°	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5	337.2	337.0	337.0
110°	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1	427.8	428.4	428.7
115°	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0	496.3	496.6	497.1
117.5°	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6	563.3	563.9	565.4
120°	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2	607.2	607.2	609.4
122.5°	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1	653.7	654.4	655.9
125°	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1	721.9	722.7	723.6
127.5°	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1	788.1	789.1	790.1
130°	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3	832.8	833.3	833.9
132.5°	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2	877.3	878.6	878.5
135°	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9	941.3	941.5	940.9
137.5°	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0	1003.2	1003.5	1002.7
140°	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7	1044.7	1044.7	1043.4
142.5°	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6	1082.3	1082.1	1081.2
145°	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0	1139.6	1139.4	1137.8
147.5°	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3	1189.7	1189.0	1188.0
150°	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5	1219.4
152.5°	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0	1250.7
155°	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5	1293.1	1291.8	1290.9
157.5°	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9	1330.0	1328.2	1327.7
160°	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0	1352.4	1350.8	1350.5
162.5°	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2	1372.3	1370.4	1370.2
165°	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1	1398.2	1396.3	1396.3
167.5°	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5	1419.6	1417.6	1417.7
170°	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3	1431.3	1429.5	1429.7
172.5°	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1	1440.2	1438.3	1438.6
175°	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7	1449.8	1447.9	1448.5
177.5°	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5	1454.0
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	11.8	11.0	9.8	8.6	8.2	7.9	8.9	9.9	9.2	8.9	8.9
90°	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2	4.5	7.7	11.1
92.5°	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9	24.3	26.7	29.1
95°	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9	66.6	69.4	72.1
97.5°	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8	119.2	121.6	124.0
100°	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1	158.2	160.5	162.7
102.5°	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4	199.2	200.9	202.6
105°	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2	265.1	265.9	266.7
107.5°	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6	332.8	334.0	335.3
110°	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9	376.5	378.1	379.8



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1	423.7	425.3	427.0
115°	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6	493.3	494.9	496.6
117.5°	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0	563.1	565.3	567.5
120°	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	609.4	611.6	613.8
122.5°	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5	652.1	654.7	657.3
125°	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3	717.8	720.2	722.7
127.5°	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5	782.6	785.7	788.9
130°	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8	823.4	827.0	830.5
132.5°	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0	868.0	870.8	873.8
135°	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5	928.5	931.6	934.5
137.5°	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2	991.6	994.1	996.5
140°	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5	1030.0	1032.5	1034.9
142.5°	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9	1069.3	1071.8	1074.2
145°	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4	1125.4	1127.2	1129.1
147.5°	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8	1176.1	1178.4	1180.7
150°	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2	1209.8	1211.5	1213.2
152.5°	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7	1240.3	1241.9	1243.6
155°	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4	1285.2	1286.1	1286.9
157.5°	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5	1324.0	1324.6	1325.2
160°	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1	1347.7	1348.2	1348.7
162.5°	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7	1368.9	1369.0	1369.1
165°	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5	1397.3	1396.9	1396.7
167.5°	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6	1420.7	1419.9	1419.1
170°	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4	1433.5	1432.7	1431.9
172.5°	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2	1442.4	1441.6	1440.8
175°	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0	1453.2	1452.4	1451.6
177.5°	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5	1457.8	1457.2	1456.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	9.2	9.8	10.4	11.5	12.7	13.6	13.5	13.0	13.0	12.8	12.5
90°	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9	41.4	40.8	40.7
92.5°	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3	39.4	39.5	39.6
95°	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7	78.7	78.7	78.4
97.5°	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2	132.2	132.2	132.2
100°	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6	169.6	169.6	169.5
102.5°	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3	210.6	210.8	210.8
105°	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5	272.1	272.6	272.9
107.5°	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5	337.7	337.9	337.4
110°	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	381.8



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1	426.5	425.8	425.2
115°	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0	495.7	495.5	494.9
117.5°	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6	562.0	561.3	560.5
120°	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2	607.2	607.2	606.7
122.5°	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1	652.4	651.8	651.1
125°	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1	720.2	719.4	718.9
127.5°	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1	786.1	785.1	784.2
130°	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3	831.7	831.1	830.3
132.5°	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2	875.0	873.8	872.7
135°	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9	940.7	940.4	939.9
137.5°	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0	1002.8	1002.6	1001.9
140°	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7	1044.7	1044.7	1044.2
142.5°	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6	1082.8	1083.0	1082.6
145°	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0	1140.2	1140.4	1140.0
147.5°	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3	1190.8	1191.5	1191.2
150°	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8
152.5°	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1
155°	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5	1295.9	1297.2	1297.5
157.5°	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9	1333.7	1335.6	1335.9
160°	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0	1355.7	1357.3	1357.6
162.5°	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2	1376.1	1377.9	1378.2
165°	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1	1402.0	1403.9	1404.2
167.5°	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5	1423.4	1425.3	1425.6
170°	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3	1435.2	1437.1	1437.2
172.5°	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1	1444.1	1445.9	1446.1
175°	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7	1453.6	1455.6	1455.7
177.5°	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	12.6	12.2	12.6	12.4	12.6	12.2	12.6	12.5	12.8	13.0	13.0
90°	41.0	41.3	41.5	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9
92.5°	39.6	39.7	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3
95°	77.9	77.3	76.7	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7
97.5°	132.2	132.1	132.1	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2
100°	169.2	168.9	168.7	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6
102.5°	210.5	210.3	209.9	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3
105°	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5
107.5°	336.1	334.8	333.6	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5
110°	381.0	380.2	379.4	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	424.6	424.0	423.4	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1
115°	494.1	493.3	492.4	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0
117.5°	559.7	558.9	558.1	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6
120°	605.9	605.1	604.3	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2
122.5°	650.5	650.0	649.3	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1
125°	718.6	718.4	718.1	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1
127.5°	783.3	782.4	781.6	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1
130°	829.2	828.2	827.0	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3
132.5°	871.9	871.0	870.1	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2
135°	939.1	938.2	937.4	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9
137.5°	1000.9	999.7	998.7	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0
140°	1043.1	1042.0	1040.9	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7
142.5°	1081.5	1080.4	1079.3	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6
145°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0
147.5°	1190.2	1189.1	1188.1	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3
150°	1222.9	1222.1	1221.3	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1
152.5°	1255.1	1254.0	1253.0	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0
155°	1296.7	1295.9	1295.1	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5
157.5°	1334.6	1333.3	1332.0	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9
160°	1356.5	1355.4	1354.4	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0
162.5°	1376.9	1375.6	1374.3	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2
165°	1402.8	1401.5	1400.1	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1
167.5°	1424.2	1422.7	1421.3	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5
170°	1435.6	1433.9	1432.3	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3
172.5°	1444.5	1442.8	1441.2	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1
175°	1454.0	1452.4	1450.7	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7
177.5°	1457.5	1456.2	1454.8	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	13.5	13.6	12.7	11.5	10.4	9.8	9.2	8.9	8.9	9.2	9.9
90°	42.5	43.0	37.0	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2
92.5°	39.2	39.1	37.7	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9
95°	78.7	78.7	78.1	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9
97.5°	132.2	132.2	131.2	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8
100°	169.6	169.6	168.8	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1
102.5°	210.2	209.9	208.9	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4
105°	270.9	270.4	269.9	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2
107.5°	337.2	337.0	337.0	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6
110°	382.3	382.3	382.3	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.8	428.4	428.7	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1
115°	496.3	496.6	497.1	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6
117.5°	563.3	563.9	565.4	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0
120°	607.2	607.2	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2
122.5°	653.7	654.4	655.9	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5
125°	721.9	722.7	723.6	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3
127.5°	788.1	789.1	790.1	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5
130°	832.8	833.3	833.9	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8
132.5°	877.3	878.6	878.5	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0
135°	941.3	941.5	940.9	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5
137.5°	1003.2	1003.5	1002.7	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2
140°	1044.7	1044.7	1043.4	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5
142.5°	1082.3	1082.1	1081.2	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9
145°	1139.6	1139.4	1137.8	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4
147.5°	1189.7	1189.0	1188.0	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8
150°	1221.3	1220.5	1219.4	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2
152.5°	1253.0	1252.0	1250.7	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7
155°	1293.1	1291.8	1290.9	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4
157.5°	1330.0	1328.2	1327.7	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5
160°	1352.4	1350.8	1350.5	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1
162.5°	1372.3	1370.4	1370.2	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7
165°	1398.2	1396.3	1396.3	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5
167.5°	1419.6	1417.6	1417.7	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6
170°	1431.3	1429.5	1429.7	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4
172.5°	1440.2	1438.3	1438.6	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2
175°	1449.8	1447.9	1448.5	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0
177.5°	1454.8	1453.5	1454.0	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.9	7.9	8.2	8.6	9.8	11.0	11.8	13.0	14.6	14.2	14.3
90°	4.5	7.7	11.1	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9
92.5°	24.3	26.7	29.1	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3
95°	66.6	69.4	72.1	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7
97.5°	119.2	121.6	124.0	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2
100°	158.2	160.5	162.7	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6
102.5°	199.2	200.9	202.6	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3
105°	265.1	265.9	266.7	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5
107.5°	332.8	334.0	335.3	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5
110°	376.5	378.1	379.8	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	423.7	425.3	427.0	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1
115°	493.3	494.9	496.6	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0
117.5°	563.1	565.3	567.5	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6
120°	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2
122.5°	652.1	654.7	657.3	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1
125°	717.8	720.2	722.7	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1
127.5°	782.6	785.7	788.9	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1
130°	823.4	827.0	830.5	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3
132.5°	868.0	870.8	873.8	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2
135°	928.5	931.6	934.5	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9
137.5°	991.6	994.1	996.5	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0
140°	1030.0	1032.5	1034.9	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7
142.5°	1069.3	1071.8	1074.2	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6
145°	1125.4	1127.2	1129.1	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0
147.5°	1176.1	1178.4	1180.7	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3
150°	1209.8	1211.5	1213.2	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1
152.5°	1240.3	1241.9	1243.6	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0
155°	1285.2	1286.1	1286.9	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5
157.5°	1324.0	1324.6	1325.2	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9
160°	1347.7	1348.2	1348.7	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0
162.5°	1368.9	1369.0	1369.1	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2
165°	1397.3	1396.9	1396.7	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1
167.5°	1420.7	1419.9	1419.1	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5
170°	1433.5	1432.7	1431.9	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3
172.5°	1442.4	1441.6	1440.8	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1
175°	1453.2	1452.4	1451.6	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7
177.5°	1457.8	1457.2	1456.5	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	13.9	13.9	13.8	13.9	13.9	13.9	13.7
90°	41.4	40.8	40.7	41.0	41.3	41.5	41.8
92.5°	39.4	39.5	39.6	39.6	39.7	39.8	39.8
95°	78.7	78.7	78.4	77.9	77.3	76.7	76.2
97.5°	132.2	132.2	132.2	132.2	132.1	132.1	132.0
100°	169.6	169.6	169.5	169.2	168.9	168.7	168.4
102.5°	210.6	210.8	210.8	210.5	210.3	209.9	209.7
105°	272.1	272.6	272.9	272.9	272.9	272.9	272.9
107.5°	337.7	337.9	337.4	336.1	334.8	333.6	332.3
110°	382.3	382.3	381.8	381.0	380.2	379.4	378.5



TEST NUMBER: P331822-930

CATALOG NUMBER: S122RDIW-S675D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	426.5	425.8	425.2	424.6	424.0	423.4	422.8
115°	495.7	495.5	494.9	494.1	493.3	492.4	491.6
117.5°	562.0	561.3	560.5	559.7	558.9	558.1	557.3
120°	607.2	607.2	606.7	605.9	605.1	604.3	603.5
122.5°	652.4	651.8	651.1	650.5	650.0	649.3	648.7
125°	720.2	719.4	718.9	718.6	718.4	718.1	717.8
127.5°	786.1	785.1	784.2	783.3	782.4	781.6	780.7
130°	831.7	831.1	830.3	829.2	828.2	827.0	826.0
132.5°	875.0	873.8	872.7	871.9	871.0	870.1	869.2
135°	940.7	940.4	939.9	939.1	938.2	937.4	936.6
137.5°	1002.8	1002.6	1001.9	1000.9	999.7	998.7	997.5
140°	1044.7	1044.7	1044.2	1043.1	1042.0	1040.9	1039.8
142.5°	1082.8	1083.0	1082.6	1081.5	1080.4	1079.3	1078.2
145°	1140.2	1140.4	1140.0	1139.0	1137.9	1136.8	1135.7
147.5°	1190.8	1191.5	1191.2	1190.2	1189.1	1188.1	1187.1
150°	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5
152.5°	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0
155°	1295.9	1297.2	1297.5	1296.7	1295.9	1295.1	1294.3
157.5°	1333.7	1335.6	1335.9	1334.6	1333.3	1332.0	1330.6
160°	1355.7	1357.3	1357.6	1356.5	1355.4	1354.4	1353.2
162.5°	1376.1	1377.9	1378.2	1376.9	1375.6	1374.3	1372.9
165°	1402.0	1403.9	1404.2	1402.8	1401.5	1400.1	1398.7
167.5°	1423.4	1425.3	1425.6	1424.2	1422.7	1421.3	1419.8
170°	1435.2	1437.1	1437.2	1435.6	1433.9	1432.3	1430.7
172.5°	1444.1	1445.9	1446.1	1444.5	1442.8	1441.2	1439.6
175°	1453.6	1455.6	1455.7	1454.0	1452.4	1450.7	1449.1
177.5°	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5

(END OF REPORT)