

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331806-930

Luminaire Tested: **S122RDIW-S675D435U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331806-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D435U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3295.6 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	102	98	94	91	95	92	89	86	81	78	76	71	69	68	62	60	59	55
2	93	86	81	76	87	81	76	72	72	68	65	63	61	58	55	53	52	48
3	86	77	70	65	80	73	67	62	65	60	56	57	53	50	50	47	45	42
4	79	69	61	56	74	65	59	53	58	53	49	52	48	44	46	42	40	37
5	73	62	54	49	69	59	52	47	53	47	43	47	43	39	42	38	36	33
6	68	56	49	43	64	53	46	41	48	42	38	43	38	35	38	35	32	29
7	63	51	44	38	59	49	42	37	44	38	34	40	35	32	35	32	29	27
8	59	47	40	34	55	45	38	33	41	35	31	37	32	29	33	29	26	24
9	55	43	36	31	52	41	35	30	38	32	28	34	29	26	31	27	24	22
10	52	40	33	28	49	38	32	27	35	29	26	32	27	24	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.5	3.4
10°-20°	316.4	9.6
20°-30°	407.7	12.4
30°-40°	387.4	11.8
40°-50°	331.9	10.1
50°-60°	252.7	7.7
60°-70°	159.8	4.8
70°-80°	79.8	2.4
80°-90°	22.5	0.7
90°-100°	27.7	0.8
100°-110°	86.1	2.6
110°-120°	147.2	4.5
120°-130°	193.6	5.9
130°-140°	217.3	6.6
140°-150°	213.1	6.5
150°-160°	178.7	5.4
160°-170°	118.6	3.6
170°-180°	41.4	1.3
0°-30°	837.6	25.4
0°-40°	1225.0	37.2
0°-60°	1809.6	54.9
0°-90°	2071.7	62.9
90°-120°	261.1	7.9
90°-150°	885.2	26.9
90°-180°	1224.0	37.1
0°-180°	3295.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	16
90°	13	0	13	0	13	6
95°	23	19	23	19	23	26
105°	82	79	82	79	82	86
115°	148	148	148	148	148	146
125°	216	215	216	215	216	192
135°	281	278	281	278	281	217
145°	341	338	341	338	341	213
155°	389	386	389	386	389	179
165°	420	420	420	420	420	119
175°	436	437	436	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	7.8	8.2	8.2	8.2	8.1	8.2	8.2	8.5	8.2	8.6	7.9
90°	12.6	12.5	12.4	12.3	12.2	12.3	12.5	12.6	12.8	13.0	11.1
92.5°	12.0	12.0	11.9	11.9	11.9	11.9	11.8	11.8	11.7	11.7	11.3
95°	22.9	23.1	23.2	23.4	23.6	23.6	23.6	23.6	23.6	23.6	23.5
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.5
100°	50.6	50.7	50.8	50.9	51.0	51.0	51.0	51.0	51.0	51.0	50.7
102.5°	63.0	63.1	63.2	63.3	63.3	63.3	63.3	63.2	63.2	63.1	62.8
105°	82.0	82.0	82.0	82.0	82.0	81.9	81.8	81.6	81.4	81.3	81.1
107.5°	99.9	100.3	100.6	101.0	101.4	101.6	101.5	101.4	101.3	101.3	101.3
110°	113.7	114.0	114.2	114.5	114.7	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	127.1	127.3	127.4	127.6	127.8	128.0	128.2	128.4	128.6	128.7	128.8
115°	147.7	148.0	148.2	148.5	148.7	148.9	149.0	149.0	149.1	149.2	149.4
117.5°	167.5	167.7	168.0	168.2	168.4	168.7	168.8	169.1	169.3	169.5	169.9
120°	181.4	181.6	181.9	182.1	182.4	182.5	182.5	182.5	182.5	182.5	183.1
122.5°	194.9	195.1	195.3	195.5	195.7	195.8	196.1	196.2	196.5	196.7	197.1
125°	215.7	215.8	215.9	216.0	216.1	216.2	216.5	216.7	217.0	217.2	217.4
127.5°	234.6	234.9	235.1	235.4	235.7	235.9	236.3	236.5	236.8	237.2	237.4
130°	248.3	248.6	248.9	249.2	249.6	249.8	250.0	250.1	250.3	250.5	250.6
132.5°	261.2	261.5	261.7	262.0	262.3	262.6	262.9	263.3	263.7	264.0	264.0
135°	281.4	281.7	281.9	282.2	282.4	282.6	282.7	282.7	282.8	282.9	282.7
137.5°	299.8	300.1	300.4	300.8	301.1	301.3	301.3	301.4	301.5	301.6	301.3
140°	312.5	312.8	313.2	313.5	313.8	314.0	314.0	314.0	314.0	314.0	313.6
142.5°	324.0	324.3	324.7	325.0	325.3	325.5	325.4	325.3	325.3	325.2	324.9
145°	341.3	341.6	341.9	342.3	342.6	342.8	342.7	342.6	342.5	342.4	341.9
147.5°	356.8	357.0	357.3	357.7	358.0	358.1	357.9	357.7	357.5	357.3	357.0
150°	366.8	367.0	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8	366.5
152.5°	376.3	376.6	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3	375.9
155°	389.0	389.2	389.5	389.7	390.0	389.9	389.5	389.1	388.7	388.2	388.0
157.5°	399.9	400.3	400.6	401.0	401.5	401.4	400.8	400.2	399.7	399.2	399.0
160°	406.7	407.0	407.3	407.6	408.0	407.9	407.4	406.9	406.4	405.9	405.9
162.5°	412.6	412.9	413.4	413.8	414.2	414.1	413.5	412.9	412.4	411.9	411.8
165°	420.4	420.8	421.2	421.6	422.0	421.9	421.3	420.8	420.2	419.6	419.6
167.5°	426.7	427.1	427.5	428.0	428.4	428.4	427.8	427.2	426.6	426.1	426.1
170°	430.0	430.5	431.0	431.5	431.9	431.9	431.3	430.7	430.2	429.6	429.7
172.5°	432.6	433.1	433.6	434.1	434.6	434.6	434.0	433.4	432.8	432.3	432.4
175°	435.5	436.0	436.5	437.0	437.5	437.4	436.8	436.3	435.7	435.1	435.3
177.5°	436.8	437.2	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8	436.9
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	7.5	7.5	7.1	6.5	6.7	6.8	8.2	9.7	8.6	7.8	7.3
90°	9.3	7.5	5.7	4.3	3.3	2.4	1.4	0.4	1.4	2.4	3.3
92.5°	10.9	10.4	10.0	9.5	8.7	8.0	7.3	6.6	7.3	8.0	8.7
95°	23.3	23.2	23.0	22.5	21.7	20.9	20.1	19.2	20.1	20.9	21.7
97.5°	39.1	38.8	38.5	38.0	37.3	36.5	35.8	35.1	35.8	36.5	37.3
100°	50.5	50.2	50.0	49.6	48.9	48.2	47.5	46.9	47.5	48.2	48.9
102.5°	62.5	62.1	61.9	61.4	60.9	60.3	59.8	59.4	59.8	60.3	60.9
105°	81.0	80.8	80.6	80.4	80.1	79.9	79.7	79.4	79.7	79.9	80.1
107.5°	101.3	101.3	101.3	101.1	100.8	100.4	100.0	99.6	100.0	100.4	100.8
110°	114.9	114.9	114.9	114.6	114.1	113.7	113.2	112.7	113.2	113.7	114.1



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	128.9	129.0	129.1	128.8	128.3	127.8	127.3	126.9	127.3	127.8	128.3
115°	149.5	149.7	149.9	149.7	149.2	148.7	148.2	147.7	148.2	148.7	149.2
117.5°	170.4	170.9	171.3	171.2	170.6	169.9	169.3	168.6	169.3	169.9	170.6
120°	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	183.1	183.8	184.4
122.5°	197.5	198.0	198.5	198.4	197.5	196.7	196.0	195.2	196.0	196.7	197.5
125°	217.7	217.9	218.2	217.9	217.2	216.5	215.7	215.0	215.7	216.5	217.2
127.5°	237.7	238.1	238.3	238.0	237.1	236.1	235.2	234.2	235.2	236.1	237.1
130°	250.8	250.9	251.1	250.6	249.6	248.5	247.4	246.4	247.4	248.5	249.6
132.5°	264.0	263.9	263.9	263.4	262.6	261.7	260.8	260.0	260.8	261.7	262.6
135°	282.6	282.4	282.3	281.8	280.9	280.0	279.1	278.2	279.1	280.0	280.9
137.5°	301.2	300.9	300.7	300.2	299.5	298.7	298.0	297.3	298.0	298.7	299.5
140°	313.2	312.7	312.3	311.8	311.0	310.3	309.6	308.8	309.6	310.3	311.0
142.5°	324.7	324.3	324.1	323.6	322.9	322.1	321.4	320.7	321.4	322.1	322.9
145°	341.4	341.0	340.5	339.9	339.3	338.8	338.2	337.6	338.2	338.8	339.3
147.5°	356.7	356.4	356.0	355.6	354.8	354.2	353.4	352.8	353.4	354.2	354.8
150°	366.2	365.8	365.5	365.1	364.6	364.1	363.6	363.1	363.6	364.1	364.6
152.5°	375.4	375.0	374.7	374.2	373.7	373.2	372.8	372.3	372.8	373.2	373.7
155°	387.8	387.5	387.3	387.0	386.8	386.5	386.2	386.0	386.2	386.5	386.8
157.5°	398.8	398.7	398.5	398.4	398.3	398.1	397.9	397.8	397.9	398.1	398.3
160°	405.8	405.7	405.6	405.5	405.4	405.2	405.0	404.9	405.0	405.2	405.4
162.5°	411.7	411.6	411.6	411.5	411.4	411.4	411.4	411.3	411.4	411.4	411.4
165°	419.6	419.6	419.6	419.6	419.7	419.8	419.9	420.0	419.9	419.8	419.7
167.5°	426.1	426.1	426.1	426.2	426.5	426.7	427.0	427.2	427.0	426.7	426.5
170°	429.7	429.8	429.9	430.1	430.3	430.6	430.8	431.0	430.8	430.6	430.3
172.5°	432.4	432.5	432.6	432.8	433.0	433.3	433.5	433.7	433.5	433.3	433.0
175°	435.5	435.6	435.8	436.0	436.3	436.5	436.8	437.0	436.8	436.5	436.3
177.5°	437.1	437.2	437.3	437.5	437.7	437.9	438.1	438.3	438.1	437.9	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	7.2	7.1	6.8	7.2	7.6	7.6	7.6	7.2	7.2	7.1	6.8
90°	4.3	5.7	7.5	9.3	11.1	13.0	12.8	12.6	12.5	12.3	12.2
92.5°	9.5	10.0	10.4	10.9	11.3	11.7	11.7	11.8	11.8	11.9	11.9
95°	22.5	23.0	23.2	23.3	23.5	23.6	23.6	23.6	23.6	23.6	23.6
97.5°	38.0	38.5	38.8	39.1	39.5	39.7	39.7	39.7	39.7	39.7	39.7
100°	49.6	50.0	50.2	50.5	50.7	51.0	51.0	51.0	51.0	51.0	51.0
102.5°	61.4	61.9	62.1	62.5	62.8	63.1	63.2	63.2	63.3	63.3	63.3
105°	80.4	80.6	80.8	81.0	81.1	81.3	81.4	81.6	81.8	81.9	82.0
107.5°	101.1	101.3	101.3	101.3	101.3	101.3	101.3	101.4	101.5	101.6	101.4
110°	114.6	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	128.8	129.1	129.0	128.9	128.8	128.7	128.6	128.4	128.2	128.0	127.8
115°	149.7	149.9	149.7	149.5	149.4	149.2	149.1	149.0	149.0	148.9	148.7
117.5°	171.2	171.3	170.9	170.4	169.9	169.5	169.3	169.1	168.8	168.7	168.4
120°	185.1	185.1	184.4	183.8	183.1	182.5	182.5	182.5	182.5	182.5	182.4
122.5°	198.4	198.5	198.0	197.5	197.1	196.7	196.5	196.2	196.1	195.8	195.7
125°	217.9	218.2	217.9	217.7	217.4	217.2	217.0	216.7	216.5	216.2	216.1
127.5°	238.0	238.3	238.1	237.7	237.4	237.2	236.8	236.5	236.3	235.9	235.7
130°	250.6	251.1	250.9	250.8	250.6	250.5	250.3	250.1	250.0	249.8	249.6
132.5°	263.4	263.9	263.9	264.0	264.0	264.0	263.7	263.3	262.9	262.6	262.3
135°	281.8	282.3	282.4	282.6	282.7	282.9	282.8	282.7	282.7	282.6	282.4
137.5°	300.2	300.7	300.9	301.2	301.3	301.6	301.5	301.4	301.3	301.3	301.1
140°	311.8	312.3	312.7	313.2	313.6	314.0	314.0	314.0	314.0	314.0	313.8
142.5°	323.6	324.1	324.3	324.7	324.9	325.2	325.3	325.3	325.4	325.5	325.3
145°	339.9	340.5	341.0	341.4	341.9	342.4	342.5	342.6	342.7	342.8	342.6
147.5°	355.6	356.0	356.4	356.7	357.0	357.3	357.5	357.7	357.9	358.1	358.0
150°	365.1	365.5	365.8	366.2	366.5	366.8	367.0	367.3	367.5	367.8	367.8
152.5°	374.2	374.7	375.0	375.4	375.9	376.3	376.6	376.8	377.2	377.5	377.5
155°	387.0	387.3	387.5	387.8	388.0	388.2	388.7	389.1	389.5	389.9	390.0
157.5°	398.4	398.5	398.7	398.8	399.0	399.2	399.7	400.2	400.8	401.4	401.5
160°	405.5	405.6	405.7	405.8	405.9	405.9	406.4	406.9	407.4	407.9	408.0
162.5°	411.5	411.6	411.6	411.7	411.8	411.9	412.4	412.9	413.5	414.1	414.2
165°	419.6	419.6	419.6	419.6	419.6	419.6	420.2	420.8	421.3	421.9	422.0
167.5°	426.2	426.1	426.1	426.1	426.1	426.1	426.6	427.2	427.8	428.4	428.4
170°	430.1	429.9	429.8	429.7	429.7	429.6	430.2	430.7	431.3	431.9	431.9
172.5°	432.8	432.6	432.5	432.4	432.4	432.3	432.8	433.4	434.0	434.6	434.6
175°	436.0	435.8	435.6	435.5	435.3	435.1	435.7	436.3	436.8	437.4	437.5
177.5°	437.5	437.3	437.2	437.1	436.9	436.8	437.2	437.7	438.0	438.4	438.4
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	6.8	6.4	6.8	6.5	6.8	6.4	6.8	6.8	7.1	7.2	7.2
90°	12.3	12.4	12.5	12.6	12.5	12.4	12.3	12.2	12.3	12.5	12.6
92.5°	11.9	11.9	12.0	12.0	12.0	11.9	11.9	11.9	11.9	11.8	11.8
95°	23.4	23.2	23.1	22.9	23.1	23.2	23.4	23.6	23.6	23.6	23.6
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	50.9	50.8	50.7	50.6	50.7	50.8	50.9	51.0	51.0	51.0	51.0
102.5°	63.3	63.2	63.1	63.0	63.1	63.2	63.3	63.3	63.3	63.3	63.2
105°	82.0	82.0	82.0	82.0	82.0	82.0	82.0	82.0	81.9	81.8	81.6
107.5°	101.0	100.6	100.3	99.9	100.3	100.6	101.0	101.4	101.6	101.5	101.4
110°	114.5	114.2	114.0	113.7	114.0	114.2	114.5	114.7	114.9	114.9	114.9



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	127.6	127.4	127.3	127.1	127.3	127.4	127.6	127.8	128.0	128.2	128.4
115°	148.5	148.2	148.0	147.7	148.0	148.2	148.5	148.7	148.9	149.0	149.0
117.5°	168.2	168.0	167.7	167.5	167.7	168.0	168.2	168.4	168.7	168.8	169.1
120°	182.1	181.9	181.6	181.4	181.6	181.9	182.1	182.4	182.5	182.5	182.5
122.5°	195.5	195.3	195.1	194.9	195.1	195.3	195.5	195.7	195.8	196.1	196.2
125°	216.0	215.9	215.8	215.7	215.8	215.9	216.0	216.1	216.2	216.5	216.7
127.5°	235.4	235.1	234.9	234.6	234.9	235.1	235.4	235.7	235.9	236.3	236.5
130°	249.2	248.9	248.6	248.3	248.6	248.9	249.2	249.6	249.8	250.0	250.1
132.5°	262.0	261.7	261.5	261.2	261.5	261.7	262.0	262.3	262.6	262.9	263.3
135°	282.2	281.9	281.7	281.4	281.7	281.9	282.2	282.4	282.6	282.7	282.7
137.5°	300.8	300.4	300.1	299.8	300.1	300.4	300.8	301.1	301.3	301.3	301.4
140°	313.5	313.2	312.8	312.5	312.8	313.2	313.5	313.8	314.0	314.0	314.0
142.5°	325.0	324.7	324.3	324.0	324.3	324.7	325.0	325.3	325.5	325.4	325.3
145°	342.3	341.9	341.6	341.3	341.6	341.9	342.3	342.6	342.8	342.7	342.6
147.5°	357.7	357.3	357.0	356.8	357.0	357.3	357.7	358.0	358.1	357.9	357.7
150°	367.5	367.3	367.0	366.8	367.0	367.3	367.5	367.8	367.8	367.5	367.3
152.5°	377.2	376.8	376.6	376.3	376.6	376.8	377.2	377.5	377.5	377.2	376.8
155°	389.7	389.5	389.2	389.0	389.2	389.5	389.7	390.0	389.9	389.5	389.1
157.5°	401.0	400.6	400.3	399.9	400.3	400.6	401.0	401.5	401.4	400.8	400.2
160°	407.6	407.3	407.0	406.7	407.0	407.3	407.6	408.0	407.9	407.4	406.9
162.5°	413.8	413.4	412.9	412.6	412.9	413.4	413.8	414.2	414.1	413.5	412.9
165°	421.6	421.2	420.8	420.4	420.8	421.2	421.6	422.0	421.9	421.3	420.8
167.5°	428.0	427.5	427.1	426.7	427.1	427.5	428.0	428.4	428.4	427.8	427.2
170°	431.5	431.0	430.5	430.0	430.5	431.0	431.5	431.9	431.9	431.3	430.7
172.5°	434.1	433.6	433.1	432.6	433.1	433.6	434.1	434.6	434.6	434.0	433.4
175°	437.0	436.5	436.0	435.5	436.0	436.5	437.0	437.5	437.4	436.8	436.3
177.5°	438.0	437.7	437.2	436.8	437.2	437.7	438.0	438.4	438.4	438.0	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	7.6	7.6	7.6	7.2	6.8	7.1	7.2	7.3	7.8	8.6	9.7
90°	12.8	13.0	11.1	9.3	7.5	5.7	4.3	3.3	2.4	1.4	0.4
92.5°	11.7	11.7	11.3	10.9	10.4	10.0	9.5	8.7	8.0	7.3	6.6
95°	23.6	23.6	23.5	23.3	23.2	23.0	22.5	21.7	20.9	20.1	19.2
97.5°	39.7	39.7	39.5	39.1	38.8	38.5	38.0	37.3	36.5	35.8	35.1
100°	51.0	51.0	50.7	50.5	50.2	50.0	49.6	48.9	48.2	47.5	46.9
102.5°	63.2	63.1	62.8	62.5	62.1	61.9	61.4	60.9	60.3	59.8	59.4
105°	81.4	81.3	81.1	81.0	80.8	80.6	80.4	80.1	79.9	79.7	79.4
107.5°	101.3	101.3	101.3	101.3	101.3	101.3	101.1	100.8	100.4	100.0	99.6
110°	114.9	114.9	114.9	114.9	114.9	114.9	114.6	114.1	113.7	113.2	112.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	128.6	128.7	128.8	128.9	129.0	129.1	128.8	128.3	127.8	127.3	126.9
115°	149.1	149.2	149.4	149.5	149.7	149.9	149.7	149.2	148.7	148.2	147.7
117.5°	169.3	169.5	169.9	170.4	170.9	171.3	171.2	170.6	169.9	169.3	168.6
120°	182.5	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5
122.5°	196.5	196.7	197.1	197.5	198.0	198.5	198.4	197.5	196.7	196.0	195.2
125°	217.0	217.2	217.4	217.7	217.9	218.2	217.9	217.2	216.5	215.7	215.0
127.5°	236.8	237.2	237.4	237.7	238.1	238.3	238.0	237.1	236.1	235.2	234.2
130°	250.3	250.5	250.6	250.8	250.9	251.1	250.6	249.6	248.5	247.4	246.4
132.5°	263.7	264.0	264.0	264.0	263.9	263.9	263.4	262.6	261.7	260.8	260.0
135°	282.8	282.9	282.7	282.6	282.4	282.3	281.8	280.9	280.0	279.1	278.2
137.5°	301.5	301.6	301.3	301.2	300.9	300.7	300.2	299.5	298.7	298.0	297.3
140°	314.0	314.0	313.6	313.2	312.7	312.3	311.8	311.0	310.3	309.6	308.8
142.5°	325.3	325.2	324.9	324.7	324.3	324.1	323.6	322.9	322.1	321.4	320.7
145°	342.5	342.4	341.9	341.4	341.0	340.5	339.9	339.3	338.8	338.2	337.6
147.5°	357.5	357.3	357.0	356.7	356.4	356.0	355.6	354.8	354.2	353.4	352.8
150°	367.0	366.8	366.5	366.2	365.8	365.5	365.1	364.6	364.1	363.6	363.1
152.5°	376.6	376.3	375.9	375.4	375.0	374.7	374.2	373.7	373.2	372.8	372.3
155°	388.7	388.2	388.0	387.8	387.5	387.3	387.0	386.8	386.5	386.2	386.0
157.5°	399.7	399.2	399.0	398.8	398.7	398.5	398.4	398.3	398.1	397.9	397.8
160°	406.4	405.9	405.9	405.8	405.7	405.6	405.5	405.4	405.2	405.0	404.9
162.5°	412.4	411.9	411.8	411.7	411.6	411.6	411.5	411.4	411.4	411.4	411.3
165°	420.2	419.6	419.6	419.6	419.6	419.6	419.6	419.7	419.8	419.9	420.0
167.5°	426.6	426.1	426.1	426.1	426.1	426.1	426.2	426.5	426.7	427.0	427.2
170°	430.2	429.6	429.7	429.7	429.8	429.9	430.1	430.3	430.6	430.8	431.0
172.5°	432.8	432.3	432.4	432.4	432.5	432.6	432.8	433.0	433.3	433.5	433.7
175°	435.7	435.1	435.3	435.5	435.6	435.8	436.0	436.3	436.5	436.8	437.0
177.5°	437.2	436.8	436.9	437.1	437.2	437.3	437.5	437.7	437.9	438.1	438.3
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.2	6.8	6.7	6.5	7.1	7.5	7.5	7.9	8.6	8.2	8.5
90°	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8	12.6
92.5°	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7	11.8
95°	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6	23.6
97.5°	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7	39.7
100°	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0	51.0
102.5°	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2	63.2
105°	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4	81.6
107.5°	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3	101.4
110°	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6	128.4
115°	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1	149.0
117.5°	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3	169.1
120°	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5	182.5
122.5°	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5	196.2
125°	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0	216.7
127.5°	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8	236.5
130°	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3	250.1
132.5°	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7	263.3
135°	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8	282.7
137.5°	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5	301.4
140°	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0	314.0
142.5°	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3	325.3
145°	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5	342.6
147.5°	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5	357.7
150°	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0	367.3
152.5°	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6	376.8
155°	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7	389.1
157.5°	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7	400.2
160°	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4	406.9
162.5°	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4	412.9
165°	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2	420.8
167.5°	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6	427.2
170°	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2	430.7
172.5°	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8	433.4
175°	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7	436.3
177.5°	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	8.2	8.2	8.1	8.2	8.2	8.2	7.8
90°	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331806-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)