

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331808-930

Luminaire Tested: **S122RDIW-S675D435U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331808-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3117.2 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	93	89	94	91	87	84	79	77	75	69	67	65	59	58	57	57	57	57	52	
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	49	45	
3	85	75	68	62	79	71	64	59	62	57	53	55	51	48	47	45	42	42	42	42	39	
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	37	37	37	34	
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	33	33	33	30	
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29	29	29	29	26	
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26	26	26	26	24	
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23	23	23	23	21	
9	53	41	34	29	50	39	32	28	35	29	26	31	27	23	28	24	21	21	21	21	19	
10	50	38	31	26	47	36	29	25	32	27	23	29	25	21	26	22	20	20	20	20	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	2.8
10°-20°	236.4	7.6
20°-30°	331.9	10.6
30°-40°	361.9	11.6
40°-50°	332.8	10.7
50°-60°	261.4	8.4
60°-70°	170.4	5.5
70°-80°	87.9	2.8
80°-90°	24.5	0.8
90°-100°	27.7	0.9
100°-110°	86.1	2.8
110°-120°	147.2	4.7
120°-130°	193.6	6.2
130°-140°	217.3	7.0
140°-150°	213.1	6.8
150°-160°	178.7	5.7
160°-170°	118.6	3.8
170°-180°	41.4	1.3
0°-30°	654.4	21.0
0°-40°	1016.3	32.6
0°-60°	1610.5	51.7
0°-90°	1893.3	60.7
90°-120°	261.1	8.4
90°-150°	885.2	28.4
90°-180°	1224.0	39.3
0°-180°	3117.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	0	5	13	12	13	2
95°	19	23	24	24	23	22
105°	79	80	81	82	82	84
115°	148	150	149	149	148	146
125°	215	218	217	216	216	192
135°	278	282	283	282	281	215
145°	338	340	342	343	341	211
155°	386	387	388	390	389	178
165°	420	420	420	422	420	118
175°	437	436	435	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.7	8.7	7.7	6.8	6.4	6.8	7.2	7.6	7.9	7.7
90°	0.4	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8
92.5°	6.6	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7
95°	19.2	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6
97.5°	35.1	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7
100°	46.9	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0
102.5°	59.4	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2
105°	79.4	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4
107.5°	99.6	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3
110°	112.7	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6
115°	147.7	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1
117.5°	168.6	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3
120°	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5
122.5°	195.2	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5
125°	215.0	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0
127.5°	234.2	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8
130°	246.4	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3
132.5°	260.0	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7
135°	278.2	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8
137.5°	297.3	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5
140°	308.8	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0
142.5°	320.7	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3
145°	337.6	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5
147.5°	352.8	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5
150°	363.1	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0
152.5°	372.3	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6
155°	386.0	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7
157.5°	397.8	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7
160°	404.9	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4
162.5°	411.3	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4
165°	420.0	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2
167.5°	427.2	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6
170°	431.0	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2
172.5°	433.7	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8
175°	437.0	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7
177.5°	438.3	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	7.6	7.3	7.2	7.1	7.1	7.2	7.2	7.2
90°	12.6	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.2	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.6	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.4	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331808-930

CATALOG NUMBER: S122RDIW-S675D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	128.4	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	169.1	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.2	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.7	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.5	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.1	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	263.3	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.4	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.3	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.6	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.7	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.1	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.2	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	406.9	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	412.9	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	420.8	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.2	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	430.7	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	433.4	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.3	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)