

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331815-930

Luminaire Tested: **S122RDIW-S675D970U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331815-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5049.3 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38					38			
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38					32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33					28				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28					24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25					21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22					18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19					16				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17					15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16					13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14					12				
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13					11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	1.7
10°-20°	236.4	4.7
20°-30°	331.9	6.6
30°-40°	361.9	7.2
40°-50°	332.8	6.6
50°-60°	261.4	5.2
60°-70°	170.4	3.4
70°-80°	87.9	1.7
80°-90°	25.4	0.5
90°-100°	35.9	0.7
100°-110°	131.7	2.6
110°-120°	352.0	7.0
120°-130°	581.1	11.5
130°-140°	618.0	12.2
140°-150°	574.4	11.4
150°-160°	461.8	9.1
160°-170°	297.6	5.9
170°-180°	102.4	2.0
0°-30°	654.4	13.0
0°-40°	1016.3	20.1
0°-60°	1610.5	31.9
0°-90°	1894.2	37.5
90°-120°	519.7	10.3
90°-150°	2293.2	45.4
90°-180°	3155.0	62.5
0°-180°	5049.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	9	16	19	21	4
95°	51	27	30	34	34	62
105°	237	247	48	56	59	253
115°	448	462	481	137	64	441
125°	633	644	658	664	666	565
135°	784	796	803	810	809	605
145°	909	909	922	927	923	568
155°	1001	995	1003	1007	1002	461
165°	1055	1051	1052	1057	1052	298
175°	1079	1074	1075	1080	1073	103
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	10.0	9.2	8.4	7.6	7.3	7.6	7.9	8.2	8.5	8.5
90°	0.8	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5
92.5°	15.7	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5
95°	50.6	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2
97.5°	100.5	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3
100°	137.9	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8
102.5°	179.0	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5
105°	236.8	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4
107.5°	302.7	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6
110°	345.1	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	385.0	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7
115°	447.9	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5
117.5°	504.2	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0
120°	545.4	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2
122.5°	580.2	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0
125°	633.3	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5
127.5°	681.5	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6
130°	712.1	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0
132.5°	743.2	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0
135°	783.7	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9
137.5°	824.7	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1
140°	851.5	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9
142.5°	873.9	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8
145°	909.1	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8
147.5°	939.9	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9
150°	959.8	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8
152.5°	976.6	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4
155°	1001.1	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4
157.5°	1020.3	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1
160°	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5
162.5°	1041.5	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0
165°	1054.8	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7
167.5°	1064.8	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5
170°	1070.4	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5
172.5°	1074.2	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3
175°	1079.0	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3
177.5°	1079.8	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	8.5	8.5	8.6	8.6	8.6	8.7	8.8	8.9
90°	17.3	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.0	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	32.1	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.1	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	47.2	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	49.2	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	51.4	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	62.6	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	101.7	84.4	67.1	58.8	59.4	60.2	60.8	61.6



TEST NUMBER: P331815-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	217.5	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	320.3	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	493.6	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	575.2	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	610.3	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	660.7	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	707.4	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	736.9	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	765.6	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	806.7	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	844.7	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	869.4	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	892.2	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	924.1	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	951.8	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	968.9	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	984.5	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1005.5	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1023.2	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1033.6	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1043.2	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1064.7	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1069.8	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1073.4	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1077.5	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.0	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)