

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331834-935

Luminaire Tested: **S122RDIW-S865D970U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331834-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D970U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5735.1 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331834-935
CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	50	49	49	43
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	45	44	42	38
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33	29
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	61	49	41	36	56	46	39	34	40	34	30	34	30	27	29	26	23	21
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19
9	53	41	34	29	49	38	32	28	34	28	25	29	25	22	25	22	20	17
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26547	26547	26547	26547
5°	29648	26712	23686	26712
10°	32893	26525	20530	26525
15°	34511	26136	16177	26136
20°	29919	25560	13998	25560
25°	19621	24772	12497	24772
30°	13207	23815	11311	23815
35°	10697	22610	10200	22610
40°	9512	21300	9440	21300
45°	8608	19763	8426	19763
50°	7834	18239	7804	18239
55°	7367	16549	7268	16549
60°	6161	14996	6090	14996
65°	5196	13620	5891	13620
70°	4801	12161	5556	12161
75°	4492	10586	5128	10586
80°	4147	8712	4575	8712
85°	3816	6873	4020	6873



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	2.7
10°-20°	434.3	7.6
20°-30°	559.6	9.8
30°-40°	531.8	9.3
40°-50°	455.6	7.9
50°-60°	346.9	6.0
60°-70°	219.3	3.8
70°-80°	109.5	1.9
80°-90°	32.6	0.6
90°-100°	65.5	1.1
100°-110°	203.4	3.5
110°-120°	347.6	6.1
120°-130°	457.2	8.0
130°-140°	513.1	8.9
140°-150°	503.1	8.8
150°-160°	422.0	7.4
160°-170°	279.9	4.9
170°-180°	97.8	1.7
0°-30°	1149.8	20.0
0°-40°	1681.6	29.3
0°-60°	2484.1	43.3
0°-90°	2845.6	49.6
90°-120°	616.5	10.7
90°-150°	2089.9	36.4
90°-180°	2890.0	50.4
0°-180°	5735.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1829	1648	1461	1648	1829	181
15°	2065	1564	968	1564	2065	557
25°	1101	1390	702	1390	1101	523
35°	543	1147	518	1147	543	347
45°	377	866	369	866	377	292
55°	262	588	258	588	262	230
65°	136	356	154	356	136	138
75°	72	170	82	170	72	76
85°	21	37	22	37	21	23
90°	30	1	30	1	30	14
95°	54	45	54	45	54	60
105°	194	188	194	188	194	204
115°	349	349	349	349	349	344
125°	509	508	509	508	509	454
135°	664	657	664	657	664	511
145°	806	797	806	797	806	503
155°	918	911	918	911	918	423
165°	992	992	992	992	992	280
175°	1028	1032	1028	1032	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1710.9	1712.3	1713.6	1710.4	1710.4	1707.7	1701.8	1697.2	1684.4	1682.6	1682.6
5°	1829.3	1828.1	1830.4	1823.0	1812.7	1810.4	1799.6	1785.3	1770.4	1753.9	1750.4
7.5°	1946.9	1945.2	1940.6	1939.4	1931.5	1914.3	1896.8	1878.2	1853.5	1829.4	1817.2
10°	2006.3	2025.2	2013.8	1993.7	1997.8	1970.9	1956.6	1932.1	1911.5	1875.5	1867.5
12.5°	2064.9	2072.3	2068.6	2057.3	2052.2	2033.5	2014.2	1992.9	1954.9	1922.6	1894.5
15°	2064.6	2075.4	2078.3	2074.9	2077.8	2076.6	2066.3	2048.6	2015.5	1980.0	1949.2
17.5°	1912.2	1919.8	1938.5	1951.1	1967.1	2001.0	2017.7	2024.1	2019.2	1999.0	1977.3
20°	1741.3	1728.7	1781.2	1808.1	1830.9	1888.1	1937.2	1956.1	1986.3	1985.8	1980.0
22.5°	1499.0	1502.0	1551.9	1583.7	1650.5	1707.5	1763.6	1834.5	1893.1	1931.8	1954.5
25°	1101.4	1123.2	1172.9	1216.2	1290.6	1396.8	1493.3	1605.3	1711.0	1794.4	1873.8
27.5°	827.2	828.8	868.2	908.4	952.4	1039.5	1161.1	1294.8	1445.4	1569.8	1712.8
30°	708.4	705.0	721.5	746.1	783.8	851.2	942.6	1074.0	1224.3	1411.6	1578.5
32.5°	624.3	624.5	637.0	655.1	686.5	731.9	794.5	901.3	1043.3	1227.4	1423.1
35°	542.7	542.2	551.3	564.4	577.6	606.7	649.5	705.5	803.2	975.2	1175.1
37.5°	484.2	486.7	491.2	499.4	513.9	530.1	555.9	593.5	663.1	764.7	932.8
40°	451.3	452.5	458.7	465.6	474.2	486.7	507.9	538.1	589.0	670.1	792.9
42.5°	421.1	422.3	426.7	433.2	439.9	452.5	469.9	496.1	537.4	600.6	702.0
45°	377.0	377.0	381.1	383.9	391.3	402.8	417.1	438.8	467.3	514.2	581.6
47.5°	335.7	335.8	338.5	343.4	348.0	357.0	371.0	388.7	409.5	445.7	503.3
50°	311.9	312.5	314.2	318.2	321.1	329.1	339.9	355.3	377.0	405.0	453.1
52.5°	292.7	292.4	294.5	296.3	298.3	303.9	312.0	325.6	345.1	369.4	409.1
55°	261.7	259.3	262.8	265.6	267.3	269.7	274.2	282.8	299.4	319.9	349.7
57.5°	222.8	221.9	224.3	226.9	232.3	238.4	242.4	247.8	256.4	271.1	300.6
60°	190.8	190.8	196.0	197.7	204.0	212.0	220.0	224.5	233.1	242.8	264.5
62.5°	162.5	162.9	165.3	167.0	170.6	180.4	191.6	201.6	209.7	219.0	233.4
65°	136.0	137.1	137.1	138.3	140.5	142.8	147.4	155.4	169.7	182.8	193.6
67.5°	115.4	115.7	116.1	117.3	117.8	120.3	122.2	125.7	129.0	141.5	154.9
70°	101.7	103.4	102.8	104.0	104.5	105.6	108.0	109.7	114.9	117.7	125.7
72.5°	88.9	90.1	90.1	90.7	92.2	92.5	94.3	96.0	99.3	101.7	106.0
75°	72.0	71.4	72.0	73.1	73.7	74.3	74.3	76.5	78.3	80.6	83.4
77.5°	55.5	56.1	56.0	56.1	56.2	57.3	57.2	58.1	59.8	61.0	62.4
80°	44.6	45.1	44.6	45.1	45.7	46.2	45.7	46.2	48.0	49.2	49.2
82.5°	34.5	34.6	35.0	35.0	35.2	35.3	36.1	36.2	37.5	37.3	37.7
85°	20.6	20.0	20.0	20.0	20.6	21.1	20.6	20.6	21.1	21.1	21.1
87.5°	13.3	13.7	13.6	13.6	13.5	13.6	13.6	14.2	13.8	14.3	13.0
90°	29.6	29.4	29.3	29.1	28.8	28.9	29.4	29.7	30.1	30.5	26.3
92.5°	28.2	28.2	28.2	28.2	28.1	28.1	28.0	27.9	27.8	27.7	26.7
95°	54.1	54.4	54.8	55.2	55.6	55.8	55.8	55.8	55.8	55.8	55.4
97.5°	93.7	93.7	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.1
100°	119.5	119.7	119.9	120.0	120.3	120.4	120.4	120.4	120.4	120.4	119.8
102.5°	148.8	149.0	149.1	149.4	149.6	149.6	149.4	149.3	149.1	149.0	148.2
105°	193.6	193.6	193.6	193.6	193.6	193.4	193.0	192.6	192.3	191.8	191.5
107.5°	235.8	236.7	237.5	238.5	239.4	239.7	239.6	239.4	239.3	239.1	239.1
110°	268.6	269.1	269.8	270.4	271.0	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.0	300.4	300.8	301.3	301.7	302.1	302.6	303.1	303.5	304.0	304.2
115°	348.8	349.4	350.0	350.6	351.1	351.5	351.7	351.9	352.1	352.3	352.7
117.5°	395.4	396.0	396.6	397.2	397.7	398.2	398.7	399.2	399.7	400.1	401.2
120°	428.2	428.8	429.4	429.9	430.5	430.8	430.8	430.8	430.8	430.8	432.4
122.5°	460.3	460.7	461.2	461.6	462.0	462.4	462.9	463.4	463.8	464.3	465.4
125°	509.3	509.5	509.7	509.9	510.1	510.5	511.0	511.6	512.2	512.8	513.3
127.5°	554.0	554.6	555.2	555.8	556.4	557.1	557.8	558.4	559.1	559.9	560.6
130°	586.0	586.8	587.5	588.3	589.1	589.7	590.1	590.5	590.9	591.2	591.7
132.5°	616.7	617.3	617.9	618.6	619.2	619.9	620.8	621.6	622.5	623.4	623.3
135°	664.5	665.1	665.6	666.2	666.8	667.2	667.4	667.6	667.8	668.0	667.6
137.5°	707.7	708.5	709.3	710.1	710.8	711.4	711.5	711.6	711.8	712.0	711.4
140°	737.8	738.6	739.3	740.1	740.9	741.2	741.2	741.2	741.2	741.2	740.3
142.5°	765.0	765.8	766.5	767.3	768.1	768.4	768.3	768.1	767.9	767.8	767.2
145°	805.8	806.6	807.4	808.1	808.9	809.2	809.0	808.8	808.6	808.4	807.3
147.5°	842.2	843.0	843.7	844.5	845.2	845.3	844.9	844.5	844.0	843.6	842.8
150°	866.0	866.5	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0	865.2
152.5°	888.3	889.0	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3	887.3
155°	918.3	918.9	919.5	920.1	920.6	920.4	919.5	918.5	917.5	916.5	915.9
157.5°	944.1	945.0	946.0	946.9	947.8	947.6	946.3	945.0	943.7	942.4	942.0
160°	960.2	961.0	961.7	962.5	963.3	963.0	961.9	960.7	959.6	958.4	958.2
162.5°	974.1	975.0	975.9	976.9	977.8	977.7	976.3	975.0	973.7	972.3	972.2
165°	992.4	993.4	994.4	995.3	996.3	996.1	994.7	993.4	992.0	990.7	990.7
167.5°	1007.5	1008.4	1009.4	1010.5	1011.4	1011.2	1010.0	1008.6	1007.2	1005.8	1005.9
170°	1015.1	1016.2	1017.4	1018.6	1019.8	1019.7	1018.3	1016.9	1015.5	1014.3	1014.4
172.5°	1021.4	1022.5	1023.7	1024.8	1026.1	1025.9	1024.6	1023.2	1021.8	1020.5	1020.7
175°	1028.2	1029.3	1030.5	1031.7	1032.9	1032.7	1031.4	1030.0	1028.6	1027.3	1027.7
177.5°	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3	1031.7
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1683.4	1679.8	1676.6	1668.4	1664.2	1655.1	1653.7	1653.3	1641.4	1630.0	1626.8
5°	1741.3	1732.2	1718.4	1702.5	1685.8	1668.7	1657.3	1648.1	1625.3	1603.6	1591.0
7.5°	1799.6	1779.9	1756.3	1726.0	1700.7	1672.4	1651.3	1632.5	1600.1	1569.0	1548.1
10°	1843.0	1810.9	1779.5	1737.8	1705.3	1673.3	1643.6	1617.9	1581.3	1540.2	1511.1
12.5°	1869.9	1834.7	1791.4	1750.7	1708.5	1667.8	1628.1	1595.0	1552.0	1509.6	1474.9
15°	1906.3	1868.6	1816.1	1757.8	1703.6	1650.5	1604.7	1563.6	1507.6	1456.7	1414.5
17.5°	1936.2	1884.3	1827.9	1760.5	1697.6	1630.1	1571.2	1518.7	1456.4	1395.1	1345.2
20°	1945.8	1894.4	1829.3	1761.9	1687.6	1608.2	1544.7	1487.6	1420.7	1353.9	1296.8
22.5°	1939.8	1899.9	1827.4	1746.7	1670.7	1587.6	1516.0	1449.7	1375.5	1307.3	1241.0
25°	1899.5	1885.8	1817.2	1729.2	1642.4	1545.9	1463.0	1390.5	1306.0	1232.9	1160.8
27.5°	1805.5	1835.0	1792.6	1698.8	1602.3	1498.8	1405.7	1323.1	1235.4	1153.1	1081.3
30°	1715.0	1783.0	1764.7	1677.8	1569.9	1468.2	1363.7	1277.4	1183.7	1099.2	1028.3
32.5°	1591.1	1703.4	1721.3	1648.6	1537.0	1425.2	1315.7	1229.9	1132.0	1042.9	973.9
35°	1394.0	1561.9	1639.0	1592.8	1480.7	1360.2	1247.1	1147.1	1048.9	960.9	892.3
37.5°	1158.6	1387.4	1516.0	1519.2	1416.4	1291.1	1167.9	1068.7	968.1	881.8	807.5
40°	1006.0	1254.0	1421.3	1458.4	1371.7	1236.2	1111.7	1010.6	912.3	827.8	742.7
42.5°	868.9	1115.9	1321.7	1386.3	1317.2	1182.8	1057.8	952.1	856.6	776.6	689.7
45°	702.7	918.6	1145.4	1260.8	1222.5	1098.0	966.0	865.5	775.8	706.7	623.3
47.5°	592.8	744.9	964.4	1120.5	1119.8	1006.2	876.3	780.1	696.8	632.1	564.6
50°	530.1	662.7	848.3	1025.5	1040.3	944.9	821.5	726.1	648.4	580.4	526.2
52.5°	473.9	583.2	750.1	919.9	962.2	879.5	759.8	671.8	596.3	533.8	487.3
55°	400.5	485.0	611.8	770.7	834.7	776.4	670.1	587.9	526.8	474.2	434.2
57.5°	338.8	402.2	503.9	631.8	706.4	669.7	582.0	515.2	462.9	415.3	383.7
60°	299.9	351.9	438.2	545.0	627.2	601.6	526.8	464.4	419.9	378.8	349.0
62.5°	263.4	308.1	381.9	468.6	544.1	533.5	472.3	420.1	381.1	343.5	318.4
65°	212.0	244.5	302.2	370.2	430.8	435.9	391.9	356.5	321.7	292.0	269.7
67.5°	168.8	190.0	230.7	287.9	333.3	349.5	322.6	295.6	267.9	245.0	225.7
70°	142.2	159.4	189.1	235.4	277.1	294.2	278.8	257.6	233.7	214.8	198.2
72.5°	115.3	132.0	153.9	187.9	223.6	242.1	236.8	221.5	202.1	186.5	170.8
75°	86.9	92.0	106.9	129.7	157.6	173.7	177.7	169.7	154.2	142.2	133.1
77.5°	64.2	67.3	74.4	86.4	104.7	118.9	124.8	123.8	113.2	106.2	97.7
80°	51.4	53.1	56.6	61.7	75.4	89.7	93.7	93.7	86.3	83.4	74.8
82.5°	39.1	40.3	42.4	45.2	51.7	64.1	68.5	69.5	64.7	61.0	54.2
85°	22.3	21.7	22.8	24.5	25.7	29.1	36.0	37.1	36.0	31.4	29.7
87.5°	12.1	11.8	10.9	9.8	9.8	9.8	11.6	13.4	12.1	11.2	10.7
90°	22.0	17.7	13.4	10.2	7.8	5.5	3.2	0.9	3.2	5.5	7.8
92.5°	25.7	24.7	23.7	22.4	20.7	18.9	17.2	15.5	17.2	18.9	20.7
95°	55.0	54.7	54.2	53.1	51.1	49.2	47.3	45.4	47.3	49.2	51.1
97.5°	92.4	91.6	90.9	89.6	88.0	86.3	84.6	82.8	84.6	86.3	88.0
100°	119.2	118.6	118.0	116.9	115.4	113.8	112.3	110.7	112.3	113.8	115.4
102.5°	147.5	146.7	146.0	145.0	143.8	142.5	141.3	140.1	141.3	142.5	143.8
105°	191.1	190.7	190.3	189.9	189.2	188.6	188.0	187.5	188.0	188.6	189.2
107.5°	239.1	239.1	239.1	238.7	237.8	236.9	236.2	235.3	236.2	236.9	237.8
110°	271.2	271.2	271.2	270.6	269.5	268.3	267.2	266.0	267.2	268.3	269.5



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	304.3	304.4	304.6	304.1	303.0	301.8	300.7	299.5	300.7	301.8	303.0
115°	353.1	353.4	353.9	353.4	352.3	351.1	350.0	348.8	350.0	351.1	352.3
117.5°	402.3	403.4	404.4	404.2	402.7	401.1	399.6	398.0	399.6	401.1	402.7
120°	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	432.4	433.9	435.5
122.5°	466.5	467.5	468.6	468.2	466.4	464.5	462.7	460.8	462.7	464.5	466.4
125°	513.9	514.5	515.1	514.5	512.8	511.0	509.3	507.6	509.3	511.0	512.8
127.5°	561.3	562.0	562.7	561.9	559.7	557.5	555.3	553.1	555.3	557.5	559.7
130°	592.0	592.5	592.8	591.8	589.3	586.7	584.2	581.7	584.2	586.7	589.3
132.5°	623.2	623.1	623.0	622.0	619.9	617.9	615.8	613.7	615.8	617.9	619.9
135°	667.2	666.8	666.4	665.2	663.1	660.9	658.8	656.7	658.8	660.9	663.1
137.5°	710.9	710.4	710.0	708.8	707.1	705.3	703.6	701.8	703.6	705.3	707.1
140°	739.3	738.4	737.4	736.0	734.3	732.5	730.8	729.0	730.8	732.5	734.3
142.5°	766.5	765.8	765.2	764.0	762.2	760.4	758.7	757.0	758.7	760.4	762.2
145°	806.1	804.9	803.7	802.5	801.2	799.8	798.4	797.0	798.4	799.8	801.2
147.5°	842.1	841.3	840.5	839.3	837.7	836.1	834.5	832.8	834.5	836.1	837.7
150°	864.4	863.7	862.9	861.9	860.7	859.5	858.4	857.2	858.4	859.5	860.7
152.5°	886.4	885.5	884.6	883.6	882.4	881.2	880.0	878.9	880.0	881.2	882.4
155°	915.4	914.8	914.2	913.6	913.1	912.5	911.9	911.3	911.9	912.5	913.1
157.5°	941.7	941.3	941.0	940.6	940.2	939.8	939.4	939.0	939.4	939.8	940.2
160°	958.0	957.9	957.6	957.3	956.9	956.6	956.1	955.8	956.1	956.6	956.9
162.5°	972.0	971.8	971.6	971.5	971.4	971.3	971.2	971.1	971.2	971.3	971.4
165°	990.7	990.7	990.7	990.8	990.9	991.2	991.4	991.5	991.4	991.2	990.9
167.5°	1005.9	1006.0	1006.0	1006.3	1006.9	1007.5	1008.1	1008.7	1008.1	1007.5	1006.9
170°	1014.6	1014.8	1015.0	1015.4	1016.0	1016.6	1017.1	1017.7	1017.1	1016.6	1016.0
172.5°	1020.9	1021.1	1021.2	1021.7	1022.3	1022.8	1023.4	1024.0	1023.4	1022.8	1022.3
175°	1028.0	1028.5	1028.8	1029.3	1029.9	1030.5	1031.0	1031.7	1031.0	1030.5	1029.9
177.5°	1031.9	1032.3	1032.5	1032.9	1033.4	1033.9	1034.3	1034.8	1034.3	1033.9	1033.4
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1620.8	1617.6	1611.7	1602.6	1597.1	1587.5	1581.1	1584.8	1585.6	1584.8	1583.8
5°	1577.3	1565.3	1548.8	1532.8	1517.9	1501.9	1492.7	1488.8	1480.7	1476.2	1473.9
7.5°	1524.7	1504.0	1480.5	1452.7	1429.0	1404.2	1391.5	1385.3	1368.9	1359.9	1352.2
10°	1485.3	1452.8	1429.3	1392.8	1370.5	1337.9	1315.7	1316.2	1293.9	1281.3	1272.2
12.5°	1441.9	1406.2	1367.2	1334.3	1303.3	1277.1	1250.3	1239.4	1215.8	1203.7	1179.0
15°	1369.9	1328.3	1287.1	1242.5	1211.1	1170.5	1131.7	1084.3	1046.0	1012.9	1003.8
17.5°	1291.3	1239.7	1198.4	1146.1	1092.3	1024.1	979.0	951.5	928.4	910.9	897.9
20°	1237.4	1184.8	1140.8	1062.0	989.5	943.2	910.1	888.9	865.0	846.1	835.8
22.5°	1180.7	1125.8	1065.9	977.9	921.4	884.2	854.7	830.4	814.2	799.4	790.1
25°	1100.3	1040.3	941.5	880.9	835.2	796.3	775.8	761.0	743.8	723.8	714.6
27.5°	1015.3	919.9	848.9	803.9	760.3	735.0	716.5	694.3	679.0	670.0	660.5
30°	951.7	856.4	800.9	751.8	720.9	692.9	671.2	658.7	643.9	628.4	622.2
32.5°	880.9	804.7	751.6	710.7	679.3	655.5	638.3	618.0	607.3	597.8	584.6
35°	792.9	735.2	686.6	653.6	623.9	604.4	584.4	572.4	553.0	545.0	539.8
37.5°	718.4	668.4	632.1	597.2	573.7	552.2	539.9	520.9	512.5	501.4	490.5
40°	676.4	627.2	592.5	563.9	537.6	521.6	506.2	490.8	478.2	473.0	459.9
42.5°	633.4	593.5	558.6	527.3	509.7	492.8	473.3	461.9	448.9	440.6	432.5
45°	574.1	538.7	509.0	483.3	463.9	446.2	433.6	414.7	407.3	390.7	383.9
47.5°	522.0	489.1	460.8	436.4	417.4	405.9	387.4	372.7	360.8	350.7	341.8
50°	485.0	457.6	430.2	408.5	391.3	374.8	355.9	348.4	330.2	325.0	319.9
52.5°	451.2	425.2	400.0	378.8	361.6	345.5	328.9	319.3	306.9	301.8	298.0
55°	403.9	378.8	354.7	335.9	318.7	302.2	292.0	279.9	274.2	270.2	265.6
57.5°	356.4	333.7	315.4	296.3	279.1	265.9	254.0	246.8	240.8	235.6	230.1
60°	326.2	304.4	287.9	270.2	252.5	241.7	232.5	223.9	217.1	209.1	206.8
62.5°	294.2	275.3	260.0	242.8	227.4	217.4	208.7	200.6	192.4	180.7	177.5
65°	250.2	235.4	219.4	205.1	191.4	181.7	169.1	160.0	156.5	155.4	154.8
67.5°	210.4	196.4	182.7	168.1	155.6	146.6	140.2	138.8	136.4	135.7	134.1
70°	183.9	170.8	157.1	143.4	131.4	129.7	127.4	125.1	122.3	121.1	119.9
72.5°	160.1	146.6	132.9	121.9	116.8	114.6	112.3	110.0	108.1	106.9	106.2
75°	122.9	110.3	101.1	97.1	94.3	92.6	89.1	87.4	86.3	84.6	83.9
77.5°	88.4	81.4	77.1	74.6	71.6	69.8	67.8	66.1	64.9	64.6	63.6
80°	67.4	64.0	61.1	57.7	56.6	54.2	53.7	52.0	52.5	50.9	50.9
82.5°	52.3	48.0	45.5	44.0	42.9	41.0	40.5	39.6	39.8	38.5	38.5
85°	26.9	25.7	24.5	23.4	23.4	21.7	22.3	21.7	21.7	20.6	20.0
87.5°	10.7	10.9	10.8	11.7	12.6	13.0	12.9	12.3	12.3	12.2	11.7
90°	10.2	13.4	17.7	22.0	26.3	30.5	30.1	29.7	29.4	28.9	28.8
92.5°	22.4	23.7	24.7	25.7	26.7	27.7	27.8	27.9	28.0	28.1	28.1
95°	53.1	54.2	54.7	55.0	55.4	55.8	55.8	55.8	55.8	55.8	55.6
97.5°	89.6	90.9	91.6	92.4	93.1	93.8	93.8	93.8	93.8	93.8	93.8
100°	116.9	118.0	118.6	119.2	119.8	120.4	120.4	120.4	120.4	120.4	120.3
102.5°	145.0	146.0	146.7	147.5	148.2	149.0	149.1	149.3	149.4	149.6	149.6
105°	189.9	190.3	190.7	191.1	191.5	191.8	192.3	192.6	193.0	193.4	193.6
107.5°	238.7	239.1	239.1	239.1	239.1	239.1	239.3	239.4	239.6	239.7	239.4
110°	270.6	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.0



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	304.1	304.6	304.4	304.3	304.2	304.0	303.5	303.1	302.6	302.1	301.7
115°	353.4	353.9	353.4	353.1	352.7	352.3	352.1	351.9	351.7	351.5	351.1
117.5°	404.2	404.4	403.4	402.3	401.2	400.1	399.7	399.2	398.7	398.2	397.7
120°	437.0	437.0	435.5	433.9	432.4	430.8	430.8	430.8	430.8	430.8	430.5
122.5°	468.2	468.6	467.5	466.5	465.4	464.3	463.8	463.4	462.9	462.4	462.0
125°	514.5	515.1	514.5	513.9	513.3	512.8	512.2	511.6	511.0	510.5	510.1
127.5°	561.9	562.7	562.0	561.3	560.6	559.9	559.1	558.4	557.8	557.1	556.4
130°	591.8	592.8	592.5	592.0	591.7	591.2	590.9	590.5	590.1	589.7	589.1
132.5°	622.0	623.0	623.1	623.2	623.3	623.4	622.5	621.6	620.8	619.9	619.2
135°	665.2	666.4	666.8	667.2	667.6	668.0	667.8	667.6	667.4	667.2	666.8
137.5°	708.8	710.0	710.4	710.9	711.4	712.0	711.8	711.6	711.5	711.4	710.8
140°	736.0	737.4	738.4	739.3	740.3	741.2	741.2	741.2	741.2	741.2	740.9
142.5°	764.0	765.2	765.8	766.5	767.2	767.8	767.9	768.1	768.3	768.4	768.1
145°	802.5	803.7	804.9	806.1	807.3	808.4	808.6	808.8	809.0	809.2	808.9
147.5°	839.3	840.5	841.3	842.1	842.8	843.6	844.0	844.5	844.9	845.3	845.2
150°	861.9	862.9	863.7	864.4	865.2	866.0	866.5	867.1	867.7	868.3	868.3
152.5°	883.6	884.6	885.5	886.4	887.3	888.3	889.0	889.8	890.5	891.2	891.2
155°	913.6	914.2	914.8	915.4	915.9	916.5	917.5	918.5	919.5	920.4	920.6
157.5°	940.6	941.0	941.3	941.7	942.0	942.4	943.7	945.0	946.3	947.6	947.8
160°	957.3	957.6	957.9	958.0	958.2	958.4	959.6	960.7	961.9	963.0	963.3
162.5°	971.5	971.6	971.8	972.0	972.2	972.3	973.7	975.0	976.3	977.7	977.8
165°	990.8	990.7	990.7	990.7	990.7	990.7	992.0	993.4	994.7	996.1	996.3
167.5°	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2	1008.6	1010.0	1011.2	1011.4
170°	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5	1016.9	1018.3	1019.7	1019.8
172.5°	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8	1023.2	1024.6	1025.9	1026.1
175°	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6	1030.0	1031.4	1032.7	1032.9
177.5°	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1578.8	1579.7	1578.3	1579.2	1578.3	1579.7	1578.8	1583.8	1584.8	1585.6	1584.8
5°	1471.0	1464.2	1463.0	1461.4	1463.0	1464.2	1471.0	1473.9	1476.2	1480.7	1488.8
7.5°	1342.4	1341.4	1338.5	1334.6	1338.5	1341.4	1342.4	1352.2	1359.9	1368.9	1385.3
10°	1259.6	1256.8	1256.3	1252.2	1256.3	1256.8	1259.6	1272.2	1281.3	1293.9	1316.2
12.5°	1162.8	1144.4	1142.5	1132.5	1142.5	1144.4	1162.8	1179.0	1203.7	1215.8	1239.4
15°	990.1	986.6	975.2	967.8	975.2	986.6	990.1	1003.8	1012.9	1046.0	1084.3
17.5°	891.3	880.1	876.6	874.9	876.6	880.1	891.3	897.9	910.9	928.4	951.5
20°	827.8	817.5	815.8	814.7	815.8	817.5	827.8	835.8	846.1	865.0	888.9
22.5°	783.9	773.2	768.7	765.3	768.7	773.2	783.9	790.1	799.4	814.2	830.4
25°	708.9	705.0	702.7	701.5	702.7	705.0	708.9	714.6	723.8	743.8	761.0
27.5°	650.3	641.5	639.8	636.9	639.8	641.5	650.3	660.5	670.0	679.0	694.3
30°	617.0	614.2	610.1	606.7	610.1	614.2	617.0	622.2	628.4	643.9	658.7
32.5°	577.6	575.3	571.7	570.2	571.7	575.3	577.6	584.6	597.8	607.3	618.0
35°	534.2	526.2	522.7	517.5	522.7	526.2	534.2	539.8	545.0	553.0	572.4
37.5°	488.1	483.9	479.1	480.8	479.1	483.9	488.1	490.5	501.4	512.5	520.9
40°	452.5	449.6	448.5	447.9	448.5	449.6	452.5	459.9	473.0	478.2	490.8
42.5°	424.1	416.2	413.3	413.1	413.3	416.2	424.1	432.5	440.6	448.9	461.9
45°	381.1	373.6	368.5	369.0	368.5	373.6	381.1	383.9	390.7	407.3	414.7
47.5°	336.9	336.7	333.6	334.6	333.6	336.7	336.9	341.8	350.7	360.8	372.7
50°	315.9	312.5	310.2	310.7	310.2	312.5	315.9	319.9	325.0	330.2	348.4
52.5°	295.8	292.8	291.0	293.4	291.0	292.8	295.8	298.0	301.8	306.9	319.3
55°	262.8	259.3	258.8	258.2	258.8	259.3	262.8	265.6	270.2	274.2	279.9
57.5°	225.9	223.6	220.2	218.7	220.2	223.6	225.9	230.1	235.6	240.8	246.8
60°	199.4	194.8	189.1	188.6	189.1	194.8	199.4	206.8	209.1	217.1	223.9
62.5°	175.1	174.3	173.1	173.0	173.1	174.3	175.1	177.5	180.7	192.4	200.6
65°	153.7	153.1	153.7	154.2	153.7	153.1	153.7	154.8	155.4	156.5	160.0
67.5°	133.9	132.9	131.8	132.3	131.8	132.9	133.9	134.1	135.7	136.4	138.8
70°	118.8	118.2	117.7	117.7	117.7	118.2	118.8	119.9	121.1	122.3	125.1
72.5°	104.2	104.1	103.5	103.1	103.5	104.1	104.2	106.2	106.9	108.1	110.0
75°	83.4	82.2	82.2	82.2	82.2	82.2	83.4	83.9	84.6	86.3	87.4
77.5°	63.5	62.9	62.4	61.9	62.4	62.9	63.5	63.6	64.6	64.9	66.1
80°	50.3	49.7	49.2	49.2	49.2	49.7	50.3	50.9	50.9	52.5	52.0
82.5°	38.4	37.8	37.7	37.3	37.7	37.8	38.4	38.5	38.5	39.8	39.6
85°	20.6	21.1	20.6	21.7	20.6	21.1	20.6	20.0	20.6	21.7	21.7
87.5°	11.8	11.4	11.8	11.5	11.8	11.4	11.8	11.7	12.2	12.3	12.3
90°	29.1	29.3	29.4	29.6	29.4	29.3	29.1	28.8	28.9	29.4	29.7
92.5°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.1	28.1	28.0	27.9
95°	55.2	54.8	54.4	54.1	54.4	54.8	55.2	55.6	55.8	55.8	55.8
97.5°	93.8	93.8	93.7	93.7	93.7	93.8	93.8	93.8	93.8	93.8	93.8
100°	120.0	119.9	119.7	119.5	119.7	119.9	120.0	120.3	120.4	120.4	120.4
102.5°	149.4	149.1	149.0	148.8	149.0	149.1	149.4	149.6	149.6	149.4	149.3
105°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.4	193.0	192.6
107.5°	238.5	237.5	236.7	235.8	236.7	237.5	238.5	239.4	239.7	239.6	239.4
110°	270.4	269.8	269.1	268.6	269.1	269.8	270.4	271.0	271.2	271.2	271.2



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	301.3	300.8	300.4	300.0	300.4	300.8	301.3	301.7	302.1	302.6	303.1
115°	350.6	350.0	349.4	348.8	349.4	350.0	350.6	351.1	351.5	351.7	351.9
117.5°	397.2	396.6	396.0	395.4	396.0	396.6	397.2	397.7	398.2	398.7	399.2
120°	429.9	429.4	428.8	428.2	428.8	429.4	429.9	430.5	430.8	430.8	430.8
122.5°	461.6	461.2	460.7	460.3	460.7	461.2	461.6	462.0	462.4	462.9	463.4
125°	509.9	509.7	509.5	509.3	509.5	509.7	509.9	510.1	510.5	511.0	511.6
127.5°	555.8	555.2	554.6	554.0	554.6	555.2	555.8	556.4	557.1	557.8	558.4
130°	588.3	587.5	586.8	586.0	586.8	587.5	588.3	589.1	589.7	590.1	590.5
132.5°	618.6	617.9	617.3	616.7	617.3	617.9	618.6	619.2	619.9	620.8	621.6
135°	666.2	665.6	665.1	664.5	665.1	665.6	666.2	666.8	667.2	667.4	667.6
137.5°	710.1	709.3	708.5	707.7	708.5	709.3	710.1	710.8	711.4	711.5	711.6
140°	740.1	739.3	738.6	737.8	738.6	739.3	740.1	740.9	741.2	741.2	741.2
142.5°	767.3	766.5	765.8	765.0	765.8	766.5	767.3	768.1	768.4	768.3	768.1
145°	808.1	807.4	806.6	805.8	806.6	807.4	808.1	808.9	809.2	809.0	808.8
147.5°	844.5	843.7	843.0	842.2	843.0	843.7	844.5	845.2	845.3	844.9	844.5
150°	867.7	867.1	866.5	866.0	866.5	867.1	867.7	868.3	868.3	867.7	867.1
152.5°	890.5	889.8	889.0	888.3	889.0	889.8	890.5	891.2	891.2	890.5	889.8
155°	920.1	919.5	918.9	918.3	918.9	919.5	920.1	920.6	920.4	919.5	918.5
157.5°	946.9	946.0	945.0	944.1	945.0	946.0	946.9	947.8	947.6	946.3	945.0
160°	962.5	961.7	961.0	960.2	961.0	961.7	962.5	963.3	963.0	961.9	960.7
162.5°	976.9	975.9	975.0	974.1	975.0	975.9	976.9	977.8	977.7	976.3	975.0
165°	995.3	994.4	993.4	992.4	993.4	994.4	995.3	996.3	996.1	994.7	993.4
167.5°	1010.5	1009.4	1008.4	1007.5	1008.4	1009.4	1010.5	1011.4	1011.2	1010.0	1008.6
170°	1018.6	1017.4	1016.2	1015.1	1016.2	1017.4	1018.6	1019.8	1019.7	1018.3	1016.9
172.5°	1024.8	1023.7	1022.5	1021.4	1022.5	1023.7	1024.8	1026.1	1025.9	1024.6	1023.2
175°	1031.7	1030.5	1029.3	1028.2	1029.3	1030.5	1031.7	1032.9	1032.7	1031.4	1030.0
177.5°	1034.1	1033.2	1032.3	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1581.1	1587.5	1597.1	1602.6	1611.7	1617.6	1620.8	1626.8	1630.0	1641.4	1653.3
5°	1492.7	1501.9	1517.9	1532.8	1548.8	1565.3	1577.3	1591.0	1603.6	1625.3	1648.1
7.5°	1391.5	1404.2	1429.0	1452.7	1480.5	1504.0	1524.7	1548.1	1569.0	1600.1	1632.5
10°	1315.7	1337.9	1370.5	1392.8	1429.3	1452.8	1485.3	1511.1	1540.2	1581.3	1617.9
12.5°	1250.3	1277.1	1303.3	1334.3	1367.2	1406.2	1441.9	1474.9	1509.6	1552.0	1595.0
15°	1131.7	1170.5	1211.1	1242.5	1287.1	1328.3	1369.9	1414.5	1456.7	1507.6	1563.6
17.5°	979.0	1024.1	1092.3	1146.1	1198.4	1239.7	1291.3	1345.2	1395.1	1456.4	1518.7
20°	910.1	943.2	989.5	1062.0	1140.8	1184.8	1237.4	1296.8	1353.9	1420.7	1487.6
22.5°	854.7	884.2	921.4	977.9	1065.9	1125.8	1180.7	1241.0	1307.3	1375.5	1449.7
25°	775.8	796.3	835.2	880.9	941.5	1040.3	1100.3	1160.8	1232.9	1306.0	1390.5
27.5°	716.5	735.0	760.3	803.9	848.9	919.9	1015.3	1081.3	1153.1	1235.4	1323.1
30°	671.2	692.9	720.9	751.8	800.9	856.4	951.7	1028.3	1099.2	1183.7	1277.4
32.5°	638.3	655.5	679.3	710.7	751.6	804.7	880.9	973.9	1042.9	1132.0	1229.9
35°	584.4	604.4	623.9	653.6	686.6	735.2	792.9	892.3	960.9	1048.9	1147.1
37.5°	539.9	552.2	573.7	597.2	632.1	668.4	718.4	807.5	881.8	968.1	1068.7
40°	506.2	521.6	537.6	563.9	592.5	627.2	676.4	742.7	827.8	912.3	1010.6
42.5°	473.3	492.8	509.7	527.3	558.6	593.5	633.4	689.7	776.6	856.6	952.1
45°	433.6	446.2	463.9	483.3	509.0	538.7	574.1	623.3	706.7	775.8	865.5
47.5°	387.4	405.9	417.4	436.4	460.8	489.1	522.0	564.6	632.1	696.8	780.1
50°	355.9	374.8	391.3	408.5	430.2	457.6	485.0	526.2	580.4	648.4	726.1
52.5°	328.9	345.5	361.6	378.8	400.0	425.2	451.2	487.3	533.8	596.3	671.8
55°	292.0	302.2	318.7	335.9	354.7	378.8	403.9	434.2	474.2	526.8	587.9
57.5°	254.0	265.9	279.1	296.3	315.4	333.7	356.4	383.7	415.3	462.9	515.2
60°	232.5	241.7	252.5	270.2	287.9	304.4	326.2	349.0	378.8	419.9	464.4
62.5°	208.7	217.4	227.4	242.8	260.0	275.3	294.2	318.4	343.5	381.1	420.1
65°	169.1	181.7	191.4	205.1	219.4	235.4	250.2	269.7	292.0	321.7	356.5
67.5°	140.2	146.6	155.6	168.1	182.7	196.4	210.4	225.7	245.0	267.9	295.6
70°	127.4	129.7	131.4	143.4	157.1	170.8	183.9	198.2	214.8	233.7	257.6
72.5°	112.3	114.6	116.8	121.9	132.9	146.6	160.1	170.8	186.5	202.1	221.5
75°	89.1	92.6	94.3	97.1	101.1	110.3	122.9	133.1	142.2	154.2	169.7
77.5°	67.8	69.8	71.6	74.6	77.1	81.4	88.4	97.7	106.2	113.2	123.8
80°	53.7	54.2	56.6	57.7	61.1	64.0	67.4	74.8	83.4	86.3	93.7
82.5°	40.5	41.0	42.9	44.0	45.5	48.0	52.3	54.2	61.0	64.7	69.5
85°	22.3	21.7	23.4	23.4	24.5	25.7	26.9	29.7	31.4	36.0	37.1
87.5°	12.9	13.0	12.6	11.7	10.8	10.9	10.7	10.7	11.2	12.1	13.4
90°	30.1	30.5	26.3	22.0	17.7	13.4	10.2	7.8	5.5	3.2	0.9
92.5°	27.8	27.7	26.7	25.7	24.7	23.7	22.4	20.7	18.9	17.2	15.5
95°	55.8	55.8	55.4	55.0	54.7	54.2	53.1	51.1	49.2	47.3	45.4
97.5°	93.8	93.8	93.1	92.4	91.6	90.9	89.6	88.0	86.3	84.6	82.8
100°	120.4	120.4	119.8	119.2	118.6	118.0	116.9	115.4	113.8	112.3	110.7
102.5°	149.1	149.0	148.2	147.5	146.7	146.0	145.0	143.8	142.5	141.3	140.1
105°	192.3	191.8	191.5	191.1	190.7	190.3	189.9	189.2	188.6	188.0	187.5
107.5°	239.3	239.1	239.1	239.1	239.1	239.1	238.7	237.8	236.9	236.2	235.3
110°	271.2	271.2	271.2	271.2	271.2	271.2	270.6	269.5	268.3	267.2	266.0



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.5	304.0	304.2	304.3	304.4	304.6	304.1	303.0	301.8	300.7	299.5
115°	352.1	352.3	352.7	353.1	353.4	353.9	353.4	352.3	351.1	350.0	348.8
117.5°	399.7	400.1	401.2	402.3	403.4	404.4	404.2	402.7	401.1	399.6	398.0
120°	430.8	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8
122.5°	463.8	464.3	465.4	466.5	467.5	468.6	468.2	466.4	464.5	462.7	460.8
125°	512.2	512.8	513.3	513.9	514.5	515.1	514.5	512.8	511.0	509.3	507.6
127.5°	559.1	559.9	560.6	561.3	562.0	562.7	561.9	559.7	557.5	555.3	553.1
130°	590.9	591.2	591.7	592.0	592.5	592.8	591.8	589.3	586.7	584.2	581.7
132.5°	622.5	623.4	623.3	623.2	623.1	623.0	622.0	619.9	617.9	615.8	613.7
135°	667.8	668.0	667.6	667.2	666.8	666.4	665.2	663.1	660.9	658.8	656.7
137.5°	711.8	712.0	711.4	710.9	710.4	710.0	708.8	707.1	705.3	703.6	701.8
140°	741.2	741.2	740.3	739.3	738.4	737.4	736.0	734.3	732.5	730.8	729.0
142.5°	767.9	767.8	767.2	766.5	765.8	765.2	764.0	762.2	760.4	758.7	757.0
145°	808.6	808.4	807.3	806.1	804.9	803.7	802.5	801.2	799.8	798.4	797.0
147.5°	844.0	843.6	842.8	842.1	841.3	840.5	839.3	837.7	836.1	834.5	832.8
150°	866.5	866.0	865.2	864.4	863.7	862.9	861.9	860.7	859.5	858.4	857.2
152.5°	889.0	888.3	887.3	886.4	885.5	884.6	883.6	882.4	881.2	880.0	878.9
155°	917.5	916.5	915.9	915.4	914.8	914.2	913.6	913.1	912.5	911.9	911.3
157.5°	943.7	942.4	942.0	941.7	941.3	941.0	940.6	940.2	939.8	939.4	939.0
160°	959.6	958.4	958.2	958.0	957.9	957.6	957.3	956.9	956.6	956.1	955.8
162.5°	973.7	972.3	972.2	972.0	971.8	971.6	971.5	971.4	971.3	971.2	971.1
165°	992.0	990.7	990.7	990.7	990.7	990.7	990.8	990.9	991.2	991.4	991.5
167.5°	1007.2	1005.8	1005.9	1005.9	1006.0	1006.0	1006.3	1006.9	1007.5	1008.1	1008.7
170°	1015.5	1014.3	1014.4	1014.6	1014.8	1015.0	1015.4	1016.0	1016.6	1017.1	1017.7
172.5°	1021.8	1020.5	1020.7	1020.9	1021.1	1021.2	1021.7	1022.3	1022.8	1023.4	1024.0
175°	1028.6	1027.3	1027.7	1028.0	1028.5	1028.8	1029.3	1029.9	1030.5	1031.0	1031.7
177.5°	1032.3	1031.3	1031.7	1031.9	1032.3	1032.5	1032.9	1033.4	1033.9	1034.3	1034.8
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935
 CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1653.7	1655.1	1664.2	1668.4	1676.6	1679.8	1683.4	1682.6	1682.6	1684.4	1697.2
5°	1657.3	1668.7	1685.8	1702.5	1718.4	1732.2	1741.3	1750.4	1753.9	1770.4	1785.3
7.5°	1651.3	1672.4	1700.7	1726.0	1756.3	1779.9	1799.6	1817.2	1829.4	1853.5	1878.2
10°	1643.6	1673.3	1705.3	1737.8	1779.5	1810.9	1843.0	1867.5	1875.5	1911.5	1932.1
12.5°	1628.1	1667.8	1708.5	1750.7	1791.4	1834.7	1869.9	1894.5	1922.6	1954.9	1992.9
15°	1604.7	1650.5	1703.6	1757.8	1816.1	1868.6	1906.3	1949.2	1980.0	2015.5	2048.6
17.5°	1571.2	1630.1	1697.6	1760.5	1827.9	1884.3	1936.2	1977.3	1999.0	2019.2	2024.1
20°	1544.7	1608.2	1687.6	1761.9	1829.3	1894.4	1945.8	1980.0	1985.8	1986.3	1956.1
22.5°	1516.0	1587.6	1670.7	1746.7	1827.4	1899.9	1939.8	1954.5	1931.8	1893.1	1834.5
25°	1463.0	1545.9	1642.4	1729.2	1817.2	1885.8	1899.5	1873.8	1794.4	1711.0	1605.3
27.5°	1405.7	1498.8	1602.3	1698.8	1792.6	1835.0	1805.5	1712.8	1569.8	1445.4	1294.8
30°	1363.7	1468.2	1569.9	1677.8	1764.7	1783.0	1715.0	1578.5	1411.6	1224.3	1074.0
32.5°	1315.7	1425.2	1537.0	1648.6	1721.3	1703.4	1591.1	1423.1	1227.4	1043.3	901.3
35°	1247.1	1360.2	1480.7	1592.8	1639.0	1561.9	1394.0	1175.1	975.2	803.2	705.5
37.5°	1167.9	1291.1	1416.4	1519.2	1516.0	1387.4	1158.6	932.8	764.7	663.1	593.5
40°	1111.7	1236.2	1371.7	1458.4	1421.3	1254.0	1006.0	792.9	670.1	589.0	538.1
42.5°	1057.8	1182.8	1317.2	1386.3	1321.7	1115.9	868.9	702.0	600.6	537.4	496.1
45°	966.0	1098.0	1222.5	1260.8	1145.4	918.6	702.7	581.6	514.2	467.3	438.8
47.5°	876.3	1006.2	1119.8	1120.5	964.4	744.9	592.8	503.3	445.7	409.5	388.7
50°	821.5	944.9	1040.3	1025.5	848.3	662.7	530.1	453.1	405.0	377.0	355.3
52.5°	759.8	879.5	962.2	919.9	750.1	583.2	473.9	409.1	369.4	345.1	325.6
55°	670.1	776.4	834.7	770.7	611.8	485.0	400.5	349.7	319.9	299.4	282.8
57.5°	582.0	669.7	706.4	631.8	503.9	402.2	338.8	300.6	271.1	256.4	247.8
60°	526.8	601.6	627.2	545.0	438.2	351.9	299.9	264.5	242.8	233.1	224.5
62.5°	472.3	533.5	544.1	468.6	381.9	308.1	263.4	233.4	219.0	209.7	201.6
65°	391.9	435.9	430.8	370.2	302.2	244.5	212.0	193.6	182.8	169.7	155.4
67.5°	322.6	349.5	333.3	287.9	230.7	190.0	168.8	154.9	141.5	129.0	125.7
70°	278.8	294.2	277.1	235.4	189.1	159.4	142.2	125.7	117.7	114.9	109.7
72.5°	236.8	242.1	223.6	187.9	153.9	132.0	115.3	106.0	101.7	99.3	96.0
75°	177.7	173.7	157.6	129.7	106.9	92.0	86.9	83.4	80.6	78.3	76.5
77.5°	124.8	118.9	104.7	86.4	74.4	67.3	64.2	62.4	61.0	59.8	58.1
80°	93.7	89.7	75.4	61.7	56.6	53.1	51.4	49.2	49.2	48.0	46.2
82.5°	68.5	64.1	51.7	45.2	42.4	40.3	39.1	37.7	37.3	37.5	36.2
85°	36.0	29.1	25.7	24.5	22.8	21.7	22.3	21.1	21.1	21.1	20.6
87.5°	11.6	9.8	9.8	9.8	10.9	11.8	12.1	13.0	14.3	13.8	14.2
90°	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1	29.7
92.5°	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8	27.9
95°	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8	55.8
97.5°	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8	93.8
100°	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4	120.4
102.5°	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1	149.3
105°	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3	192.6
107.5°	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3	239.4
110°	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5	303.1
115°	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1	351.9
117.5°	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7	399.2
120°	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8	430.8
122.5°	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8	463.4
125°	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2	511.6
127.5°	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1	558.4
130°	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9	590.5
132.5°	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5	621.6
135°	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8	667.6
137.5°	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8	711.6
140°	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2	741.2
142.5°	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9	768.1
145°	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6	808.8
147.5°	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0	844.5
150°	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5	867.1
152.5°	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0	889.8
155°	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5	918.5
157.5°	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7	945.0
160°	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6	960.7
162.5°	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7	975.0
165°	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0	993.4
167.5°	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2	1008.6
170°	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5	1016.9
172.5°	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8	1023.2
175°	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6	1030.0
177.5°	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3	1033.2
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1701.8	1707.7	1710.4	1710.4	1713.6	1712.3	1710.9
5°	1799.6	1810.4	1812.7	1823.0	1830.4	1828.1	1829.3
7.5°	1896.8	1914.3	1931.5	1939.4	1940.6	1945.2	1946.9
10°	1956.6	1970.9	1997.8	1993.7	2013.8	2025.2	2006.3
12.5°	2014.2	2033.5	2052.2	2057.3	2068.6	2072.3	2064.9
15°	2066.3	2076.6	2077.8	2074.9	2078.3	2075.4	2064.6
17.5°	2017.7	2001.0	1967.1	1951.1	1938.5	1919.8	1912.2
20°	1937.2	1888.1	1830.9	1808.1	1781.2	1728.7	1741.3
22.5°	1763.6	1707.5	1650.5	1583.7	1551.9	1502.0	1499.0
25°	1493.3	1396.8	1290.6	1216.2	1172.9	1123.2	1101.4
27.5°	1161.1	1039.5	952.4	908.4	868.2	828.8	827.2
30°	942.6	851.2	783.8	746.1	721.5	705.0	708.4
32.5°	794.5	731.9	686.5	655.1	637.0	624.5	624.3
35°	649.5	606.7	577.6	564.4	551.3	542.2	542.7
37.5°	555.9	530.1	513.9	499.4	491.2	486.7	484.2
40°	507.9	486.7	474.2	465.6	458.7	452.5	451.3
42.5°	469.9	452.5	439.9	433.2	426.7	422.3	421.1
45°	417.1	402.8	391.3	383.9	381.1	377.0	377.0
47.5°	371.0	357.0	348.0	343.4	338.5	335.8	335.7
50°	339.9	329.1	321.1	318.2	314.2	312.5	311.9
52.5°	312.0	303.9	298.3	296.3	294.5	292.4	292.7
55°	274.2	269.7	267.3	265.6	262.8	259.3	261.7
57.5°	242.4	238.4	232.3	226.9	224.3	221.9	222.8
60°	220.0	212.0	204.0	197.7	196.0	190.8	190.8
62.5°	191.6	180.4	170.6	167.0	165.3	162.9	162.5
65°	147.4	142.8	140.5	138.3	137.1	137.1	136.0
67.5°	122.2	120.3	117.8	117.3	116.1	115.7	115.4
70°	108.0	105.6	104.5	104.0	102.8	103.4	101.7
72.5°	94.3	92.5	92.2	90.7	90.1	90.1	88.9
75°	74.3	74.3	73.7	73.1	72.0	71.4	72.0
77.5°	57.2	57.3	56.2	56.1	56.0	56.1	55.5
80°	45.7	46.2	45.7	45.1	44.6	45.1	44.6
82.5°	36.1	35.3	35.2	35.0	35.0	34.6	34.5
85°	20.6	21.1	20.6	20.0	20.0	20.0	20.6
87.5°	13.6	13.6	13.5	13.6	13.6	13.7	13.3
90°	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.0	270.4	269.8	269.1	268.6



TEST NUMBER: P331834-935

CATALOG NUMBER: S122RDIW-S865D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)