

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331840-930

Luminaire Tested: **S122RDIW-S865D1240U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331840-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1240U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5966.6 lumens  
Efficiency: N/A  
Efficacy: 85.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41																				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36																				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30																				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26																				
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23																				
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20																				
6	63	51	43	37	57	47	40	35	39	34	30	32	28	26	26	23	21	18																				
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16																				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.9	1.9
10°-20°	307.2	5.1
20°-30°	431.5	7.2
30°-40°	470.5	7.9
40°-50°	432.6	7.3
50°-60°	339.7	5.7
60°-70°	221.5	3.7
70°-80°	114.2	1.9
80°-90°	34.6	0.6
90°-100°	79.4	1.3
100°-110°	246.5	4.1
110°-120°	421.4	7.1
120°-130°	554.2	9.3
130°-140°	622.0	10.4
140°-150°	609.9	10.2
150°-160°	511.5	8.6
160°-170°	339.3	5.7
170°-180°	118.6	2.0
0°-30°	850.6	14.3
0°-40°	1321.1	22.1
0°-60°	2093.4	35.1
0°-90°	2463.7	41.3
90°-120°	747.3	12.5
90°-150°	2533.4	42.5
90°-180°	3503.0	58.7
0°-180°	5966.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	1	14	37	35	36	5
95°	55	65	68	68	66	63
105°	227	230	233	235	235	240
115°	423	429	427	426	423	418
125°	615	624	622	619	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	603
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1251	1248	1245	1252	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	14.0	13.0	12.1	11.2	10.2	10.2	11.3	12.2	13.3	14.3	14.0
90°	1.1	3.9	6.7	9.5	12.3	16.3	21.5	26.7	31.8	37.0	36.5
92.5°	18.8	20.9	23.0	25.0	27.1	28.7	29.9	31.1	32.4	33.6	33.7
95°	55.0	57.3	59.7	62.0	64.4	65.8	66.3	66.7	67.2	67.7	67.7
97.5°	100.4	102.5	104.6	106.6	108.7	110.1	111.0	111.9	112.8	113.7	113.7
100°	134.3	136.2	138.0	139.9	141.8	143.1	143.7	144.5	145.2	145.9	145.9
102.5°	169.7	171.3	172.8	174.3	175.8	177.0	177.9	178.8	179.7	180.6	180.8
105°	227.3	228.0	228.7	229.4	230.1	230.7	231.1	231.6	232.1	232.6	233.0
107.5°	285.2	286.3	287.3	288.3	289.3	289.8	289.8	289.8	289.8	289.8	290.1
110°	322.5	323.8	325.2	326.7	328.1	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.1	364.4	365.8	367.3	368.7	369.2	369.1	368.9	368.7	368.5	367.9
115°	422.9	424.3	425.7	427.1	428.5	428.9	428.5	428.0	427.5	427.1	426.9
117.5°	482.5	484.4	486.2	488.1	490.0	490.3	488.9	487.6	486.3	485.0	484.5
120°	522.2	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	522.2
122.5°	558.6	560.8	563.1	565.3	567.6	568.1	566.8	565.5	564.1	562.8	562.2
125°	615.2	617.3	619.5	621.6	623.7	624.4	623.7	623.1	622.3	621.6	620.9
127.5°	670.4	673.1	675.8	678.5	681.2	682.1	681.3	680.4	679.6	678.7	677.8
130°	705.2	708.2	711.3	714.3	717.3	718.6	718.2	717.7	717.2	716.7	716.2
132.5°	744.0	746.5	749.0	751.5	754.0	755.3	755.4	755.5	755.5	755.6	754.6
135°	796.1	798.6	801.2	803.8	806.4	807.9	808.4	808.9	809.3	809.8	809.5
137.5°	850.8	852.9	855.0	857.1	859.2	860.6	861.2	861.9	862.4	863.1	862.9
140°	883.8	885.9	888.0	890.1	892.3	893.9	895.0	896.3	897.4	898.5	898.5
142.5°	917.6	919.7	921.9	924.0	926.1	927.5	928.3	929.1	929.9	930.7	930.9
145°	966.2	967.9	969.6	971.2	972.8	974.4	975.8	977.1	978.6	980.0	980.2
147.5°	1009.6	1011.5	1013.5	1015.5	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2
150°	1039.2	1040.6	1042.0	1043.4	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4
152.5°	1065.4	1066.8	1068.2	1069.6	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7
155°	1104.7	1105.5	1106.1	1106.9	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2
157.5°	1138.3	1138.8	1139.3	1139.8	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9
160°	1158.6	1159.1	1159.6	1160.1	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2
162.5°	1177.2	1177.4	1177.5	1177.5	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3
165°	1202.0	1201.8	1201.5	1201.3	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6
167.5°	1222.7	1222.0	1221.3	1220.6	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0
170°	1233.7	1233.0	1232.3	1231.6	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1
172.5°	1241.3	1240.6	1239.9	1239.2	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8
175°	1250.6	1249.9	1249.2	1248.5	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0
177.5°	1254.4	1253.8	1253.3	1252.7	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	13.8	13.5	13.2	13.0	13.1	13.1	13.2	13.2
90°	36.0	35.6	35.1	35.0	35.2	35.5	35.7	36.0
92.5°	33.8	33.9	34.0	34.1	34.1	34.2	34.2	34.2
95°	67.7	67.7	67.7	67.4	66.9	66.4	66.0	65.6
97.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.6
100°	145.9	145.9	145.9	145.8	145.5	145.3	145.0	144.8
102.5°	180.9	181.2	181.3	181.3	181.1	180.8	180.6	180.3
105°	233.5	234.0	234.5	234.7	234.7	234.7	234.7	234.7
107.5°	290.2	290.4	290.7	290.2	289.1	288.0	286.9	285.8
110°	328.8	328.8	328.8	328.4	327.8	327.0	326.3	325.6





TEST NUMBER: P331840-930

CATALOG NUMBER: S122RDIW-S865D1240U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	367.4	366.8	366.2	365.7	365.2	364.7	364.2	363.6
115°	426.6	426.4	426.2	425.7	425.0	424.3	423.5	422.9
117.5°	483.9	483.3	482.7	482.2	481.4	480.7	480.0	479.3
120°	522.2	522.2	522.2	521.9	521.1	520.5	519.8	519.1
122.5°	561.7	561.2	560.6	560.0	559.5	559.0	558.5	558.0
125°	620.2	619.5	618.8	618.3	618.1	617.8	617.6	617.3
127.5°	677.0	676.1	675.3	674.5	673.8	673.0	672.3	671.5
130°	715.8	715.3	714.9	714.2	713.2	712.3	711.3	710.4
132.5°	753.6	752.5	751.5	750.6	749.9	749.1	748.4	747.6
135°	809.3	809.1	808.9	808.4	807.6	807.0	806.2	805.5
137.5°	862.7	862.5	862.3	861.8	860.8	859.9	858.9	858.0
140°	898.5	898.5	898.5	898.1	897.2	896.3	895.3	894.4
142.5°	931.1	931.3	931.5	931.1	930.2	929.2	928.3	927.3
145°	980.5	980.7	980.9	980.6	979.7	978.7	977.8	976.8
147.5°	1023.7	1024.3	1024.7	1024.6	1023.7	1022.8	1021.9	1021.0
150°	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8
152.5°	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8
155°	1113.5	1114.6	1115.7	1116.0	1115.3	1114.6	1113.9	1113.2
157.5°	1145.6	1147.1	1148.8	1149.0	1147.9	1146.7	1145.6	1144.4
160°	1164.7	1166.0	1167.4	1167.7	1166.8	1165.8	1164.9	1163.9
162.5°	1181.9	1183.5	1185.1	1185.4	1184.2	1183.1	1181.9	1180.9
165°	1204.2	1205.8	1207.5	1207.7	1206.6	1205.4	1204.2	1203.1
167.5°	1222.6	1224.3	1225.9	1226.1	1224.9	1223.7	1222.5	1221.2
170°	1232.7	1234.4	1236.1	1236.2	1234.8	1233.4	1231.9	1230.5
172.5°	1240.4	1242.0	1243.7	1243.7	1242.4	1241.0	1239.6	1238.1
175°	1248.6	1250.3	1251.9	1252.1	1250.6	1249.2	1247.8	1246.3
177.5°	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7

(END OF REPORT)