

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331829-930

Luminaire Tested: **S122RDIW-S865D710U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331829-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D710U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5004.1 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45	41
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	39	36
4	77	67	60	54	72	63	56	51	55	49	45	47	43	40	40	37	35	31
5	71	60	53	47	66	56	50	45	49	44	40	43	39	35	36	33	31	28
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23
8	57	45	38	33	53	43	36	31	38	32	29	33	29	26	29	25	23	21
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19
10	50	38	32	27	47	36	30	26	32	27	24	29	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	2.9
10°-20°	411.2	8.2
20°-30°	529.9	10.6
30°-40°	503.6	10.1
40°-50°	431.4	8.6
50°-60°	328.5	6.6
60°-70°	207.7	4.2
70°-80°	103.7	2.1
80°-90°	28.9	0.6
90°-100°	26.3	0.5
100°-110°	96.5	1.9
110°-120°	257.9	5.2
120°-130°	425.7	8.5
130°-140°	452.8	9.0
140°-150°	420.8	8.4
150°-160°	338.4	6.8
160°-170°	218.0	4.4
170°-180°	75.1	1.5
0°-30°	1088.7	21.8
0°-40°	1592.3	31.8
0°-60°	2352.3	47.0
0°-90°	2692.6	53.8
90°-120°	380.7	7.6
90°-150°	1680.1	33.6
90°-180°	2312.0	46.2
0°-180°	5004.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	21
90°	15	1	15	1	15	8
95°	24	37	24	37	24	23
105°	43	174	43	174	43	45
115°	47	328	47	328	47	117
125°	488	464	488	464	488	422
135°	593	574	593	574	593	457
145°	676	666	676	666	676	423
155°	734	733	734	733	734	339
165°	771	773	771	773	771	218
175°	786	790	786	790	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	10.0	10.4	10.4	10.3	10.3	10.1	10.0	10.4	9.8	10.1	9.5
90°	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7	12.1	11.4	10.4
92.5°	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9	13.5	13.2	12.7
95°	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6	22.9	22.3	21.4
97.5°	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8	30.3	29.8	27.7
100°	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6	33.5	32.5	30.4
102.5°	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1	34.7	33.4	31.4
105°	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6	36.2	34.8	32.5
107.5°	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9	47.3	48.8	50.3
110°	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5	87.2	99.9	136.6



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4	205.7	251.9	261.0
115°	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7	293.4	352.1	348.9
117.5°	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7	375.9	390.0	387.8
120°	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4	419.9	418.3	416.0
122.5°	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1	446.2	445.3	442.8
125°	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0	483.1	482.2	479.9
127.5°	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2	516.9	515.6	513.8
130°	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9	538.5	537.1	535.7
132.5°	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9	559.7	558.6	557.2
135°	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0	589.7	588.5	587.3
137.5°	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9	617.7	616.4	615.1
140°	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0	635.9	634.7	633.2
142.5°	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6	652.6	651.6	650.0
145°	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9	676.1	675.2	673.0
147.5°	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3	696.7	695.9	693.8
150°	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8	709.1	708.3	706.3
152.5°	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2	720.5	719.7	717.8
155°	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6	735.9	735.2	733.6
157.5°	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7	748.8	747.9	746.8
160°	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2	756.4	755.7	754.9
162.5°	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3	763.4	762.5	761.9
165°	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1	770.7
167.5°	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1	779.2	778.3	778.0
170°	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7	782.9	782.0	781.7
172.5°	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4	785.5	784.6	784.4
175°	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5	788.6	787.7	787.4
177.5°	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8	789.0	788.3	788.2
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	9.2	9.5	9.3	8.6	8.7	8.9	10.8	12.6	11.3	10.2	9.6
90°	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6	2.0	3.3	4.7
92.5°	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5	11.4	11.3	11.2
95°	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1	32.9	28.7	24.5
97.5°	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6	61.8	50.1	38.2
100°	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0	83.6	66.3	48.9
102.5°	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2	127.5	123.8	120.1
105°	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5	177.3	181.2	184.9
107.5°	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8	224.9	228.0	231.0
110°	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8	255.5	258.2	260.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1	284.5	286.8	289.1
115°	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2	330.4	332.5	334.7
117.5°	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4	371.8	374.2	376.6
120°	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5	401.5	403.3	405.2
122.5°	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1	427.1	429.1	431.1
125°	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0	465.7	467.3	469.0
127.5°	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3	501.1	503.0	504.8
130°	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6	523.7	525.7	527.7
132.5°	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5	546.3	548.0	549.7
135°	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2	576.2	578.2	580.2
137.5°	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2	605.6	607.1	608.5
140°	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9	624.8	625.8	626.9
142.5°	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3	641.2	642.1	643.0
145°	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1	665.9	665.9	665.7
147.5°	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5	688.1	687.6	687.1
150°	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2	702.3	701.4	700.5
152.5°	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5	714.5	713.5	712.5
155°	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4	732.3	731.2	730.0
157.5°	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5	746.5	745.5	744.5
160°	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	754.9	754.2	753.4
162.5°	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0	762.2	761.5	760.7
165°	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8	772.0	771.3	770.5
167.5°	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1	779.3	778.6	777.8
170°	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2	783.4	782.7	782.0
172.5°	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9	786.2	785.5	784.6
175°	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5	789.6	788.7	787.8
177.5°	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1	790.4	789.6	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	9.5	9.3	8.6	8.8	9.0	8.8	8.9	8.6	8.7	8.9	8.5
90°	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7	13.3	13.9	14.4
92.5°	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9	14.3	14.6	14.8
95°	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6	24.1	24.8	25.0
97.5°	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8	31.3	31.8	32.1
100°	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6	35.5	36.6	37.3
102.5°	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1	37.4	38.7	39.5
105°	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6	39.0	40.4	41.3
107.5°	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9	44.5	43.0	42.6
110°	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5	61.8	49.2	43.0



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4	113.2	66.9	43.9
115°	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7	175.9	117.2	83.3
117.5°	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7	347.4	333.2	311.1
120°	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4	422.9	424.4	416.6
122.5°	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1	448.0	449.0	447.8
125°	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0	484.9	485.8	486.5
127.5°	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2	519.5	520.8	521.5
130°	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9	541.3	542.7	543.3
132.5°	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9	562.1	563.3	563.9
135°	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0	592.2	593.5	594.0
137.5°	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9	620.1	621.4	621.8
140°	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0	638.1	639.3	639.5
142.5°	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6	654.7	655.7	655.9
145°	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9	677.8	678.7	678.9
147.5°	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3	698.0	698.6	698.7
150°	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8	710.6	711.3	711.4
152.5°	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2	722.0	722.8	722.8
155°	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6	737.4	738.2	738.0
157.5°	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7	750.5	751.4	751.3
160°	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2	758.0	758.7	758.6
162.5°	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3	765.1	766.0	765.9
165°	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9	773.7	774.6	774.6
167.5°	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1	781.0	781.8	781.7
170°	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7	784.6	785.5	785.4
172.5°	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4	787.3	788.2	788.1
175°	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5	790.3	791.2	791.0
177.5°	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8	790.4	791.2	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	8.6	8.2	8.6	8.2	8.6	8.2	8.6	8.5	8.9	8.7	8.6
90°	14.7	14.9	15.2	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7
92.5°	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9
95°	24.9	24.8	24.7	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6
97.5°	32.3	32.4	32.6	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8
100°	37.5	37.7	38.0	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6
102.5°	39.9	40.3	40.6	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1
105°	41.8	42.4	42.9	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6
107.5°	43.1	43.6	44.1	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9
110°	43.5	44.1	44.6	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.4	44.8	45.2	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4
115°	74.2	65.1	55.9	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7
117.5°	281.1	251.1	221.1	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7
120°	399.5	382.4	365.3	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4
122.5°	444.4	441.1	437.8	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1
125°	486.8	487.2	487.6	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0
127.5°	521.5	521.6	521.7	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2
130°	543.2	543.1	542.9	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9
132.5°	563.7	563.6	563.5	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9
135°	593.8	593.5	593.3	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0
137.5°	621.3	620.9	620.5	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9
140°	638.9	638.2	637.6	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0
142.5°	655.3	654.7	654.0	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6
145°	678.2	677.6	676.9	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9
147.5°	698.1	697.7	697.1	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3
150°	710.8	710.1	709.5	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8
152.5°	721.9	721.1	720.2	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2
155°	737.0	736.1	735.0	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6
157.5°	750.3	749.3	748.4	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7
160°	757.7	756.8	756.0	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2
162.5°	764.8	763.7	762.5	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3
165°	773.7	772.9	772.0	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9
167.5°	780.6	779.4	778.3	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1
170°	784.2	783.1	782.0	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7
172.5°	786.9	785.8	784.6	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4
175°	789.7	788.5	787.2	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5
177.5°	790.2	789.2	788.3	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	8.9	8.8	9.0	8.8	8.6	9.3	9.5	9.6	10.2	11.3	12.6
90°	12.1	11.4	10.4	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5
95°	22.9	22.3	21.4	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1
97.5°	30.3	29.8	27.7	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6
100°	33.5	32.5	30.4	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0
102.5°	34.7	33.4	51.4	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2
105°	36.2	34.8	69.5	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5
107.5°	47.3	48.8	90.3	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8
110°	87.2	99.9	136.6	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.7	251.9	261.0	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1
115°	293.4	352.1	348.9	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2
117.5°	375.9	390.0	387.8	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4
120°	419.9	418.3	416.0	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5
122.5°	446.2	445.3	442.8	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1
125°	483.1	482.2	479.9	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0
127.5°	516.9	515.6	513.8	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3
130°	538.5	537.1	535.7	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6
132.5°	559.7	558.6	557.2	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5
135°	589.7	588.5	587.3	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2
137.5°	617.7	616.4	615.1	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2
140°	635.9	634.7	633.2	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9
142.5°	652.6	651.6	650.0	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3
145°	676.1	675.2	673.0	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1
147.5°	696.7	695.9	693.8	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5
150°	709.1	708.3	706.3	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2
152.5°	720.5	719.7	717.8	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5
155°	735.9	735.2	733.6	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4
157.5°	748.8	747.9	746.8	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5
160°	756.4	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7
162.5°	763.4	762.5	761.9	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0
165°	772.0	771.1	770.7	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8
167.5°	779.2	778.3	778.0	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1
170°	782.9	782.0	781.7	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2
172.5°	785.5	784.6	784.4	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9
175°	788.6	787.7	787.4	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5
177.5°	789.0	788.3	788.2	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	10.8	8.9	8.7	8.6	9.3	9.5	9.2	9.5	10.1	9.8	10.4
90°	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7
92.5°	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9
95°	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6
97.5°	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8
100°	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6
102.5°	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1
105°	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6
107.5°	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9
110°	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4
115°	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7
117.5°	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7
120°	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4
122.5°	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1
125°	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0
127.5°	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2
130°	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9
132.5°	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9
135°	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0
137.5°	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9
140°	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0
142.5°	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6
145°	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9
147.5°	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3
150°	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8
152.5°	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2
155°	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6
157.5°	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7
160°	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2
162.5°	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3
165°	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9
167.5°	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1
170°	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7
172.5°	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4
175°	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5
177.5°	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	10.0	10.1	10.3	10.3	10.4	10.4	10.0
90°	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331829-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)