

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331585-840

Luminaire Tested: **S122DIW-S1005D435U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331585-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6192.2 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	72	1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62							
	2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53	53	3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	46							
	4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40	40	5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35							
	6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31	31	7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28							
	8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25	25	9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23							
	10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21	21																										

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	3.1
10°-20°	557.5	9.0
20°-30°	809.1	13.1
30°-40°	853.9	13.8
40°-50°	756.0	12.2
50°-60°	603.3	9.7
60°-70°	410.1	6.6
70°-80°	210.2	3.4
80°-90°	52.2	0.8
90°-100°	19.9	0.3
100°-110°	73.0	1.2
110°-120°	195.0	3.1
120°-130°	322.0	5.2
130°-140°	342.4	5.5
140°-150°	318.3	5.1
150°-160°	255.9	4.1
160°-170°	164.9	2.7
170°-180°	56.8	0.9
0°-30°	1558.5	25.2
0°-40°	2412.3	39.0
0°-60°	3771.7	60.9
0°-90°	4444.1	71.8
90°-120°	287.9	4.6
90°-150°	1270.6	20.5
90°-180°	1748.0	28.2
0°-180°	6192.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	12	0	12	0	12	7
95°	19	28	19	28	19	17
105°	33	131	33	131	33	34
115°	35	248	35	248	35	89
125°	369	351	369	351	369	319
135°	448	434	448	434	448	346
145°	512	504	512	504	512	320
155°	555	555	555	555	555	256
165°	583	584	583	584	583	165
175°	594	598	594	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	18.4	18.4	19.0	18.3	18.3	18.8	18.7	18.0	18.6	19.1	19.5
90°	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6	9.1	8.6	7.9
92.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5	10.3	10.0	9.6
95°	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8	17.3	16.9	16.2
97.5°	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3	22.9	22.5	21.0
100°	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2	25.3	24.6	22.9
102.5°	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3	26.3	25.2	39.0
105°	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5	27.4	26.4	52.5
107.5°	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7	35.7	36.9	68.3
110°	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4	65.9	75.5	103.2



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6	155.5	190.6	197.3
115°	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5	221.9	266.3	263.9
117.5°	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5	284.3	295.0	293.4
120°	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7	317.5	316.4	314.7
122.5°	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1	337.5	336.8	334.9
125°	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1	365.4	364.8	362.9
127.5°	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9	390.9	389.9	388.6
130°	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3	407.2	406.2	405.2
132.5°	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2	423.3	422.4	421.3
135°	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0	446.0	445.0	444.1
137.5°	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1	467.1	466.2	465.1
140°	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7	480.8	480.0	478.9
142.5°	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3	493.5	492.7	491.5
145°	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0	511.3	510.6	509.0
147.5°	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4	526.8	526.3	524.7
150°	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8	536.2	535.6	534.1
152.5°	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4	544.8	544.3	542.8
155°	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1	556.5	555.9	554.8
157.5°	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9	566.2	565.6	564.8
160°	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6	572.1	571.5	570.9
162.5°	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9	577.3	576.6	576.1
165°	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1	582.9
167.5°	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0	589.3	588.5	588.3
170°	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7	592.0	591.4	591.2
172.5°	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7	594.1	593.4	593.2
175°	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0	596.3	595.6	595.4
177.5°	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2	596.7	596.1	596.1
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	20.0	19.8	19.7	20.7	18.7	18.5	15.8	13.7	13.3	12.9	11.8
90°	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7	8.6	8.5	8.4
95°	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1	24.8	21.7	18.6
97.5°	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6	46.8	37.9	28.9
100°	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4	63.2	50.1	37.0
102.5°	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2	96.4	93.6	90.9
105°	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2	134.1	136.9	139.9
107.5°	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7	170.1	172.4	174.7
110°	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2	193.2	195.2	197.2



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3	215.1	216.9	218.6
115°	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2	249.8	251.5	253.1
117.5°	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3	281.1	283.0	284.8
120°	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2	303.6	305.0	306.5
122.5°	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4	323.0	324.5	326.0
125°	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9	352.1	353.5	354.7
127.5°	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6	379.0	380.3	381.7
130°	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6	396.1	397.6	399.1
132.5°	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8	413.0	414.3	415.7
135°	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2	435.8	437.3	438.8
137.5°	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0	458.0	459.1	460.2
140°	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8	472.5	473.3	474.0
142.5°	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2	484.9	485.5	486.3
145°	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7	503.6	503.5	503.4
147.5°	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7	520.4	520.0	519.7
150°	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8	531.1	530.4	529.8
152.5°	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1	540.4	539.6	538.9
155°	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6	553.8	552.9	552.1
157.5°	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2	564.5	563.8	563.1
160°	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	570.9	570.4	569.8
162.5°	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0	576.4	575.8	575.3
165°	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4	583.9	583.3	582.7
167.5°	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0	589.4	588.9	588.2
170°	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1	592.5	591.9	591.4
172.5°	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1	594.6	594.0	593.4
175°	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8	597.1	596.4	595.8
177.5°	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2	597.7	597.1	596.6
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	11.4	11.0	10.5	10.7	10.2	9.8	9.3	9.4	9.5	8.3	8.4
90°	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6	10.1	10.5	10.9
92.5°	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5	10.8	11.0	11.2
95°	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8	18.3	18.8	19.0
97.5°	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3	23.7	24.0	24.3
100°	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2	26.9	27.7	28.2
102.5°	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3	28.3	29.3	29.9
105°	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5	29.5	30.6	31.3
107.5°	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7	33.6	32.5	32.2
110°	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4	46.8	37.2	32.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6	85.5	50.6	33.2
115°	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5	133.1	88.7	63.0
117.5°	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5	262.8	252.0	235.3
120°	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7	319.8	321.0	315.1
122.5°	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1	338.8	339.5	338.6
125°	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1	366.8	367.4	367.9
127.5°	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9	392.8	393.8	394.4
130°	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3	409.3	410.4	410.9
132.5°	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2	425.1	426.0	426.4
135°	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0	447.9	448.9	449.2
137.5°	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1	469.0	469.9	470.2
140°	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7	482.6	483.4	483.6
142.5°	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3	495.1	495.9	496.0
145°	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0	512.6	513.3	513.4
147.5°	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4	527.9	528.4	528.4
150°	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8	537.3	538.0	538.1
152.5°	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4	546.0	546.6	546.5
155°	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1	557.6	558.3	558.2
157.5°	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9	567.5	568.3	568.2
160°	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6	573.2	573.8	573.7
162.5°	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9	578.7	579.3	579.2
165°	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5	585.1	585.8	585.8
167.5°	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0	590.6	591.3	591.2
170°	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7	593.4	594.0	593.9
172.5°	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7	595.4	596.1	596.0
175°	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0	597.6	598.3	598.2
177.5°	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2	597.7	598.3	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	8.4	7.8	7.9	7.3	7.9	7.8	8.4	8.4	8.3	9.5	9.4
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6
92.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5
95°	18.9	18.8	18.7	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8
97.5°	24.4	24.5	24.6	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3
100°	28.4	28.6	28.7	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2
102.5°	30.2	30.5	30.7	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3
105°	31.6	32.0	32.4	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5
107.5°	32.6	33.0	33.3	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7
110°	32.9	33.3	33.7	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6
115°	56.1	49.2	42.3	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5
117.5°	212.6	189.9	167.2	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5
120°	302.2	289.2	276.2	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7
122.5°	336.1	333.6	331.0	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1
125°	368.2	368.5	368.8	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1
127.5°	394.5	394.5	394.6	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9
130°	410.8	410.7	410.6	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3
132.5°	426.3	426.2	426.2	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2
135°	449.1	448.9	448.7	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0
137.5°	469.9	469.6	469.3	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1
140°	483.1	482.6	482.2	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7
142.5°	495.5	495.1	494.6	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3
145°	512.9	512.4	512.0	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0
147.5°	528.0	527.6	527.1	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4
150°	537.6	537.0	536.5	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8
152.5°	545.9	545.3	544.6	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4
155°	557.3	556.6	555.8	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1
157.5°	567.4	566.6	565.9	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9
160°	573.1	572.4	571.7	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6
162.5°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9
165°	585.1	584.5	583.8	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5
167.5°	590.3	589.5	588.5	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0
170°	593.1	592.2	591.4	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7
172.5°	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7
175°	597.2	596.3	595.3	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0
177.5°	597.5	596.8	596.1	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	9.3	9.8	10.2	10.7	10.5	11.0	11.4	11.8	12.9	13.3	13.7
90°	9.1	8.6	7.9	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4
92.5°	10.3	10.0	9.6	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7
95°	17.3	16.9	16.2	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1
97.5°	22.9	22.5	21.0	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6
100°	25.3	24.6	22.9	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4
102.5°	26.3	25.2	39.0	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2
105°	27.4	26.4	52.5	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2
107.5°	35.7	36.9	68.3	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7
110°	65.9	75.5	103.2	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	155.5	190.6	197.3	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3
115°	221.9	266.3	263.9	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2
117.5°	284.3	295.0	293.4	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3
120°	317.5	316.4	314.7	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2
122.5°	337.5	336.8	334.9	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4
125°	365.4	364.8	362.9	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9
127.5°	390.9	389.9	388.6	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6
130°	407.2	406.2	405.2	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6
132.5°	423.3	422.4	421.3	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8
135°	446.0	445.0	444.1	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2
137.5°	467.1	466.2	465.1	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0
140°	480.8	480.0	478.9	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8
142.5°	493.5	492.7	491.5	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2
145°	511.3	510.6	509.0	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7
147.5°	526.8	526.3	524.7	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7
150°	536.2	535.6	534.1	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8
152.5°	544.8	544.3	542.8	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1
155°	556.5	555.9	554.8	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6
157.5°	566.2	565.6	564.8	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2
160°	572.1	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5
162.5°	577.3	576.6	576.1	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0
165°	583.8	583.1	582.9	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4
167.5°	589.3	588.5	588.3	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0
170°	592.0	591.4	591.2	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1
172.5°	594.1	593.4	593.2	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1
175°	596.3	595.6	595.4	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8
177.5°	596.7	596.1	596.1	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	15.8	18.5	18.7	20.7	19.7	19.8	20.0	19.5	19.1	18.6	18.0
90°	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6
92.5°	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5
95°	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8
97.5°	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3
100°	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2
102.5°	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3
105°	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5
107.5°	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7
110°	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6
115°	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5
117.5°	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5
120°	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7
122.5°	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1
125°	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1
127.5°	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9
130°	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3
132.5°	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2
135°	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0
137.5°	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1
140°	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7
142.5°	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3
145°	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0
147.5°	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4
150°	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8
152.5°	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4
155°	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1
157.5°	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9
160°	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6
162.5°	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9
165°	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5
167.5°	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0
170°	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7
172.5°	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7
175°	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0
177.5°	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	18.7	18.8	18.3	18.3	19.0	18.4	18.4
90°	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331585-840

CATALOG NUMBER: S122DIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)