

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331835-930

Luminaire Tested: **S122RDIW-S865D970U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331835-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D970U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5616.5 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44					44			
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43	38					38			
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32					32			
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32	28					28			
4	74	64	56	50	68	59	52	47	49	45	41	41	37	34	33	30	28	24					24			
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21					21			
6	63	51	44	38	58	47	41	36	40	35	31	33	29	26	27	24	22	19					19			
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17					17			
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15					15			
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14					14			
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.9	2.0
10°-20°	307.2	5.5
20°-30°	431.5	7.7
30°-40°	470.5	8.4
40°-50°	432.6	7.7
50°-60°	339.7	6.0
60°-70°	221.5	3.9
70°-80°	114.2	2.0
80°-90°	32.3	0.6
90°-100°	35.9	0.6
100°-110°	131.7	2.3
110°-120°	352.0	6.3
120°-130°	581.1	10.3
130°-140°	618.0	11.0
140°-150°	574.4	10.2
150°-160°	461.8	8.2
160°-170°	297.6	5.3
170°-180°	102.4	1.8
0°-30°	850.6	15.1
0°-40°	1321.1	23.5
0°-60°	2093.4	37.3
0°-90°	2461.4	43.8
90°-120°	519.7	9.3
90°-150°	2293.2	40.8
90°-180°	3155.0	56.2
0°-180°	5616.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	1	9	16	19	21	4
95°	51	27	30	34	34	62
105°	237	247	48	56	59	253
115°	448	462	481	137	64	441
125°	633	644	658	664	666	565
135°	784	796	803	810	809	605
145°	909	909	922	927	923	568
155°	1001	995	1003	1007	1002	461
165°	1055	1051	1052	1057	1052	298
175°	1079	1074	1075	1080	1073	103
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	14.0	12.9	11.7	10.5	9.4	9.0	9.2	9.5	9.8	10.0	10.0
90°	0.8	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5
92.5°	15.7	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5
95°	50.6	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2
97.5°	100.5	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3
100°	137.9	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8
102.5°	179.0	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5
105°	236.8	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4
107.5°	302.7	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6
110°	345.1	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0



TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	385.0	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7
115°	447.9	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5
117.5°	504.2	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0
120°	545.4	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2
122.5°	580.2	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0
125°	633.3	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5
127.5°	681.5	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6
130°	712.1	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0
132.5°	743.2	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0
135°	783.7	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9
137.5°	824.7	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1
140°	851.5	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9
142.5°	873.9	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8
145°	909.1	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8
147.5°	939.9	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9
150°	959.8	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8
152.5°	976.6	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4
155°	1001.1	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4
157.5°	1020.3	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1
160°	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5
162.5°	1041.5	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0
165°	1054.8	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7
167.5°	1064.8	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5
170°	1070.4	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5
172.5°	1074.2	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3
175°	1079.0	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3
177.5°	1079.8	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	10.0	9.9	9.9	10.0	10.0	10.1	10.2	10.3
90°	17.3	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.0	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	32.1	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.1	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	47.2	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	49.2	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	51.4	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	62.6	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	101.7	84.4	67.1	58.8	59.4	60.2	60.8	61.6





TEST NUMBER: P331835-930

CATALOG NUMBER: S122RDIW-S865D970U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	217.5	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	320.3	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	493.6	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	575.2	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	610.3	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	660.7	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	707.4	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	736.9	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	765.6	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	806.7	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	844.7	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	869.4	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	892.2	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	924.1	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	951.8	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	968.9	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	984.5	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1005.5	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1023.2	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1033.6	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1043.2	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1064.7	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1069.8	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1073.4	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1077.5	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.0	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)