

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331592-840

Luminaire Tested: **S122DIW-S1005D710U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331592-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6929.2 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64								
1	102	97	94	90	95	92	88	85	81	79	76	71	69	68	62	61	60	55								
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51	47								
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	50	47	44	41								
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	36								
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31								
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30	28								
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25								
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	28	25	22								
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	22	20								
10	51	38	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21	19								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.8
10°-20°	557.5	8.0
20°-30°	809.1	11.7
30°-40°	853.9	12.3
40°-50°	756.0	10.9
50°-60°	603.3	8.7
60°-70°	410.1	5.9
70°-80°	210.2	3.0
80°-90°	54.2	0.8
90°-100°	56.3	0.8
100°-110°	174.8	2.5
110°-120°	298.7	4.3
120°-130°	392.8	5.7
130°-140°	440.9	6.4
140°-150°	432.3	6.2
150°-160°	362.6	5.2
160°-170°	240.5	3.5
170°-180°	84.1	1.2
0°-30°	1558.5	22.5
0°-40°	2412.3	34.8
0°-60°	3771.7	54.4
0°-90°	4446.2	64.2
90°-120°	529.8	7.6
90°-150°	1795.8	25.9
90°-180°	2483.0	35.8
0°-180°	6929.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	25	1	25	1	25	13
95°	46	39	46	39	46	52
105°	166	161	166	161	166	175
115°	300	300	300	300	300	296
125°	438	436	438	436	438	390
135°	571	564	571	564	571	440
145°	692	685	692	685	692	432
155°	789	783	789	783	789	363
165°	853	852	853	852	853	241
175°	884	886	884	886	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	21.2	21.2	21.7	21.1	21.1	21.7	21.7	21.2	21.9	22.6	22.4
90°	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5	25.9	26.3	22.5
92.5°	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9	23.9	23.8	22.9
95°	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0	48.0	48.0	47.7
97.5°	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.0
100°	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4	103.4	103.4	102.9
102.5°	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3	128.2	127.9	127.3
105°	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5	165.2	164.9	164.5
107.5°	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7	205.6	205.5	205.5
110°	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4	260.8	261.3	261.4
115°	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5	302.6	302.8	303.1
117.5°	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1	343.5	343.9	344.8
120°	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2	370.2	370.2	371.5
122.5°	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2	398.6	399.0	399.9
125°	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6	440.1	440.6	441.1
127.5°	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9	480.5	481.1	481.7
130°	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5	507.8	508.1	508.4
132.5°	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2	534.9	535.6	535.6
135°	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7	573.8	574.0	573.7
137.5°	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5	611.7	611.8	611.4
140°	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9	636.9	636.9	636.1
142.5°	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0	659.8	659.7	659.1
145°	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0	694.8	694.7	693.7
147.5°	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7	725.3	725.0	724.3
150°	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2	743.5
152.5°	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4	762.5
155°	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2	788.4	787.6	787.1
157.5°	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0	810.9	809.8	809.5
160°	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6	824.6	823.5	823.3
162.5°	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8	836.7	835.6	835.4
165°	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6	852.4	851.3	851.3
167.5°	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7	865.5	864.3	864.3
170°	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8	872.7	871.5	871.7
172.5°	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3	878.1	876.9	877.1
175°	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0	883.9	882.7	883.1
177.5°	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2	886.5
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	22.3	21.6	20.9	21.6	19.3	18.9	16.1	13.7	13.5	13.3	12.5
90°	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7	2.7	4.7	6.8
92.5°	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3	14.8	16.3	17.8
95°	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0	40.6	42.3	43.9
97.5°	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2	72.6	74.1	75.5
100°	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1	96.5	97.9	99.2
102.5°	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4	121.4	122.5	123.5
105°	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1	161.6	162.1	162.6
107.5°	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2	202.9	203.7	204.4
110°	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5	229.5	230.6	231.6



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3	258.3	259.3	260.3
115°	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7	300.7	301.7	302.8
117.5°	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0	343.4	344.7	346.0
120°	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	371.5	372.8	374.2
122.5°	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0	397.6	399.2	400.7
125°	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2	437.7	439.1	440.6
127.5°	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2	477.2	479.1	480.9
130°	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8	502.0	504.1	506.3
132.5°	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5	529.2	531.0	532.7
135°	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3	566.1	567.9	569.8
137.5°	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1	604.6	606.1	607.6
140°	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5	627.9	629.4	631.0
142.5°	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5	652.0	653.5	655.0
145°	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9	686.1	687.2	688.4
147.5°	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7	717.0	718.4	719.8
150°	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6	737.6	738.6	739.6
152.5°	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2	756.2	757.2	758.2
155°	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0	783.6	784.1	784.6
157.5°	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9	807.3	807.6	807.9
160°	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3	821.6	821.9	822.3
162.5°	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5	834.6	834.7	834.7
165°	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0	851.8	851.7	851.5
167.5°	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8	866.3	865.8	865.3
170°	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5	874.0	873.5	873.0
172.5°	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9	879.4	878.9	878.4
175°	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5	886.1	885.6	885.0
177.5°	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2	888.8	888.4	888.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	12.3	12.2	12.3	13.0	13.2	13.3	12.6	12.5	12.5	11.2	11.1
90°	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5	25.2	24.9	24.8
92.5°	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9	24.0	24.1	24.1
95°	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0	48.0	48.0	47.8
97.5°	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6	80.6	80.6	80.6
100°	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4	103.4	103.4	103.3
102.5°	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3	128.4	128.6	128.6
105°	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5	165.8	166.2	166.3
107.5°	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7	205.9	206.0	205.7
110°	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	232.8



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4	260.0	259.6	259.2
115°	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5	302.3	302.1	301.7
117.5°	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1	342.6	342.2	341.7
120°	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2	370.2	370.2	369.9
122.5°	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2	397.8	397.4	397.0
125°	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6	439.1	438.6	438.3
127.5°	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9	479.3	478.7	478.2
130°	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5	507.1	506.8	506.2
132.5°	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2	533.4	532.7	532.1
135°	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7	573.5	573.4	573.0
137.5°	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5	611.4	611.3	610.9
140°	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9	636.9	636.9	636.6
142.5°	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0	660.1	660.2	660.0
145°	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0	695.2	695.3	695.1
147.5°	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7	726.0	726.4	726.3
150°	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1	745.6	746.1	746.1
152.5°	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6	765.2	765.9	765.9
155°	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2	790.1	790.9	791.1
157.5°	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0	813.1	814.3	814.5
160°	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6	826.6	827.6	827.7
162.5°	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8	839.0	840.1	840.2
165°	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6	854.7	856.0	856.2
167.5°	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7	867.8	869.0	869.1
170°	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8	875.0	876.2	876.3
172.5°	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3	880.4	881.6	881.6
175°	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0	886.3	887.5	887.5
177.5°	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8	888.6	889.4	889.4
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	11.2	10.6	10.6	10.1	10.6	10.6	11.2	11.1	11.2	12.5	12.5
90°	24.9	25.1	25.3	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5
92.5°	24.1	24.2	24.2	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9
95°	47.5	47.2	46.8	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0
97.5°	80.6	80.6	80.5	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6
100°	103.2	103.0	102.8	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4
102.5°	128.4	128.2	128.1	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3
105°	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5
107.5°	204.9	204.2	203.4	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7
110°	232.3	231.8	231.3	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.5	258.1	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4
115°	301.2	300.7	300.2	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5
117.5°	341.2	340.7	340.2	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1
120°	369.4	368.9	368.4	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2
122.5°	396.6	396.3	395.9	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2
125°	438.2	438.0	437.8	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6
127.5°	477.6	477.1	476.6	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9
130°	505.5	504.9	504.2	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5
132.5°	531.6	531.0	530.5	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2
135°	572.5	572.0	571.5	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7
137.5°	610.2	609.6	608.8	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5
140°	636.0	635.3	634.6	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9
142.5°	659.3	658.6	658.0	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0
145°	694.4	693.8	693.1	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0
147.5°	725.7	725.0	724.4	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7
150°	745.6	745.1	744.7	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1
152.5°	765.2	764.6	764.0	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6
155°	790.6	790.1	789.6	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2
157.5°	813.6	812.8	812.0	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0
160°	827.1	826.4	825.8	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6
162.5°	839.4	838.7	837.9	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8
165°	855.3	854.4	853.6	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6
167.5°	868.3	867.4	866.6	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7
170°	875.3	874.2	873.2	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8
172.5°	880.7	879.7	878.7	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3
175°	886.5	885.6	884.5	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0
177.5°	888.6	887.8	887.0	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	12.6	13.3	13.2	13.0	12.3	12.2	12.3	12.5	13.3	13.5	13.7
90°	25.9	26.3	22.5	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7
92.5°	23.9	23.8	22.9	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3
95°	48.0	48.0	47.7	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0
97.5°	80.6	80.6	80.0	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2
100°	103.4	103.4	102.9	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1
102.5°	128.2	127.9	127.3	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4
105°	165.2	164.9	164.5	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1
107.5°	205.6	205.5	205.5	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2
110°	233.1	233.1	233.1	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.8	261.3	261.4	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3
115°	302.6	302.8	303.1	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7
117.5°	343.5	343.9	344.8	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0
120°	370.2	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2
122.5°	398.6	399.0	399.9	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0
125°	440.1	440.6	441.1	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2
127.5°	480.5	481.1	481.7	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2
130°	507.8	508.1	508.4	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8
132.5°	534.9	535.6	535.6	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5
135°	573.8	574.0	573.7	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3
137.5°	611.7	611.8	611.4	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1
140°	636.9	636.9	636.1	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5
142.5°	659.8	659.7	659.1	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5
145°	694.8	694.7	693.7	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9
147.5°	725.3	725.0	724.3	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7
150°	744.7	744.2	743.5	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6
152.5°	764.0	763.4	762.5	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2
155°	788.4	787.6	787.1	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0
157.5°	810.9	809.8	809.5	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9
160°	824.6	823.5	823.3	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3
162.5°	836.7	835.6	835.4	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5
165°	852.4	851.3	851.3	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0
167.5°	865.5	864.3	864.3	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8
170°	872.7	871.5	871.7	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5
172.5°	878.1	876.9	877.1	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9
175°	883.9	882.7	883.1	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5
177.5°	887.0	886.2	886.5	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.1	18.9	19.3	21.6	20.9	21.6	22.3	22.4	22.6	21.9	21.2
90°	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5
92.5°	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9
95°	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0
97.5°	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6
100°	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4
102.5°	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3
105°	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5
107.5°	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7
110°	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4
115°	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5
117.5°	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1
120°	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2
122.5°	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2
125°	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6
127.5°	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9
130°	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5
132.5°	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2
135°	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7
137.5°	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5
140°	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9
142.5°	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0
145°	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0
147.5°	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7
150°	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1
152.5°	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6
155°	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2
157.5°	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0
160°	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6
162.5°	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8
165°	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6
167.5°	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7
170°	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8
172.5°	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3
175°	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0
177.5°	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	21.7	21.7	21.1	21.1	21.7	21.2	21.2
90°	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331592-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)