

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331606

Luminaire Tested: **S122DIW-S1005D1240U835-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U835-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8336.8 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	62	54	52	51	42	41	39	34
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	22
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	19	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17073	17073	17073
5°	17157	16435	16373
10°	17049	15949	15770
15°	16814	15435	15136
20°	16517	14884	14525
25°	16223	14353	13970
30°	15810	13808	13414
35°	15392	13280	13021
40°	14952	12831	12629
45°	14535	12429	12294
50°	14086	12066	11964
55°	13616	11675	11627
60°	13040	11269	11271
65°	12441	10795	10850
70°	11770	10285	10393
75°	10911	9784	9973
80°	9555	9272	9549
85°	8259	8830	9217



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	1.2
10°-20°	287.3	3.4
20°-30°	435.4	5.2
30°-40°	530.3	6.4
40°-50°	570.5	6.8
50°-60°	554.1	6.6
60°-70°	483.8	5.8
70°-80°	372.4	4.5
80°-90°	256.1	3.1
90°-100°	269.6	3.2
100°-110°	428.1	5.1
110°-120°	599.9	7.2
120°-130°	726.1	8.7
130°-140°	782.4	9.4
140°-150°	751.4	9.0
150°-160°	627.4	7.5
160°-170°	416.2	5.0
170°-180°	145.5	1.7
0°-30°	822.9	9.9
0°-40°	1353.3	16.2
0°-60°	2477.9	29.7
0°-90°	3590.2	43.1
90°-120°	1297.6	15.6
90°-150°	3557.5	42.7
90°-180°	4747.0	56.9
0°-180°	8336.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1057	1057	1057	1057	1057	
5°	1060	1056	1047	1055	1054	101
15°	1012	1014	1014	1028	1027	285
25°	920	930	944	962	967	423
35°	792	819	848	880	892	495
45°	650	692	745	790	808	501
55°	498	555	633	686	708	445
65°	340	416	506	566	588	338
75°	188	275	372	436	458	199
85°	55	150	248	310	334	59
90°	17	122	248	304	326	14
95°	80	165	259	315	333	87
105°	286	337	417	471	490	303
115°	525	552	616	659	673	518
125°	758	771	814	851	864	677
135°	978	992	1010	1040	1049	756
145°	1185	1194	1202	1212	1215	740
155°	1355	1359	1363	1369	1365	623
165°	1474	1473	1473	1481	1476	416
175°	1534	1530	1527	1536	1529	146
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4
2.5°	1063.6	1062.8	1061.9	1061.1	1060.3	1058.9	1057.0	1055.1	1053.2	1051.3	1052.7
5°	1060.5	1059.5	1058.5	1057.4	1056.4	1054.9	1052.9	1050.8	1048.8	1046.7	1048.8
7.5°	1051.0	1050.3	1049.6	1049.0	1048.3	1047.2	1045.6	1044.0	1042.5	1040.9	1043.3
10°	1043.7	1043.0	1042.3	1041.6	1040.9	1040.1	1039.1	1038.0	1037.0	1036.0	1038.7
12.5°	1031.4	1031.5	1031.7	1031.8	1031.9	1031.6	1030.9	1030.1	1029.4	1028.6	1031.4
15°	1011.5	1012.2	1012.8	1013.5	1014.2	1014.5	1014.5	1014.5	1014.5	1014.5	1017.6
17.5°	985.7	987.2	988.6	990.0	991.4	992.7	993.8	994.9	996.0	997.1	1000.3
20°	968.6	970.3	972.0	973.7	975.4	976.9	978.3	979.6	981.0	982.4	986.1
22.5°	950.2	952.1	954.1	956.1	958.1	960.0	961.9	963.8	965.7	967.6	971.4
25°	919.5	921.9	924.3	926.7	929.1	931.8	934.8	937.9	941.0	944.0	948.1
27.5°	882.7	886.6	890.5	894.4	898.3	902.0	905.6	909.2	912.8	916.5	921.6
30°	858.2	862.6	867.1	871.5	875.9	880.4	884.8	889.2	893.6	898.1	903.5
32.5°	831.2	836.2	841.2	846.2	851.1	856.2	861.5	866.7	872.0	877.2	883.5
35°	792.3	798.1	803.9	809.7	815.5	821.6	828.1	834.5	841.0	847.5	855.0
37.5°	750.0	756.7	763.4	770.0	776.7	784.2	792.6	801.0	809.4	817.8	826.1
40°	721.8	729.3	736.8	744.3	751.8	760.1	769.3	778.5	787.7	796.9	805.8
42.5°	694.9	702.3	709.8	717.3	724.8	733.8	744.4	755.0	765.5	776.1	785.7
45°	649.8	659.0	668.2	677.4	686.6	697.1	709.1	721.0	732.9	744.8	755.4
47.5°	605.4	615.4	625.4	635.4	645.4	657.4	671.4	685.3	699.3	713.2	724.3
50°	574.7	585.3	595.8	606.4	616.9	629.9	645.2	660.5	675.8	691.2	702.8
52.5°	545.3	556.4	567.5	578.6	589.7	603.3	619.4	635.6	651.7	667.9	679.7
55°	498.1	510.3	522.6	534.9	547.1	562.1	579.8	597.5	615.2	632.9	645.2
57.5°	451.5	465.3	479.1	493.0	506.8	522.7	540.8	558.8	576.9	594.9	608.1
60°	418.4	433.0	447.7	462.3	477.0	494.0	513.4	532.8	552.2	571.6	584.6
62.5°	389.0	404.1	419.3	434.5	449.7	467.0	486.4	505.8	525.3	544.7	558.4
65°	340.2	356.9	373.6	390.3	407.0	425.4	445.5	465.5	485.6	505.7	519.7
67.5°	295.5	312.9	330.3	347.8	365.2	384.2	404.8	425.4	445.9	466.5	480.6
70°	263.6	281.3	299.0	316.7	334.4	353.8	375.0	396.1	417.2	438.3	452.9
72.5°	234.2	252.4	270.7	288.9	307.2	327.0	348.4	369.8	391.2	412.6	426.9
75°	188.5	207.6	226.6	245.7	264.8	285.2	307.0	328.8	350.6	372.4	387.0
77.5°	144.4	164.3	184.3	204.2	224.2	245.2	267.4	289.5	311.6	333.8	348.4
80°	114.9	135.7	156.5	177.3	198.0	219.5	241.6	263.8	285.9	308.0	322.3
82.5°	90.4	110.9	131.4	151.9	172.4	193.9	216.3	238.7	261.1	283.5	297.8
85°	55.2	76.3	97.4	118.5	139.6	161.1	182.9	204.7	226.5	248.3	262.6
87.5°	30.3	51.3	72.3	93.3	114.3	136.3	159.3	182.4	205.5	228.5	242.3
90°	16.6	39.8	63.0	86.3	109.5	135.1	163.3	191.4	219.5	247.7	260.7
92.5°	37.2	58.1	79.0	100.0	120.9	142.6	165.1	187.5	210.0	232.5	246.0
95°	79.7	98.6	117.5	136.3	155.2	175.2	196.2	217.2	238.2	259.2	272.2
97.5°	133.9	150.7	167.5	184.2	201.0	219.7	240.4	261.2	281.9	302.6	315.2
100°	175.4	190.3	205.2	220.1	235.0	252.4	272.4	292.3	312.3	332.2	344.8
102.5°	217.7	231.1	244.5	257.8	271.2	287.7	307.3	326.9	346.5	366.1	378.7
105°	286.4	297.2	307.9	318.7	329.4	343.9	362.2	380.5	398.8	417.1	429.6
107.5°	357.2	366.4	375.5	384.7	393.9	406.9	423.9	440.9	457.8	474.8	486.4
110°	401.6	410.1	418.7	427.2	435.8	448.4	465.1	481.8	498.4	515.1	526.0



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.4	458.8	466.3	473.7	481.2	492.7	508.4	524.0	539.7	555.3	565.5
115°	524.8	530.3	535.7	541.2	546.7	556.8	571.5	586.3	601.0	615.8	625.7
117.5°	596.4	601.1	605.9	610.7	615.4	624.1	636.6	649.2	661.7	674.3	683.7
120°	645.1	648.8	652.5	656.1	659.8	667.3	678.6	689.9	701.3	712.6	722.1
122.5°	689.7	693.1	696.4	699.7	703.0	710.2	721.4	732.6	743.8	755.0	763.6
125°	757.7	760.3	762.9	765.5	768.1	774.4	784.4	794.5	804.5	814.5	822.9
127.5°	825.4	828.3	831.3	834.2	837.2	842.5	850.3	858.0	865.8	873.5	880.9
130°	867.9	871.3	874.7	878.1	881.5	886.5	893.1	899.7	906.3	912.8	920.4
132.5°	915.6	918.4	921.1	923.8	926.5	930.7	936.3	941.9	947.6	953.2	959.8
135°	977.9	981.1	984.2	987.4	990.6	994.2	998.1	1002.1	1006.1	1010.1	1017.0
137.5°	1045.1	1047.6	1050.1	1052.6	1055.2	1057.6	1059.8	1062.1	1064.3	1066.5	1072.6
140°	1085.5	1087.8	1090.0	1092.3	1094.5	1096.7	1098.8	1101.0	1103.1	1105.2	1110.7
142.5°	1127.0	1129.3	1131.5	1133.8	1136.0	1137.7	1138.8	1139.9	1141.1	1142.2	1146.8
145°	1185.1	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1204.3
147.5°	1238.3	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.3
150°	1274.6	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4
152.5°	1306.8	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9
155°	1355.0	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2
157.5°	1396.2	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1
160°	1421.1	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7
162.5°	1443.9	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7
165°	1474.3	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0
167.5°	1499.7	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6
170°	1513.2	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0
172.5°	1522.5	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4
175°	1533.9	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5
177.5°	1538.6	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4
2.5°	1054.0	1055.4	1056.8	1057.2	1056.6	1056.1	1055.5	1055.0
5°	1050.8	1052.9	1054.9	1055.7	1055.4	1055.1	1054.7	1054.4
7.5°	1045.8	1048.3	1050.7	1051.8	1051.4	1051.1	1050.7	1050.4
10°	1041.4	1044.2	1046.9	1048.1	1047.7	1047.4	1047.1	1046.7
12.5°	1034.1	1036.8	1039.5	1040.7	1040.4	1040.0	1039.7	1039.4
15°	1020.7	1023.7	1026.8	1028.2	1027.8	1027.5	1027.1	1026.8
17.5°	1003.5	1006.7	1009.9	1011.5	1011.5	1011.5	1011.5	1011.5
20°	989.8	993.6	997.3	999.2	999.2	999.2	999.2	999.2
22.5°	975.1	978.9	982.6	984.8	985.3	985.9	986.4	987.0
25°	952.2	956.3	960.4	962.9	964.0	965.0	966.0	967.0
27.5°	926.8	932.0	937.2	940.1	940.9	941.6	942.4	943.1
30°	909.0	914.4	919.9	923.1	924.1	925.1	926.2	927.2
32.5°	889.8	896.0	902.3	906.3	908.2	910.0	911.9	913.7
35°	862.5	870.0	877.5	882.4	884.8	887.2	889.6	891.9
37.5°	834.4	842.7	851.0	856.4	858.9	861.5	864.0	866.5
40°	814.6	823.5	832.3	838.3	841.4	844.4	847.5	850.6
42.5°	795.4	805.1	814.8	821.1	824.2	827.3	830.3	833.4
45°	765.9	776.5	787.0	794.0	797.4	800.8	804.2	807.6
47.5°	735.3	746.3	757.4	764.8	768.5	772.3	776.0	779.8
50°	714.3	725.9	737.5	745.2	748.9	752.6	756.4	760.1
52.5°	691.6	703.4	715.3	723.2	727.2	731.3	735.3	739.3
55°	657.5	669.7	682.0	690.3	694.7	699.2	703.6	708.0
57.5°	621.4	634.6	647.8	656.6	661.1	665.6	670.1	674.6
60°	597.5	610.5	623.4	632.3	637.0	641.8	646.6	651.3
62.5°	572.2	585.9	599.7	608.8	613.3	617.8	622.3	626.8
65°	533.7	547.6	561.6	570.8	575.2	579.6	584.1	588.5
67.5°	494.7	508.8	522.9	532.3	536.9	541.5	546.2	550.8
70°	467.6	482.2	496.9	506.2	510.3	514.4	518.5	522.6
72.5°	441.3	455.7	470.0	479.7	484.6	489.5	494.4	499.3
75°	401.7	416.3	431.0	440.5	444.9	449.4	453.8	458.2
77.5°	362.9	377.5	392.1	401.8	406.5	411.3	416.1	420.8
80°	336.6	351.0	365.3	374.8	379.6	384.3	389.1	393.9
82.5°	312.1	326.4	340.7	350.1	354.6	359.1	363.6	368.1
85°	276.9	291.2	305.5	315.0	319.8	324.6	329.3	334.1
87.5°	256.1	269.9	283.7	292.8	297.2	301.6	306.0	310.4
90°	273.8	286.8	299.9	308.6	312.9	317.3	321.7	326.1
92.5°	259.4	272.9	286.4	295.2	299.3	303.4	307.6	311.7
95°	285.1	298.1	311.0	319.2	322.7	326.2	329.7	333.3
97.5°	327.8	340.4	353.0	361.3	365.2	369.2	373.1	377.1
100°	357.4	370.0	382.6	390.6	394.1	397.5	401.0	404.5
102.5°	391.3	403.8	416.4	424.4	427.8	431.3	434.8	438.2
105°	442.1	454.5	467.0	475.2	478.9	482.7	486.4	490.1
107.5°	498.1	509.8	521.5	528.5	530.9	533.4	535.8	538.2
110°	536.9	547.8	558.7	565.6	568.5	571.4	574.3	577.1



TEST NUMBER: P331606

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	575.7	585.9	596.1	602.8	605.9	609.0	612.1	615.2
115°	635.7	645.6	655.5	661.9	664.8	667.7	670.6	673.4
117.5°	693.1	702.5	711.8	717.8	720.5	723.1	725.7	728.3
120°	731.6	741.2	750.7	756.9	759.8	762.7	765.6	768.5
122.5°	772.1	780.7	789.3	794.9	797.4	800.0	802.6	805.1
125°	831.2	839.5	847.9	853.4	856.2	859.0	861.7	864.5
127.5°	888.3	895.7	903.2	907.9	910.0	912.0	914.1	916.2
130°	928.0	935.6	943.2	947.8	949.4	951.0	952.5	954.1
132.5°	966.5	973.1	979.7	984.0	985.8	987.6	989.4	991.2
135°	1023.8	1030.7	1037.5	1041.9	1043.8	1045.6	1047.5	1049.3
137.5°	1078.6	1084.7	1090.7	1094.3	1095.5	1096.6	1097.8	1098.9
140°	1116.1	1121.6	1127.0	1130.2	1131.1	1132.0	1132.9	1133.7
142.5°	1151.4	1155.9	1160.5	1163.1	1163.8	1164.4	1165.0	1165.6
145°	1206.7	1209.0	1211.3	1212.8	1213.3	1213.9	1214.4	1215.0
147.5°	1256.2	1257.1	1258.0	1258.3	1258.0	1257.8	1257.5	1257.2
150°	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1365.7	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1405.1	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1428.5	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1449.7	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1477.0	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1499.6	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1512.0	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1521.4	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1531.5	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)