

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331601-840

Luminaire Tested: **S122DIW-S1005D970U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331601-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8006.3 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	1.9
10°-20°	425.9	5.3
20°-30°	626.0	7.8
30°-40°	727.1	9.1
40°-50°	726.3	9.1
50°-60°	633.4	7.9
60°-70°	468.3	5.8
70°-80°	265.3	3.3
80°-90°	74.6	0.9
90°-100°	44.5	0.6
100°-110°	163.1	2.0
110°-120°	436.1	5.4
120°-130°	719.8	9.0
130°-140°	765.5	9.6
140°-150°	711.5	8.9
150°-160°	572.1	7.1
160°-170°	368.6	4.6
170°-180°	126.9	1.6
0°-30°	1203.2	15.0
0°-40°	1930.3	24.1
0°-60°	3290.0	41.1
0°-90°	4098.2	51.2
90°-120°	643.7	8.0
90°-150°	2840.5	35.5
90°-180°	3908.0	48.8
0°-180°	8006.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	1	11	19	24	26	6
95°	63	33	38	42	42	77
105°	293	306	59	69	73	313
115°	555	572	595	170	79	546
125°	784	797	815	822	825	699
135°	971	986	995	1004	1003	750
145°	1126	1126	1142	1148	1144	704
155°	1240	1232	1243	1248	1241	571
165°	1307	1301	1304	1310	1304	369
175°	1336	1330	1332	1338	1329	127
180°	1334	1334	1334	1334	1334	



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.5	22.4	22.3	22.2	22.1	22.0	21.8	21.6	21.4	21.2	20.6
90°	1.0	3.3	5.7	8.1	10.4	12.4	14.1	15.9	17.6	19.3	20.4
92.5°	19.5	19.3	19.1	18.9	18.7	19.0	19.8	20.7	21.5	22.4	22.9
95°	62.7	55.6	48.6	41.5	34.4	31.6	33.1	34.6	36.2	37.7	38.7
97.5°	124.5	104.5	84.6	64.6	44.7	36.5	40.0	43.4	46.9	50.4	51.2
100°	170.8	141.4	112.0	82.7	53.3	40.4	44.0	47.7	51.4	55.0	56.8
102.5°	221.8	215.5	209.3	203.1	196.8	178.5	148.0	117.5	87.1	56.6	58.8
105°	293.4	299.8	306.2	312.7	319.1	293.1	234.5	175.9	117.4	58.9	61.2
107.5°	375.0	380.2	385.4	390.5	395.8	363.2	293.1	222.8	152.6	82.4	80.0
110°	427.5	432.0	436.5	441.0	445.5	416.8	354.8	292.9	230.9	168.8	147.4



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	476.9	480.9	484.8	488.9	492.8	487.2	471.9	456.6	441.2	426.0	347.7
115°	554.8	558.5	562.2	565.8	569.5	573.9	579.3	584.6	590.1	595.4	496.0
117.5°	624.5	628.6	632.7	636.7	640.9	644.7	648.4	652.1	655.8	659.4	635.4
120°	675.5	678.7	681.9	685.1	688.3	691.9	695.7	699.6	703.5	707.3	709.9
122.5°	718.7	722.1	725.5	728.8	732.3	736.1	740.2	744.5	748.6	752.9	754.4
125°	784.5	787.3	790.1	792.8	795.7	799.1	803.1	807.3	811.3	815.4	816.9
127.5°	844.1	847.3	850.3	853.4	856.5	859.6	862.6	865.7	868.7	871.7	873.9
130°	882.0	885.4	888.9	892.2	895.6	898.6	900.9	903.3	905.6	908.1	910.4
132.5°	920.6	923.5	926.5	929.3	932.2	934.8	937.3	939.6	941.9	944.3	946.3
135°	970.8	974.2	977.7	981.1	984.5	987.1	989.1	991.0	992.9	994.9	997.0
137.5°	1021.5	1023.9	1026.3	1028.7	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3
140°	1054.7	1056.4	1058.1	1059.9	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0
142.5°	1082.5	1084.0	1085.6	1087.1	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4
145°	1126.1	1125.9	1125.7	1125.5	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1
147.5°	1164.2	1163.3	1162.5	1161.6	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8
150°	1188.8	1187.3	1185.8	1184.4	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8
152.5°	1209.7	1208.0	1206.3	1204.7	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1
155°	1240.0	1238.0	1236.1	1234.2	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2
157.5°	1263.7	1262.1	1260.4	1258.8	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0
160°	1277.6	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9
162.5°	1290.0	1288.7	1287.4	1286.1	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6
165°	1306.6	1305.3	1303.9	1302.7	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1
167.5°	1318.9	1317.6	1316.4	1315.0	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3
170°	1325.9	1324.5	1323.3	1322.0	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5
172.5°	1330.5	1329.2	1327.9	1326.7	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2
175°	1336.5	1334.9	1333.4	1332.0	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1
177.5°	1337.5	1336.3	1335.0	1333.8	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	20.0	19.4	18.8	18.4	18.2	18.0	17.8	17.6
90°	21.4	22.5	23.6	24.3	24.7	25.1	25.7	26.1
92.5°	23.5	24.0	24.6	25.0	25.2	25.5	25.8	26.1
95°	39.8	40.9	41.9	42.3	42.1	41.9	41.7	41.5
97.5°	52.1	52.9	53.8	54.3	54.6	54.8	55.1	55.3
100°	58.5	60.2	61.9	62.9	63.3	63.8	64.2	64.6
102.5°	61.0	63.2	65.4	66.9	67.5	68.1	68.7	69.3
105°	63.6	65.9	68.3	69.9	70.8	71.6	72.5	73.3
107.5°	77.6	75.2	72.8	72.0	72.9	73.7	74.6	75.4
110°	125.9	104.5	83.1	72.8	73.6	74.5	75.3	76.2



TEST NUMBER: P331601-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.4	191.3	113.0	74.2	74.9	75.6	76.3	77.1
115°	396.8	297.5	198.2	140.9	125.4	110.0	94.5	79.2
117.5°	611.4	587.4	563.4	526.0	475.2	424.5	373.9	323.1
120°	712.5	715.0	717.6	704.4	675.5	646.5	617.5	588.7
122.5°	756.0	757.5	759.0	757.0	751.3	745.8	740.1	734.6
125°	818.4	819.9	821.4	822.4	823.1	823.7	824.4	825.1
127.5°	876.2	878.3	880.5	881.6	881.8	881.9	882.0	882.1
130°	912.7	915.1	917.5	918.6	918.3	918.1	917.9	917.7
132.5°	948.4	950.4	952.4	953.3	953.0	952.8	952.6	952.4
135°	999.2	1001.3	1003.4	1004.3	1003.9	1003.4	1003.0	1002.6
137.5°	1046.3	1048.4	1050.6	1051.3	1050.6	1049.8	1049.0	1048.3
140°	1076.9	1078.8	1080.8	1081.2	1080.2	1079.0	1077.9	1076.9
142.5°	1105.1	1106.9	1108.6	1108.9	1107.9	1106.8	1105.8	1104.7
145°	1144.6	1146.1	1147.5	1147.8	1146.7	1145.6	1144.6	1143.5
147.5°	1178.9	1180.0	1181.1	1181.2	1180.3	1179.4	1178.5	1177.6
150°	1200.1	1201.3	1202.6	1202.7	1201.7	1200.6	1199.5	1198.5
152.5°	1219.4	1220.6	1221.9	1221.9	1220.5	1219.1	1217.7	1216.3
155°	1245.5	1246.7	1248.0	1247.8	1246.1	1244.4	1242.6	1240.9
157.5°	1267.4	1268.9	1270.3	1270.2	1268.5	1266.9	1265.2	1263.5
160°	1280.2	1281.4	1282.7	1282.6	1281.1	1279.6	1278.2	1276.7
162.5°	1292.1	1293.5	1295.1	1294.8	1292.9	1291.1	1289.3	1287.5
165°	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6
167.5°	1318.8	1320.3	1321.8	1321.6	1319.7	1317.8	1315.9	1313.9
170°	1325.0	1326.5	1328.0	1327.8	1325.9	1323.9	1322.0	1320.1
172.5°	1329.6	1331.1	1332.6	1332.4	1330.5	1328.6	1326.7	1324.7
175°	1334.6	1336.2	1337.7	1337.4	1335.1	1333.0	1330.9	1328.8
177.5°	1335.2	1336.4	1337.6	1337.5	1335.8	1334.3	1332.8	1331.3
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5

(END OF REPORT)