

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331609

Luminaire Tested: **S122DIW-S1005D1440U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331609  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1440U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10164.2 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43																				
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37																				
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																				
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24																				
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21																				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																				
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18	15																				
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.9	1.9
10°-20°	552.1	5.4
20°-30°	801.2	7.9
30°-40°	845.5	8.3
40°-50°	748.6	7.4
50°-60°	597.4	5.9
60°-70°	406.1	4.0
70°-80°	208.2	2.0
80°-90°	55.0	0.5
90°-100°	65.6	0.6
100°-110°	240.4	2.4
110°-120°	642.7	6.3
120°-130°	1060.9	10.4
130°-140°	1128.3	11.1
140°-150°	1048.7	10.3
150°-160°	843.1	8.3
160°-170°	543.3	5.3
170°-180°	187.0	1.8
0°-30°	1543.2	15.2
0°-40°	2388.7	23.5
0°-60°	3734.8	36.7
0°-90°	4404.1	43.3
90°-120°	948.7	9.3
90°-150°	4186.6	41.2
90°-180°	5760.0	56.7
0°-180°	10164.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	46
90°	38	1	38	1	38	19
95°	61	92	61	92	61	57
105°	108	432	108	432	108	112
115°	117	818	117	818	117	292
125°	1216	1156	1216	1156	1216	1052
135°	1478	1431	1478	1431	1478	1139
145°	1685	1660	1685	1660	1685	1054
155°	1829	1828	1829	1828	1829	844
165°	1921	1926	1921	1926	1921	542
175°	1958	1970	1958	1970	1958	187
180°	1966	1966	1966	1966	1966	



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	23.6	23.5	24.0	23.2	23.1	23.5	23.2	22.3	22.6	22.9	23.0
90°	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6	30.0	28.4	25.9
92.5°	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6	33.8	33.0	31.7
95°	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6	57.0	55.5	53.3
97.5°	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8	75.5	74.2	69.1
100°	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1	83.6	81.1	75.7
102.5°	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9	86.6	83.3	128.3
105°	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7	90.2	86.8	173.0
107.5°	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4	117.9	121.5	224.9
110°	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7	217.3	248.9	340.2



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2	512.5	627.8	650.3
115°	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9	731.2	877.5	869.6
117.5°	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2	936.6	972.0	966.5
120°	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1	1046.3	1042.5	1036.8
122.5°	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2	1111.9	1109.6	1103.4
125°	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2	1204.0	1201.8	1195.8
127.5°	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3	1288.1	1284.9	1280.4
130°	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3	1341.8	1338.3	1334.8
132.5°	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7	1394.8	1391.8	1388.3
135°	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6	1469.5	1466.3	1463.5
137.5°	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2	1539.1	1536.0	1532.8
140°	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2	1584.4	1581.5	1578.1
142.5°	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8	1626.2	1623.6	1619.6
145°	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9	1684.7	1682.5	1677.1
147.5°	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6	1735.9	1734.3	1729.0
150°	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8	1766.9	1765.0	1759.9
152.5°	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2	1795.3	1793.4	1788.6
155°	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6	1833.7	1831.8	1828.1
157.5°	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0	1865.9	1863.7	1861.0
160°	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8	1884.9	1883.0	1881.1
162.5°	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4	1902.3	1900.1	1898.5
165°	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4	1920.5
167.5°	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8	1941.6	1939.4	1938.5
170°	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9	1950.7	1948.5	1947.8
172.5°	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7	1957.5	1955.3	1954.7
175°	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1	1964.9	1962.7	1962.1
177.5°	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9	1966.2	1964.4	1964.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	23.1	22.6	22.1	22.7	20.1	19.5	16.3	13.8	13.9	13.9	13.4
90°	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4	4.9	8.4	11.9
92.5°	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7	28.4	28.1	27.8
95°	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4	82.0	71.6	61.2
97.5°	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5	154.1	124.7	95.3
100°	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7	208.4	165.1	121.8
102.5°	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8	317.7	308.5	299.3
105°	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4	441.8	451.3	460.8
107.5°	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7	560.3	568.0	575.6
110°	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1	636.7	643.3	650.0





TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9	708.7	714.6	720.5
115°	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8	823.2	828.5	833.9
117.5°	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5	926.5	932.5	938.5
120°	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6	1000.3	1005.0	1009.8
122.5°	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3	1064.3	1069.3	1074.3
125°	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3	1160.4	1164.5	1168.6
127.5°	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2	1248.7	1253.3	1257.8
130°	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9	1305.0	1310.0	1315.1
132.5°	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8	1361.1	1365.4	1369.7
135°	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8	1435.8	1440.9	1445.9
137.5°	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6	1509.1	1512.7	1516.2
140°	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5	1557.0	1559.6	1562.1
142.5°	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5	1597.7	1600.0	1602.3
145°	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8	1659.4	1659.1	1658.8
147.5°	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8	1714.6	1713.4	1712.2
150°	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2	1750.0	1747.8	1745.6
152.5°	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9	1780.5	1778.0	1775.5
155°	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6	1824.7	1821.9	1819.0
157.5°	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6	1860.2	1857.8	1855.4
160°	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1881.1	1879.3	1877.4
162.5°	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2	1899.4	1897.5	1895.6
165°	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7	1923.8	1921.9	1920.0
167.5°	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9	1942.0	1940.1	1938.2
170°	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2	1952.3	1950.4	1948.5
172.5°	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0	1959.1	1957.2	1955.3
175°	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8	1967.6	1965.4	1963.2
177.5°	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2	1969.5	1967.7	1965.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	13.5	13.5	13.4	13.9	13.8	13.7	13.4	13.7	14.0	13.1	13.3
90°	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6	33.2	34.8	35.9
92.5°	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6	35.5	36.3	36.9
95°	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6	60.2	61.8	62.4
97.5°	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8	78.0	79.3	80.1
100°	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1	88.7	91.2	92.8
102.5°	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9	93.2	96.5	98.6
105°	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7	97.2	100.7	103.0
107.5°	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4	110.8	107.3	106.2
110°	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7	154.1	122.5	107.3



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2	281.9	166.6	109.4
115°	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9	438.5	292.2	207.6
117.5°	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2	865.8	830.4	775.3
120°	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1	1053.9	1057.7	1038.2
122.5°	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2	1116.5	1118.7	1115.7
125°	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2	1208.4	1210.6	1212.2
127.5°	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3	1294.5	1297.7	1299.5
130°	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3	1348.8	1352.2	1353.8
132.5°	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7	1400.7	1403.7	1405.0
135°	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6	1475.8	1479.0	1480.2
137.5°	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2	1545.3	1548.4	1549.4
140°	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2	1590.1	1592.9	1593.5
142.5°	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8	1631.4	1634.0	1634.5
145°	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9	1689.1	1691.4	1691.7
147.5°	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6	1739.2	1740.9	1741.0
150°	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8	1770.7	1772.6	1772.7
152.5°	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2	1799.1	1801.0	1800.9
155°	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6	1837.5	1839.4	1839.1
157.5°	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0	1870.1	1872.3	1872.1
160°	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8	1888.7	1890.6	1890.5
162.5°	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4	1906.6	1908.7	1908.4
165°	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3
167.5°	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8	1946.0	1948.2	1947.9
170°	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9	1955.1	1957.3	1957.0
172.5°	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7	1961.9	1964.1	1963.8
175°	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1	1969.3	1971.5	1971.1
177.5°	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9	1969.7	1971.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	13.4	12.9	13.1	12.6	13.1	12.9	13.4	13.3	13.1	14.0	13.7
90°	36.5	37.1	37.8	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6
92.5°	37.3	37.6	38.0	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6
95°	62.1	61.8	61.5	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6
97.5°	80.5	80.9	81.3	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8
100°	93.4	94.0	94.7	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1
102.5°	99.5	100.3	101.2	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9
105°	104.3	105.6	106.8	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7
107.5°	107.4	108.7	110.0	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4
110°	108.6	109.8	111.1	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	110.5	111.5	112.5	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2
115°	184.9	162.1	139.4	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9
117.5°	700.5	625.7	550.9	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2
120°	995.6	952.9	910.2	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1
122.5°	1107.4	1099.2	1090.9	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2
125°	1213.2	1214.1	1215.1	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2
127.5°	1299.6	1299.8	1300.0	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3
130°	1353.5	1353.2	1352.9	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3
132.5°	1404.7	1404.4	1404.1	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7
135°	1479.6	1479.0	1478.3	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6
137.5°	1548.3	1547.3	1546.2	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2
140°	1592.0	1590.4	1588.8	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2
142.5°	1632.9	1631.3	1629.8	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8
145°	1690.1	1688.5	1686.9	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9
147.5°	1739.7	1738.4	1737.0	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6
150°	1771.2	1769.6	1768.0	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8
152.5°	1798.8	1796.8	1794.7	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2
155°	1836.6	1834.1	1831.5	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6
157.5°	1869.7	1867.2	1864.7	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0
160°	1888.3	1886.0	1883.8	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8
162.5°	1905.7	1903.0	1900.3	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4
165°	1928.1	1925.9	1923.7	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9
167.5°	1945.1	1942.2	1939.4	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8
170°	1954.2	1951.3	1948.5	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9
172.5°	1961.0	1958.1	1955.3	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7
175°	1967.9	1964.7	1961.6	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1
177.5°	1968.9	1966.7	1964.4	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	13.4	13.7	13.8	13.9	13.4	13.5	13.5	13.4	13.9	13.9	13.8
90°	30.0	28.4	25.9	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4
92.5°	33.8	33.0	31.7	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7
95°	57.0	55.5	53.3	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4
97.5°	75.5	74.2	69.1	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5
100°	83.6	81.1	75.7	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7
102.5°	86.6	83.3	128.3	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8
105°	90.2	86.8	173.0	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4
107.5°	117.9	121.5	224.9	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7
110°	217.3	248.9	340.2	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	512.5	627.8	650.3	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9
115°	731.2	877.5	869.6	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8
117.5°	936.6	972.0	966.5	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5
120°	1046.3	1042.5	1036.8	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6
122.5°	1111.9	1109.6	1103.4	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3
125°	1204.0	1201.8	1195.8	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3
127.5°	1288.1	1284.9	1280.4	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2
130°	1341.8	1338.3	1334.8	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9
132.5°	1394.8	1391.8	1388.3	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8
135°	1469.5	1466.3	1463.5	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8
137.5°	1539.1	1536.0	1532.8	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6
140°	1584.4	1581.5	1578.1	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5
142.5°	1626.2	1623.6	1619.6	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5
145°	1684.7	1682.5	1677.1	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8
147.5°	1735.9	1734.3	1729.0	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8
150°	1766.9	1765.0	1759.9	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2
152.5°	1795.3	1793.4	1788.6	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9
155°	1833.7	1831.8	1828.1	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6
157.5°	1865.9	1863.7	1861.0	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6
160°	1884.9	1883.0	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0
162.5°	1902.3	1900.1	1898.5	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2
165°	1923.7	1921.4	1920.5	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7
167.5°	1941.6	1939.4	1938.5	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9
170°	1950.7	1948.5	1947.8	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2
172.5°	1957.5	1955.3	1954.7	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0
175°	1964.9	1962.7	1962.1	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8
177.5°	1966.2	1964.4	1964.1	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	16.3	19.5	20.1	22.7	22.1	22.6	23.1	23.0	22.9	22.6	22.3
90°	4.9	8.4	11.9	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6
92.5°	28.4	28.1	27.8	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6
95°	82.0	71.6	61.2	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6
97.5°	154.1	124.7	95.3	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8
100°	208.4	165.1	121.8	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1
102.5°	317.7	308.5	299.3	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9
105°	441.8	451.3	460.8	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7
107.5°	560.3	568.0	575.6	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4
110°	636.7	643.3	650.0	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7





TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	708.7	714.6	720.5	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2
115°	823.2	828.5	833.9	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9
117.5°	926.5	932.5	938.5	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2
120°	1000.3	1005.0	1009.8	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1
122.5°	1064.3	1069.3	1074.3	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2
125°	1160.4	1164.5	1168.6	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2
127.5°	1248.7	1253.3	1257.8	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3
130°	1305.0	1310.0	1315.1	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3
132.5°	1361.1	1365.4	1369.7	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7
135°	1435.8	1440.9	1445.9	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6
137.5°	1509.1	1512.7	1516.2	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2
140°	1557.0	1559.6	1562.1	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2
142.5°	1597.7	1600.0	1602.3	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8
145°	1659.4	1659.1	1658.8	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9
147.5°	1714.6	1713.4	1712.2	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6
150°	1750.0	1747.8	1745.6	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8
152.5°	1780.5	1778.0	1775.5	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2
155°	1824.7	1821.9	1819.0	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6
157.5°	1860.2	1857.8	1855.4	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0
160°	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8
162.5°	1899.4	1897.5	1895.6	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4
165°	1923.8	1921.9	1920.0	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9
167.5°	1942.0	1940.1	1938.2	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8
170°	1952.3	1950.4	1948.5	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9
172.5°	1959.1	1957.2	1955.3	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7
175°	1967.6	1965.4	1963.2	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1
177.5°	1969.5	1967.7	1965.9	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	23.2	23.5	23.1	23.2	24.0	23.5	23.6
90°	33.2	34.8	35.9	36.5	37.1	37.8	38.4
92.5°	35.5	36.3	36.9	37.3	37.6	38.0	38.4
95°	60.2	61.8	62.4	62.1	61.8	61.5	61.2
97.5°	78.0	79.3	80.1	80.5	80.9	81.3	81.6
100°	88.7	91.2	92.8	93.4	94.0	94.7	95.3
102.5°	93.2	96.5	98.6	99.5	100.3	101.2	102.1
105°	97.2	100.7	103.0	104.3	105.6	106.8	108.1
107.5°	110.8	107.3	106.2	107.4	108.7	110.0	111.2
110°	154.1	122.5	107.3	108.6	109.8	111.1	112.4



TEST NUMBER: P331609

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	281.9	166.6	109.4	110.5	111.5	112.5	113.5
115°	438.5	292.2	207.6	184.9	162.1	139.4	116.6
117.5°	865.8	830.4	775.3	700.5	625.7	550.9	476.2
120°	1053.9	1057.7	1038.2	995.6	952.9	910.2	867.6
122.5°	1116.5	1118.7	1115.7	1107.4	1099.2	1090.9	1082.6
125°	1208.4	1210.6	1212.2	1213.2	1214.1	1215.1	1216.0
127.5°	1294.5	1297.7	1299.5	1299.6	1299.8	1300.0	1300.2
130°	1348.8	1352.2	1353.8	1353.5	1353.2	1352.9	1352.5
132.5°	1400.7	1403.7	1405.0	1404.7	1404.4	1404.1	1403.7
135°	1475.8	1479.0	1480.2	1479.6	1479.0	1478.3	1477.7
137.5°	1545.3	1548.4	1549.4	1548.3	1547.3	1546.2	1545.1
140°	1590.1	1592.9	1593.5	1592.0	1590.4	1588.8	1587.2
142.5°	1631.4	1634.0	1634.5	1632.9	1631.3	1629.8	1628.2
145°	1689.1	1691.4	1691.7	1690.1	1688.5	1686.9	1685.4
147.5°	1739.2	1740.9	1741.0	1739.7	1738.4	1737.0	1735.7
150°	1770.7	1772.6	1772.7	1771.2	1769.6	1768.0	1766.4
152.5°	1799.1	1801.0	1800.9	1798.8	1796.8	1794.7	1792.6
155°	1837.5	1839.4	1839.1	1836.6	1834.1	1831.5	1829.0
157.5°	1870.1	1872.3	1872.1	1869.7	1867.2	1864.7	1862.3
160°	1888.7	1890.6	1890.5	1888.3	1886.0	1883.8	1881.6
162.5°	1906.6	1908.7	1908.4	1905.7	1903.0	1900.3	1897.6
165°	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4
167.5°	1946.0	1948.2	1947.9	1945.1	1942.2	1939.4	1936.5
170°	1955.1	1957.3	1957.0	1954.2	1951.3	1948.5	1945.6
172.5°	1961.9	1964.1	1963.8	1961.0	1958.1	1955.3	1952.4
175°	1969.3	1971.5	1971.1	1967.9	1964.7	1961.6	1958.4
177.5°	1969.7	1971.5	1971.2	1968.9	1966.7	1964.4	1962.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5

(END OF REPORT)