

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331469-840

Luminaire Tested: **S122DIW-S290D435U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331469-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D435U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2963.4 lumens  
Efficiency: N/A  
Efficacy: 128.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	42	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7703	7703	7703
5°	7733	7621	7666
10°	7688	7543	7581
15°	7590	7447	7438
20°	7455	7301	7290
25°	7322	7119	7119
30°	7150	6952	6893
35°	6991	6753	6654
40°	6787	6555	6431
45°	6588	6357	6202
50°	6373	6154	5935
55°	6145	5917	5695
60°	5896	5628	5422
65°	5624	5349	5100
70°	5282	4999	4763
75°	4810	4604	4492
80°	4258	4138	3924
85°	3483	3316	2983



TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.9	1.5
10°-20°	126.2	4.3
20°-30°	185.5	6.3
30°-40°	215.5	7.3
40°-50°	215.3	7.3
50°-60°	187.7	6.3
60°-70°	138.8	4.7
70°-80°	78.6	2.7
80°-90°	22.6	0.8
90°-100°	19.9	0.7
100°-110°	73.0	2.5
110°-120°	195.0	6.6
120°-130°	322.0	10.9
130°-140°	342.4	11.6
140°-150°	318.3	10.7
150°-160°	255.9	8.6
160°-170°	164.9	5.6
170°-180°	56.8	1.9
0°-30°	356.6	12.0
0°-40°	572.2	19.3
0°-60°	975.2	32.9
0°-90°	1215.3	41.0
90°-120°	287.9	9.7
90°-150°	1270.6	42.9
90°-180°	1748.0	59.0
0°-180°	2963.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	477	477	477	477	477	
5°	477	475	470	474	473	45
15°	454	451	446	447	445	128
25°	411	407	400	400	400	189
35°	355	350	343	340	338	221
45°	288	285	278	274	272	223
55°	218	215	210	205	202	195
65°	147	144	140	136	134	146
75°	77	76	74	71	72	82
85°	19	18	18	17	16	22
90°	0	5	9	11	12	2
95°	28	15	17	19	19	34
105°	131	137	26	31	33	140
115°	248	256	266	76	35	244
125°	351	357	365	368	369	313
135°	434	441	445	449	448	335
145°	504	504	511	513	512	315
155°	555	551	556	558	555	255
165°	584	582	583	586	583	165
175°	598	595	596	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	479.3	478.9	478.5	478.1	477.7	477.1	476.2	475.2	474.3	473.4	474.2
5°	477.1	476.7	476.3	475.8	475.4	474.7	473.6	472.5	471.3	470.2	471.0
7.5°	472.9	472.2	471.6	471.0	470.4	469.5	468.4	467.2	466.1	464.9	465.7
10°	468.9	468.2	467.5	466.8	466.0	465.0	463.8	462.6	461.4	460.1	460.9
12.5°	463.3	462.7	462.1	461.4	460.8	459.9	458.7	457.5	456.3	455.0	455.6
15°	454.1	453.5	452.9	452.3	451.7	450.8	449.4	448.1	446.8	445.5	445.9
17.5°	442.4	441.8	441.2	440.6	440.0	439.0	437.7	436.3	434.9	433.6	434.0
20°	433.9	433.3	432.7	432.1	431.5	430.5	429.1	427.7	426.3	424.9	425.2
22.5°	425.6	424.6	423.8	422.9	422.1	421.0	419.7	418.3	417.0	415.7	415.7
25°	411.0	410.2	409.4	408.6	407.8	406.5	404.8	403.0	401.3	399.6	399.8
27.5°	394.6	393.8	393.0	392.3	391.6	390.5	389.2	387.8	386.5	385.1	384.8
30°	383.5	382.7	381.9	381.1	380.2	379.1	377.6	376.1	374.5	372.9	372.6
32.5°	371.7	371.1	370.5	369.8	369.2	368.0	366.4	364.9	363.2	361.6	361.0
35°	354.7	353.6	352.5	351.5	350.5	349.2	347.6	346.0	344.4	342.6	342.0
37.5°	335.3	334.4	333.5	332.5	331.6	330.4	328.8	327.2	325.5	323.9	323.2
40°	322.0	321.2	320.4	319.6	318.8	317.6	315.9	314.3	312.7	311.0	310.1
42.5°	309.2	308.4	307.6	306.8	306.0	304.7	303.1	301.4	299.8	298.2	297.2
45°	288.5	287.8	287.1	286.4	285.7	284.6	283.1	281.6	280.0	278.4	277.3
47.5°	268.0	267.3	266.7	266.0	265.3	264.2	262.6	261.1	259.4	257.8	256.6
50°	253.7	253.2	252.7	252.2	251.7	250.6	249.2	247.8	246.4	245.0	243.6
52.5°	239.7	239.0	238.4	237.7	237.0	236.0	234.7	233.4	232.0	230.7	229.4
55°	218.3	217.7	217.1	216.5	215.9	215.0	213.8	212.6	211.4	210.2	208.8
57.5°	196.9	196.4	195.9	195.4	194.9	194.0	192.7	191.4	190.0	188.6	187.4
60°	182.6	182.2	181.8	181.4	181.0	180.1	178.6	177.2	175.7	174.3	173.2
62.5°	168.6	167.9	167.3	166.7	166.0	165.1	164.0	163.0	161.9	160.8	159.7
65°	147.2	146.6	146.0	145.4	144.8	144.0	143.0	142.0	141.0	140.0	139.0
67.5°	125.5	125.0	124.5	124.0	123.6	122.9	121.9	121.0	120.1	119.2	118.5
70°	111.9	111.5	111.1	110.7	110.3	109.7	108.8	107.9	106.8	105.9	105.2
72.5°	98.0	97.6	97.1	96.7	96.3	95.8	95.2	94.7	94.1	93.5	92.8
75°	77.1	76.9	76.6	76.4	76.2	75.9	75.4	74.8	74.3	73.8	73.2
77.5°	58.4	58.0	57.7	57.4	57.0	56.7	56.5	56.2	56.0	55.8	55.5
80°	45.8	45.7	45.6	45.5	45.4	45.3	45.1	44.9	44.7	44.5	44.2
82.5°	34.1	34.1	34.1	34.0	34.0	33.9	33.8	33.7	33.6	33.5	33.1
85°	18.8	18.7	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.6
87.5°	6.7	6.8	6.8	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.8
90°	0.4	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1
92.5°	8.7	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3
95°	28.1	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3
97.5°	55.6	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9
100°	76.4	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3
102.5°	99.2	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3
105°	131.2	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4
107.5°	167.7	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7
110°	191.2	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9



TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.3	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5
115°	248.2	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9
117.5°	279.3	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3
120°	302.2	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5
122.5°	321.4	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5
125°	350.9	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4
127.5°	377.6	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9
130°	394.6	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2
132.5°	411.8	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3
135°	434.2	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0
137.5°	457.0	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1
140°	471.8	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8
142.5°	484.2	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5
145°	503.7	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3
147.5°	520.7	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8
150°	531.8	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2
152.5°	541.1	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8
155°	554.6	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5
157.5°	565.2	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2
160°	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1
162.5°	577.0	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3
165°	584.4	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8
167.5°	590.0	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3
170°	593.1	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0
172.5°	595.1	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1
175°	597.8	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3
177.5°	598.2	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	475.0	475.8	476.7	477.1	476.9	476.7	476.6	476.4
5°	471.9	472.7	473.5	473.8	473.6	473.4	473.2	473.0
7.5°	466.6	467.4	468.2	468.5	468.3	468.0	467.8	467.6
10°	461.8	462.6	463.4	463.6	463.3	463.0	462.7	462.4
12.5°	456.2	456.7	457.3	457.5	457.3	457.0	456.8	456.6
15°	446.3	446.7	447.1	447.1	446.6	446.1	445.6	445.0
17.5°	434.5	435.0	435.5	435.5	434.9	434.5	434.0	433.5
20°	425.5	425.8	426.1	426.0	425.6	425.2	424.7	424.3
22.5°	415.8	415.9	415.9	415.8	415.6	415.3	415.1	414.9
25°	400.0	400.2	400.4	400.4	400.2	400.0	399.8	399.6
27.5°	384.5	384.2	383.8	383.4	382.9	382.4	382.0	381.5
30°	372.3	372.0	371.7	371.4	371.0	370.6	370.2	369.7
32.5°	360.5	359.9	359.4	358.9	358.5	358.1	357.7	357.3
35°	341.4	340.8	340.2	339.7	339.2	338.7	338.2	337.6
37.5°	322.3	321.6	320.8	320.2	319.7	319.2	318.8	318.3
40°	309.2	308.3	307.4	306.7	306.3	305.9	305.5	305.1
42.5°	296.2	295.2	294.2	293.4	292.9	292.3	291.8	291.1
45°	276.2	275.1	274.0	273.2	272.8	272.4	272.0	271.6
47.5°	255.5	254.3	253.1	252.2	251.7	251.1	250.4	249.8
50°	242.2	240.7	239.2	238.3	237.8	237.3	236.8	236.3
52.5°	228.3	227.1	225.9	225.0	224.3	223.7	223.0	222.3
55°	207.6	206.4	205.2	204.4	203.9	203.3	202.8	202.3
57.5°	186.2	185.0	183.8	183.0	182.7	182.3	181.9	181.5
60°	172.1	171.0	169.9	169.2	168.8	168.5	168.2	167.9
62.5°	158.6	157.6	156.6	155.9	155.5	155.1	154.7	154.3
65°	138.0	137.1	136.2	135.5	135.0	134.5	134.0	133.5
67.5°	117.8	117.0	116.3	115.7	115.3	114.9	114.5	114.1
70°	104.5	103.8	103.1	102.6	102.2	101.7	101.3	100.9
72.5°	92.1	91.4	90.7	90.1	89.8	89.5	89.2	88.8
75°	72.6	72.0	71.4	71.2	71.4	71.6	71.8	72.0
77.5°	55.2	54.9	54.6	54.3	54.0	53.8	53.5	53.2
80°	43.9	43.6	43.3	43.0	42.8	42.6	42.4	42.2
82.5°	32.7	32.3	31.9	31.7	31.7	31.6	31.6	31.6
85°	17.3	17.0	16.7	16.5	16.4	16.3	16.2	16.1
87.5°	6.6	6.5	6.3	6.2	6.2	6.1	6.1	6.0
90°	9.6	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.5	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	17.8	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.3	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.2	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	27.3	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	28.5	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	34.7	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	56.4	46.8	37.2	32.5	32.9	33.3	33.7	34.1





TEST NUMBER: P331469-840

CATALOG NUMBER: S122DIW-S290D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	120.6	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	177.5	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	273.5	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	318.7	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.1	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.1	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	391.9	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	408.3	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	424.2	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.0	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	468.1	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	481.7	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	494.3	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.0	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.4	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	536.8	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	545.4	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.1	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	566.9	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	572.6	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	577.9	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.0	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	592.7	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	594.7	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.0	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.2	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)