

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331589

Luminaire Tested: **S122DIW-S1005D435U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331589  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D435U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5787.4 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	2.6
10°-20°	421.7	7.3
20°-30°	619.8	10.7
30°-40°	720.0	12.4
40°-50°	719.2	12.4
50°-60°	627.2	10.8
60°-70°	463.8	8.0
70°-80°	262.7	4.5
80°-90°	72.1	1.2
90°-100°	19.7	0.3
100°-110°	72.3	1.2
110°-120°	193.1	3.3
120°-130°	318.8	5.5
130°-140°	339.1	5.9
140°-150°	315.2	5.4
150°-160°	253.4	4.4
160°-170°	163.3	2.8
170°-180°	56.2	1.0
0°-30°	1191.4	20.6
0°-40°	1911.4	33.0
0°-60°	3257.9	56.3
0°-90°	4056.4	70.1
90°-120°	285.1	4.9
90°-150°	1258.2	21.7
90°-180°	1731.0	29.9
0°-180°	5787.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	0	5	8	11	12	4
95°	28	15	17	19	18	34
105°	130	136	26	31	32	139
115°	246	253	264	75	35	242
125°	348	353	361	364	365	310
135°	430	437	441	445	444	332
145°	499	499	506	508	506	312
155°	549	546	550	553	550	253
165°	579	576	577	580	577	163
175°	592	589	590	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.2	21.8	21.5	21.1	20.8	20.4	20.1	19.7	19.3	18.9	18.2
90°	0.4	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2
95°	27.8	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1
97.5°	55.1	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7
100°	75.7	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1
102.5°	98.2	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0
105°	129.9	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1
107.5°	166.1	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4
110°	189.3	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3



TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0
115°	245.8	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7
117.5°	276.6	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5
120°	299.2	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4
122.5°	318.3	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2
125°	347.5	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8
127.5°	373.9	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1
130°	390.7	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2
132.5°	407.8	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2
135°	430.0	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6
137.5°	452.5	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5
140°	467.2	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1
142.5°	479.5	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7
145°	498.8	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3
147.5°	515.6	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7
150°	526.6	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0
152.5°	535.8	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5
155°	549.2	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1
157.5°	559.7	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7
160°	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5
162.5°	571.4	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7
165°	578.7	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1
167.5°	584.2	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5
170°	587.3	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2
172.5°	589.3	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3
175°	592.0	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5
177.5°	592.4	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	17.4	16.7	16.0	15.5	15.3	15.0	14.8	14.6
90°	9.5	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	17.6	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.1	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	25.9	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	27.0	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	28.2	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	34.4	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	55.8	46.3	36.8	32.2	32.6	33.0	33.4	33.8





TEST NUMBER: P331589

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	119.4	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	175.8	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	270.8	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	315.6	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	334.8	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	362.5	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	388.1	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	404.3	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.1	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	442.6	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	463.5	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.0	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	489.5	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.0	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.2	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	531.6	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.1	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	551.7	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	561.4	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.0	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	572.3	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.2	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	586.9	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	588.9	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.2	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.4	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)