

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331513-840

Luminaire Tested: **S122DIW-S485D1240U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331513-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7172.3 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.3
10°-20°	271.7	3.8
20°-30°	394.3	5.5
30°-40°	416.1	5.8
40°-50°	368.4	5.1
50°-60°	294.0	4.1
60°-70°	199.8	2.8
70°-80°	102.5	1.4
80°-90°	28.9	0.4
90°-100°	56.9	0.8
100°-110°	208.8	2.9
110°-120°	558.2	7.8
120°-130°	921.5	12.8
130°-140°	980.0	13.7
140°-150°	910.9	12.7
150°-160°	732.3	10.2
160°-170°	471.9	6.6
170°-180°	162.4	2.3
0°-30°	759.5	10.6
0°-40°	1175.6	16.4
0°-60°	1838.0	25.6
0°-90°	2169.2	30.2
90°-120°	824.0	11.5
90°-150°	3636.4	50.7
90°-180°	5003.0	69.8
0°-180°	7172.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	33	1	33	1	33	16
95°	53	80	53	80	53	50
105°	94	376	94	376	94	98
115°	101	710	101	710	101	254
125°	1056	1004	1056	1004	1056	914
135°	1284	1243	1284	1243	1284	989
145°	1464	1442	1464	1442	1464	915
155°	1589	1587	1589	1587	1589	733
165°	1669	1673	1669	1673	1669	471
175°	1701	1711	1701	1711	1701	162
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	14.5	14.4	14.6	14.1	14.0	14.1	13.9	13.3	13.3	13.4	13.2
90°	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5	26.1	24.7	22.5
92.5°	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1	29.4	28.7	27.6
95°	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9	49.6	48.2	46.3
97.5°	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7	65.5	64.5	60.1
100°	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8	72.6	70.4	65.7
102.5°	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1	75.2	72.4	111.4
105°	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4	78.4	75.3	150.3
107.5°	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4	102.4	105.5	195.4
110°	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3	188.7	216.2	295.5



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0	445.1	545.2	564.9
115°	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0	635.1	762.2	755.4
117.5°	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7	813.4	844.2	839.5
120°	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1	908.8	905.4	900.6
122.5°	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8	965.7	963.8	958.5
125°	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7	1045.8	1043.9	1038.6
127.5°	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6	1118.8	1116.0	1112.1
130°	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5	1165.5	1162.5	1159.4
132.5°	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1	1211.4	1208.9	1205.9
135°	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1	1276.4	1273.6	1271.1
137.5°	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5	1336.9	1334.1	1331.3
140°	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7	1376.1	1373.7	1370.7
142.5°	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7	1412.5	1410.3	1406.7
145°	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2	1463.3	1461.4	1456.7
147.5°	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2	1507.8	1506.3	1501.8
150°	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3	1534.7	1533.1	1528.6
152.5°	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0	1559.4	1557.7	1553.6
155°	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4	1592.8	1591.1	1587.8
157.5°	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6	1620.6	1618.8	1616.5
160°	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9	1637.2	1635.6	1634.0
162.5°	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2	1652.2	1650.4	1649.0
165°	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9	1668.1
167.5°	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3	1686.4	1684.5	1683.7
170°	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3	1694.4	1692.4	1691.8
172.5°	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1	1700.2	1698.3	1697.8
175°	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6	1706.7	1704.8	1704.2
177.5°	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3	1707.8	1706.3	1706.0
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	13.1	12.7	12.2	12.3	10.8	10.2	8.4	6.9	7.2	7.5	7.5
90°	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2	4.2	7.3	10.3
92.5°	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9	24.6	24.4	24.1
95°	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3	71.2	62.2	53.1
97.5°	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4	133.8	108.3	82.8
100°	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6	181.1	143.4	105.8
102.5°	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9	275.9	267.9	260.0
105°	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6	383.7	392.0	400.2
107.5°	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1	486.7	493.3	500.0
110°	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2	553.0	558.8	564.5



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5	615.6	620.7	625.8
115°	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3	715.0	719.6	724.3
117.5°	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5	804.8	809.9	815.2
120°	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7	868.9	872.9	877.1
122.5°	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1	924.4	928.8	933.1
125°	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3	1007.8	1011.5	1015.0
127.5°	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7	1084.6	1088.5	1092.6
130°	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1	1133.5	1137.9	1142.3
132.5°	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5	1182.2	1186.0	1189.7
135°	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7	1247.1	1251.5	1255.9
137.5°	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7	1310.8	1313.8	1317.0
140°	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2	1352.4	1354.6	1356.8
142.5°	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8	1387.8	1389.8	1391.7
145°	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6	1441.4	1441.1	1440.8
147.5°	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3	1489.2	1488.2	1487.1
150°	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0	1520.0	1518.1	1516.1
152.5°	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6	1546.5	1544.3	1542.2
155°	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4	1584.9	1582.5	1579.9
157.5°	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8	1615.7	1613.6	1611.5
160°	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1634.0	1632.2	1630.6
162.5°	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4	1649.7	1648.1	1646.5
165°	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6	1671.0	1669.3	1667.7
167.5°	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5	1686.8	1685.2	1683.5
170°	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4	1695.7	1694.0	1692.4
172.5°	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2	1701.6	1700.0	1698.3
175°	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9	1709.0	1707.1	1705.2
177.5°	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1	1710.6	1709.1	1707.6
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	7.8	8.0	8.2	8.6	8.7	8.9	8.9	9.1	9.4	9.1	9.3
90°	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5	28.8	30.2	31.2
92.5°	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1	30.8	31.5	32.0
95°	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9	52.3	53.6	54.2
97.5°	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7	67.8	68.9	69.6
100°	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8	77.0	79.2	80.6
102.5°	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1	81.0	83.8	85.6
105°	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4	84.4	87.5	89.5
107.5°	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4	96.2	93.2	92.2
110°	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3	133.8	106.3	93.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0	244.9	144.7	95.0
115°	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0	380.9	253.8	180.4
117.5°	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7	751.9	721.2	673.4
120°	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1	915.3	918.7	901.8
122.5°	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8	969.8	971.7	969.1
125°	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7	1049.7	1051.6	1052.9
127.5°	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6	1124.4	1127.2	1128.7
130°	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5	1171.5	1174.5	1175.9
132.5°	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1	1216.6	1219.2	1220.3
135°	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1	1281.8	1284.6	1285.7
137.5°	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5	1342.2	1344.9	1345.7
140°	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7	1381.1	1383.6	1384.1
142.5°	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7	1417.0	1419.3	1419.7
145°	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2	1467.1	1469.1	1469.4
147.5°	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2	1510.7	1512.1	1512.2
150°	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3	1538.0	1539.6	1539.7
152.5°	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0	1562.7	1564.4	1564.3
155°	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4	1596.1	1597.7	1597.4
157.5°	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6	1624.4	1626.3	1626.1
160°	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9	1640.5	1642.1	1642.0
162.5°	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2	1656.0	1657.9	1657.6
165°	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6
167.5°	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3	1690.2	1692.1	1691.9
170°	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3	1698.2	1700.1	1699.8
172.5°	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1	1704.0	1706.0	1705.8
175°	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6	1710.5	1712.4	1712.0
177.5°	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3	1710.8	1712.4	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	9.4	9.2	9.3	9.1	9.3	9.2	9.4	9.3	9.1	9.4	9.1
90°	31.7	32.2	32.8	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5
92.5°	32.3	32.7	33.0	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1
95°	53.9	53.6	53.4	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9
97.5°	69.9	70.3	70.6	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7
100°	81.1	81.7	82.2	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8
102.5°	86.3	87.2	88.0	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1
105°	90.6	91.7	92.8	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4
107.5°	93.3	94.4	95.5	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4
110°	94.3	95.4	96.5	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.9	96.8	97.7	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0
115°	160.6	140.9	121.1	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0
117.5°	608.4	543.5	478.6	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7
120°	864.7	827.7	790.6	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1
122.5°	961.9	954.7	947.6	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8
125°	1053.7	1054.6	1055.4	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7
127.5°	1128.8	1129.0	1129.1	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6
130°	1175.6	1175.4	1175.1	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5
132.5°	1220.1	1219.8	1219.5	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1
135°	1285.2	1284.6	1284.0	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1
137.5°	1344.8	1343.9	1343.0	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5
140°	1382.7	1381.4	1380.0	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7
142.5°	1418.4	1416.9	1415.5	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7
145°	1467.9	1466.6	1465.2	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2
147.5°	1511.1	1509.8	1508.7	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2
150°	1538.4	1537.0	1535.6	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3
152.5°	1562.5	1560.6	1558.8	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0
155°	1595.2	1593.1	1590.8	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4
157.5°	1624.0	1621.8	1619.7	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6
160°	1640.1	1638.2	1636.3	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9
162.5°	1655.3	1652.8	1650.5	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2
165°	1674.7	1672.7	1670.8	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7
167.5°	1689.4	1687.0	1684.5	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3
170°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3
172.5°	1703.2	1700.8	1698.3	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1
175°	1709.3	1706.6	1703.7	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6
177.5°	1710.2	1708.2	1706.3	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	8.9	8.9	8.7	8.6	8.2	8.0	7.8	7.5	7.5	7.2	6.9
90°	26.1	24.7	22.5	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2
92.5°	29.4	28.7	27.6	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9
95°	49.6	48.2	46.3	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3
97.5°	65.5	64.5	60.1	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4
100°	72.6	70.4	65.7	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6
102.5°	75.2	72.4	111.4	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9
105°	78.4	75.3	150.3	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6
107.5°	102.4	105.5	195.4	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1
110°	188.7	216.2	295.5	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	445.1	545.2	564.9	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5
115°	635.1	762.2	755.4	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3
117.5°	813.4	844.2	839.5	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5
120°	908.8	905.4	900.6	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7
122.5°	965.7	963.8	958.5	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1
125°	1045.8	1043.9	1038.6	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3
127.5°	1118.8	1116.0	1112.1	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7
130°	1165.5	1162.5	1159.4	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1
132.5°	1211.4	1208.9	1205.9	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5
135°	1276.4	1273.6	1271.1	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7
137.5°	1336.9	1334.1	1331.3	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7
140°	1376.1	1373.7	1370.7	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2
142.5°	1412.5	1410.3	1406.7	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8
145°	1463.3	1461.4	1456.7	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6
147.5°	1507.8	1506.3	1501.8	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3
150°	1534.7	1533.1	1528.6	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0
152.5°	1559.4	1557.7	1553.6	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6
155°	1592.8	1591.1	1587.8	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4
157.5°	1620.6	1618.8	1616.5	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8
160°	1637.2	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6
162.5°	1652.2	1650.4	1649.0	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4
165°	1670.8	1668.9	1668.1	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6
167.5°	1686.4	1684.5	1683.7	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5
170°	1694.4	1692.4	1691.8	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4
172.5°	1700.2	1698.3	1697.8	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2
175°	1706.7	1704.8	1704.2	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9
177.5°	1707.8	1706.3	1706.0	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	8.4	10.2	10.8	12.3	12.2	12.7	13.1	13.2	13.4	13.3	13.3
90°	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5
92.5°	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1
95°	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9
97.5°	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7
100°	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8
102.5°	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1
105°	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4
107.5°	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4
110°	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0
115°	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0
117.5°	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7
120°	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1
122.5°	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8
125°	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7
127.5°	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6
130°	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5
132.5°	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1
135°	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1
137.5°	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5
140°	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7
142.5°	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7
145°	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2
147.5°	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2
150°	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3
152.5°	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0
155°	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4
157.5°	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6
160°	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9
162.5°	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2
165°	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7
167.5°	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3
170°	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3
172.5°	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1
175°	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6
177.5°	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	13.9	14.1	14.0	14.1	14.6	14.4	14.5
90°	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331513-840

CATALOG NUMBER: S122DIW-S485D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)