

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331496-840

Luminaire Tested: **S122DIW-S485D435U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331496-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3683.2 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	38	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.5
10°-20°	271.7	7.4
20°-30°	394.3	10.7
30°-40°	416.1	11.3
40°-50°	368.4	10.0
50°-60°	294.0	8.0
60°-70°	199.8	5.4
70°-80°	102.5	2.8
80°-90°	26.9	0.7
90°-100°	34.4	0.9
100°-110°	106.7	2.9
110°-120°	182.4	5.0
120°-130°	239.9	6.5
130°-140°	269.2	7.3
140°-150°	263.9	7.2
150°-160°	221.4	6.0
160°-170°	146.8	4.0
170°-180°	51.3	1.4
0°-30°	759.5	20.6
0°-40°	1175.6	31.9
0°-60°	1838.0	49.9
0°-90°	2167.2	58.8
90°-120°	323.4	8.8
90°-150°	1096.4	29.8
90°-180°	1516.0	41.2
0°-180°	3683.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	16	0	16	0	16	8
95°	28	24	28	24	28	32
105°	102	98	102	98	102	107
115°	183	183	183	183	183	181
125°	267	266	267	266	267	238
135°	349	345	349	345	349	268
145°	423	418	423	418	423	264
155°	482	478	482	478	482	222
165°	521	520	521	520	521	147
175°	540	541	540	541	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	10.9	10.9	11.2	10.9	10.9	11.2	11.2	11.0	11.3	11.6	11.5
90°	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7	15.9	16.1	13.7
92.5°	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6	14.5	14.5	14.0
95°	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3	29.3	29.3	29.1
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	48.9
100°	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1	63.1	63.1	62.8
102.5°	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3	78.3	78.2	77.8
105°	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1	100.9	100.7	100.5
107.5°	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6	125.5	125.4	125.4
110°	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1	159.3	159.5	159.6
115°	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6	184.7	184.8	185.0
117.5°	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4	209.6	210.0	210.5
120°	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0	226.0	226.0	226.8
122.5°	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1	243.4	243.6	244.2
125°	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4	268.7	269.0	269.3
127.5°	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0	293.4	293.8	294.1
130°	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8	310.0	310.2	310.4
132.5°	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2	326.6	327.0	327.0
135°	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2	350.3	350.4	350.2
137.5°	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3	373.4	373.5	373.2
140°	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9	388.9	388.9	388.4
142.5°	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9	402.9	402.8	402.4
145°	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3	424.2	424.1	423.5
147.5°	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0	442.8	442.6	442.2
150°	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3	453.9
152.5°	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1	465.5
155°	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9	481.4	480.9	480.6
157.5°	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7	495.1	494.4	494.2
160°	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0	503.4	502.8	502.7
162.5°	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5	510.8	510.2	510.1
165°	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2	520.5	519.8	519.8
167.5°	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2	528.5	527.8	527.8
170°	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5	532.8	532.1	532.2
172.5°	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8	536.1	535.4	535.5
175°	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4	539.7	539.0	539.2
177.5°	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1	541.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	11.3	10.9	10.5	10.7	9.6	9.3	7.9	6.8	6.7	6.6	6.3
90°	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2	9.1	9.9	10.8
95°	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8	24.8	25.9	26.9
97.5°	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4	44.3	45.2	46.2
100°	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1	58.9	59.7	60.6
102.5°	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5	74.1	74.7	75.4
105°	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4	98.7	99.0	99.3
107.5°	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4	123.9	124.3	124.8
110°	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6	140.2	140.8	141.4



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1	157.7	158.3	159.0
115°	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0	183.6	184.2	184.8
117.5°	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8	209.6	210.5	211.3
120°	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.8	227.6	228.4
122.5°	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8	242.8	243.7	244.7
125°	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3	267.2	268.1	269.0
127.5°	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1	291.3	292.5	293.7
130°	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2	306.5	307.8	309.1
132.5°	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0	323.1	324.2	325.3
135°	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6	345.7	346.8	347.9
137.5°	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2	369.1	370.0	370.9
140°	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5	383.4	384.4	385.3
142.5°	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2	398.1	399.0	399.9
145°	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2	418.9	419.6	420.3
147.5°	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0	437.8	438.7	439.5
150°	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8	450.4	451.0	451.6
152.5°	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1	461.7	462.3	462.9
155°	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1	478.4	478.7	479.1
157.5°	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7	492.9	493.1	493.3
160°	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5	501.7	501.9	502.1
162.5°	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5	509.6	509.6	509.6
165°	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2	520.1	520.0	519.9
167.5°	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2	528.9	528.6	528.3
170°	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9	533.6	533.3	533.0
172.5°	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2	536.9	536.6	536.3
175°	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3	541.0	540.7	540.4
177.5°	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9	542.7	542.4	542.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	6.2	6.3	6.4	6.9	7.0	7.2	6.8	6.8	6.7	6.1	6.1
90°	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7	15.5	15.2	15.1
92.5°	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6	14.6	14.7	14.7
95°	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3	29.3	29.3	29.2
97.5°	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2	49.2	49.2	49.2
100°	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1	63.1	63.1	63.1
102.5°	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3	78.4	78.5	78.5
105°	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1	101.3	101.5	101.6
107.5°	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6	125.7	125.8	125.6
110°	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.1



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1	158.8	158.5	158.2
115°	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6	184.5	184.4	184.2
117.5°	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4	209.1	208.9	208.6
120°	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0	226.0	226.0	225.9
122.5°	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1	242.9	242.6	242.4
125°	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4	268.1	267.8	267.6
127.5°	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0	292.7	292.3	292.0
130°	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8	309.6	309.4	309.1
132.5°	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2	325.7	325.3	324.9
135°	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2	350.1	350.0	349.8
137.5°	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3	373.2	373.2	372.9
140°	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9	388.9	388.9	388.7
142.5°	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9	403.0	403.1	402.9
145°	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3	424.4	424.5	424.3
147.5°	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0	443.3	443.5	443.4
150°	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9	455.2	455.6	455.6
152.5°	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8	467.2	467.6	467.6
155°	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9	482.4	482.9	483.0
157.5°	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7	496.4	497.2	497.3
160°	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0	504.6	505.2	505.3
162.5°	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5	512.2	512.9	513.0
165°	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2	521.9	522.6	522.7
167.5°	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2	529.9	530.6	530.7
170°	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5	534.2	534.9	535.0
172.5°	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8	537.6	538.3	538.3
175°	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4	541.1	541.8	541.9
177.5°	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1	542.5	543.0	543.0
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	6.1	5.8	5.8	5.6	5.8	5.8	6.1	6.1	6.1	6.7	6.8
90°	15.2	15.3	15.5	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7
92.5°	14.7	14.7	14.8	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6
95°	29.0	28.8	28.6	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.0	62.9	62.8	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1
102.5°	78.4	78.3	78.2	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3
105°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1
107.5°	125.1	124.6	124.2	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6
110°	141.8	141.5	141.2	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	158.0	157.8	157.6	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1
115°	183.9	183.6	183.3	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6
117.5°	208.3	208.0	207.7	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4
120°	225.6	225.3	225.0	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0
122.5°	242.2	242.0	241.7	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1
125°	267.5	267.4	267.3	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4
127.5°	291.5	291.2	290.9	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0
130°	308.7	308.3	307.9	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8
132.5°	324.6	324.2	323.9	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2
135°	349.5	349.2	348.9	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2
137.5°	372.5	372.1	371.7	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3
140°	388.3	387.9	387.5	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9
142.5°	402.5	402.1	401.7	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9
145°	423.9	423.5	423.1	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3
147.5°	443.0	442.6	442.2	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0
150°	455.2	454.9	454.6	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9
152.5°	467.2	466.8	466.5	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8
155°	482.7	482.4	482.1	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9
157.5°	496.8	496.2	495.8	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7
160°	504.9	504.5	504.1	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0
162.5°	512.5	512.0	511.5	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5
165°	522.2	521.7	521.2	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2
167.5°	530.1	529.6	529.1	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2
170°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5
172.5°	537.7	537.0	536.4	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8
175°	541.3	540.7	540.1	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4
177.5°	542.5	542.1	541.6	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	6.8	7.2	7.0	6.9	6.4	6.3	6.2	6.3	6.6	6.7	6.8
90°	15.9	16.1	13.7	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5
92.5°	14.5	14.5	14.0	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2
95°	29.3	29.3	29.1	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8
97.5°	49.2	49.2	48.9	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4
100°	63.1	63.1	62.8	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1
102.5°	78.3	78.2	77.8	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5
105°	100.9	100.7	100.5	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4
107.5°	125.5	125.4	125.4	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4
110°	142.3	142.3	142.3	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	159.3	159.5	159.6	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1
115°	184.7	184.8	185.0	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0
117.5°	209.6	210.0	210.5	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8
120°	226.0	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0
122.5°	243.4	243.6	244.2	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8
125°	268.7	269.0	269.3	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3
127.5°	293.4	293.8	294.1	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1
130°	310.0	310.2	310.4	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2
132.5°	326.6	327.0	327.0	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0
135°	350.3	350.4	350.2	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6
137.5°	373.4	373.5	373.2	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2
140°	388.9	388.9	388.4	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5
142.5°	402.9	402.8	402.4	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2
145°	424.2	424.1	423.5	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2
147.5°	442.8	442.6	442.2	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0
150°	454.6	454.3	453.9	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8
152.5°	466.5	466.1	465.5	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1
155°	481.4	480.9	480.6	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1
157.5°	495.1	494.4	494.2	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7
160°	503.4	502.8	502.7	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5
162.5°	510.8	510.2	510.1	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5
165°	520.5	519.8	519.8	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2
167.5°	528.5	527.8	527.8	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2
170°	532.8	532.1	532.2	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9
172.5°	536.1	535.4	535.5	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2
175°	539.7	539.0	539.2	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3
177.5°	541.6	541.1	541.2	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	7.9	9.3	9.6	10.7	10.5	10.9	11.3	11.5	11.6	11.3	11.0
90°	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7
92.5°	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6
95°	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3
97.5°	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2
100°	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1
102.5°	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3
105°	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1
107.5°	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6
110°	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1
115°	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6
117.5°	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4
120°	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0
122.5°	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1
125°	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4
127.5°	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0
130°	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8
132.5°	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2
135°	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2
137.5°	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3
140°	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9
142.5°	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9
145°	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3
147.5°	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0
150°	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9
152.5°	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8
155°	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9
157.5°	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7
160°	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0
162.5°	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5
165°	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2
167.5°	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2
170°	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5
172.5°	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8
175°	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4
177.5°	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	11.2	11.2	10.9	10.9	11.2	10.9	10.9
90°	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331496-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)