

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331602

Luminaire Tested: **S122DIW-S1005D970U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331602
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7415.8 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55				
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	53	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	421.7	5.7
20°-30°	619.8	8.4
30°-40°	720.0	9.7
40°-50°	719.2	9.7
50°-60°	627.2	8.5
60°-70°	463.8	6.3
70°-80°	262.7	3.5
80°-90°	75.4	1.0
90°-100°	76.0	1.0
100°-110°	236.2	3.2
110°-120°	403.8	5.4
120°-130°	531.0	7.2
130°-140°	595.9	8.0
140°-150°	584.3	7.9
150°-160°	490.1	6.6
160°-170°	325.1	4.4
170°-180°	113.6	1.5
0°-30°	1191.4	16.1
0°-40°	1911.4	25.8
0°-60°	3257.9	43.9
0°-90°	4059.7	54.7
90°-120°	716.0	9.7
90°-150°	2427.3	32.7
90°-180°	3356.0	45.3
0°-180°	7415.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	14	35	34	34	6
95°	53	62	65	65	63	60
105°	218	221	223	225	225	230
115°	405	411	409	408	405	401
125°	590	598	596	593	592	527
135°	763	773	776	775	772	589
145°	926	933	939	940	936	578
155°	1058	1061	1064	1069	1066	487
165°	1152	1151	1151	1157	1153	325
175°	1198	1195	1193	1200	1194	114
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.3	22.3	22.3	22.3	22.3	22.5	22.9	23.4	23.8	24.3	23.3
90°	1.0	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0
92.5°	18.0	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3
95°	52.7	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8
97.5°	96.2	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0
100°	128.6	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8
102.5°	162.7	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2
105°	217.8	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3
107.5°	273.3	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9
110°	308.9	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.8	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5
115°	405.1	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0
117.5°	462.3	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2
120°	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4
122.5°	535.2	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7
125°	589.5	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9
127.5°	642.4	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4
130°	675.6	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3
132.5°	712.8	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0
135°	762.7	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6
137.5°	815.1	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7
140°	846.7	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9
142.5°	879.2	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9
145°	925.7	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1
147.5°	967.3	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3
150°	995.6	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4
152.5°	1020.8	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5
155°	1058.4	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6
157.5°	1090.6	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0
160°	1110.1	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5
162.5°	1127.9	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9
165°	1151.6	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2
167.5°	1171.5	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8
170°	1182.0	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5
172.5°	1189.3	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8
175°	1198.2	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7
177.5°	1201.9	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	22.4	21.5	20.6	20.1	19.8	19.6	19.4	19.1
90°	34.5	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.4	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.4	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	223.7	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.1	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331602

CATALOG NUMBER: S122DIW-S1005D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.0	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.7	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.6	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	538.2	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	594.2	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	648.6	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.8	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	722.0	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.4	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.5	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.1	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.4	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	980.8	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1066.8	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1097.6	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1115.8	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1132.4	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1153.8	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1171.4	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1181.1	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1188.4	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1196.3	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)