

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331499-840

Luminaire Tested: **S122DIW-S485D435U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331499-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3745.1 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	59	48	41	35	41	36	31	35	31	27	30	26	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	2.0
10°-20°	207.5	5.5
20°-30°	305.0	8.1
30°-40°	354.3	9.5
40°-50°	354.0	9.5
50°-60°	308.7	8.2
60°-70°	228.2	6.1
70°-80°	129.3	3.5
80°-90°	36.2	1.0
90°-100°	19.9	0.5
100°-110°	73.0	1.9
110°-120°	195.0	5.2
120°-130°	322.0	8.6
130°-140°	342.4	9.1
140°-150°	318.3	8.5
150°-160°	255.9	6.8
160°-170°	164.9	4.4
170°-180°	56.8	1.5
0°-30°	586.3	15.7
0°-40°	940.7	25.1
0°-60°	1603.3	42.8
0°-90°	1997.0	53.3
90°-120°	287.9	7.7
90°-150°	1270.6	33.9
90°-180°	1748.0	46.7
0°-180°	3745.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	0	5	9	11	12	3
95°	28	15	17	19	19	34
105°	131	137	26	31	33	140
115°	248	256	266	76	35	244
125°	351	357	365	368	369	313
135°	434	441	445	449	448	335
145°	504	504	511	513	512	315
155°	555	551	556	558	555	255
165°	584	582	583	586	583	165
175°	598	595	596	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	10.9	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.3	10.2	9.9
90°	0.4	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1
92.5°	8.7	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3
95°	28.1	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3
97.5°	55.6	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9
100°	76.4	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3
102.5°	99.2	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3
105°	131.2	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4
107.5°	167.7	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7
110°	191.2	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.3	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5
115°	248.2	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9
117.5°	279.3	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3
120°	302.2	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5
122.5°	321.4	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5
125°	350.9	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4
127.5°	377.6	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9
130°	394.6	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2
132.5°	411.8	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3
135°	434.2	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0
137.5°	457.0	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1
140°	471.8	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8
142.5°	484.2	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5
145°	503.7	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3
147.5°	520.7	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8
150°	531.8	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2
152.5°	541.1	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8
155°	554.6	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5
157.5°	565.2	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2
160°	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1
162.5°	577.0	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3
165°	584.4	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8
167.5°	590.0	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3
170°	593.1	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0
172.5°	595.1	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1
175°	597.8	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3
177.5°	598.2	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	9.6	9.3	9.0	8.8	8.7	8.6	8.5	8.4
90°	9.6	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.5	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	17.8	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.3	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.2	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	27.3	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	28.5	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	34.7	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	56.4	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331499-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	120.6	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	177.5	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	273.5	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	318.7	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.1	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.1	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	391.9	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	408.3	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	424.2	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.0	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	468.1	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	481.7	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	494.3	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.0	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.4	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	536.8	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	545.4	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.1	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	566.9	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	572.6	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	577.9	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.0	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	592.7	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	594.7	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.0	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.2	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)