

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331471

Luminaire Tested: **S122DIW-S290D710U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331471
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D710U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4141.6 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	17	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.4
10°-20°	163.7	4.0
20°-30°	237.5	5.7
30°-40°	250.6	6.1
40°-50°	221.9	5.4
50°-60°	177.1	4.3
60°-70°	120.4	2.9
70°-80°	61.7	1.5
80°-90°	17.3	0.4
90°-100°	32.3	0.8
100°-110°	118.3	2.9
110°-120°	316.3	7.6
120°-130°	522.2	12.6
130°-140°	555.4	13.4
140°-150°	516.2	12.5
150°-160°	415.0	10.0
160°-170°	267.4	6.5
170°-180°	92.1	2.2
0°-30°	457.5	11.0
0°-40°	708.1	17.1
0°-60°	1107.1	26.7
0°-90°	1306.4	31.5
90°-120°	467.0	11.3
90°-150°	2060.7	49.8
90°-180°	2835.0	68.5
0°-180°	4141.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	53	213	53	213	53	55
115°	57	402	57	402	57	144
125°	598	569	598	569	598	518
135°	727	704	727	704	727	561
145°	830	817	830	817	830	519
155°	900	900	900	900	900	415
165°	946	948	946	948	946	267
175°	964	970	964	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	8.5	8.4	8.6	8.3	8.3	8.3	8.2	7.8	7.9	7.9	7.8
90°	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6	14.8	14.0	12.8
92.5°	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1	16.6	16.2	15.6
95°	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9	28.1	27.3	26.2
97.5°	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8	37.2	36.5	34.0
100°	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4	41.1	39.9	37.3
102.5°	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3	42.6	41.0	63.1
105°	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1	44.4	42.7	85.2
107.5°	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3	58.0	59.8	110.7
110°	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4	107.0	122.5	167.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5	252.3	309.0	320.1
115°	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9	359.9	431.9	428.0
117.5°	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6	461.0	478.4	475.7
120°	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9	515.0	513.1	510.3
122.5°	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4	547.3	546.2	543.1
125°	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7	592.6	591.5	588.6
127.5°	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6	634.0	632.4	630.2
130°	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2	660.5	658.8	657.0
132.5°	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0	686.5	685.1	683.4
135°	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9	723.3	721.8	720.4
137.5°	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1	757.6	756.1	754.5
140°	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3	779.9	778.5	776.7
142.5°	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7	800.5	799.2	797.2
145°	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3	829.3	828.2	825.5
147.5°	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3	854.5	853.6	851.0
150°	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6	869.7	868.8	866.3
152.5°	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6	883.7	882.8	880.4
155°	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5	902.6	901.7	899.8
157.5°	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5	918.4	917.3	916.0
160°	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7	927.8	926.9	925.9
162.5°	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4	936.3	935.3	934.5
165°	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8	945.3
167.5°	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8	955.7	954.6	954.2
170°	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3	960.2	959.1	958.8
172.5°	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6	963.5	962.4	962.1
175°	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3	967.2	966.1	965.8
177.5°	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7	967.8	966.9	966.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	7.8	7.5	7.3	7.3	6.4	6.1	5.0	4.1	4.3	4.5	4.4
90°	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1	14.0	13.8	13.7
95°	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5	40.4	35.2	30.1
97.5°	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3	75.8	61.4	46.9
100°	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9	102.6	81.3	60.0
102.5°	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9	156.4	151.8	147.3
105°	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8	217.5	222.2	226.8
107.5°	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0	275.8	279.6	283.3
110°	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1	313.4	316.7	319.9



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0	348.9	351.8	354.6
115°	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5	405.2	407.8	410.5
117.5°	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1	456.0	459.0	461.9
120°	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0	492.4	494.7	497.0
122.5°	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4	523.9	526.3	528.8
125°	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1	571.2	573.2	575.2
127.5°	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4	614.6	616.9	619.1
130°	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8	642.3	644.8	647.3
132.5°	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9	670.0	672.1	674.2
135°	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3	706.7	709.2	711.7
137.5°	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1	742.8	744.6	746.3
140°	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2	766.4	767.6	768.9
142.5°	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3	786.4	787.6	788.7
145°	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0	816.8	816.7	816.5
147.5°	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5	844.0	843.4	842.8
150°	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5	861.4	860.3	859.2
152.5°	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6	876.4	875.2	873.9
155°	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6	898.2	896.8	895.4
157.5°	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8	915.6	914.4	913.2
160°	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	925.9	925.0	924.1
162.5°	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8	934.9	934.0	933.0
165°	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9	946.9	946.0	945.1
167.5°	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8	955.9	955.0	954.0
170°	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9	960.9	960.0	959.1
172.5°	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2	964.3	963.4	962.4
175°	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6	968.5	967.4	966.3
177.5°	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3	969.4	968.5	967.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	4.6	4.7	4.8	5.0	5.1	5.2	5.1	5.3	5.4	5.2	5.3
90°	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1	17.7
92.5°	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1	17.5	17.9	18.2
95°	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9	29.6	30.4	30.7
97.5°	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8	38.4	39.0	39.4
100°	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4	43.6	44.9	45.7
102.5°	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3	45.9	47.5	48.5
105°	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1	47.8	49.5	50.7
107.5°	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3	54.6	52.8	52.3
110°	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4	75.8	60.3	52.8



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5	138.8	82.0	53.9
115°	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9	215.8	143.8	102.2
117.5°	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6	426.1	408.7	381.6
120°	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9	518.7	520.6	511.0
122.5°	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4	549.5	550.7	549.2
125°	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7	594.8	595.9	596.7
127.5°	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6	637.2	638.8	639.6
130°	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2	663.9	665.6	666.4
132.5°	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0	689.5	690.9	691.6
135°	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9	726.4	728.0	728.6
137.5°	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1	760.6	762.2	762.7
140°	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3	782.7	784.1	784.4
142.5°	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7	803.0	804.3	804.5
145°	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3	831.4	832.5	832.7
147.5°	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3	856.1	856.9	857.0
150°	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6	871.6	872.5	872.6
152.5°	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6	885.6	886.5	886.5
155°	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5	904.5	905.4	905.2
157.5°	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5	920.5	921.6	921.5
160°	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7	929.7	930.6	930.5
162.5°	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4	938.4	939.5	939.4
165°	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0	949.0	950.1	950.1
167.5°	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8	957.9	958.9	958.8
170°	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3	962.3	963.4	963.3
172.5°	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6	965.7	966.8	966.6
175°	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3	969.3	970.4	970.2
177.5°	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7	969.5	970.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	5.4	5.3	5.4	5.2	5.4	5.3	5.4	5.3	5.2	5.4	5.3
90°	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6
92.5°	18.3	18.5	18.7	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1
95°	30.6	30.4	30.3	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9
97.5°	39.6	39.8	40.0	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8
100°	46.0	46.3	46.6	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4
102.5°	49.0	49.4	49.8	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3
105°	51.3	52.0	52.6	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1
107.5°	52.9	53.5	54.1	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3
110°	53.4	54.1	54.7	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.4	54.9	55.4	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5
115°	91.0	79.8	68.6	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9
117.5°	344.8	308.0	271.2	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6
120°	490.0	469.0	448.0	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9
122.5°	545.1	541.0	537.0	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4
125°	597.1	597.6	598.1	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7
127.5°	639.7	639.8	639.9	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6
130°	666.2	666.1	665.9	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2
132.5°	691.4	691.3	691.1	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0
135°	728.3	728.0	727.7	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9
137.5°	762.1	761.6	761.1	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1
140°	783.6	782.8	782.0	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3
142.5°	803.8	803.0	802.2	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7
145°	831.9	831.1	830.3	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3
147.5°	856.3	855.7	855.0	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3
150°	871.8	871.0	870.2	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6
152.5°	885.4	884.4	883.4	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6
155°	904.0	902.8	901.5	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5
157.5°	920.3	919.1	917.9	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5
160°	929.4	928.3	927.3	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7
162.5°	938.0	936.7	935.3	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4
165°	949.0	948.0	946.9	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0
167.5°	957.4	956.0	954.6	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8
170°	961.9	960.5	959.1	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3
172.5°	965.2	963.8	962.4	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6
175°	968.6	967.1	965.5	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3
177.5°	969.2	968.0	966.9	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	5.1	5.2	5.1	5.0	4.8	4.7	4.6	4.4	4.5	4.3	4.1
90°	14.8	14.0	12.8	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7
92.5°	16.6	16.2	15.6	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1
95°	28.1	27.3	26.2	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5
97.5°	37.2	36.5	34.0	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3
100°	41.1	39.9	37.3	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9
102.5°	42.6	41.0	63.1	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9
105°	44.4	42.7	85.2	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8
107.5°	58.0	59.8	110.7	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0
110°	107.0	122.5	167.5	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	252.3	309.0	320.1	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0
115°	359.9	431.9	428.0	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5
117.5°	461.0	478.4	475.7	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1
120°	515.0	513.1	510.3	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0
122.5°	547.3	546.2	543.1	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4
125°	592.6	591.5	588.6	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1
127.5°	634.0	632.4	630.2	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4
130°	660.5	658.8	657.0	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8
132.5°	686.5	685.1	683.4	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9
135°	723.3	721.8	720.4	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3
137.5°	757.6	756.1	754.5	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1
140°	779.9	778.5	776.7	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2
142.5°	800.5	799.2	797.2	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3
145°	829.3	828.2	825.5	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0
147.5°	854.5	853.6	851.0	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5
150°	869.7	868.8	866.3	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5
152.5°	883.7	882.8	880.4	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6
155°	902.6	901.7	899.8	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6
157.5°	918.4	917.3	916.0	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8
160°	927.8	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9
162.5°	936.3	935.3	934.5	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8
165°	946.9	945.8	945.3	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9
167.5°	955.7	954.6	954.2	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8
170°	960.2	959.1	958.8	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9
172.5°	963.5	962.4	962.1	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2
175°	967.2	966.1	965.8	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6
177.5°	967.8	966.9	966.8	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.0	6.1	6.4	7.3	7.3	7.5	7.8	7.8	7.9	7.9	7.8
90°	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6
92.5°	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1
95°	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9
97.5°	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8
100°	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4
102.5°	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3
105°	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1
107.5°	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3
110°	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5
115°	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9
117.5°	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6
120°	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9
122.5°	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4
125°	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7
127.5°	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6
130°	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2
132.5°	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0
135°	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9
137.5°	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1
140°	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3
142.5°	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7
145°	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3
147.5°	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3
150°	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6
152.5°	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6
155°	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5
157.5°	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5
160°	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7
162.5°	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4
165°	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0
167.5°	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8
170°	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3
172.5°	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6
175°	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3
177.5°	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	8.2	8.3	8.3	8.3	8.6	8.4	8.5
90°	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331471

CATALOG NUMBER: S122DIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)