

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331505-840

Luminaire Tested: **S122DIW-S485D710U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331505-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4861.1 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41																												
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35																												
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29																												
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25																												
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21																												
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18																												
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16																												
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14																												
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																												
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12																												
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.5
10°-20°	207.5	4.3
20°-30°	305.0	6.3
30°-40°	354.3	7.3
40°-50°	354.0	7.3
50°-60°	308.7	6.3
60°-70°	228.2	4.7
70°-80°	129.3	2.7
80°-90°	37.2	0.8
90°-100°	32.6	0.7
100°-110°	119.5	2.5
110°-120°	319.5	6.6
120°-130°	527.3	10.8
130°-140°	560.8	11.5
140°-150°	521.3	10.7
150°-160°	419.1	8.6
160°-170°	270.1	5.6
170°-180°	93.0	1.9
0°-30°	586.3	12.1
0°-40°	940.7	19.4
0°-60°	1603.3	33.0
0°-90°	1997.9	41.1
90°-120°	471.6	9.7
90°-150°	2081.0	42.8
90°-180°	2863.0	58.9
0°-180°	4861.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	8	14	18	19	4
95°	46	24	28	31	30	56
105°	215	224	43	51	54	230
115°	406	419	436	124	58	400
125°	575	584	597	602	604	512
135°	711	722	729	736	735	549
145°	825	825	836	841	838	516
155°	908	903	911	914	909	418
165°	957	953	955	960	955	270
175°	979	974	976	980	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.0	11.1	11.1	11.2	11.3	11.3	11.3	11.3	11.3	11.3	11.0
90°	0.7	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9
92.5°	14.2	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8
95°	45.9	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4
97.5°	91.2	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6
100°	125.1	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5
102.5°	162.5	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0
105°	214.9	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8
107.5°	274.7	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6
110°	313.2	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	349.4	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8
115°	406.5	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5
117.5°	457.6	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5
120°	494.8	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1
122.5°	526.5	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7
125°	574.7	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4
127.5°	618.4	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3
130°	646.1	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0
132.5°	674.5	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3
135°	711.2	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4
137.5°	748.4	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1
140°	772.7	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6
142.5°	793.0	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4
145°	825.1	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5
147.5°	852.8	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9
150°	871.0	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3
152.5°	886.3	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4
155°	908.5	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5
157.5°	925.8	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5
160°	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0
162.5°	945.0	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5
165°	957.3	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2
167.5°	966.2	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1
170°	971.4	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7
172.5°	974.7	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0
175°	979.2	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7
177.5°	979.9	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	10.8	10.5	10.3	10.1	10.1	10.0	9.9	9.9
90°	15.8	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.3	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.2	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.2	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	42.8	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	44.7	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	46.6	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	56.9	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	92.3	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331505-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	197.4	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	290.7	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	448.0	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	522.0	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	553.8	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	599.6	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	641.9	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	668.7	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	694.8	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	732.1	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	766.6	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	789.0	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	809.6	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	838.5	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	863.7	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	879.2	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	893.3	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	912.4	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	928.6	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	937.9	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	946.6	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	966.2	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	970.8	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	974.1	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	977.9	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	978.3	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)