

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331513

Luminaire Tested: **S122DIW-S485D1240U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331513  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D1240U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7102.2 lumens  
Efficiency: N/A  
Efficacy: 132.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	1.3
10°-20°	269.0	3.8
20°-30°	390.5	5.5
30°-40°	412.0	5.8
40°-50°	364.8	5.1
50°-60°	291.1	4.1
60°-70°	197.9	2.8
70°-80°	101.5	1.4
80°-90°	28.6	0.4
90°-100°	56.4	0.8
100°-110°	206.8	2.9
110°-120°	552.8	7.8
120°-130°	912.5	12.8
130°-140°	970.4	13.7
140°-150°	902.0	12.7
150°-160°	725.2	10.2
160°-170°	467.3	6.6
170°-180°	160.9	2.3
0°-30°	752.0	10.6
0°-40°	1164.1	16.4
0°-60°	1820.1	25.6
0°-90°	2148.0	30.2
90°-120°	816.0	11.5
90°-150°	3600.9	50.7
90°-180°	4954.0	69.8
0°-180°	7102.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	33	1	33	1	33	16
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	703	100	703	100	251
125°	1046	994	1046	994	1046	905
135°	1271	1231	1271	1231	1271	980
145°	1450	1428	1450	1428	1450	907
155°	1573	1572	1573	1572	1573	726
165°	1653	1656	1653	1656	1653	467
175°	1684	1694	1684	1694	1684	160
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	14.4	14.3	14.5	14.0	13.9	14.0	13.8	13.2	13.2	13.3	13.1
90°	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2	25.8	24.5	22.3
92.5°	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8	29.1	28.4	27.3
95°	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4	49.1	47.7	45.8
97.5°	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0	64.9	63.9	59.5
100°	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1	71.9	69.7	65.1
102.5°	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3	74.5	71.7	110.3
105°	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6	77.6	74.6	148.8
107.5°	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4	101.4	104.5	193.5
110°	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7	186.9	214.1	292.6



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6	440.8	539.9	559.4
115°	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0	628.9	754.8	748.0
117.5°	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1	805.5	836.0	831.3
120°	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2	899.9	896.6	891.8
122.5°	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3	956.3	954.4	949.1
125°	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5	1035.6	1033.7	1028.5
127.5°	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6	1107.9	1105.1	1101.2
130°	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1	1154.1	1151.1	1148.1
132.5°	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2	1199.6	1197.1	1194.1
135°	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6	1263.9	1261.2	1258.7
137.5°	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4	1323.8	1321.1	1318.3
140°	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2	1362.7	1360.3	1357.3
142.5°	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9	1398.7	1396.5	1393.0
145°	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9	1449.0	1447.1	1442.5
147.5°	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5	1493.1	1491.6	1487.1
150°	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3	1519.7	1518.1	1513.7
152.5°	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8	1544.2	1542.5	1538.4
155°	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8	1577.2	1575.6	1572.3
157.5°	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7	1604.8	1603.0	1600.7
160°	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9	1621.2	1619.6	1618.0
162.5°	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0	1636.1	1634.3	1632.9
165°	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6	1651.8
167.5°	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8	1669.9	1668.0	1667.3
170°	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7	1677.8	1675.9	1675.3
172.5°	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5	1683.6	1681.7	1681.2
175°	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9	1690.0	1688.1	1687.6
177.5°	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6	1691.1	1689.6	1689.3
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	13.0	12.6	12.1	12.2	10.7	10.1	8.3	6.8	7.1	7.4	7.4
90°	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7	24.4	24.2	23.9
95°	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5	70.5	61.6	52.6
97.5°	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8	132.5	107.2	82.0
100°	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5	179.3	142.0	104.8
102.5°	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1	273.2	265.3	257.5
105°	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9	380.0	388.2	396.3
107.5°	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4	481.9	488.5	495.1
110°	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9	547.6	553.3	559.0





TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5	609.6	614.6	619.7
115°	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4	708.0	712.6	717.2
117.5°	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7	796.9	802.0	807.2
120°	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3	860.4	864.4	868.5
122.5°	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1	915.4	919.7	924.0
125°	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5	998.0	1001.6	1005.1
127.5°	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1	1074.0	1077.9	1081.9
130°	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1	1122.4	1126.8	1131.1
132.5°	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0	1170.7	1174.4	1178.1
135°	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6	1234.9	1239.3	1243.6
137.5°	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9	1298.0	1301.0	1304.1
140°	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0	1339.2	1341.4	1343.5
142.5°	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3	1374.2	1376.2	1378.1
145°	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5	1427.3	1427.0	1426.7
147.5°	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7	1474.7	1473.7	1472.6
150°	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1	1505.2	1503.3	1501.3
152.5°	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5	1531.4	1529.2	1527.1
155°	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9	1569.4	1567.0	1564.5
157.5°	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0	1599.9	1597.8	1595.8
160°	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1618.0	1616.3	1614.7
162.5°	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3	1633.6	1632.0	1630.4
165°	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3	1654.7	1653.0	1651.4
167.5°	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0	1670.3	1668.7	1667.1
170°	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8	1679.1	1677.5	1675.9
172.5°	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6	1685.0	1683.4	1681.7
175°	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2	1692.3	1690.4	1688.5
177.5°	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4	1693.9	1692.4	1690.9
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	7.7	7.9	8.1	8.5	8.6	8.8	8.8	9.0	9.3	9.0	9.2
90°	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2	28.5	29.9	30.9
92.5°	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8	30.5	31.2	31.7
95°	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4	51.8	53.1	53.7
97.5°	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0	67.1	68.2	68.9
100°	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1	76.2	78.4	79.8
102.5°	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3	80.2	83.0	84.8
105°	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6	83.6	86.6	88.6
107.5°	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4	95.3	92.3	91.3
110°	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7	132.5	105.3	92.3



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6	242.5	143.3	94.1
115°	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0	377.2	251.3	178.6
117.5°	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1	744.6	714.2	666.8
120°	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2	906.4	909.7	893.0
122.5°	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3	960.3	962.2	959.6
125°	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5	1039.4	1041.3	1042.6
127.5°	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6	1113.4	1116.2	1117.7
130°	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1	1160.1	1163.0	1164.4
132.5°	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2	1204.7	1207.3	1208.4
135°	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6	1269.3	1272.1	1273.1
137.5°	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4	1329.1	1331.8	1332.6
140°	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2	1367.6	1370.1	1370.6
142.5°	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9	1403.2	1405.4	1405.8
145°	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9	1452.8	1454.7	1455.0
147.5°	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5	1495.9	1497.3	1497.4
150°	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3	1523.0	1524.6	1524.7
152.5°	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8	1547.4	1549.1	1549.0
155°	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8	1580.5	1582.1	1581.8
157.5°	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7	1608.5	1610.4	1610.2
160°	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9	1624.5	1626.1	1626.0
162.5°	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0	1639.8	1641.7	1641.4
165°	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2
167.5°	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8	1673.7	1675.6	1675.4
170°	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7	1681.6	1683.5	1683.2
172.5°	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5	1687.4	1689.3	1689.1
175°	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9	1693.8	1695.7	1695.3
177.5°	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6	1694.1	1695.7	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	9.3	9.1	9.2	9.0	9.2	9.1	9.3	9.2	9.0	9.3	9.0
90°	31.4	31.9	32.5	33.0	32.5	31.9	31.4	30.9	29.9	28.5	27.2
92.5°	32.0	32.4	32.7	33.0	32.7	32.4	32.0	31.7	31.2	30.5	29.8
95°	53.4	53.1	52.9	52.6	52.9	53.1	53.4	53.7	53.1	51.8	50.4
97.5°	69.2	69.6	69.9	70.2	69.9	69.6	69.2	68.9	68.2	67.1	66.0
100°	80.3	80.9	81.4	82.0	81.4	80.9	80.3	79.8	78.4	76.2	74.1
102.5°	85.5	86.3	87.1	87.8	87.1	86.3	85.5	84.8	83.0	80.2	77.3
105°	89.7	90.8	91.9	93.0	91.9	90.8	89.7	88.6	86.6	83.6	80.6
107.5°	92.4	93.5	94.6	95.7	94.6	93.5	92.4	91.3	92.3	95.3	98.4
110°	93.4	94.5	95.6	96.6	95.6	94.5	93.4	92.3	105.3	132.5	159.7



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.0	95.9	96.7	97.6	96.7	95.9	95.0	94.1	143.3	242.5	341.6
115°	159.0	139.5	119.9	100.3	119.9	139.5	159.0	178.6	251.3	377.2	503.0
117.5°	602.5	538.2	473.9	409.5	473.9	538.2	602.5	666.8	714.2	744.6	775.1
120°	856.3	819.6	782.9	746.2	782.9	819.6	856.3	893.0	909.7	906.4	903.2
122.5°	952.5	945.4	938.3	931.1	938.3	945.4	952.5	959.6	962.2	960.3	958.3
125°	1043.4	1044.3	1045.1	1045.9	1045.1	1044.3	1043.4	1042.6	1041.3	1039.4	1037.5
127.5°	1117.8	1118.0	1118.1	1118.3	1118.1	1118.0	1117.8	1117.7	1116.2	1113.4	1110.6
130°	1164.1	1163.9	1163.6	1163.3	1163.6	1163.9	1164.1	1164.4	1163.0	1160.1	1157.1
132.5°	1208.2	1207.9	1207.6	1207.4	1207.6	1207.9	1208.2	1208.4	1207.3	1204.7	1202.2
135°	1272.6	1272.1	1271.5	1271.0	1271.5	1272.1	1272.6	1273.1	1272.1	1269.3	1266.6
137.5°	1331.7	1330.8	1329.9	1328.9	1329.9	1330.8	1331.7	1332.6	1331.8	1329.1	1326.4
140°	1369.2	1367.9	1366.5	1365.2	1366.5	1367.9	1369.2	1370.6	1370.1	1367.6	1365.2
142.5°	1404.5	1403.1	1401.7	1400.4	1401.7	1403.1	1404.5	1405.8	1405.4	1403.2	1400.9
145°	1453.6	1452.3	1450.9	1449.6	1450.9	1452.3	1453.6	1455.0	1454.7	1452.8	1450.9
147.5°	1496.3	1495.1	1494.0	1492.9	1494.0	1495.1	1496.3	1497.4	1497.3	1495.9	1494.5
150°	1523.4	1522.0	1520.6	1519.3	1520.6	1522.0	1523.4	1524.7	1524.6	1523.0	1521.3
152.5°	1547.2	1545.4	1543.6	1541.8	1543.6	1545.4	1547.2	1549.0	1549.1	1547.4	1545.8
155°	1579.6	1577.5	1575.3	1573.1	1575.3	1577.5	1579.6	1581.8	1582.1	1580.5	1578.8
157.5°	1608.1	1606.0	1603.9	1601.7	1603.9	1606.0	1608.1	1610.2	1610.4	1608.5	1606.7
160°	1624.1	1622.2	1620.3	1618.4	1620.3	1622.2	1624.1	1626.0	1626.1	1624.5	1622.9
162.5°	1639.1	1636.7	1634.4	1632.1	1634.4	1636.7	1639.1	1641.4	1641.7	1639.8	1638.0
165°	1658.3	1656.4	1654.5	1652.6	1654.5	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4
167.5°	1672.9	1670.5	1668.0	1665.6	1668.0	1670.5	1672.9	1675.4	1675.6	1673.7	1671.8
170°	1680.8	1678.3	1675.9	1673.4	1675.9	1678.3	1680.8	1683.2	1683.5	1681.6	1679.7
172.5°	1686.6	1684.2	1681.7	1679.3	1681.7	1684.2	1686.6	1689.1	1689.3	1687.4	1685.5
175°	1692.6	1689.9	1687.1	1684.4	1687.1	1689.9	1692.6	1695.3	1695.7	1693.8	1691.9
177.5°	1693.5	1691.5	1689.6	1687.6	1689.6	1691.5	1693.5	1695.4	1695.7	1694.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	8.8	8.8	8.6	8.5	8.1	7.9	7.7	7.4	7.4	7.1	6.8
90°	25.8	24.5	22.3	20.1	17.9	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.2	25.1	24.0	23.6	23.9	24.2	24.4	24.7
95°	49.1	47.7	45.8	43.9	42.0	40.1	43.6	52.6	61.6	70.5	79.5
97.5°	64.9	63.9	59.5	55.0	50.6	46.2	56.7	82.0	107.2	132.5	157.8
100°	71.9	69.7	65.1	60.5	55.9	51.2	67.6	104.8	142.0	179.3	216.5
102.5°	74.5	71.7	110.3	149.0	187.6	226.3	249.6	257.5	265.3	273.2	281.1
105°	77.6	74.6	148.8	223.0	297.3	371.5	404.5	396.3	388.2	380.0	371.9
107.5°	101.4	104.5	193.5	282.5	371.5	460.5	501.7	495.1	488.5	481.9	475.4
110°	186.9	214.1	292.6	371.2	449.8	528.3	564.7	559.0	553.3	547.6	541.9



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	440.8	539.9	559.4	578.8	598.2	617.6	624.8	619.7	614.6	609.6	604.5
115°	628.9	754.8	748.0	741.2	734.4	727.6	721.9	717.2	712.6	708.0	703.4
117.5°	805.5	836.0	831.3	826.6	821.9	817.3	812.4	807.2	802.0	796.9	791.7
120°	899.9	896.6	891.8	886.9	882.0	877.1	872.6	868.5	864.4	860.4	856.3
122.5°	956.3	954.4	949.1	943.7	938.4	933.1	928.3	924.0	919.7	915.4	911.1
125°	1035.6	1033.7	1028.5	1023.3	1018.2	1013.0	1008.6	1005.1	1001.6	998.0	994.5
127.5°	1107.9	1105.1	1101.2	1097.4	1093.5	1089.7	1085.8	1081.9	1077.9	1074.0	1070.1
130°	1154.1	1151.1	1148.1	1145.1	1142.1	1139.1	1135.5	1131.1	1126.8	1122.4	1118.1
132.5°	1199.6	1197.1	1194.1	1191.1	1188.1	1185.1	1181.8	1178.1	1174.4	1170.7	1167.0
135°	1263.9	1261.2	1258.7	1256.3	1253.8	1251.4	1248.0	1243.6	1239.3	1234.9	1230.6
137.5°	1323.8	1321.1	1318.3	1315.6	1312.8	1310.0	1307.1	1304.1	1301.0	1298.0	1294.9
140°	1362.7	1360.3	1357.3	1354.3	1351.3	1348.3	1345.7	1343.5	1341.4	1339.2	1337.0
142.5°	1398.7	1396.5	1393.0	1389.6	1386.2	1382.8	1380.1	1378.1	1376.2	1374.2	1372.3
145°	1449.0	1447.1	1442.5	1437.9	1433.3	1428.6	1426.5	1426.7	1427.0	1427.3	1427.5
147.5°	1493.1	1491.6	1487.1	1482.5	1477.9	1473.4	1471.6	1472.6	1473.7	1474.7	1475.7
150°	1519.7	1518.1	1513.7	1509.4	1505.0	1500.7	1499.4	1501.3	1503.3	1505.2	1507.1
152.5°	1544.2	1542.5	1538.4	1534.3	1530.1	1526.0	1525.0	1527.1	1529.2	1531.4	1533.5
155°	1577.2	1575.6	1572.3	1569.0	1565.8	1562.5	1562.1	1564.5	1567.0	1569.4	1571.9
157.5°	1604.8	1603.0	1600.7	1598.4	1596.1	1593.8	1593.7	1595.8	1597.8	1599.9	1602.0
160°	1621.2	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6
162.5°	1636.1	1634.3	1632.9	1631.4	1630.0	1628.6	1628.7	1630.4	1632.0	1633.6	1635.3
165°	1654.5	1652.6	1651.8	1651.0	1650.2	1649.4	1649.8	1651.4	1653.0	1654.7	1656.3
167.5°	1669.9	1668.0	1667.3	1666.5	1665.8	1665.0	1665.4	1667.1	1668.7	1670.3	1672.0
170°	1677.8	1675.9	1675.3	1674.8	1674.2	1673.7	1674.2	1675.9	1677.5	1679.1	1680.8
172.5°	1683.6	1681.7	1681.2	1680.6	1680.1	1679.6	1680.1	1681.7	1683.4	1685.0	1686.6
175°	1690.0	1688.1	1687.6	1687.0	1686.5	1685.9	1686.6	1688.5	1690.4	1692.3	1694.2
177.5°	1691.1	1689.6	1689.3	1689.1	1688.9	1688.7	1689.3	1690.9	1692.4	1693.9	1695.4
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.3	10.1	10.7	12.2	12.1	12.6	13.0	13.1	13.3	13.2	13.2
90°	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8	27.2
92.5°	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1	29.8
95°	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1	50.4
97.5°	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9	66.0
100°	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9	74.1
102.5°	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5	77.3
105°	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6	80.6
107.5°	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4	98.4
110°	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9	159.7





TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8	341.6
115°	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9	503.0
117.5°	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5	775.1
120°	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9	903.2
122.5°	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3	958.3
125°	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6	1037.5
127.5°	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9	1110.6
130°	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1	1157.1
132.5°	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6	1202.2
135°	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9	1266.6
137.5°	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8	1326.4
140°	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7	1365.2
142.5°	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7	1400.9
145°	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0	1450.9
147.5°	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1	1494.5
150°	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7	1521.3
152.5°	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2	1545.8
155°	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2	1578.8
157.5°	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8	1606.7
160°	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2	1622.9
162.5°	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1	1638.0
165°	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5	1656.4
167.5°	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9	1671.8
170°	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8	1679.7
172.5°	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6	1685.5
175°	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0	1691.9
177.5°	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1	1692.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	13.8	14.0	13.9	14.0	14.5	14.3	14.4
90°	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331513

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)