

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331506-840

Luminaire Tested: **S122DIW-S485D710U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331506-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4482.1 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.6
10°-20°	207.5	4.6
20°-30°	305.0	6.8
30°-40°	354.3	7.9
40°-50°	354.0	7.9
50°-60°	308.7	6.9
60°-70°	228.2	5.1
70°-80°	129.3	2.9
80°-90°	38.3	0.9
90°-100°	56.3	1.3
100°-110°	174.8	3.9
110°-120°	298.7	6.7
120°-130°	392.8	8.8
130°-140°	440.9	9.8
140°-150°	432.3	9.6
150°-160°	362.6	8.1
160°-170°	240.5	5.4
170°-180°	84.1	1.9
0°-30°	586.3	13.1
0°-40°	940.7	21.0
0°-60°	1603.3	35.8
0°-90°	1999.1	44.6
90°-120°	529.8	11.8
90°-150°	1795.8	40.1
90°-180°	2483.0	55.4
0°-180°	4482.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	10	26	25	25	4
95°	39	46	48	48	46	45
105°	161	163	165	166	166	170
115°	300	304	303	302	300	296
125°	436	442	441	438	438	390
135°	564	572	574	573	571	436
145°	685	690	695	695	692	428
155°	783	785	788	791	789	360
165°	852	851	851	856	853	240
175°	886	884	883	888	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.0	11.1	11.3	11.4	11.5	11.8	12.3	12.7	13.2	13.7	13.2
90°	0.7	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9
92.5°	13.3	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9
95°	39.0	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0
97.5°	71.2	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6
100°	95.1	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4
102.5°	120.4	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2
105°	161.1	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2
107.5°	202.2	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6
110°	228.5	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.3	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8
115°	299.7	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6
117.5°	342.0	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5
120°	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2
122.5°	396.0	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6
125°	436.2	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1
127.5°	475.2	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5
130°	499.8	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8
132.5°	527.5	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9
135°	564.3	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8
137.5°	603.1	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7
140°	626.5	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9
142.5°	650.5	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8
145°	684.9	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8
147.5°	715.7	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3
150°	736.6	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7
152.5°	755.2	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0
155°	783.0	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4
157.5°	806.9	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9
160°	821.3	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6
162.5°	834.5	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7
165°	852.0	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4
167.5°	866.8	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5
170°	874.5	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7
172.5°	879.9	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1
175°	886.5	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9
177.5°	889.2	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	12.7	12.3	11.8	11.5	11.4	11.3	11.2	11.1
90°	25.5	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	23.9	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.3	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.5	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.7	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331506-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.4	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.5	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	343.1	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	398.2	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.6	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.9	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.5	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	534.2	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.7	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.5	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.0	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.0	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	725.7	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	789.2	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	812.0	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	825.6	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	837.8	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	853.6	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	866.7	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	873.8	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	879.3	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	885.0	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)