

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331518

Luminaire Tested: **S122DIW-S485D1240U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331518
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6278.6 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	39	39	39	32		
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	33	33	33	33	33	33	27		
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	28	28	28	28	28	28	22		
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	24	24	24	24	24	24	19		
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	20	20	20	20	20	20	16		
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	18	18	18	18	18	18	14		
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	16	16	16	16	16	16	12		
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	14	14	14	14	14	14	11		
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	12	12	12	12	12	12	10		
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	11	11	11	11	11	11	9		
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	10	10	10	10	10	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.2
10°-20°	205.5	3.3
20°-30°	302.1	4.8
30°-40°	350.9	5.6
40°-50°	350.5	5.6
50°-60°	305.6	4.9
60°-70°	226.0	3.6
70°-80°	128.0	2.0
80°-90°	40.5	0.6
90°-100°	97.4	1.6
100°-110°	302.4	4.8
110°-120°	516.9	8.2
120°-130°	679.7	10.8
130°-140°	762.9	12.2
140°-150°	748.1	11.9
150°-160°	627.4	10.0
160°-170°	416.2	6.6
170°-180°	145.5	2.3
0°-30°	580.6	9.2
0°-40°	931.5	14.8
0°-60°	1587.6	25.3
0°-90°	1982.2	31.6
90°-120°	916.6	14.6
90°-150°	3107.4	49.5
90°-180°	4296.0	68.4
0°-180°	6278.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	1	18	45	43	44	5
95°	67	80	83	83	80	77
105°	279	283	285	288	288	294
115°	519	526	524	522	519	513
125°	755	765	762	759	757	674
135°	976	990	993	992	988	754
145°	1185	1194	1202	1203	1198	740
155°	1355	1359	1363	1369	1365	623
165°	1474	1473	1473	1481	1476	416
175°	1534	1530	1527	1536	1529	146
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	11.0	11.4	11.9	12.3	12.7	13.4	14.4	15.4	16.4	17.4	16.9
90°	1.3	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8
92.5°	23.1	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3
95°	67.4	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0
97.5°	123.2	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5
100°	164.7	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9
102.5°	208.2	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7
105°	278.8	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8
107.5°	349.8	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8
110°	395.5	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.3	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3
115°	518.7	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6
117.5°	591.8	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2
120°	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5
122.5°	685.1	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6
125°	754.6	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6
127.5°	822.3	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4
130°	864.9	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5
132.5°	912.6	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6
135°	976.4	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9
137.5°	1043.5	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4
140°	1084.0	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1
142.5°	1125.5	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8
145°	1185.1	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3
147.5°	1238.3	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0
150°	1274.6	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4
152.5°	1306.8	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9
155°	1355.0	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2
157.5°	1396.2	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1
160°	1421.1	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7
162.5°	1443.9	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7
165°	1474.3	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0
167.5°	1499.7	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6
170°	1513.2	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0
172.5°	1522.5	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4
175°	1533.9	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5
177.5°	1538.6	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	16.4	15.9	15.4	15.1	15.0	14.9	14.9	14.8
90°	44.2	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.5	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	221.9	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	286.4	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.0	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331518

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.6	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.3	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	593.5	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	689.0	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	760.7	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	830.4	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	878.0	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	924.3	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.7	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1058.1	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.0	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.6	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1255.6	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1365.7	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1405.1	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1428.5	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1449.7	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1477.0	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1499.6	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1512.0	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1521.4	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1531.5	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)