

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331544-840

Luminaire Tested: **S122DIW-S675D1240U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331544-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D1240U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7304.3 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	1.7
10°-20°	371.4	5.1
20°-30°	539.0	7.4
30°-40°	568.8	7.8
40°-50°	503.6	6.9
50°-60°	401.9	5.5
60°-70°	273.2	3.7
70°-80°	140.0	1.9
80°-90°	40.0	0.5
90°-100°	98.3	1.3
100°-110°	305.4	4.2
110°-120°	522.0	7.1
120°-130°	686.4	9.4
130°-140°	770.4	10.5
140°-150°	755.4	10.3
150°-160°	633.6	8.7
160°-170°	420.3	5.8
170°-180°	146.9	2.0
0°-30°	1038.1	14.2
0°-40°	1606.9	22.0
0°-60°	2512.4	34.4
0°-90°	2965.5	40.6
90°-120°	925.7	12.7
90°-150°	3138.0	43.0
90°-180°	4339.0	59.4
0°-180°	7304.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	32
90°	44	1	44	1	44	21
95°	81	68	81	68	81	91
105°	291	282	291	282	291	306
115°	524	524	524	524	524	517
125°	765	762	765	762	765	682
135°	998	986	998	986	998	768
145°	1210	1197	1210	1197	1210	756
155°	1379	1368	1379	1368	1379	635
165°	1490	1489	1490	1489	1490	420
175°	1544	1549	1544	1549	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	19.6	19.6	19.9	19.5	19.4	19.8	20.0	19.7	20.2	20.7	19.9
90°	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6	45.2	45.8	39.4
92.5°	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9	41.7	41.6	40.1
95°	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8	83.8	83.8	83.2
97.5°	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9	140.9	140.9	139.8
100°	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7	180.7	180.7	179.9
102.5°	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1	223.9	223.7	222.6
105°	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2	288.6	288.1	287.5
107.5°	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5	359.3	359.0	359.0
110°	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0	455.8	456.5	456.7
115°	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5	528.8	529.0	529.6
117.5°	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4	600.1	600.8	602.4
120°	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8	646.8	646.8	649.1
122.5°	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8	696.4	697.1	698.7
125°	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2	769.1	769.9	770.8
127.5°	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6	839.6	840.6	841.7
130°	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7	887.2	887.8	888.4
132.5°	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4	934.7	935.9	935.8
135°	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5	1002.7	1003.0	1002.5
137.5°	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5	1068.8	1069.0	1068.2
140°	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0	1113.0	1113.0	1111.6
142.5°	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3	1153.1	1152.9	1151.9
145°	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5	1214.2	1213.9	1212.1
147.5°	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0	1267.4	1266.8	1265.6
150°	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3	1299.1
152.5°	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8	1332.4
155°	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2	1377.7	1376.2	1375.3
157.5°	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0	1416.9	1415.0	1414.4
160°	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6	1440.8	1439.1	1438.8
162.5°	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0	1462.0	1460.1	1459.8
165°	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6	1489.6	1487.5	1487.5
167.5°	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4	1512.4	1510.3	1510.4
170°	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9	1524.9	1522.9	1523.2
172.5°	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4	1534.4	1532.3	1532.6
175°	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6	1544.6	1542.5	1543.1
177.5°	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5	1549.0
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	19.0	17.7	16.5	16.3	14.3	13.6	11.3	9.3	9.6	9.9	9.8
90°	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3	4.8	8.3	11.8
92.5°	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3	25.9	28.5	31.0
95°	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1	71.0	73.9	76.9
97.5°	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4	126.9	129.6	132.1
100°	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3	168.6	171.0	173.3
102.5°	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3	212.2	214.0	215.9
105°	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6	282.4	283.3	284.2
107.5°	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3	354.6	355.9	357.1
110°	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4	401.1	402.8	404.7





TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7	451.4	453.1	454.9
115°	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8	525.5	527.3	529.0
117.5°	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6	600.0	602.3	604.6
120°	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	649.1	651.6	653.9
122.5°	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9	694.7	697.5	700.2
125°	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0	764.7	767.3	769.9
127.5°	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4	833.7	837.1	840.4
130°	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4	877.2	881.0	884.7
132.5°	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6	924.6	927.8	930.8
135°	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0	989.2	992.4	995.6
137.5°	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8	1056.4	1059.0	1061.7
140°	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7	1097.3	1099.9	1102.6
142.5°	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6	1139.2	1141.9	1144.5
145°	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8	1198.9	1200.9	1203.0
147.5°	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5	1252.9	1255.4	1257.9
150°	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2	1288.9	1290.7	1292.4
152.5°	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7	1321.4	1323.1	1324.8
155°	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4	1369.3	1370.1	1371.0
157.5°	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0	1410.6	1411.2	1411.8
160°	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1	1435.7	1436.3	1436.9
162.5°	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1	1458.3	1458.4	1458.5
165°	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8	1488.5	1488.2	1487.9
167.5°	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5	1513.6	1512.8	1511.9
170°	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1	1527.2	1526.4	1525.5
172.5°	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5	1536.7	1535.8	1534.9
175°	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0	1548.2	1547.3	1546.4
177.5°	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8	1553.1	1552.4	1551.7
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	10.1	10.6	11.5	12.8	13.6	14.5	14.0	13.8	13.7	12.8	12.8
90°	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6	44.1	43.5	43.3
92.5°	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9	42.0	42.1	42.2
95°	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8	83.8	83.8	83.5
97.5°	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9	140.9	140.9	140.9
100°	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7	180.7	180.7	180.6
102.5°	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1	224.4	224.6	224.6
105°	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2	289.8	290.4	290.7
107.5°	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5	359.7	360.0	359.4
110°	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	406.8



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0	454.3	453.6	453.0
115°	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5	528.2	527.9	527.3
117.5°	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4	598.6	597.9	597.2
120°	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8	646.8	646.8	646.4
122.5°	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8	695.1	694.4	693.7
125°	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2	767.3	766.5	765.9
127.5°	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6	837.5	836.5	835.5
130°	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7	886.1	885.4	884.6
132.5°	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4	932.1	930.9	929.8
135°	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5	1002.2	1001.9	1001.3
137.5°	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5	1068.3	1068.1	1067.4
140°	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0	1113.0	1113.0	1112.5
142.5°	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3	1153.6	1153.8	1153.3
145°	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5	1214.8	1215.0	1214.6
147.5°	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0	1268.7	1269.3	1269.1
150°	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7
152.5°	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2
155°	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2	1380.6	1382.0	1382.3
157.5°	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0	1420.9	1422.9	1423.2
160°	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6	1444.3	1446.0	1446.3
162.5°	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0	1465.9	1467.9	1468.2
165°	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6	1493.6	1495.7	1495.9
167.5°	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4	1516.4	1518.4	1518.7
170°	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9	1528.9	1531.1	1531.2
172.5°	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4	1538.4	1540.4	1540.5
175°	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6	1548.6	1550.6	1550.8
177.5°	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	12.8	12.5	12.5	12.2	12.5	12.5	12.8	12.8	12.8	13.7	13.8
90°	43.6	43.9	44.2	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6
92.5°	42.2	42.3	42.4	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9
95°	82.9	82.3	81.8	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8
97.5°	140.8	140.8	140.7	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9
100°	180.3	180.0	179.7	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7
102.5°	224.3	224.0	223.7	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1
105°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2
107.5°	358.1	356.8	355.4	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5
110°	406.0	405.1	404.1	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.3	451.7	451.1	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0
115°	526.4	525.5	524.6	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5
117.5°	596.3	595.4	594.6	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4
120°	645.5	644.7	643.8	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8
122.5°	693.1	692.4	691.8	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8
125°	765.6	765.3	765.0	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2
127.5°	834.6	833.6	832.7	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6
130°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7
132.5°	928.9	927.9	927.0	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4
135°	1000.4	999.6	998.7	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5
137.5°	1066.2	1065.1	1063.9	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5
140°	1111.3	1110.1	1108.9	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0
142.5°	1152.2	1150.9	1149.8	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3
145°	1213.5	1212.2	1211.1	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5
147.5°	1268.0	1266.9	1265.8	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0
150°	1302.9	1302.0	1301.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0
152.5°	1337.1	1336.1	1334.9	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1
155°	1381.5	1380.6	1379.7	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2
157.5°	1421.8	1420.4	1419.0	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0
160°	1445.2	1444.0	1442.9	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6
162.5°	1466.8	1465.4	1464.0	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0
165°	1494.5	1493.1	1491.6	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6
167.5°	1517.2	1515.7	1514.2	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4
170°	1529.4	1527.7	1525.9	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9
172.5°	1538.8	1537.1	1535.4	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4
175°	1549.0	1547.3	1545.6	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6
177.5°	1552.8	1551.4	1549.9	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	14.0	14.5	13.6	12.8	11.5	10.6	10.1	9.8	9.9	9.6	9.3
90°	45.2	45.8	39.4	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3
92.5°	41.7	41.6	40.1	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3
95°	83.8	83.8	83.2	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1
97.5°	140.9	140.9	139.8	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4
100°	180.7	180.7	179.9	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3
102.5°	223.9	223.7	222.6	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3
105°	288.6	288.1	287.5	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6
107.5°	359.3	359.0	359.0	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3
110°	407.3	407.3	407.3	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.8	456.5	456.7	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7
115°	528.8	529.0	529.6	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8
117.5°	600.1	600.8	602.4	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6
120°	646.8	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8
122.5°	696.4	697.1	698.7	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9
125°	769.1	769.9	770.8	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0
127.5°	839.6	840.6	841.7	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4
130°	887.2	887.8	888.4	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4
132.5°	934.7	935.9	935.8	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6
135°	1002.7	1003.0	1002.5	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0
137.5°	1068.8	1069.0	1068.2	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8
140°	1113.0	1113.0	1111.6	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7
142.5°	1153.1	1152.9	1151.9	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6
145°	1214.2	1213.9	1212.1	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8
147.5°	1267.4	1266.8	1265.6	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5
150°	1301.1	1300.3	1299.1	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2
152.5°	1334.9	1333.8	1332.4	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7
155°	1377.7	1376.2	1375.3	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4
157.5°	1416.9	1415.0	1414.4	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0
160°	1440.8	1439.1	1438.8	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1
162.5°	1462.0	1460.1	1459.8	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1
165°	1489.6	1487.5	1487.5	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8
167.5°	1512.4	1510.3	1510.4	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5
170°	1524.9	1522.9	1523.2	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1
172.5°	1534.4	1532.3	1532.6	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5
175°	1544.6	1542.5	1543.1	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0
177.5°	1549.9	1548.5	1549.0	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.3	13.6	14.3	16.3	16.5	17.7	19.0	19.9	20.7	20.2	19.7
90°	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6
92.5°	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9
95°	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8
97.5°	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9
100°	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7
102.5°	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1
105°	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2
107.5°	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5
110°	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3





TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0
115°	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5
117.5°	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4
120°	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8
122.5°	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8
125°	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2
127.5°	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6
130°	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7
132.5°	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4
135°	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5
137.5°	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5
140°	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0
142.5°	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3
145°	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5
147.5°	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0
150°	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0
152.5°	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1
155°	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2
157.5°	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0
160°	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6
162.5°	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0
165°	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6
167.5°	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4
170°	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9
172.5°	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4
175°	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6
177.5°	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	20.0	19.8	19.4	19.5	19.9	19.6	19.6
90°	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331544-840

CATALOG NUMBER: S122DIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)