

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331554-840

Luminaire Tested: **S122DIW-S675D1440U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331554-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7779.5 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.3
10°-20°	283.7	3.6
20°-30°	417.0	5.4
30°-40°	484.3	6.2
40°-50°	483.8	6.2
50°-60°	421.9	5.4
60°-70°	312.0	4.0
70°-80°	176.7	2.3
80°-90°	54.7	0.7
90°-100°	114.3	1.5
100°-110°	355.0	4.6
110°-120°	606.9	7.8
120°-130°	798.1	10.3
130°-140°	895.8	11.5
140°-150°	878.3	11.3
150°-160°	736.7	9.5
160°-170°	488.6	6.3
170°-180°	170.8	2.2
0°-30°	801.5	10.3
0°-40°	1285.8	16.5
0°-60°	2191.5	28.2
0°-90°	2734.9	35.2
90°-120°	1076.2	13.8
90°-150°	3648.4	46.9
90°-180°	5045.0	64.9
0°-180°	7779.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	2	21	53	50	52	6
95°	79	94	98	97	94	91
105°	327	332	335	338	338	346
115°	609	617	615	613	609	602
125°	886	899	895	891	889	791
135°	1146	1162	1166	1165	1160	885
145°	1392	1402	1411	1412	1407	869
155°	1591	1596	1600	1607	1603	732
165°	1731	1730	1730	1739	1732	488
175°	1801	1797	1793	1803	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	15.1	15.6	16.1	16.5	17.0	17.7	18.9	20.0	21.1	22.2	21.5
90°	1.5	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6
92.5°	27.1	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6
95°	79.2	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5
97.5°	144.6	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8
100°	193.4	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1
102.5°	244.5	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3
105°	327.3	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6
107.5°	410.7	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7
110°	464.3	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	522.8	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9
115°	608.9	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7
117.5°	694.9	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7
120°	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0
122.5°	804.5	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7
125°	886.1	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1
127.5°	965.5	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1
130°	1015.4	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6
132.5°	1071.5	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7
135°	1146.4	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9
137.5°	1225.3	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6
140°	1272.7	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0
142.5°	1321.5	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6
145°	1391.5	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6
147.5°	1453.9	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6
150°	1496.5	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8
152.5°	1534.3	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1
155°	1590.9	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7
157.5°	1639.3	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4
160°	1668.6	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2
162.5°	1695.4	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8
165°	1731.0	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8
167.5°	1760.8	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4
170°	1776.7	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9
172.5°	1787.7	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9
175°	1801.0	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8
177.5°	1806.5	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	20.8	20.2	19.5	19.1	19.0	18.8	18.7	18.6
90°	51.9	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.7	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.5	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	336.3	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.0	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	473.5	472.9	471.9	470.9	469.9	468.9



TEST NUMBER: P331554-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	529.1	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.4	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.9	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.9	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	893.1	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	974.9	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.9	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1085.3	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.5	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.3	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1340.9	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.0	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1474.3	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1603.5	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1649.7	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1677.2	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1702.1	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1734.2	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1760.7	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1775.3	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1786.2	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1798.2	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)