

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331520

Luminaire Tested: **S122DIW-S485D1440U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331520
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1440U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7146.2 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	11
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	1.3
10°-20°	269.0	3.8
20°-30°	390.5	5.5
30°-40°	412.0	5.8
40°-50°	364.8	5.1
50°-60°	291.1	4.1
60°-70°	197.9	2.8
70°-80°	101.5	1.4
80°-90°	31.6	0.4
90°-100°	113.2	1.6
100°-110°	351.6	4.9
110°-120°	601.0	8.4
120°-130°	790.3	11.1
130°-140°	887.0	12.4
140°-150°	869.7	12.2
150°-160°	729.5	10.2
160°-170°	483.8	6.8
170°-180°	169.1	2.4
0°-30°	752.0	10.5
0°-40°	1164.1	16.3
0°-60°	1820.1	25.5
0°-90°	2151.0	30.1
90°-120°	1065.7	14.9
90°-150°	3612.8	50.6
90°-180°	4995.0	69.9
0°-180°	7146.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	51	2	51	2	51	23
95°	94	78	94	78	94	104
105°	335	324	335	324	335	352
115°	603	603	603	603	603	596
125°	880	877	880	877	880	785
135°	1149	1135	1149	1135	1149	884
145°	1393	1378	1393	1378	1393	870
155°	1588	1575	1588	1575	1588	731
165°	1716	1714	1716	1714	1716	484
175°	1777	1783	1777	1783	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	18.0	18.0	18.2	17.8	17.8	18.1	18.2	18.1	18.5	18.9	17.7
90°	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4	52.1	52.8	45.4
92.5°	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2	48.1	47.9	46.2
95°	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5	96.5	96.5	95.8
97.5°	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2	162.2	162.2	160.9
100°	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0	208.0	208.0	207.0
102.5°	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0	257.8	257.5	256.2
105°	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0	332.3	331.7	331.0
107.5°	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9	413.6	413.4	413.4
110°	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9	524.7	525.5	525.8
115°	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4	608.7	609.1	609.7
117.5°	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1	690.9	691.7	693.5
120°	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7	744.7	744.7	747.4
122.5°	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0	801.8	802.6	804.5
125°	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4	885.4	886.4	887.5
127.5°	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4	966.6	967.9	969.1
130°	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8	1021.5	1022.1	1022.8
132.5°	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7	1076.1	1077.6	1077.5
135°	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1	1154.5	1154.8	1154.1
137.5°	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2	1230.5	1230.8	1229.9
140°	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4	1281.4	1281.4	1279.8
142.5°	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8	1327.5	1327.3	1326.1
145°	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2	1397.8	1397.5	1395.5
147.5°	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9	1459.2	1458.4	1457.1
150°	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0	1495.7
152.5°	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6	1534.0
155°	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8	1586.1	1584.4	1583.4
157.5°	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6	1631.3	1629.1	1628.5
160°	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8	1658.8	1656.8	1656.5
162.5°	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5	1683.2	1680.9	1680.6
165°	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3	1714.9	1712.6	1712.6
167.5°	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5	1741.2	1738.8	1738.9
170°	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0	1755.6	1753.3	1753.6
172.5°	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8	1766.5	1764.1	1764.5
175°	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6	1778.3	1775.9	1776.6
177.5°	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8	1783.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	16.6	15.1	13.6	13.1	11.4	10.6	8.6	6.9	7.4	7.9	8.1
90°	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5	5.5	9.5	13.6
92.5°	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8	29.8	32.7	35.7
95°	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4	81.7	85.1	88.4
97.5°	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2	146.2	149.1	152.1
100°	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5	194.1	196.8	199.5
102.5°	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1	244.3	246.4	248.5
105°	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1	325.1	326.1	327.1
107.5°	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7	408.2	409.7	411.2
110°	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8	461.8	463.8	465.8



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7	519.7	521.7	523.7
115°	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0	605.0	607.0	609.1
117.5°	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1	690.7	693.4	696.1
120°	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	747.4	750.1	752.8
122.5°	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6	799.8	803.0	806.2
125°	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4	880.4	883.4	886.4
127.5°	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1	959.9	963.7	967.6
130°	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5	1009.9	1014.3	1018.6
132.5°	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0	1064.6	1068.1	1071.7
135°	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2	1138.9	1142.6	1146.2
137.5°	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3	1216.3	1219.3	1222.3
140°	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3	1263.3	1266.4	1269.4
142.5°	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6	1311.6	1314.6	1317.6
145°	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9	1380.3	1382.6	1384.9
147.5°	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7	1442.5	1445.3	1448.2
150°	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9	1483.9	1486.0	1488.0
152.5°	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3	1521.3	1523.3	1525.3
155°	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4	1576.4	1577.4	1578.4
157.5°	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3	1624.0	1624.7	1625.4
160°	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3	1653.0	1653.6	1654.3
162.5°	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8	1679.0	1679.1	1679.2
165°	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1
167.5°	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6	1742.6	1741.6	1740.6
170°	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3	1758.3	1757.3	1756.3
172.5°	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2	1769.2	1768.2	1767.2
175°	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4	1782.4	1781.4	1780.4
177.5°	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9	1788.1	1787.3	1786.5
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	8.6	9.4	10.6	12.1	13.3	14.4	14.0	13.9	13.7	13.0	13.0
90°	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4	50.8	50.1	49.9
92.5°	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2	48.3	48.5	48.6
95°	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5	96.5	96.5	96.1
97.5°	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2	162.2	162.2	162.2
100°	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0	208.0	208.0	207.9
102.5°	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0	258.3	258.6	258.5
105°	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0	333.7	334.3	334.7
107.5°	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9	414.2	414.4	413.8
110°	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.3



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9	523.1	522.3	521.5
115°	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4	608.0	607.7	607.0
117.5°	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1	689.3	688.5	687.5
120°	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7	744.7	744.7	744.2
122.5°	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0	800.2	799.4	798.6
125°	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4	883.4	882.4	881.8
127.5°	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4	964.2	963.0	961.9
130°	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8	1020.1	1019.4	1018.4
132.5°	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7	1073.2	1071.7	1070.4
135°	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1	1153.8	1153.5	1152.8
137.5°	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2	1230.0	1229.7	1228.9
140°	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4	1281.4	1281.4	1280.8
142.5°	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8	1328.1	1328.3	1327.8
145°	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2	1398.5	1398.8	1398.3
147.5°	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9	1460.6	1461.4	1461.1
150°	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0
152.5°	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7
155°	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8	1589.5	1591.1	1591.5
157.5°	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6	1635.9	1638.2	1638.5
160°	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8	1662.8	1664.8	1665.2
162.5°	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5	1687.8	1690.0	1690.4
165°	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3	1719.6	1722.0	1722.3
167.5°	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5	1745.9	1748.2	1748.5
170°	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0	1760.3	1762.7	1762.8
172.5°	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8	1771.2	1773.5	1773.7
175°	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6	1782.9	1785.3	1785.5
177.5°	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	13.0	12.8	12.9	12.6	12.9	12.8	13.0	13.0	13.0	13.7	13.9
90°	50.3	50.6	50.9	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4
92.5°	48.6	48.7	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2
95°	95.5	94.8	94.1	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5
97.5°	162.1	162.0	162.0	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2
100°	207.5	207.2	206.9	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0
102.5°	258.2	257.9	257.5	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0
105°	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0
107.5°	412.3	410.7	409.2	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9
110°	467.3	466.3	465.3	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.8	520.1	519.3	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9
115°	606.0	605.0	604.0	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4
117.5°	686.5	685.5	684.5	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1
120°	743.2	742.2	741.2	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7
122.5°	797.9	797.2	796.4	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0
125°	881.4	881.1	880.8	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4
127.5°	960.8	959.7	958.7	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4
130°	1017.1	1015.8	1014.4	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8
132.5°	1069.4	1068.3	1067.2	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7
135°	1151.8	1150.8	1149.8	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1
137.5°	1227.6	1226.2	1224.9	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2
140°	1279.4	1278.1	1276.7	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4
142.5°	1326.5	1325.1	1323.8	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8
145°	1397.0	1395.7	1394.3	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2
147.5°	1459.8	1458.5	1457.3	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9
150°	1500.0	1499.0	1498.0	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0
152.5°	1539.4	1538.1	1536.9	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1
155°	1590.5	1589.5	1588.5	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8
157.5°	1636.9	1635.3	1633.7	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6
160°	1663.8	1662.5	1661.2	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8
162.5°	1688.8	1687.2	1685.6	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5
165°	1720.6	1719.0	1717.3	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3
167.5°	1746.8	1745.0	1743.3	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5
170°	1760.8	1758.8	1756.8	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0
172.5°	1771.7	1769.7	1767.7	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8
175°	1783.4	1781.4	1779.4	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6
177.5°	1787.7	1786.1	1784.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	14.0	14.4	13.3	12.1	10.6	9.4	8.6	8.1	7.9	7.4	6.9
90°	52.1	52.8	45.4	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5
92.5°	48.1	47.9	46.2	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8
95°	96.5	96.5	95.8	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4
97.5°	162.2	162.2	160.9	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2
100°	208.0	208.0	207.0	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5
102.5°	257.8	257.5	256.2	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1
105°	332.3	331.7	331.0	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1
107.5°	413.6	413.4	413.4	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7
110°	468.9	468.9	468.9	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	524.7	525.5	525.8	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7
115°	608.7	609.1	609.7	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0
117.5°	690.9	691.7	693.5	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1
120°	744.7	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7
122.5°	801.8	802.6	804.5	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6
125°	885.4	886.4	887.5	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4
127.5°	966.6	967.9	969.1	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1
130°	1021.5	1022.1	1022.8	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5
132.5°	1076.1	1077.6	1077.5	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0
135°	1154.5	1154.8	1154.1	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2
137.5°	1230.5	1230.8	1229.9	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3
140°	1281.4	1281.4	1279.8	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3
142.5°	1327.5	1327.3	1326.1	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6
145°	1397.8	1397.5	1395.5	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9
147.5°	1459.2	1458.4	1457.1	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7
150°	1498.0	1497.0	1495.7	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9
152.5°	1536.9	1535.6	1534.0	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3
155°	1586.1	1584.4	1583.4	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4
157.5°	1631.3	1629.1	1628.5	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3
160°	1658.8	1656.8	1656.5	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3
162.5°	1683.2	1680.9	1680.6	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8
165°	1714.9	1712.6	1712.6	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1
167.5°	1741.2	1738.8	1738.9	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6
170°	1755.6	1753.3	1753.6	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3
172.5°	1766.5	1764.1	1764.5	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2
175°	1778.3	1775.9	1776.6	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4
177.5°	1784.4	1782.8	1783.4	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.6	10.6	11.4	13.1	13.6	15.1	16.6	17.7	18.9	18.5	18.1
90°	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4
92.5°	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2
95°	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5
97.5°	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2
100°	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0
102.5°	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0
105°	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0
107.5°	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9
110°	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9
115°	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4
117.5°	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1
120°	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7
122.5°	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0
125°	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4
127.5°	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4
130°	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8
132.5°	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7
135°	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1
137.5°	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2
140°	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4
142.5°	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8
145°	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2
147.5°	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9
150°	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0
152.5°	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1
155°	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8
157.5°	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6
160°	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8
162.5°	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5
165°	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3
167.5°	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5
170°	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0
172.5°	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8
175°	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6
177.5°	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	18.2	18.1	17.8	17.8	18.2	18.0	18.0
90°	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331520

CATALOG NUMBER: S122DIW-S485D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)