

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331526-840

Luminaire Tested: **S122DIW-S675D435U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331526-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D435U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4477.5 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	98	94	91	96	92	89	86	82	80	77	72	71	69	64	62	61	57
2	93	86	80	75	88	81	76	72	73	69	65	64	61	59	57	55	53	49
3	86	76	69	63	80	72	66	61	65	60	55	58	54	50	51	48	45	42
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29
7	62	50	42	37	59	48	41	35	43	37	33	39	34	30	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	2.9
10°-20°	371.4	8.3
20°-30°	539.0	12.0
30°-40°	568.8	12.7
40°-50°	503.6	11.2
50°-60°	401.9	9.0
60°-70°	273.2	6.1
70°-80°	140.0	3.1
80°-90°	35.9	0.8
90°-100°	34.4	0.8
100°-110°	106.7	2.4
110°-120°	182.4	4.1
120°-130°	239.9	5.4
130°-140°	269.2	6.0
140°-150°	263.9	5.9
150°-160°	221.4	4.9
160°-170°	146.8	3.3
170°-180°	51.3	1.1
0°-30°	1038.1	23.2
0°-40°	1606.9	35.9
0°-60°	2512.4	56.1
0°-90°	2961.5	66.1
90°-120°	323.4	7.2
90°-150°	1096.4	24.5
90°-180°	1516.0	33.9
0°-180°	4477.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	16	0	16	0	16	8
95°	28	24	28	24	28	32
105°	102	98	102	98	102	107
115°	183	183	183	183	183	181
125°	267	266	267	266	267	238
135°	349	345	349	345	349	268
145°	423	418	423	418	423	264
155°	482	478	482	478	482	222
165°	521	520	521	520	521	147
175°	540	541	540	541	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	13.8	13.8	14.2	13.7	13.7	14.1	14.2	13.8	14.3	14.7	14.7
90°	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7	15.9	16.1	13.7
92.5°	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6	14.5	14.5	14.0
95°	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3	29.3	29.3	29.1
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	48.9
100°	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1	63.1	63.1	62.8
102.5°	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3	78.3	78.2	77.8
105°	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1	100.9	100.7	100.5
107.5°	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6	125.5	125.4	125.4
110°	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1	159.3	159.5	159.6
115°	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6	184.7	184.8	185.0
117.5°	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4	209.6	210.0	210.5
120°	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0	226.0	226.0	226.8
122.5°	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1	243.4	243.6	244.2
125°	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4	268.7	269.0	269.3
127.5°	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0	293.4	293.8	294.1
130°	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8	310.0	310.2	310.4
132.5°	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2	326.6	327.0	327.0
135°	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2	350.3	350.4	350.2
137.5°	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3	373.4	373.5	373.2
140°	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9	388.9	388.9	388.4
142.5°	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9	402.9	402.8	402.4
145°	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3	424.2	424.1	423.5
147.5°	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0	442.8	442.6	442.2
150°	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3	453.9
152.5°	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1	465.5
155°	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9	481.4	480.9	480.6
157.5°	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7	495.1	494.4	494.2
160°	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0	503.4	502.8	502.7
162.5°	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5	510.8	510.2	510.1
165°	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2	520.5	519.8	519.8
167.5°	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2	528.5	527.8	527.8
170°	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5	532.8	532.1	532.2
172.5°	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8	536.1	535.4	535.5
175°	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4	539.7	539.0	539.2
177.5°	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1	541.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	14.6	14.2	13.8	14.2	12.8	12.5	10.6	9.2	9.0	8.8	8.3
90°	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2	9.1	9.9	10.8
95°	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8	24.8	25.9	26.9
97.5°	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4	44.3	45.2	46.2
100°	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1	58.9	59.7	60.6
102.5°	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5	74.1	74.7	75.4
105°	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4	98.7	99.0	99.3
107.5°	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4	123.9	124.3	124.8
110°	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6	140.2	140.8	141.4





TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1	157.7	158.3	159.0
115°	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0	183.6	184.2	184.8
117.5°	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8	209.6	210.5	211.3
120°	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.8	227.6	228.4
122.5°	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8	242.8	243.7	244.7
125°	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3	267.2	268.1	269.0
127.5°	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1	291.3	292.5	293.7
130°	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2	306.5	307.8	309.1
132.5°	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0	323.1	324.2	325.3
135°	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6	345.7	346.8	347.9
137.5°	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2	369.1	370.0	370.9
140°	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5	383.4	384.4	385.3
142.5°	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2	398.1	399.0	399.9
145°	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2	418.9	419.6	420.3
147.5°	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0	437.8	438.7	439.5
150°	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8	450.4	451.0	451.6
152.5°	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1	461.7	462.3	462.9
155°	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1	478.4	478.7	479.1
157.5°	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7	492.9	493.1	493.3
160°	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5	501.7	501.9	502.1
162.5°	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5	509.6	509.6	509.6
165°	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2	520.1	520.0	519.9
167.5°	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2	528.9	528.6	528.3
170°	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9	533.6	533.3	533.0
172.5°	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2	536.9	536.6	536.3
175°	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3	541.0	540.7	540.4
177.5°	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9	542.7	542.4	542.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	8.1	8.0	8.1	8.5	8.5	8.6	8.1	8.1	8.1	7.2	7.2
90°	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7	15.5	15.2	15.1
92.5°	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6	14.6	14.7	14.7
95°	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3	29.3	29.3	29.2
97.5°	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2	49.2	49.2	49.2
100°	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1	63.1	63.1	63.1
102.5°	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3	78.4	78.5	78.5
105°	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1	101.3	101.5	101.6
107.5°	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6	125.7	125.8	125.6
110°	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.1



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1	158.8	158.5	158.2
115°	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6	184.5	184.4	184.2
117.5°	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4	209.1	208.9	208.6
120°	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0	226.0	226.0	225.9
122.5°	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1	242.9	242.6	242.4
125°	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4	268.1	267.8	267.6
127.5°	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0	292.7	292.3	292.0
130°	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8	309.6	309.4	309.1
132.5°	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2	325.7	325.3	324.9
135°	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2	350.1	350.0	349.8
137.5°	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3	373.2	373.2	372.9
140°	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9	388.9	388.9	388.7
142.5°	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9	403.0	403.1	402.9
145°	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3	424.4	424.5	424.3
147.5°	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0	443.3	443.5	443.4
150°	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9	455.2	455.6	455.6
152.5°	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8	467.2	467.6	467.6
155°	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9	482.4	482.9	483.0
157.5°	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7	496.4	497.2	497.3
160°	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0	504.6	505.2	505.3
162.5°	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5	512.2	512.9	513.0
165°	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2	521.9	522.6	522.7
167.5°	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2	529.9	530.6	530.7
170°	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5	534.2	534.9	535.0
172.5°	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8	537.6	538.3	538.3
175°	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4	541.1	541.8	541.9
177.5°	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1	542.5	543.0	543.0
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	7.2	6.8	6.8	6.4	6.8	6.8	7.2	7.2	7.2	8.1	8.1
90°	15.2	15.3	15.5	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7
92.5°	14.7	14.7	14.8	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6
95°	29.0	28.8	28.6	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.0	62.9	62.8	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1
102.5°	78.4	78.3	78.2	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3
105°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1
107.5°	125.1	124.6	124.2	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6
110°	141.8	141.5	141.2	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	158.0	157.8	157.6	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1
115°	183.9	183.6	183.3	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6
117.5°	208.3	208.0	207.7	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4
120°	225.6	225.3	225.0	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0
122.5°	242.2	242.0	241.7	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1
125°	267.5	267.4	267.3	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4
127.5°	291.5	291.2	290.9	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0
130°	308.7	308.3	307.9	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8
132.5°	324.6	324.2	323.9	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2
135°	349.5	349.2	348.9	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2
137.5°	372.5	372.1	371.7	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3
140°	388.3	387.9	387.5	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9
142.5°	402.5	402.1	401.7	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9
145°	423.9	423.5	423.1	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3
147.5°	443.0	442.6	442.2	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0
150°	455.2	454.9	454.6	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9
152.5°	467.2	466.8	466.5	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8
155°	482.7	482.4	482.1	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9
157.5°	496.8	496.2	495.8	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7
160°	504.9	504.5	504.1	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0
162.5°	512.5	512.0	511.5	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5
165°	522.2	521.7	521.2	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2
167.5°	530.1	529.6	529.1	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2
170°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5
172.5°	537.7	537.0	536.4	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8
175°	541.3	540.7	540.1	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4
177.5°	542.5	542.1	541.6	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	8.1	8.6	8.5	8.5	8.1	8.0	8.1	8.3	8.8	9.0	9.2
90°	15.9	16.1	13.7	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5
92.5°	14.5	14.5	14.0	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2
95°	29.3	29.3	29.1	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8
97.5°	49.2	49.2	48.9	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4
100°	63.1	63.1	62.8	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1
102.5°	78.3	78.2	77.8	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5
105°	100.9	100.7	100.5	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4
107.5°	125.5	125.4	125.4	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4
110°	142.3	142.3	142.3	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	159.3	159.5	159.6	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1
115°	184.7	184.8	185.0	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0
117.5°	209.6	210.0	210.5	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8
120°	226.0	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0
122.5°	243.4	243.6	244.2	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8
125°	268.7	269.0	269.3	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3
127.5°	293.4	293.8	294.1	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1
130°	310.0	310.2	310.4	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2
132.5°	326.6	327.0	327.0	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0
135°	350.3	350.4	350.2	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6
137.5°	373.4	373.5	373.2	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2
140°	388.9	388.9	388.4	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5
142.5°	402.9	402.8	402.4	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2
145°	424.2	424.1	423.5	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2
147.5°	442.8	442.6	442.2	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0
150°	454.6	454.3	453.9	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8
152.5°	466.5	466.1	465.5	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1
155°	481.4	480.9	480.6	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1
157.5°	495.1	494.4	494.2	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7
160°	503.4	502.8	502.7	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5
162.5°	510.8	510.2	510.1	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5
165°	520.5	519.8	519.8	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2
167.5°	528.5	527.8	527.8	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2
170°	532.8	532.1	532.2	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9
172.5°	536.1	535.4	535.5	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2
175°	539.7	539.0	539.2	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3
177.5°	541.6	541.1	541.2	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.6	12.5	12.8	14.2	13.8	14.2	14.6	14.7	14.7	14.3	13.8
90°	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7
92.5°	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6
95°	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3
97.5°	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2
100°	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1
102.5°	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3
105°	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1
107.5°	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6
110°	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3





TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1
115°	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6
117.5°	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4
120°	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0
122.5°	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1
125°	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4
127.5°	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0
130°	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8
132.5°	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2
135°	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2
137.5°	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3
140°	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9
142.5°	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9
145°	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3
147.5°	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0
150°	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9
152.5°	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8
155°	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9
157.5°	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7
160°	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0
162.5°	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5
165°	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2
167.5°	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2
170°	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5
172.5°	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8
175°	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4
177.5°	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	14.2	14.1	13.7	13.7	14.2	13.8	13.8
90°	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331526-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)