

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331530-840

Luminaire Tested: **S122DIW-S675D435U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331530-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4245.9 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	67	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	40	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	2.4
10°-20°	283.7	6.7
20°-30°	417.0	9.8
30°-40°	484.3	11.4
40°-50°	483.8	11.4
50°-60°	421.9	9.9
60°-70°	312.0	7.3
70°-80°	176.7	4.2
80°-90°	49.7	1.2
90°-100°	34.4	0.8
100°-110°	106.7	2.5
110°-120°	182.4	4.3
120°-130°	239.9	5.6
130°-140°	269.2	6.3
140°-150°	263.9	6.2
150°-160°	221.4	5.2
160°-170°	146.8	3.5
170°-180°	51.3	1.2
0°-30°	801.5	18.9
0°-40°	1285.8	30.3
0°-60°	2191.5	51.6
0°-90°	2729.9	64.3
90°-120°	323.4	7.6
90°-150°	1096.4	25.8
90°-180°	1516.0	35.7
0°-180°	4245.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	0	6	16	15	16	3
95°	24	28	29	29	28	27
105°	98	100	101	102	102	104
115°	183	186	185	184	183	181
125°	266	270	269	268	267	238
135°	345	349	350	350	349	266
145°	418	421	424	424	423	261
155°	478	480	481	483	482	220
165°	520	520	520	523	521	147
175°	541	540	539	542	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	14.9	14.8	14.6	14.5	14.4	14.4	14.5	14.5	14.6	14.7	14.1
90°	0.5	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9
92.5°	8.2	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5
95°	23.8	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3
97.5°	43.4	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2
100°	58.1	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1
102.5°	73.5	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3
105°	98.4	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9
107.5°	123.4	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5
110°	139.6	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.1	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3
115°	183.0	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7
117.5°	208.8	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6
120°	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0
122.5°	241.8	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4
125°	266.3	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7
127.5°	290.1	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4
130°	305.2	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0
132.5°	322.0	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6
135°	344.6	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3
137.5°	368.2	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4
140°	382.5	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9
142.5°	397.2	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9
145°	418.2	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2
147.5°	437.0	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8
150°	449.8	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6
152.5°	461.1	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5
155°	478.1	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4
157.5°	492.7	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1
160°	501.5	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4
162.5°	509.5	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8
165°	520.2	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5
167.5°	529.2	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5
170°	533.9	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8
172.5°	537.2	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1
175°	541.3	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7
177.5°	542.9	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	13.5	13.0	12.4	12.0	11.8	11.7	11.5	11.3
90°	15.7	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.3	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.1	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.6	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331530-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.1	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.6	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.4	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	243.1	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.4	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	293.0	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.8	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	326.2	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.2	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.3	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	402.9	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.3	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.0	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	481.9	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	495.7	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.0	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	511.5	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.2	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.2	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	533.5	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	536.8	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	540.4	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)