

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331577-840

Luminaire Tested: **S122DIW-S865D1240U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331577-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8552.9 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42					42			
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35					35			
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	38	36	34	29					29			
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25					25			
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21					21			
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	18					18			
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16					16			
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14					14			
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13					13			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12					12			
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	1.5
10°-20°	368.7	4.3
20°-30°	542.0	6.3
30°-40°	629.6	7.4
40°-50°	628.9	7.4
50°-60°	548.4	6.4
60°-70°	405.5	4.7
70°-80°	229.7	2.7
80°-90°	66.0	0.8
90°-100°	56.9	0.7
100°-110°	208.8	2.4
110°-120°	558.2	6.5
120°-130°	921.5	10.8
130°-140°	980.0	11.5
140°-150°	910.9	10.6
150°-160°	732.3	8.6
160°-170°	471.9	5.5
170°-180°	162.4	1.9
0°-30°	1041.8	12.2
0°-40°	1671.3	19.5
0°-60°	2848.6	33.3
0°-90°	3549.8	41.5
90°-120°	824.0	9.6
90°-150°	3636.4	42.5
90°-180°	5003.0	58.5
0°-180°	8552.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	1	15	25	31	33	6
95°	80	42	48	54	53	98
105°	376	392	75	88	94	401
115°	710	732	762	217	101	699
125°	1004	1021	1044	1052	1056	895
135°	1243	1262	1274	1285	1284	959
145°	1442	1442	1461	1469	1464	901
155°	1587	1578	1591	1598	1589	731
165°	1673	1666	1669	1677	1669	472
175°	1711	1703	1705	1712	1701	163
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.6	19.7	19.8	19.9	20.1	20.1	20.1	20.0	20.0	20.0	19.5
90°	1.2	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1
92.5°	24.9	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4
95°	80.3	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6
97.5°	159.4	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5
100°	218.6	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6
102.5°	283.9	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2
105°	375.6	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4
107.5°	480.1	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4
110°	547.2	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	610.5	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1
115°	710.3	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1
117.5°	799.5	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4
120°	864.7	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8
122.5°	920.1	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7
125°	1004.3	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8
127.5°	1080.7	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8
130°	1129.1	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5
132.5°	1178.5	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4
135°	1242.7	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4
137.5°	1307.7	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9
140°	1350.2	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1
142.5°	1385.8	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5
145°	1441.6	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3
147.5°	1490.3	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8
150°	1522.0	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7
152.5°	1548.6	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4
155°	1587.4	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8
157.5°	1617.8	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6
160°	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2
162.5°	1651.4	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2
165°	1672.6	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8
167.5°	1688.5	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4
170°	1697.4	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4
172.5°	1703.2	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2
175°	1710.9	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7
177.5°	1712.1	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	19.1	18.6	18.2	17.9	17.8	17.7	17.5	17.4
90°	27.5	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.1	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	50.9	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	66.7	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	74.8	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	78.1	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	81.4	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	99.4	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	161.3	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331577-840

CATALOG NUMBER: S122DIW-S865D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	345.0	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	508.0	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	782.7	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	912.1	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	967.8	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1047.7	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1121.6	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1168.5	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1214.1	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1279.1	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1339.5	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1378.7	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1414.7	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1465.2	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1509.2	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1536.3	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1561.0	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1594.4	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1622.6	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1638.9	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1654.2	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1688.3	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1696.3	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1702.1	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1708.6	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1709.3	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)