

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331537

Luminaire Tested: **S122DIW-S675D970U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331537  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D970U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6803.6 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



57% Up

43% Dn



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43				43
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37				37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32				32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27				27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21				21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19				19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17				17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	18	15				15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14				14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13				13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.5	1.9
10°-20°	367.8	5.4
20°-30°	533.7	7.8
30°-40°	563.2	8.3
40°-50°	498.7	7.3
50°-60°	398.0	5.8
60°-70°	270.5	4.0
70°-80°	138.7	2.0
80°-90°	36.7	0.5
90°-100°	44.1	0.6
100°-110°	161.5	2.4
110°-120°	431.8	6.3
120°-130°	712.8	10.5
130°-140°	758.0	11.1
140°-150°	704.6	10.4
150°-160°	566.5	8.3
160°-170°	365.0	5.4
170°-180°	125.6	1.8
0°-30°	1028.0	15.1
0°-40°	1591.2	23.4
0°-60°	2487.8	36.6
0°-90°	2933.7	43.1
90°-120°	637.4	9.4
90°-150°	2812.8	41.3
90°-180°	3870.0	56.9
0°-180°	6803.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	26	1	26	1	26	13
95°	41	62	41	62	41	38
105°	73	290	73	290	73	76
115°	78	549	78	549	78	196
125°	817	777	817	777	817	707
135°	993	961	993	961	993	765
145°	1132	1115	1132	1115	1132	708
155°	1229	1228	1229	1228	1229	567
165°	1291	1294	1291	1294	1291	364
175°	1316	1323	1316	1323	1316	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	15.8	15.7	16.0	15.5	15.4	15.7	15.5	14.9	15.1	15.3	15.3
90°	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2	20.2	19.1	17.4
92.5°	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3	22.7	22.2	21.3
95°	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4	38.3	37.3	35.8
97.5°	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6	50.7	49.9	46.4
100°	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9	56.2	54.5	50.9
102.5°	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4	58.2	56.0	86.2
105°	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0	60.6	58.3	116.3
107.5°	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8	79.2	81.6	151.1
110°	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7	146.0	167.2	228.6



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8	344.3	421.8	436.9
115°	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9	491.2	589.6	584.3
117.5°	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4	629.2	653.0	649.4
120°	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5	703.0	700.4	696.6
122.5°	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6	747.0	745.5	741.3
125°	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4	808.9	807.4	803.4
127.5°	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6	865.4	863.2	860.2
130°	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8	901.5	899.2	896.8
132.5°	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1	937.1	935.1	932.7
135°	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4	987.3	985.2	983.2
137.5°	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1	1034.1	1032.0	1029.8
140°	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4	1064.5	1062.6	1060.2
142.5°	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3	1092.6	1090.8	1088.2
145°	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4	1131.9	1130.4	1126.8
147.5°	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4	1166.3	1165.2	1161.6
150°	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4	1187.1	1185.8	1182.4
152.5°	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5	1206.2	1204.9	1201.7
155°	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3	1232.0	1230.7	1228.2
157.5°	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0	1253.6	1252.1	1250.3
160°	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7	1266.4	1265.1	1263.9
162.5°	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5	1278.0	1276.6	1275.5
165°	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9	1290.3
167.5°	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9	1304.4	1303.0	1302.4
170°	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1	1310.6	1309.1	1308.7
172.5°	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6	1315.2	1313.7	1313.2
175°	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6	1320.1	1318.6	1318.2
177.5°	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2	1321.0	1319.8	1319.6
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	15.4	15.1	14.7	15.1	13.4	13.0	10.9	9.2	9.2	9.3	8.9
90°	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0	3.3	5.6	8.0
92.5°	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3	19.1	18.9	18.7
95°	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1	55.1	48.1	41.1
97.5°	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3	103.5	83.8	64.0
100°	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1	140.0	110.9	81.9
102.5°	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6	213.4	207.3	201.1
105°	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5	296.9	303.2	309.6
107.5°	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3	376.5	381.6	386.7
110°	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3	427.8	432.2	436.7





TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2	476.2	480.1	484.1
115°	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4	553.0	556.7	560.3
117.5°	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4	622.5	626.5	630.5
120°	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9	672.1	675.2	678.4
122.5°	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7	715.0	718.4	721.7
125°	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8	779.6	782.4	785.1
127.5°	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9	839.0	842.0	845.1
130°	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4	876.8	880.2	883.5
132.5°	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6	914.5	917.4	920.2
135°	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3	964.7	968.1	971.5
137.5°	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5	1013.9	1016.3	1018.7
140°	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4	1046.1	1047.8	1049.5
142.5°	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9	1073.4	1075.0	1076.5
145°	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1	1114.9	1114.7	1114.5
147.5°	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8	1151.9	1151.1	1150.3
150°	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2	1175.7	1174.2	1172.8
152.5°	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9	1196.2	1194.5	1192.9
155°	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9	1225.9	1224.0	1222.1
157.5°	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4	1249.8	1248.1	1246.5
160°	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1263.9	1262.6	1261.3
162.5°	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4	1276.1	1274.8	1273.5
165°	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8	1292.5	1291.2	1290.0
167.5°	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0	1304.7	1303.5	1302.2
170°	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9	1311.6	1310.4	1309.1
172.5°	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5	1316.2	1314.9	1313.7
175°	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4	1321.9	1320.4	1319.0
177.5°	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4	1323.2	1322.0	1320.8
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	9.0	9.0	8.9	9.3	9.2	9.1	8.9	9.1	9.4	8.8	8.9
90°	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2	22.3	23.4	24.1
92.5°	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3	23.8	24.4	24.8
95°	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4	40.5	41.5	41.9
97.5°	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6	52.4	53.3	53.8
100°	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9	59.6	61.3	62.3
102.5°	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4	62.6	64.8	66.2
105°	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0	65.3	67.6	69.2
107.5°	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8	74.5	72.1	71.3
110°	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7	103.5	82.3	72.1



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8	189.4	111.9	73.5
115°	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9	294.6	196.3	139.5
117.5°	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4	581.7	557.9	520.9
120°	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5	708.0	710.6	697.5
122.5°	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6	750.1	751.6	749.6
125°	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4	811.9	813.4	814.4
127.5°	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6	869.7	871.9	873.0
130°	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8	906.2	908.5	909.6
132.5°	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1	941.1	943.1	944.0
135°	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4	991.5	993.6	994.5
137.5°	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1	1038.2	1040.3	1041.0
140°	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4	1068.3	1070.2	1070.6
142.5°	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3	1096.1	1097.8	1098.1
145°	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4	1134.9	1136.3	1136.6
147.5°	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4	1168.5	1169.6	1169.7
150°	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4	1189.6	1190.9	1191.0
152.5°	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5	1208.7	1210.0	1210.0
155°	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3	1234.5	1235.8	1235.6
157.5°	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0	1256.5	1257.9	1257.8
160°	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7	1268.9	1270.2	1270.1
162.5°	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5	1280.9	1282.4	1282.2
165°	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9
167.5°	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9	1307.4	1308.9	1308.7
170°	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1	1313.5	1315.0	1314.8
172.5°	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6	1318.1	1319.6	1319.4
175°	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6	1323.1	1324.6	1324.3
177.5°	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2	1323.3	1324.5	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	9.0	8.7	8.8	8.4	8.8	8.7	9.0	8.9	8.8	9.4	9.1
90°	24.5	24.9	25.4	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2
92.5°	25.0	25.3	25.5	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3
95°	41.7	41.5	41.3	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4
97.5°	54.1	54.3	54.6	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6
100°	62.7	63.2	63.6	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9
102.5°	66.8	67.4	68.0	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4
105°	70.1	70.9	71.8	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0
107.5°	72.2	73.0	73.9	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8
110°	72.9	73.8	74.6	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	74.2	74.9	75.6	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8
115°	124.2	108.9	93.6	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9
117.5°	470.6	420.4	370.2	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4
120°	668.9	640.2	611.5	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5
122.5°	744.0	738.5	732.9	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6
125°	815.1	815.7	816.3	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4
127.5°	873.2	873.3	873.4	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6
130°	909.3	909.1	908.9	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8
132.5°	943.7	943.5	943.3	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1
135°	994.1	993.6	993.2	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4
137.5°	1040.3	1039.5	1038.8	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1
140°	1069.6	1068.5	1067.4	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4
142.5°	1097.1	1096.0	1095.0	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3
145°	1135.5	1134.4	1133.4	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4
147.5°	1168.8	1167.9	1167.0	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4
150°	1190.0	1188.9	1187.8	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4
152.5°	1208.6	1207.2	1205.8	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5
155°	1233.9	1232.2	1230.5	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3
157.5°	1256.1	1254.5	1252.8	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0
160°	1268.6	1267.1	1265.7	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7
162.5°	1280.3	1278.5	1276.7	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5
165°	1295.4	1293.9	1292.4	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9
167.5°	1306.8	1304.9	1303.0	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9
170°	1312.9	1311.0	1309.1	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1
172.5°	1317.5	1315.6	1313.7	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6
175°	1322.1	1320.0	1317.9	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6
177.5°	1322.8	1321.3	1319.8	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	8.9	9.1	9.2	9.3	8.9	9.0	9.0	8.9	9.3	9.2	9.2
90°	20.2	19.1	17.4	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0
92.5°	22.7	22.2	21.3	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3
95°	38.3	37.3	35.8	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1
97.5°	50.7	49.9	46.4	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3
100°	56.2	54.5	50.9	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1
102.5°	58.2	56.0	86.2	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6
105°	60.6	58.3	116.3	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5
107.5°	79.2	81.6	151.1	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3
110°	146.0	167.2	228.6	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	344.3	421.8	436.9	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2
115°	491.2	589.6	584.3	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4
117.5°	629.2	653.0	649.4	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4
120°	703.0	700.4	696.6	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9
122.5°	747.0	745.5	741.3	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7
125°	808.9	807.4	803.4	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8
127.5°	865.4	863.2	860.2	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9
130°	901.5	899.2	896.8	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4
132.5°	937.1	935.1	932.7	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6
135°	987.3	985.2	983.2	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3
137.5°	1034.1	1032.0	1029.8	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5
140°	1064.5	1062.6	1060.2	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4
142.5°	1092.6	1090.8	1088.2	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9
145°	1131.9	1130.4	1126.8	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1
147.5°	1166.3	1165.2	1161.6	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8
150°	1187.1	1185.8	1182.4	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2
152.5°	1206.2	1204.9	1201.7	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9
155°	1232.0	1230.7	1228.2	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9
157.5°	1253.6	1252.1	1250.3	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4
160°	1266.4	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1
162.5°	1278.0	1276.6	1275.5	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4
165°	1292.4	1290.9	1290.3	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8
167.5°	1304.4	1303.0	1302.4	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0
170°	1310.6	1309.1	1308.7	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9
172.5°	1315.2	1313.7	1313.2	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5
175°	1320.1	1318.6	1318.2	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4
177.5°	1321.0	1319.8	1319.6	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.9	13.0	13.4	15.1	14.7	15.1	15.4	15.3	15.3	15.1	14.9
90°	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2
92.5°	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3
95°	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4
97.5°	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6
100°	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9
102.5°	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4
105°	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0
107.5°	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8
110°	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7





TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8
115°	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9
117.5°	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4
120°	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5
122.5°	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6
125°	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4
127.5°	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6
130°	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8
132.5°	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1
135°	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4
137.5°	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1
140°	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4
142.5°	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3
145°	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4
147.5°	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4
150°	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4
152.5°	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5
155°	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3
157.5°	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0
160°	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7
162.5°	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5
165°	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9
167.5°	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9
170°	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1
172.5°	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6
175°	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6
177.5°	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	15.5	15.7	15.4	15.5	16.0	15.7	15.8
90°	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	103.5	82.3	72.1	72.9	73.8	74.6	75.5



TEST NUMBER: P331537

CATALOG NUMBER: S122DIW-S675D970U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)