

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331583-840

Luminaire Tested: **S122DIW-S865D1440U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331583-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9367.4 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	79	76	67	65	63	53	51	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	27
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	23
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	28	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14	12
9	48	36	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	1.4
10°-20°	368.7	3.9
20°-30°	542.0	5.8
30°-40°	629.6	6.7
40°-50°	628.9	6.7
50°-60°	548.4	5.9
60°-70°	405.5	4.3
70°-80°	229.7	2.5
80°-90°	66.7	0.7
90°-100°	66.2	0.7
100°-110°	242.8	2.6
110°-120°	649.0	6.9
120°-130°	1071.4	11.4
130°-140°	1139.4	12.2
140°-150°	1059.0	11.3
150°-160°	851.5	9.1
160°-170°	548.7	5.9
170°-180°	188.9	2.0
0°-30°	1041.8	11.1
0°-40°	1671.3	17.8
0°-60°	2848.6	30.4
0°-90°	3550.5	37.9
90°-120°	958.1	10.2
90°-150°	4227.9	45.1
90°-180°	5817.0	62.1
0°-180°	9367.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	1	17	29	36	39	7
95°	93	49	56	63	62	114
105°	437	456	88	103	109	467
115°	826	851	886	252	118	813
125°	1168	1187	1214	1223	1228	1041
135°	1445	1467	1481	1494	1492	1116
145°	1676	1676	1699	1708	1702	1048
155°	1846	1834	1850	1857	1847	850
165°	1945	1937	1940	1949	1940	549
175°	1989	1980	1982	1991	1978	189
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.6	19.8	20.0	20.3	20.5	20.6	20.6	20.7	20.7	20.8	20.4
90°	1.4	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3
92.5°	29.0	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1
95°	93.3	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6
97.5°	185.3	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2
100°	254.2	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4
102.5°	330.0	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5
105°	436.7	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1
107.5°	558.2	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1
110°	636.3	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	709.8	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6
115°	825.9	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4
117.5°	929.6	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8
120°	1005.4	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6
122.5°	1069.8	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9
125°	1167.7	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9
127.5°	1256.5	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8
130°	1312.7	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0
132.5°	1370.2	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6
135°	1444.9	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0
137.5°	1520.5	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3
140°	1569.8	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0
142.5°	1611.2	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2
145°	1676.2	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3
147.5°	1732.7	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0
150°	1769.5	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3
152.5°	1800.5	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0
155°	1845.6	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8
157.5°	1881.0	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3
160°	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5
162.5°	1920.0	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1
165°	1944.7	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7
167.5°	1963.1	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8
170°	1973.5	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9
172.5°	1980.3	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8
175°	1989.2	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3
177.5°	1990.6	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	20.0	19.6	19.2	18.9	18.8	18.7	18.6	18.5
90°	31.9	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	34.9	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	59.2	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	77.6	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	86.9	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	90.8	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	94.6	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	115.5	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	187.5	155.6	123.7	108.4	109.7	110.9	112.2	113.5



TEST NUMBER: P331583-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.1	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	590.7	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	910.1	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1060.5	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1125.2	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1218.1	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1304.0	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1358.6	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1411.5	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1487.1	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1557.4	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1602.9	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1644.9	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1703.5	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1754.7	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1786.2	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1814.9	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1853.7	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1886.4	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1905.4	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1923.2	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1963.0	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1972.2	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1979.0	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1986.5	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1987.3	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)