

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331561

Luminaire Tested: **S122DIW-S865D710U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331561  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D710U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6646.7 lumens  
Efficiency: N/A  
Efficacy: 124.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57																												
1	100	96	92	89	93	89	86	83	77	75	73	67	65	63	56	55	54	49																												
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46	42																												
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36																												
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35	32																												
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31	28																												
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25																												
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22																												
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20																												
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18																												
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.4	2.5
10°-20°	478.0	7.2
20°-30°	693.8	10.4
30°-40°	732.1	11.0
40°-50°	648.2	9.8
50°-60°	517.3	7.8
60°-70°	351.6	5.3
70°-80°	180.3	2.7
80°-90°	45.8	0.7
90°-100°	32.3	0.5
100°-110°	118.3	1.8
110°-120°	316.3	4.8
120°-130°	522.2	7.9
130°-140°	555.4	8.4
140°-150°	516.2	7.8
150°-160°	415.0	6.2
160°-170°	267.4	4.0
170°-180°	92.1	1.4
0°-30°	1336.2	20.1
0°-40°	2068.3	31.1
0°-60°	3233.8	48.7
0°-90°	3811.5	57.3
90°-120°	467.0	7.0
90°-150°	2060.7	31.0
90°-180°	2835.0	42.7
0°-180°	6646.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	19	1	19	1	19	10
95°	30	46	30	46	30	28
105°	53	213	53	213	53	55
115°	57	402	57	402	57	144
125°	598	569	598	569	598	518
135°	727	704	727	704	727	561
145°	830	817	830	817	830	519
155°	900	900	900	900	900	415
165°	946	948	946	948	946	267
175°	964	970	964	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	17.6	17.5	18.0	17.4	17.3	17.8	17.6	16.9	17.3	17.7	17.9
90°	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6	14.8	14.0	12.8
92.5°	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1	16.6	16.2	15.6
95°	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9	28.1	27.3	26.2
97.5°	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8	37.2	36.5	34.0
100°	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4	41.1	39.9	37.3
102.5°	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3	42.6	41.0	63.1
105°	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1	44.4	42.7	85.2
107.5°	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3	58.0	59.8	110.7
110°	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4	107.0	122.5	167.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5	252.3	309.0	320.1
115°	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9	359.9	431.9	428.0
117.5°	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6	461.0	478.4	475.7
120°	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9	515.0	513.1	510.3
122.5°	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4	547.3	546.2	543.1
125°	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7	592.6	591.5	588.6
127.5°	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6	634.0	632.4	630.2
130°	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2	660.5	658.8	657.0
132.5°	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0	686.5	685.1	683.4
135°	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9	723.3	721.8	720.4
137.5°	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1	757.6	756.1	754.5
140°	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3	779.9	778.5	776.7
142.5°	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7	800.5	799.2	797.2
145°	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3	829.3	828.2	825.5
147.5°	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3	854.5	853.6	851.0
150°	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6	869.7	868.8	866.3
152.5°	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6	883.7	882.8	880.4
155°	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5	902.6	901.7	899.8
157.5°	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5	918.4	917.3	916.0
160°	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7	927.8	926.9	925.9
162.5°	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4	936.3	935.3	934.5
165°	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8	945.3
167.5°	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8	955.7	954.6	954.2
170°	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3	960.2	959.1	958.8
172.5°	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6	963.5	962.4	962.1
175°	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3	967.2	966.1	965.8
177.5°	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7	967.8	966.9	966.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	18.2	18.0	17.7	18.5	16.6	16.2	13.8	11.8	11.6	11.4	10.7
90°	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1	14.0	13.8	13.7
95°	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5	40.4	35.2	30.1
97.5°	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3	75.8	61.4	46.9
100°	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9	102.6	81.3	60.0
102.5°	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9	156.4	151.8	147.3
105°	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8	217.5	222.2	226.8
107.5°	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0	275.8	279.6	283.3
110°	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1	313.4	316.7	319.9





TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0	348.9	351.8	354.6
115°	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5	405.2	407.8	410.5
117.5°	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1	456.0	459.0	461.9
120°	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0	492.4	494.7	497.0
122.5°	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4	523.9	526.3	528.8
125°	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1	571.2	573.2	575.2
127.5°	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4	614.6	616.9	619.1
130°	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8	642.3	644.8	647.3
132.5°	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9	670.0	672.1	674.2
135°	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3	706.7	709.2	711.7
137.5°	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1	742.8	744.6	746.3
140°	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2	766.4	767.6	768.9
142.5°	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3	786.4	787.6	788.7
145°	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0	816.8	816.7	816.5
147.5°	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5	844.0	843.4	842.8
150°	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5	861.4	860.3	859.2
152.5°	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6	876.4	875.2	873.9
155°	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6	898.2	896.8	895.4
157.5°	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8	915.6	914.4	913.2
160°	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	925.9	925.0	924.1
162.5°	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8	934.9	934.0	933.0
165°	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9	946.9	946.0	945.1
167.5°	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8	955.9	955.0	954.0
170°	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9	960.9	960.0	959.1
172.5°	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2	964.3	963.4	962.4
175°	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6	968.5	967.4	966.3
177.5°	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3	969.4	968.5	967.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	10.5	10.3	10.0	10.3	10.0	9.7	9.3	9.5	9.6	8.7	8.8
90°	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1	17.7
92.5°	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1	17.5	17.9	18.2
95°	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9	29.6	30.4	30.7
97.5°	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8	38.4	39.0	39.4
100°	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4	43.6	44.9	45.7
102.5°	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3	45.9	47.5	48.5
105°	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1	47.8	49.5	50.7
107.5°	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3	54.6	52.8	52.3
110°	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4	75.8	60.3	52.8



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5	138.8	82.0	53.9
115°	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9	215.8	143.8	102.2
117.5°	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6	426.1	408.7	381.6
120°	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9	518.7	520.6	511.0
122.5°	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4	549.5	550.7	549.2
125°	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7	594.8	595.9	596.7
127.5°	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6	637.2	638.8	639.6
130°	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2	663.9	665.6	666.4
132.5°	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0	689.5	690.9	691.6
135°	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9	726.4	728.0	728.6
137.5°	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1	760.6	762.2	762.7
140°	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3	782.7	784.1	784.4
142.5°	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7	803.0	804.3	804.5
145°	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3	831.4	832.5	832.7
147.5°	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3	856.1	856.9	857.0
150°	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6	871.6	872.5	872.6
152.5°	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6	885.6	886.5	886.5
155°	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5	904.5	905.4	905.2
157.5°	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5	920.5	921.6	921.5
160°	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7	929.7	930.6	930.5
162.5°	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4	938.4	939.5	939.4
165°	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0	949.0	950.1	950.1
167.5°	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8	957.9	958.9	958.8
170°	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3	962.3	963.4	963.3
172.5°	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6	965.7	966.8	966.6
175°	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3	969.3	970.4	970.2
177.5°	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7	969.5	970.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	8.9	8.4	8.5	8.0	8.5	8.4	8.9	8.8	8.7	9.6	9.5
90°	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6
92.5°	18.3	18.5	18.7	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1
95°	30.6	30.4	30.3	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9
97.5°	39.6	39.8	40.0	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8
100°	46.0	46.3	46.6	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4
102.5°	49.0	49.4	49.8	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3
105°	51.3	52.0	52.6	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1
107.5°	52.9	53.5	54.1	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3
110°	53.4	54.1	54.7	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.4	54.9	55.4	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5
115°	91.0	79.8	68.6	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9
117.5°	344.8	308.0	271.2	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6
120°	490.0	469.0	448.0	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9
122.5°	545.1	541.0	537.0	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4
125°	597.1	597.6	598.1	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7
127.5°	639.7	639.8	639.9	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6
130°	666.2	666.1	665.9	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2
132.5°	691.4	691.3	691.1	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0
135°	728.3	728.0	727.7	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9
137.5°	762.1	761.6	761.1	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1
140°	783.6	782.8	782.0	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3
142.5°	803.8	803.0	802.2	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7
145°	831.9	831.1	830.3	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3
147.5°	856.3	855.7	855.0	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3
150°	871.8	871.0	870.2	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6
152.5°	885.4	884.4	883.4	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6
155°	904.0	902.8	901.5	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5
157.5°	920.3	919.1	917.9	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5
160°	929.4	928.3	927.3	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7
162.5°	938.0	936.7	935.3	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4
165°	949.0	948.0	946.9	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0
167.5°	957.4	956.0	954.6	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8
170°	961.9	960.5	959.1	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3
172.5°	965.2	963.8	962.4	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6
175°	968.6	967.1	965.5	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3
177.5°	969.2	968.0	966.9	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	9.3	9.7	10.0	10.3	10.0	10.3	10.5	10.7	11.4	11.6	11.8
90°	14.8	14.0	12.8	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7
92.5°	16.6	16.2	15.6	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1
95°	28.1	27.3	26.2	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5
97.5°	37.2	36.5	34.0	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3
100°	41.1	39.9	37.3	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9
102.5°	42.6	41.0	63.1	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9
105°	44.4	42.7	85.2	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8
107.5°	58.0	59.8	110.7	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0
110°	107.0	122.5	167.5	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	252.3	309.0	320.1	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0
115°	359.9	431.9	428.0	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5
117.5°	461.0	478.4	475.7	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1
120°	515.0	513.1	510.3	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0
122.5°	547.3	546.2	543.1	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4
125°	592.6	591.5	588.6	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1
127.5°	634.0	632.4	630.2	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4
130°	660.5	658.8	657.0	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8
132.5°	686.5	685.1	683.4	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9
135°	723.3	721.8	720.4	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3
137.5°	757.6	756.1	754.5	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1
140°	779.9	778.5	776.7	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2
142.5°	800.5	799.2	797.2	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3
145°	829.3	828.2	825.5	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0
147.5°	854.5	853.6	851.0	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5
150°	869.7	868.8	866.3	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5
152.5°	883.7	882.8	880.4	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6
155°	902.6	901.7	899.8	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6
157.5°	918.4	917.3	916.0	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8
160°	927.8	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9
162.5°	936.3	935.3	934.5	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8
165°	946.9	945.8	945.3	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9
167.5°	955.7	954.6	954.2	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8
170°	960.2	959.1	958.8	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9
172.5°	963.5	962.4	962.1	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2
175°	967.2	966.1	965.8	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6
177.5°	967.8	966.9	966.8	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.8	16.2	16.6	18.5	17.7	18.0	18.2	17.9	17.7	17.3	16.9
90°	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6
92.5°	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1
95°	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9
97.5°	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8
100°	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4
102.5°	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3
105°	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1
107.5°	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3
110°	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4





TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5
115°	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9
117.5°	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6
120°	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9
122.5°	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4
125°	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7
127.5°	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6
130°	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2
132.5°	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0
135°	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9
137.5°	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1
140°	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3
142.5°	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7
145°	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3
147.5°	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3
150°	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6
152.5°	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6
155°	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5
157.5°	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5
160°	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7
162.5°	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4
165°	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0
167.5°	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8
170°	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3
172.5°	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6
175°	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3
177.5°	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	17.6	17.8	17.3	17.4	18.0	17.5	17.6
90°	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331561

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)