

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331555-840

Luminaire Tested: **S122DIW-S865D435U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331555-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5596.3 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69								
1	103	98	95	91	97	93	90	87	83	81	79	74	72	71	66	65	63	59								
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	51								
3	86	77	70	64	81	73	67	61	66	61	56	59	55	52	53	50	47	44								
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38								
5	73	62	54	48	69	59	51	46	53	47	43	48	43	39	43	39	36	34								
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32	30								
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27								
8	59	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24								
9	55	42	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22								
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	3.0
10°-20°	482.7	8.6
20°-30°	700.6	12.5
30°-40°	739.3	13.2
40°-50°	654.6	11.7
50°-60°	522.4	9.3
60°-70°	355.1	6.3
70°-80°	182.0	3.3
80°-90°	45.4	0.8
90°-100°	19.9	0.4
100°-110°	73.0	1.3
110°-120°	195.0	3.5
120°-130°	322.0	5.8
130°-140°	342.4	6.1
140°-150°	318.3	5.7
150°-160°	255.9	4.6
160°-170°	164.9	2.9
170°-180°	56.8	1.0
0°-30°	1349.4	24.1
0°-40°	2088.7	37.3
0°-60°	3265.7	58.4
0°-90°	3848.2	68.8
90°-120°	287.9	5.1
90°-150°	1270.6	22.7
90°-180°	1748.0	31.2
0°-180°	5596.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	40
90°	12	0	12	0	12	7
95°	19	28	19	28	19	17
105°	33	131	33	131	33	34
115°	35	248	35	248	35	89
125°	369	351	369	351	369	319
135°	448	434	448	434	448	346
145°	512	504	512	504	512	320
155°	555	555	555	555	555	256
165°	583	584	583	584	583	165
175°	594	598	594	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	16.3	16.3	16.8	16.2	16.2	16.6	16.5	15.9	16.3	16.8	17.2
90°	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6	9.1	8.6	7.9
92.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5	10.3	10.0	9.6
95°	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8	17.3	16.9	16.2
97.5°	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3	22.9	22.5	21.0
100°	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2	25.3	24.6	22.9
102.5°	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3	26.3	25.2	39.0
105°	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5	27.4	26.4	52.5
107.5°	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7	35.7	36.9	68.3
110°	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4	65.9	75.5	103.2



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6	155.5	190.6	197.3
115°	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5	221.9	266.3	263.9
117.5°	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5	284.3	295.0	293.4
120°	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7	317.5	316.4	314.7
122.5°	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1	337.5	336.8	334.9
125°	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1	365.4	364.8	362.9
127.5°	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9	390.9	389.9	388.6
130°	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3	407.2	406.2	405.2
132.5°	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2	423.3	422.4	421.3
135°	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0	446.0	445.0	444.1
137.5°	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1	467.1	466.2	465.1
140°	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7	480.8	480.0	478.9
142.5°	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3	493.5	492.7	491.5
145°	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0	511.3	510.6	509.0
147.5°	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4	526.8	526.3	524.7
150°	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8	536.2	535.6	534.1
152.5°	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4	544.8	544.3	542.8
155°	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1	556.5	555.9	554.8
157.5°	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9	566.2	565.6	564.8
160°	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6	572.1	571.5	570.9
162.5°	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9	577.3	576.6	576.1
165°	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1	582.9
167.5°	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0	589.3	588.5	588.3
170°	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7	592.0	591.4	591.2
172.5°	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7	594.1	593.4	593.2
175°	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0	596.3	595.6	595.4
177.5°	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2	596.7	596.1	596.1
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	17.5	17.4	17.2	18.1	16.3	16.1	13.7	11.9	11.5	11.2	10.4
90°	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7	8.6	8.5	8.4
95°	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1	24.8	21.7	18.6
97.5°	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6	46.8	37.9	28.9
100°	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4	63.2	50.1	37.0
102.5°	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2	96.4	93.6	90.9
105°	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2	134.1	136.9	139.9
107.5°	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7	170.1	172.4	174.7
110°	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2	193.2	195.2	197.2



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3	215.1	216.9	218.6
115°	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2	249.8	251.5	253.1
117.5°	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3	281.1	283.0	284.8
120°	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2	303.6	305.0	306.5
122.5°	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4	323.0	324.5	326.0
125°	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9	352.1	353.5	354.7
127.5°	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6	379.0	380.3	381.7
130°	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6	396.1	397.6	399.1
132.5°	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8	413.0	414.3	415.7
135°	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2	435.8	437.3	438.8
137.5°	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0	458.0	459.1	460.2
140°	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8	472.5	473.3	474.0
142.5°	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2	484.9	485.5	486.3
145°	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7	503.6	503.5	503.4
147.5°	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7	520.4	520.0	519.7
150°	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8	531.1	530.4	529.8
152.5°	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1	540.4	539.6	538.9
155°	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6	553.8	552.9	552.1
157.5°	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2	564.5	563.8	563.1
160°	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	570.9	570.4	569.8
162.5°	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0	576.4	575.8	575.3
165°	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4	583.9	583.3	582.7
167.5°	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0	589.4	588.9	588.2
170°	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1	592.5	591.9	591.4
172.5°	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1	594.6	594.0	593.4
175°	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8	597.1	596.4	595.8
177.5°	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2	597.7	597.1	596.6
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	10.0	9.7	9.3	9.5	9.1	8.7	8.3	8.4	8.5	7.5	7.6
90°	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6	10.1	10.5	10.9
92.5°	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5	10.8	11.0	11.2
95°	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8	18.3	18.8	19.0
97.5°	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3	23.7	24.0	24.3
100°	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2	26.9	27.7	28.2
102.5°	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3	28.3	29.3	29.9
105°	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5	29.5	30.6	31.3
107.5°	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7	33.6	32.5	32.2
110°	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4	46.8	37.2	32.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6	85.5	50.6	33.2
115°	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5	133.1	88.7	63.0
117.5°	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5	262.8	252.0	235.3
120°	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7	319.8	321.0	315.1
122.5°	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1	338.8	339.5	338.6
125°	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1	366.8	367.4	367.9
127.5°	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9	392.8	393.8	394.4
130°	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3	409.3	410.4	410.9
132.5°	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2	425.1	426.0	426.4
135°	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0	447.9	448.9	449.2
137.5°	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1	469.0	469.9	470.2
140°	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7	482.6	483.4	483.6
142.5°	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3	495.1	495.9	496.0
145°	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0	512.6	513.3	513.4
147.5°	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4	527.9	528.4	528.4
150°	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8	537.3	538.0	538.1
152.5°	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4	546.0	546.6	546.5
155°	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1	557.6	558.3	558.2
157.5°	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9	567.5	568.3	568.2
160°	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6	573.2	573.8	573.7
162.5°	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9	578.7	579.3	579.2
165°	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5	585.1	585.8	585.8
167.5°	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0	590.6	591.3	591.2
170°	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7	593.4	594.0	593.9
172.5°	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7	595.4	596.1	596.0
175°	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0	597.6	598.3	598.2
177.5°	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2	597.7	598.3	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	7.6	7.1	7.1	6.7	7.1	7.1	7.6	7.6	7.5	8.5	8.4
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6
92.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5
95°	18.9	18.8	18.7	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8
97.5°	24.4	24.5	24.6	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3
100°	28.4	28.6	28.7	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2
102.5°	30.2	30.5	30.7	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3
105°	31.6	32.0	32.4	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5
107.5°	32.6	33.0	33.3	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7
110°	32.9	33.3	33.7	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6
115°	56.1	49.2	42.3	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5
117.5°	212.6	189.9	167.2	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5
120°	302.2	289.2	276.2	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7
122.5°	336.1	333.6	331.0	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1
125°	368.2	368.5	368.8	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1
127.5°	394.5	394.5	394.6	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9
130°	410.8	410.7	410.6	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3
132.5°	426.3	426.2	426.2	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2
135°	449.1	448.9	448.7	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0
137.5°	469.9	469.6	469.3	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1
140°	483.1	482.6	482.2	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7
142.5°	495.5	495.1	494.6	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3
145°	512.9	512.4	512.0	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0
147.5°	528.0	527.6	527.1	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4
150°	537.6	537.0	536.5	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8
152.5°	545.9	545.3	544.6	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4
155°	557.3	556.6	555.8	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1
157.5°	567.4	566.6	565.9	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9
160°	573.1	572.4	571.7	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6
162.5°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9
165°	585.1	584.5	583.8	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5
167.5°	590.3	589.5	588.5	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0
170°	593.1	592.2	591.4	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7
172.5°	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7
175°	597.2	596.3	595.3	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0
177.5°	597.5	596.8	596.1	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	8.3	8.7	9.1	9.5	9.3	9.7	10.0	10.4	11.2	11.5	11.9
90°	9.1	8.6	7.9	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4
92.5°	10.3	10.0	9.6	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7
95°	17.3	16.9	16.2	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1
97.5°	22.9	22.5	21.0	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6
100°	25.3	24.6	22.9	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4
102.5°	26.3	25.2	39.0	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2
105°	27.4	26.4	52.5	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2
107.5°	35.7	36.9	68.3	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7
110°	65.9	75.5	103.2	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	155.5	190.6	197.3	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3
115°	221.9	266.3	263.9	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2
117.5°	284.3	295.0	293.4	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3
120°	317.5	316.4	314.7	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2
122.5°	337.5	336.8	334.9	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4
125°	365.4	364.8	362.9	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9
127.5°	390.9	389.9	388.6	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6
130°	407.2	406.2	405.2	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6
132.5°	423.3	422.4	421.3	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8
135°	446.0	445.0	444.1	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2
137.5°	467.1	466.2	465.1	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0
140°	480.8	480.0	478.9	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8
142.5°	493.5	492.7	491.5	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2
145°	511.3	510.6	509.0	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7
147.5°	526.8	526.3	524.7	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7
150°	536.2	535.6	534.1	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8
152.5°	544.8	544.3	542.8	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1
155°	556.5	555.9	554.8	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6
157.5°	566.2	565.6	564.8	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2
160°	572.1	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5
162.5°	577.3	576.6	576.1	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0
165°	583.8	583.1	582.9	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4
167.5°	589.3	588.5	588.3	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0
170°	592.0	591.4	591.2	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1
172.5°	594.1	593.4	593.2	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1
175°	596.3	595.6	595.4	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8
177.5°	596.7	596.1	596.1	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	13.7	16.1	16.3	18.1	17.2	17.4	17.5	17.2	16.8	16.3	15.9
90°	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6
92.5°	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5
95°	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8
97.5°	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3
100°	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2
102.5°	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3
105°	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5
107.5°	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7
110°	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6
115°	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5
117.5°	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5
120°	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7
122.5°	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1
125°	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1
127.5°	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9
130°	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3
132.5°	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2
135°	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0
137.5°	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1
140°	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7
142.5°	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3
145°	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0
147.5°	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4
150°	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8
152.5°	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4
155°	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1
157.5°	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9
160°	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6
162.5°	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9
165°	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5
167.5°	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0
170°	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7
172.5°	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7
175°	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0
177.5°	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	16.5	16.6	16.2	16.2	16.8	16.3	16.3
90°	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331555-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)