

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331566

Luminaire Tested: **S122DIW-S865D710U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331566
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D710U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5973.2 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																				
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	55	54	50																				
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	41																				
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35																				
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30																				
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26																				
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23																				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20																				
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18																				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16																				
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22281	22281	22281
5°	22366	22044	22174
10°	22233	21820	21930
15°	21959	21538	21514
20°	21569	21113	21089
25°	21180	20591	20591
30°	20681	20113	19939
35°	20217	19537	19249
40°	19633	18963	18598
45°	19057	18393	17938
50°	18432	17799	17166
55°	17779	17106	16473
60°	17053	16281	15684
65°	16275	15461	14751
70°	15286	14469	13780
75°	13905	13325	12994
80°	12338	11967	11353
85°	10078	9596	8596



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	2.2
10°-20°	365.1	6.1
20°-30°	536.7	9.0
30°-40°	623.4	10.4
40°-50°	622.7	10.4
50°-60°	543.1	9.1
60°-70°	401.6	6.7
70°-80°	227.4	3.8
80°-90°	64.7	1.1
90°-100°	55.7	0.9
100°-110°	173.1	2.9
110°-120°	295.8	5.0
120°-130°	389.0	6.5
130°-140°	436.6	7.3
140°-150°	428.1	7.2
150°-160°	359.1	6.0
160°-170°	238.2	4.0
170°-180°	83.2	1.4
0°-30°	1031.6	17.3
0°-40°	1655.0	27.7
0°-60°	2820.8	47.2
0°-90°	3514.5	58.8
90°-120°	524.6	8.8
90°-150°	1778.3	29.8
90°-180°	2459.0	41.2
0°-180°	5973.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1380	1374	1360	1370	1368	131
15°	1314	1305	1288	1293	1287	370
25°	1189	1178	1156	1158	1156	547
35°	1026	1012	991	983	977	640
45°	835	825	806	791	786	644
55°	632	623	608	592	585	565
65°	426	418	405	393	386	421
75°	223	220	214	206	208	238
85°	54	53	52	48	46	62
90°	1	10	26	25	25	5
95°	39	46	48	47	46	44
105°	160	162	163	165	165	168
115°	297	301	300	299	297	294
125°	432	438	436	434	433	386
135°	559	567	568	568	565	431
145°	678	683	688	688	686	424
155°	775	778	780	783	781	357
165°	844	843	843	848	844	238
175°	878	876	874	879	875	83
180°	879	879	879	879	879	



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1386.4	1385.2	1384.0	1382.9	1381.7	1379.8	1377.2	1374.6	1372.0	1369.4	1371.8
5°	1380.0	1378.8	1377.7	1376.5	1375.3	1373.1	1369.9	1366.6	1363.4	1360.1	1362.5
7.5°	1367.8	1366.0	1364.2	1362.3	1360.5	1357.9	1354.6	1351.3	1348.0	1344.7	1347.1
10°	1356.1	1354.1	1352.0	1349.9	1347.9	1345.1	1341.5	1338.0	1334.5	1330.9	1333.3
12.5°	1340.2	1338.4	1336.6	1334.7	1332.9	1330.2	1326.7	1323.1	1319.6	1316.1	1317.7
15°	1313.7	1311.9	1310.1	1308.4	1306.6	1303.8	1300.0	1296.1	1292.3	1288.5	1289.6
17.5°	1279.7	1277.9	1276.2	1274.4	1272.6	1269.8	1265.9	1262.0	1258.1	1254.2	1255.6
20°	1255.3	1253.5	1251.8	1250.0	1248.2	1245.3	1241.1	1237.0	1232.9	1228.8	1229.6
22.5°	1230.9	1228.4	1225.9	1223.4	1221.0	1217.8	1213.9	1210.0	1206.1	1202.2	1202.4
25°	1188.9	1186.6	1184.2	1181.9	1179.5	1175.8	1170.8	1165.8	1160.8	1155.8	1156.4
27.5°	1141.2	1139.1	1136.9	1134.8	1132.7	1129.6	1125.7	1121.7	1117.8	1113.8	1113.0
30°	1109.3	1107.0	1104.6	1102.3	1099.9	1096.5	1092.1	1087.7	1083.2	1078.8	1077.9
32.5°	1075.4	1073.5	1071.6	1069.7	1067.8	1064.5	1059.9	1055.2	1050.6	1045.9	1044.3
35°	1025.7	1022.8	1019.8	1016.9	1013.9	1010.1	1005.4	1000.7	995.9	991.2	989.5
37.5°	969.7	967.1	964.5	961.9	959.4	955.7	951.0	946.3	941.5	936.8	934.6
40°	931.5	929.2	926.8	924.4	922.1	918.5	913.8	909.1	904.4	899.7	897.0
42.5°	894.4	892.0	889.6	887.3	884.9	881.4	876.7	872.0	867.2	862.5	859.6
45°	834.6	832.6	830.5	828.5	826.4	823.1	818.7	814.3	809.9	805.5	802.2
47.5°	775.2	773.3	771.3	769.4	767.4	764.1	759.5	754.9	750.3	745.7	742.3
50°	733.8	732.3	730.9	729.4	727.9	725.1	721.0	716.8	712.7	708.6	704.5
52.5°	693.5	691.5	689.6	687.6	685.7	682.8	678.9	675.0	671.1	667.2	663.8
55°	631.6	629.9	628.1	626.3	624.5	621.9	618.4	614.8	611.3	607.7	604.2
57.5°	569.5	568.1	566.7	565.3	563.9	561.2	557.3	553.4	549.5	545.6	542.2
60°	528.1	526.9	525.8	524.6	523.4	520.8	516.6	512.5	508.4	504.2	501.0
62.5°	487.8	485.9	484.0	482.1	480.2	477.7	474.5	471.3	468.1	465.0	462.0
65°	426.0	424.2	422.4	420.6	418.9	416.5	413.6	410.6	407.7	404.7	402.1
67.5°	363.1	361.6	360.2	358.8	357.4	355.4	352.7	350.0	347.4	344.7	342.7
70°	323.8	322.6	321.4	320.2	319.1	317.1	314.5	311.8	309.2	306.5	304.5
72.5°	283.4	282.3	281.1	279.9	278.7	277.3	275.6	273.9	272.1	270.4	268.4
75°	222.9	222.3	221.7	221.2	220.6	219.5	218.1	216.6	215.1	213.6	211.9
77.5°	168.8	167.8	166.8	165.8	164.8	164.0	163.4	162.8	162.2	161.6	160.7
80°	132.7	132.4	132.1	131.8	131.5	131.1	130.5	129.9	129.3	128.7	127.8
82.5°	98.7	98.7	98.6	98.5	98.5	98.3	97.9	97.6	97.2	96.9	95.7
85°	54.4	54.1	53.8	53.5	53.2	52.9	52.6	52.3	52.0	51.8	50.9
87.5°	19.3	19.2	19.1	19.0	19.0	19.0	19.3	19.5	19.8	20.1	19.3
90°	0.7	2.7	4.7	6.7	8.7	11.5	15.1	18.7	22.3	26.0	25.6
92.5°	13.2	14.7	16.1	17.6	19.0	20.2	21.0	21.9	22.7	23.6	23.7
95°	38.6	40.2	41.9	43.5	45.2	46.2	46.5	46.8	47.2	47.5	47.5
97.5°	70.5	71.9	73.4	74.8	76.3	77.3	78.0	78.6	79.2	79.8	79.8
100°	94.2	95.6	96.9	98.2	99.5	100.4	100.9	101.4	101.9	102.4	102.4
102.5°	119.2	120.2	121.3	122.3	123.4	124.2	124.9	125.5	126.1	126.7	126.9
105°	159.5	160.0	160.5	161.0	161.5	161.9	162.3	162.6	162.9	163.3	163.6
107.5°	200.2	200.9	201.7	202.4	203.1	203.5	203.5	203.5	203.5	203.5	203.6
110°	226.3	227.3	228.3	229.3	230.3	230.8	230.8	230.8	230.8	230.8	230.8



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.8	255.8	256.8	257.8	258.8	259.2	259.1	258.9	258.8	258.7	258.3
115°	296.8	297.8	298.8	299.8	300.8	301.1	300.8	300.4	300.1	299.8	299.6
117.5°	338.7	340.0	341.3	342.6	343.9	344.1	343.2	342.3	341.4	340.5	340.1
120°	366.6	367.9	369.2	370.5	371.8	371.8	370.5	369.2	367.9	366.6	366.6
122.5°	392.1	393.7	395.3	396.8	398.4	398.8	397.8	396.9	396.0	395.1	394.7
125°	431.9	433.4	434.8	436.3	437.8	438.3	437.8	437.3	436.8	436.3	435.8
127.5°	470.6	472.5	474.4	476.2	478.1	478.8	478.2	477.6	477.0	476.4	475.8
130°	494.9	497.1	499.2	501.4	503.5	504.4	504.1	503.8	503.4	503.1	502.8
132.5°	522.3	524.0	525.8	527.5	529.2	530.2	530.2	530.3	530.4	530.4	529.7
135°	558.8	560.6	562.4	564.2	566.0	567.1	567.4	567.8	568.1	568.4	568.2
137.5°	597.2	598.7	600.2	601.7	603.1	604.1	604.5	605.0	605.4	605.8	605.7
140°	620.4	621.8	623.3	624.8	626.3	627.4	628.3	629.1	629.9	630.7	630.7
142.5°	644.1	645.6	647.1	648.6	650.0	651.1	651.6	652.2	652.7	653.3	653.4
145°	678.2	679.4	680.5	681.7	682.9	683.9	684.9	685.9	686.9	687.9	688.0
147.5°	708.7	710.0	711.4	712.8	714.2	715.2	715.9	716.5	717.2	717.9	718.2
150°	729.4	730.4	731.4	732.4	733.4	734.2	734.9	735.5	736.2	736.9	737.4
152.5°	747.8	748.8	749.8	750.8	751.8	752.7	753.5	754.3	755.1	755.9	756.5
155°	775.4	775.9	776.4	776.9	777.4	777.9	778.4	778.9	779.4	779.9	780.7
157.5°	799.0	799.4	799.7	800.0	800.4	800.7	801.0	801.3	801.6	801.9	803.0
160°	813.3	813.6	813.9	814.3	814.6	814.9	815.0	815.2	815.3	815.5	816.5
162.5°	826.3	826.4	826.5	826.5	826.6	826.7	826.9	827.1	827.2	827.4	828.5
165°	843.7	843.5	843.4	843.2	843.1	843.0	843.0	843.0	843.0	843.0	844.1
167.5°	858.3	857.8	857.3	856.8	856.3	856.0	856.0	855.9	855.9	855.9	857.0
170°	866.0	865.5	865.0	864.5	864.0	863.7	863.5	863.3	863.2	863.0	864.2
172.5°	871.3	870.8	870.3	869.8	869.3	869.0	868.8	868.7	868.5	868.3	869.5
175°	877.8	877.4	876.9	876.4	875.9	875.5	875.1	874.8	874.5	874.1	875.3
177.5°	880.5	880.1	879.7	879.3	878.9	878.6	878.3	878.1	877.8	877.5	878.3
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1374.1	1376.5	1378.8	1379.8	1379.3	1378.8	1378.4	1377.9
5°	1364.8	1367.2	1369.6	1370.4	1369.9	1369.3	1368.7	1368.1
7.5°	1349.4	1351.8	1354.2	1355.0	1354.4	1353.7	1353.1	1352.4
10°	1335.6	1338.0	1340.4	1341.1	1340.2	1339.3	1338.4	1337.6
12.5°	1319.4	1321.0	1322.7	1323.2	1322.5	1321.9	1321.2	1320.6
15°	1290.8	1292.0	1293.2	1293.0	1291.6	1290.1	1288.6	1287.1
17.5°	1256.9	1258.3	1259.7	1259.6	1258.2	1256.8	1255.4	1254.0
20°	1230.5	1231.4	1232.3	1232.1	1231.0	1229.8	1228.6	1227.4
22.5°	1202.6	1202.7	1202.9	1202.7	1201.9	1201.2	1200.5	1199.8
25°	1157.0	1157.5	1158.1	1158.1	1157.5	1157.0	1156.4	1155.8
27.5°	1112.1	1111.2	1110.3	1109.2	1107.7	1106.3	1104.9	1103.5
30°	1077.0	1076.2	1075.3	1074.2	1073.1	1071.9	1070.7	1069.5
32.5°	1042.7	1041.1	1039.5	1038.1	1037.0	1035.8	1034.6	1033.4
35°	987.7	985.9	984.2	982.5	981.1	979.6	978.1	976.6
37.5°	932.5	930.3	928.1	926.3	924.9	923.5	922.1	920.6
40°	894.4	891.7	889.1	887.1	886.0	884.8	883.6	882.4
42.5°	856.7	853.8	851.0	848.7	847.0	845.4	843.7	842.1
45°	799.0	795.7	792.5	790.3	789.1	787.9	786.7	785.6
47.5°	738.9	735.5	732.1	729.5	727.8	726.1	724.4	722.7
50°	700.3	696.2	692.1	689.3	687.8	686.3	684.9	683.4
52.5°	660.3	656.9	653.5	650.8	648.9	646.9	645.0	643.0
55°	600.7	597.1	593.6	591.1	589.6	588.1	586.7	585.2
57.5°	538.7	535.2	531.7	529.4	528.3	527.2	526.1	524.9
60°	497.8	494.5	491.3	489.2	488.3	487.4	486.5	485.7
62.5°	458.9	455.9	452.9	450.9	449.7	448.6	447.5	446.4
65°	399.4	396.8	394.1	392.0	390.6	389.1	387.6	386.1
67.5°	340.6	338.5	336.5	334.9	333.7	332.5	331.3	330.1
70°	302.4	300.3	298.3	296.6	295.5	294.3	293.1	291.9
72.5°	266.3	264.2	262.2	260.7	259.7	258.8	257.8	256.9
75°	210.1	208.3	206.6	206.0	206.6	207.2	207.7	208.3
77.5°	159.9	159.0	158.1	157.2	156.4	155.6	154.8	153.9
80°	126.9	126.1	125.2	124.4	123.8	123.3	122.7	122.1
82.5°	94.6	93.5	92.4	91.8	91.6	91.5	91.4	91.3
85°	50.0	49.1	48.2	47.6	47.3	47.0	46.7	46.4
87.5°	18.5	17.7	17.0	16.5	16.3	16.1	15.9	15.7
90°	25.3	25.0	24.7	24.6	24.7	24.9	25.1	25.2
92.5°	23.7	23.8	23.9	23.9	23.9	24.0	24.0	24.0
95°	47.5	47.5	47.5	47.3	47.0	46.7	46.3	46.0
97.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.7	79.7
100°	102.4	102.4	102.4	102.3	102.2	102.0	101.8	101.7
102.5°	127.0	127.1	127.3	127.3	127.1	126.9	126.8	126.6
105°	163.9	164.2	164.6	164.7	164.7	164.7	164.7	164.7
107.5°	203.7	203.9	204.0	203.7	202.9	202.2	201.4	200.7
110°	230.8	230.8	230.8	230.5	230.0	229.5	229.0	228.6



TEST NUMBER: P331566

CATALOG NUMBER: S122DIW-S865D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.5	257.1	256.7	256.4	256.0	255.6	255.3
115°	299.5	299.3	299.1	298.8	298.3	297.8	297.3	296.8
117.5°	339.7	339.3	338.9	338.4	337.9	337.4	336.9	336.4
120°	366.6	366.6	366.6	366.3	365.8	365.3	364.8	364.3
122.5°	394.3	393.9	393.5	393.1	392.7	392.4	392.0	391.7
125°	435.3	434.8	434.3	434.0	433.9	433.7	433.5	433.4
127.5°	475.2	474.6	474.0	473.5	472.9	472.4	471.9	471.4
130°	502.5	502.1	501.8	501.3	500.6	500.0	499.3	498.7
132.5°	529.0	528.2	527.5	526.9	526.4	525.8	525.3	524.8
135°	568.1	567.9	567.8	567.4	566.9	566.4	565.9	565.4
137.5°	605.5	605.4	605.3	604.9	604.2	603.6	602.9	602.2
140°	630.7	630.7	630.7	630.4	629.8	629.1	628.4	627.8
142.5°	653.6	653.7	653.8	653.6	652.9	652.2	651.6	650.9
145°	688.2	688.4	688.5	688.3	687.6	687.0	686.3	685.7
147.5°	718.6	718.9	719.3	719.2	718.6	717.9	717.3	716.7
150°	737.8	738.3	738.8	738.8	738.3	737.8	737.4	736.9
152.5°	757.1	757.7	758.4	758.4	757.7	757.1	756.5	755.9
155°	781.5	782.4	783.2	783.4	782.9	782.4	781.9	781.4
157.5°	804.1	805.2	806.3	806.5	805.7	804.9	804.1	803.3
160°	817.5	818.5	819.5	819.6	819.0	818.3	817.7	817.0
162.5°	829.6	830.8	831.9	832.0	831.2	830.5	829.7	828.9
165°	845.3	846.4	847.6	847.8	846.9	846.1	845.3	844.5
167.5°	858.2	859.3	860.5	860.6	859.8	858.9	858.1	857.2
170°	865.3	866.5	867.6	867.7	866.7	865.7	864.7	863.7
172.5°	870.7	871.8	873.0	873.0	872.1	871.1	870.1	869.1
175°	876.4	877.6	878.8	878.8	877.8	876.9	875.9	874.9
177.5°	879.1	879.9	880.7	880.7	879.9	879.1	878.3	877.5
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3

(END OF REPORT)