

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331556-840

Luminaire Tested: **S122DIW-S865D435U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331556-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5364.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53
3	87	78	70	64	82	74	67	62	67	62	58	61	57	53	55	52	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	3.1
10°-20°	482.7	9.0
20°-30°	700.6	13.1
30°-40°	739.3	13.8
40°-50°	654.6	12.2
50°-60°	522.4	9.7
60°-70°	355.1	6.6
70°-80°	182.0	3.4
80°-90°	46.1	0.9
90°-100°	34.4	0.6
100°-110°	106.7	2.0
110°-120°	182.4	3.4
120°-130°	239.9	4.5
130°-140°	269.2	5.0
140°-150°	263.9	4.9
150°-160°	221.4	4.1
160°-170°	146.8	2.7
170°-180°	51.3	1.0
0°-30°	1349.4	25.2
0°-40°	2088.7	38.9
0°-60°	3265.7	60.9
0°-90°	3848.9	71.7
90°-120°	323.4	6.0
90°-150°	1096.4	20.4
90°-180°	1516.0	28.3
0°-180°	5364.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	40
90°	16	0	16	0	16	9
95°	28	24	28	24	28	32
105°	102	98	102	98	102	107
115°	183	183	183	183	183	181
125°	267	266	267	266	267	238
135°	349	345	349	345	349	268
145°	423	418	423	418	423	264
155°	482	478	482	478	482	222
165°	521	520	521	520	521	147
175°	540	541	540	541	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	17.1	17.1	17.6	17.0	17.0	17.5	17.6	17.1	17.7	18.2	18.3
90°	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7	15.9	16.1	13.7
92.5°	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6	14.5	14.5	14.0
95°	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3	29.3	29.3	29.1
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	48.9
100°	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1	63.1	63.1	62.8
102.5°	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3	78.3	78.2	77.8
105°	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1	100.9	100.7	100.5
107.5°	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6	125.5	125.4	125.4
110°	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1	159.3	159.5	159.6
115°	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6	184.7	184.8	185.0
117.5°	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4	209.6	210.0	210.5
120°	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0	226.0	226.0	226.8
122.5°	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1	243.4	243.6	244.2
125°	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4	268.7	269.0	269.3
127.5°	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0	293.4	293.8	294.1
130°	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8	310.0	310.2	310.4
132.5°	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2	326.6	327.0	327.0
135°	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2	350.3	350.4	350.2
137.5°	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3	373.4	373.5	373.2
140°	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9	388.9	388.9	388.4
142.5°	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9	402.9	402.8	402.4
145°	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3	424.2	424.1	423.5
147.5°	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0	442.8	442.6	442.2
150°	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3	453.9
152.5°	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1	465.5
155°	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9	481.4	480.9	480.6
157.5°	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7	495.1	494.4	494.2
160°	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0	503.4	502.8	502.7
162.5°	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5	510.8	510.2	510.1
165°	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2	520.5	519.8	519.8
167.5°	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2	528.5	527.8	527.8
170°	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5	532.8	532.1	532.2
172.5°	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8	536.1	535.4	535.5
175°	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4	539.7	539.0	539.2
177.5°	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1	541.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	18.4	18.0	17.5	18.2	16.4	16.2	13.7	11.9	11.6	11.3	10.5
90°	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2	9.1	9.9	10.8
95°	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8	24.8	25.9	26.9
97.5°	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4	44.3	45.2	46.2
100°	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1	58.9	59.7	60.6
102.5°	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5	74.1	74.7	75.4
105°	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4	98.7	99.0	99.3
107.5°	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4	123.9	124.3	124.8
110°	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6	140.2	140.8	141.4



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1	157.7	158.3	159.0
115°	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0	183.6	184.2	184.8
117.5°	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8	209.6	210.5	211.3
120°	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.8	227.6	228.4
122.5°	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8	242.8	243.7	244.7
125°	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3	267.2	268.1	269.0
127.5°	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1	291.3	292.5	293.7
130°	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2	306.5	307.8	309.1
132.5°	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0	323.1	324.2	325.3
135°	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6	345.7	346.8	347.9
137.5°	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2	369.1	370.0	370.9
140°	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5	383.4	384.4	385.3
142.5°	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2	398.1	399.0	399.9
145°	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2	418.9	419.6	420.3
147.5°	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0	437.8	438.7	439.5
150°	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8	450.4	451.0	451.6
152.5°	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1	461.7	462.3	462.9
155°	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1	478.4	478.7	479.1
157.5°	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7	492.9	493.1	493.3
160°	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5	501.7	501.9	502.1
162.5°	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5	509.6	509.6	509.6
165°	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2	520.1	520.0	519.9
167.5°	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2	528.9	528.6	528.3
170°	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9	533.6	533.3	533.0
172.5°	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2	536.9	536.6	536.3
175°	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3	541.0	540.7	540.4
177.5°	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9	542.7	542.4	542.2
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	10.2	10.0	9.9	10.3	10.3	10.2	9.6	9.6	9.5	8.4	8.4
90°	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7	15.5	15.2	15.1
92.5°	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6	14.6	14.7	14.7
95°	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3	29.3	29.3	29.2
97.5°	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2	49.2	49.2	49.2
100°	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1	63.1	63.1	63.1
102.5°	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3	78.4	78.5	78.5
105°	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1	101.3	101.5	101.6
107.5°	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6	125.7	125.8	125.6
110°	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.1



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1	158.8	158.5	158.2
115°	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6	184.5	184.4	184.2
117.5°	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4	209.1	208.9	208.6
120°	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0	226.0	226.0	225.9
122.5°	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1	242.9	242.6	242.4
125°	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4	268.1	267.8	267.6
127.5°	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0	292.7	292.3	292.0
130°	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8	309.6	309.4	309.1
132.5°	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2	325.7	325.3	324.9
135°	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2	350.1	350.0	349.8
137.5°	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3	373.2	373.2	372.9
140°	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9	388.9	388.9	388.7
142.5°	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9	403.0	403.1	402.9
145°	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3	424.4	424.5	424.3
147.5°	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0	443.3	443.5	443.4
150°	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9	455.2	455.6	455.6
152.5°	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8	467.2	467.6	467.6
155°	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9	482.4	482.9	483.0
157.5°	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7	496.4	497.2	497.3
160°	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0	504.6	505.2	505.3
162.5°	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5	512.2	512.9	513.0
165°	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2	521.9	522.6	522.7
167.5°	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2	529.9	530.6	530.7
170°	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5	534.2	534.9	535.0
172.5°	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8	537.6	538.3	538.3
175°	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4	541.1	541.8	541.9
177.5°	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1	542.5	543.0	543.0
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	8.4	7.9	7.9	7.4	7.9	7.9	8.4	8.4	8.4	9.5	9.6
90°	15.2	15.3	15.5	15.6	15.5	15.3	15.2	15.1	15.2	15.5	15.7
92.5°	14.7	14.7	14.8	14.8	14.8	14.7	14.7	14.7	14.7	14.6	14.6
95°	29.0	28.8	28.6	28.4	28.6	28.8	29.0	29.2	29.3	29.3	29.3
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.0	62.9	62.8	62.7	62.8	62.9	63.0	63.1	63.1	63.1	63.1
102.5°	78.4	78.3	78.2	78.1	78.2	78.3	78.4	78.5	78.5	78.4	78.3
105°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.5	101.3	101.1
107.5°	125.1	124.6	124.2	123.7	124.2	124.6	125.1	125.6	125.8	125.7	125.6
110°	141.8	141.5	141.2	140.9	141.2	141.5	141.8	142.1	142.3	142.3	142.3



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	158.0	157.8	157.6	157.4	157.6	157.8	158.0	158.2	158.5	158.8	159.1
115°	183.9	183.6	183.3	183.0	183.3	183.6	183.9	184.2	184.4	184.5	184.6
117.5°	208.3	208.0	207.7	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.4
120°	225.6	225.3	225.0	224.7	225.0	225.3	225.6	225.9	226.0	226.0	226.0
122.5°	242.2	242.0	241.7	241.5	241.7	242.0	242.2	242.4	242.6	242.9	243.1
125°	267.5	267.4	267.3	267.2	267.3	267.4	267.5	267.6	267.8	268.1	268.4
127.5°	291.5	291.2	290.9	290.6	290.9	291.2	291.5	292.0	292.3	292.7	293.0
130°	308.7	308.3	307.9	307.5	307.9	308.3	308.7	309.1	309.4	309.6	309.8
132.5°	324.6	324.2	323.9	323.6	323.9	324.2	324.6	324.9	325.3	325.7	326.2
135°	349.5	349.2	348.9	348.6	348.9	349.2	349.5	349.8	350.0	350.1	350.2
137.5°	372.5	372.1	371.7	371.3	371.7	372.1	372.5	372.9	373.2	373.2	373.3
140°	388.3	387.9	387.5	387.1	387.5	387.9	388.3	388.7	388.9	388.9	388.9
142.5°	402.5	402.1	401.7	401.3	401.7	402.1	402.5	402.9	403.1	403.0	402.9
145°	423.9	423.5	423.1	422.7	423.1	423.5	423.9	424.3	424.5	424.4	424.3
147.5°	443.0	442.6	442.2	441.9	442.2	442.6	443.0	443.4	443.5	443.3	443.0
150°	455.2	454.9	454.6	454.3	454.6	454.9	455.2	455.6	455.6	455.2	454.9
152.5°	467.2	466.8	466.5	466.1	466.5	466.8	467.2	467.6	467.6	467.2	466.8
155°	482.7	482.4	482.1	481.8	482.1	482.4	482.7	483.0	482.9	482.4	481.9
157.5°	496.8	496.2	495.8	495.3	495.8	496.2	496.8	497.3	497.2	496.4	495.7
160°	504.9	504.5	504.1	503.7	504.1	504.5	504.9	505.3	505.2	504.6	504.0
162.5°	512.5	512.0	511.5	511.1	511.5	512.0	512.5	513.0	512.9	512.2	511.5
165°	522.2	521.7	521.2	520.7	521.2	521.7	522.2	522.7	522.6	521.9	521.2
167.5°	530.1	529.6	529.1	528.6	529.1	529.6	530.1	530.7	530.6	529.9	529.2
170°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	534.9	534.2	533.5
172.5°	537.7	537.0	536.4	535.8	536.4	537.0	537.7	538.3	538.3	537.6	536.8
175°	541.3	540.7	540.1	539.5	540.1	540.7	541.3	541.9	541.8	541.1	540.4
177.5°	542.5	542.1	541.6	541.1	541.6	542.1	542.5	543.0	543.0	542.5	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	9.6	10.2	10.3	10.3	9.9	10.0	10.2	10.5	11.3	11.6	11.9
90°	15.9	16.1	13.7	11.5	9.3	7.1	5.4	4.1	2.9	1.7	0.5
92.5°	14.5	14.5	14.0	13.5	12.9	12.4	11.7	10.8	9.9	9.1	8.2
95°	29.3	29.3	29.1	28.9	28.7	28.5	27.9	26.9	25.9	24.8	23.8
97.5°	49.2	49.2	48.9	48.5	48.1	47.7	47.1	46.2	45.2	44.3	43.4
100°	63.1	63.1	62.8	62.5	62.2	61.9	61.4	60.6	59.7	58.9	58.1
102.5°	78.3	78.2	77.8	77.4	77.0	76.6	76.0	75.4	74.7	74.1	73.5
105°	100.9	100.7	100.5	100.3	100.1	99.9	99.6	99.3	99.0	98.7	98.4
107.5°	125.5	125.4	125.4	125.4	125.4	125.4	125.2	124.8	124.3	123.9	123.4
110°	142.3	142.3	142.3	142.3	142.3	142.3	142.0	141.4	140.8	140.2	139.6



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	159.3	159.5	159.6	159.7	159.8	159.9	159.6	159.0	158.3	157.7	157.1
115°	184.7	184.8	185.0	185.2	185.4	185.6	185.4	184.8	184.2	183.6	183.0
117.5°	209.6	210.0	210.5	211.1	211.7	212.2	212.1	211.3	210.5	209.6	208.8
120°	226.0	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0
122.5°	243.4	243.6	244.2	244.7	245.3	245.9	245.7	244.7	243.7	242.8	241.8
125°	268.7	269.0	269.3	269.6	269.9	270.2	269.9	269.0	268.1	267.2	266.3
127.5°	293.4	293.8	294.1	294.5	294.9	295.2	294.8	293.7	292.5	291.3	290.1
130°	310.0	310.2	310.4	310.6	310.8	311.0	310.4	309.1	307.8	306.5	305.2
132.5°	326.6	327.0	327.0	327.0	326.9	326.9	326.3	325.3	324.2	323.1	322.0
135°	350.3	350.4	350.2	350.0	349.8	349.6	349.0	347.9	346.8	345.7	344.6
137.5°	373.4	373.5	373.2	373.0	372.7	372.4	371.8	370.9	370.0	369.1	368.2
140°	388.9	388.9	388.4	387.9	387.4	386.9	386.2	385.3	384.4	383.4	382.5
142.5°	402.9	402.8	402.4	402.1	401.7	401.4	400.8	399.9	399.0	398.1	397.2
145°	424.2	424.1	423.5	422.9	422.3	421.7	421.0	420.3	419.6	418.9	418.2
147.5°	442.8	442.6	442.2	441.8	441.4	441.0	440.4	439.5	438.7	437.8	437.0
150°	454.6	454.3	453.9	453.5	453.1	452.7	452.2	451.6	451.0	450.4	449.8
152.5°	466.5	466.1	465.5	465.0	464.5	464.1	463.5	462.9	462.3	461.7	461.1
155°	481.4	480.9	480.6	480.3	480.0	479.7	479.4	479.1	478.7	478.4	478.1
157.5°	495.1	494.4	494.2	494.0	493.8	493.6	493.5	493.3	493.1	492.9	492.7
160°	503.4	502.8	502.7	502.6	502.5	502.4	502.3	502.1	501.9	501.7	501.5
162.5°	510.8	510.2	510.1	510.0	509.9	509.8	509.7	509.6	509.6	509.6	509.5
165°	520.5	519.8	519.8	519.8	519.8	519.8	519.8	519.9	520.0	520.1	520.2
167.5°	528.5	527.8	527.8	527.8	527.8	527.8	528.0	528.3	528.6	528.9	529.2
170°	532.8	532.1	532.2	532.3	532.4	532.5	532.7	533.0	533.3	533.6	533.9
172.5°	536.1	535.4	535.5	535.6	535.7	535.8	536.0	536.3	536.6	536.9	537.2
175°	539.7	539.0	539.2	539.4	539.6	539.8	540.1	540.4	540.7	541.0	541.3
177.5°	541.6	541.1	541.2	541.4	541.6	541.7	541.9	542.2	542.4	542.7	542.9
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	13.7	16.2	16.4	18.2	17.5	18.0	18.4	18.3	18.2	17.7	17.1
90°	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9	15.7
92.5°	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5	14.6
95°	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3	29.3
97.5°	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2	49.2
100°	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1	63.1
102.5°	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3	78.3
105°	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9	101.1
107.5°	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5	125.6
110°	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3	159.1
115°	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7	184.6
117.5°	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6	209.4
120°	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0	226.0
122.5°	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4	243.1
125°	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7	268.4
127.5°	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4	293.0
130°	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0	309.8
132.5°	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6	326.2
135°	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3	350.2
137.5°	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4	373.3
140°	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9	388.9
142.5°	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9	402.9
145°	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2	424.3
147.5°	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8	443.0
150°	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6	454.9
152.5°	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5	466.8
155°	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4	481.9
157.5°	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1	495.7
160°	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4	504.0
162.5°	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8	511.5
165°	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5	521.2
167.5°	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5	529.2
170°	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8	533.5
172.5°	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1	536.8
175°	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7	540.4
177.5°	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6	542.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	17.6	17.5	17.0	17.0	17.6	17.1	17.1
90°	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331556-840

CATALOG NUMBER: S122DIW-S865D435U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)