

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331845

Luminaire Tested: **S122RDIW-S1005D435U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331845  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D435U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5544.0 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69								
1	103	99	95	92	97	94	91	88	84	82	79	75	73	71	67	65	64	60								
2	95	88	82	77	89	83	78	74	75	71	68	67	64	61	60	58	56	52								
3	87	78	71	66	82	74	68	63	67	62	58	60	57	53	54	51	49	46								
4	81	70	63	57	76	67	60	55	61	55	51	55	50	47	49	46	43	40								
5	75	63	56	50	70	60	53	48	55	49	45	50	45	42	45	41	38	36								
6	69	58	50	44	65	55	48	43	50	44	40	46	41	37	41	38	35	32								
7	64	53	45	39	61	50	43	38	46	40	36	42	37	34	38	34	31	29								
8	60	48	41	35	57	46	39	34	42	37	32	39	34	31	36	32	29	26								
9	56	44	37	32	53	43	36	31	39	34	30	36	31	28	33	29	26	24								
10	53	41	34	29	50	40	33	29	37	31	27	34	29	26	31	27	24	22								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.1	3.8
10°-20°	582.5	10.5
20°-30°	750.7	13.5
30°-40°	713.4	12.9
40°-50°	611.1	11.0
50°-60°	465.4	8.4
60°-70°	294.2	5.3
70°-80°	146.9	2.6
80°-90°	39.7	0.7
90°-100°	19.7	0.4
100°-110°	72.3	1.3
110°-120°	193.1	3.5
120°-130°	318.8	5.8
130°-140°	339.1	6.1
140°-150°	315.2	5.7
150°-160°	253.4	4.6
160°-170°	163.3	2.9
170°-180°	56.2	1.0
0°-30°	1542.3	27.8
0°-40°	2255.7	40.7
0°-60°	3332.1	60.1
0°-90°	3812.9	68.8
90°-120°	285.1	5.1
90°-150°	1258.2	22.7
90°-180°	1731.0	31.2
0°-180°	5544.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	30
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	130	32	130	32	34
115°	35	246	35	246	35	88
125°	365	348	365	348	365	316
135°	444	430	444	430	444	342
145°	506	499	506	499	506	317
155°	550	549	550	549	550	254
165°	577	579	577	579	577	163
175°	589	592	589	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	12.1	12.7	12.7	12.6	12.6	12.5	12.4	12.9	12.2	12.7	12.0
90°	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5	9.0	8.5	7.8
92.5°	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4	10.2	9.9	9.5
95°	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6	17.1	16.7	16.0
97.5°	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1	22.7	22.3	20.8
100°	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9	25.1	24.4	22.7
102.5°	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0	26.0	25.0	38.6
105°	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2	27.1	26.1	52.0
107.5°	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4	35.4	36.5	67.6
110°	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8	65.3	74.8	102.2



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4	154.0	188.7	195.4
115°	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8	219.7	263.7	261.3
117.5°	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8	281.5	292.1	290.5
120°	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6	314.4	313.3	311.6
122.5°	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8	334.2	333.5	331.6
125°	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5	361.8	361.2	359.4
127.5°	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1	387.1	386.1	384.8
130°	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3	403.2	402.2	401.2
132.5°	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1	419.2	418.3	417.2
135°	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6	441.6	440.7	439.8
137.5°	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5	462.5	461.6	460.6
140°	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0	476.1	475.3	474.2
142.5°	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5	488.7	487.9	486.7
145°	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0	506.3	505.6	504.0
147.5°	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2	521.7	521.2	519.6
150°	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6	531.0	530.4	528.9
152.5°	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1	539.5	539.0	537.5
155°	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7	551.1	550.5	549.4
157.5°	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4	560.7	560.1	559.3
160°	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0	566.5	565.9	565.3
162.5°	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3	571.7	571.0	570.5
165°	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4	577.2
167.5°	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2	583.5	582.8	582.6
170°	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9	586.2	585.6	585.4
172.5°	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9	588.3	587.6	587.4
175°	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2	590.5	589.8	589.6
177.5°	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4	590.9	590.3	590.3
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	11.8	12.3	12.1	11.3	11.7	12.2	15.0	17.9	15.6	14.0	13.0
90°	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8	24.6	21.5	18.4
97.5°	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1	46.3	37.5	28.6
100°	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7	62.6	49.6	36.6
102.5°	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2	95.5	92.7	90.0
105°	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9	132.8	135.6	138.5
107.5°	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1	168.4	170.7	173.0
110°	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3	191.3	193.3	195.3





TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2	213.0	214.8	216.5
115°	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8	247.4	249.0	250.6
117.5°	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6	278.4	280.2	282.0
120°	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2	300.6	302.0	303.5
122.5°	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3	319.8	321.3	322.8
125°	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5	348.7	350.0	351.2
127.5°	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9	375.3	376.6	378.0
130°	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7	392.2	393.7	395.2
132.5°	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8	409.0	410.3	411.6
135°	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0	431.5	433.0	434.5
137.5°	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5	453.5	454.6	455.7
140°	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2	467.9	468.7	469.4
142.5°	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5	480.2	480.8	481.5
145°	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5
147.5°	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6	515.3	514.9	514.6
150°	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6	525.9	525.2	524.6
152.5°	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8	535.1	534.3	533.6
155°	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2	548.4	547.5	546.7
157.5°	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7	559.0	558.3	557.6
160°	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	565.3	564.8	564.2
162.5°	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4	570.8	570.2	569.7
165°	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7	578.2	577.6	577.0
167.5°	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2	583.6	583.1	582.5
170°	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3	586.7	586.1	585.6
172.5°	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3	588.8	588.2	587.6
175°	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0	591.3	590.6	590.0
177.5°	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4	591.9	591.3	590.8
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	12.6	12.1	11.1	11.2	11.4	10.9	11.0	10.5	10.6	10.7	10.1
90°	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5	10.0	10.4	10.8
92.5°	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4	10.7	10.9	11.1
95°	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6	18.1	18.6	18.8
97.5°	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1	23.5	23.8	24.1
100°	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9	26.6	27.4	27.9
102.5°	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0	28.0	29.0	29.6
105°	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2	29.2	30.3	31.0
107.5°	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4	33.3	32.2	31.9
110°	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8	46.3	36.8	32.2



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4	84.7	50.1	32.9
115°	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8	131.8	87.8	62.4
117.5°	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8	260.2	249.5	233.0
120°	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6	316.7	317.9	312.0
122.5°	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8	335.5	336.2	335.3
125°	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5	363.2	363.8	364.3
127.5°	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1	389.0	390.0	390.5
130°	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3	405.3	406.4	406.9
132.5°	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1	420.9	421.8	422.2
135°	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6	443.5	444.5	444.8
137.5°	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5	464.4	465.3	465.6
140°	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0	477.9	478.7	478.9
142.5°	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5	490.3	491.1	491.2
145°	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0	507.6	508.3	508.4
147.5°	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2	522.7	523.2	523.2
150°	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6	532.1	532.7	532.8
152.5°	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1	540.7	541.3	541.2
155°	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7	552.2	552.8	552.7
157.5°	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4	562.0	562.7	562.6
160°	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0	567.6	568.2	568.1
162.5°	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3	573.0	573.6	573.5
165°	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8	579.4	580.1	580.1
167.5°	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2	584.8	585.5	585.4
170°	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9	587.6	588.2	588.1
172.5°	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9	589.6	590.3	590.2
175°	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2	591.8	592.5	592.4
177.5°	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4	591.9	592.5	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	10.2	9.6	10.2	9.7	10.2	9.6	10.2	10.1	10.7	10.6	10.5
90°	11.0	11.2	11.4	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4
95°	18.7	18.6	18.5	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6
97.5°	24.2	24.3	24.4	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1
100°	28.1	28.3	28.4	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9
102.5°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0
105°	31.3	31.7	32.1	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2
107.5°	32.3	32.7	33.0	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4
110°	32.6	33.0	33.4	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.2	33.5	33.8	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4
115°	55.6	48.7	41.9	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8
117.5°	210.5	188.0	165.6	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8
120°	299.2	286.4	273.5	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6
122.5°	332.8	330.3	327.8	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8
125°	364.6	364.9	365.2	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5
127.5°	390.6	390.6	390.7	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1
130°	406.8	406.7	406.6	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3
132.5°	422.1	422.0	422.0	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1
135°	444.7	444.5	444.3	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6
137.5°	465.3	465.0	464.7	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5
140°	478.4	477.9	477.5	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0
142.5°	490.7	490.3	489.8	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5
145°	507.9	507.4	507.0	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0
147.5°	522.8	522.4	522.0	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2
150°	532.3	531.8	531.3	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6
152.5°	540.6	540.0	539.3	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1
155°	551.9	551.2	550.4	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7
157.5°	561.9	561.1	560.4	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4
160°	567.5	566.8	566.1	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0
162.5°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3
165°	579.4	578.8	578.1	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8
167.5°	584.5	583.7	582.8	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2
170°	587.3	586.4	585.6	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9
172.5°	589.3	588.5	587.6	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9
175°	591.4	590.5	589.5	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2
177.5°	591.7	591.0	590.3	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	11.0	10.9	11.4	11.2	11.1	12.1	12.6	13.0	14.0	15.6	17.9
90°	9.0	8.5	7.8	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4
92.5°	10.2	9.9	9.5	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6
95°	17.1	16.7	16.0	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8
97.5°	22.7	22.3	20.8	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1
100°	25.1	24.4	22.7	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7
102.5°	26.0	25.0	38.6	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2
105°	27.1	26.1	52.0	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9
107.5°	35.4	36.5	67.6	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1
110°	65.3	74.8	102.2	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.0	188.7	195.4	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2
115°	219.7	263.7	261.3	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8
117.5°	281.5	292.1	290.5	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6
120°	314.4	313.3	311.6	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2
122.5°	334.2	333.5	331.6	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3
125°	361.8	361.2	359.4	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5
127.5°	387.1	386.1	384.8	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9
130°	403.2	402.2	401.2	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7
132.5°	419.2	418.3	417.2	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8
135°	441.6	440.7	439.8	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0
137.5°	462.5	461.6	460.6	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5
140°	476.1	475.3	474.2	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2
142.5°	488.7	487.9	486.7	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5
145°	506.3	505.6	504.0	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8
147.5°	521.7	521.2	519.6	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6
150°	531.0	530.4	528.9	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6
152.5°	539.5	539.0	537.5	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8
155°	551.1	550.5	549.4	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2
157.5°	560.7	560.1	559.3	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7
160°	566.5	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9
162.5°	571.7	571.0	570.5	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4
165°	578.1	577.4	577.2	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7
167.5°	583.5	582.8	582.6	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2
170°	586.2	585.6	585.4	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3
172.5°	588.3	587.6	587.4	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3
175°	590.5	589.8	589.6	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0
177.5°	590.9	590.3	590.3	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	15.0	12.2	11.7	11.3	12.1	12.3	11.8	12.0	12.7	12.2	12.9
90°	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4
95°	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6
97.5°	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1
100°	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9
102.5°	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0
105°	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2
107.5°	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4
110°	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8





TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4
115°	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8
117.5°	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8
120°	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6
122.5°	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8
125°	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5
127.5°	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1
130°	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3
132.5°	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1
135°	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6
137.5°	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5
140°	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0
142.5°	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5
145°	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0
147.5°	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2
150°	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6
152.5°	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1
155°	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7
157.5°	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4
160°	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0
162.5°	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3
165°	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8
167.5°	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2
170°	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9
172.5°	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9
175°	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2
177.5°	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	12.4	12.5	12.6	12.6	12.7	12.7	12.1
90°	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331845

CATALOG NUMBER: S122RDIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)