

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331851

Luminaire Tested: **S122RDIW-S1005D710U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331851
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6320.6 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	55	53	52	47
2	91	84	78	73	84	78	73	69	68	64	60	58	55	52	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	31
5	70	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	2.5
10°-20°	435.2	6.9
20°-30°	611.2	9.7
30°-40°	666.5	10.5
40°-50°	612.8	9.7
50°-60°	481.3	7.6
60°-70°	313.8	5.0
70°-80°	161.8	2.6
80°-90°	44.4	0.7
90°-100°	32.3	0.5
100°-110°	118.3	1.9
110°-120°	316.3	5.0
120°-130°	522.2	8.3
130°-140°	555.4	8.8
140°-150°	516.2	8.2
150°-160°	415.0	6.6
160°-170°	267.4	4.2
170°-180°	92.1	1.5
0°-30°	1204.9	19.1
0°-40°	1871.4	29.6
0°-60°	2965.4	46.9
0°-90°	3485.4	55.1
90°-120°	467.0	7.4
90°-150°	2060.7	32.6
90°-180°	2835.0	44.9
0°-180°	6320.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	1	8	14	17	19	5
95°	46	24	27	31	30	56
105°	213	222	43	50	53	227
115°	402	415	432	123	57	396
125°	569	578	592	596	598	507
135°	704	715	722	728	727	544
145°	817	817	828	833	830	511
155°	900	894	902	905	900	414
165°	948	944	946	950	946	268
175°	970	965	966	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.8	17.9	16.1	14.2	12.4	11.6	11.9	12.1	12.4	12.6	12.5
90°	0.7	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8
92.5°	14.1	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6
95°	45.5	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1
97.5°	90.3	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2
100°	123.9	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1
102.5°	160.9	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6
105°	212.8	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4
107.5°	272.0	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0
110°	310.1	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.0	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3
115°	402.5	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9
117.5°	453.1	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0
120°	490.0	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0
122.5°	521.4	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3
125°	569.1	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6
127.5°	612.4	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0
130°	639.8	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5
132.5°	667.9	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5
135°	704.3	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3
137.5°	741.1	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6
140°	765.2	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9
142.5°	785.3	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5
145°	817.0	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3
147.5°	844.5	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5
150°	862.5	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7
152.5°	877.6	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7
155°	899.6	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6
157.5°	916.8	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4
160°	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8
162.5°	935.8	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3
165°	947.9	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9
167.5°	956.8	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7
170°	961.9	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2
172.5°	965.2	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5
175°	969.6	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2
177.5°	970.3	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	12.4	12.3	12.1	12.1	12.2	12.2	12.3	12.4
90°	15.6	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.1	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	28.9	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	37.8	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	42.4	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	44.3	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	46.1	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	56.3	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	91.4	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331851

CATALOG NUMBER: S122RDIW-S1005D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	195.5	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	287.9	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	443.6	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	516.9	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	548.4	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	593.7	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	635.6	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	662.2	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	688.0	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	724.9	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	759.1	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	781.3	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	801.7	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	830.3	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	855.3	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	870.6	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	884.6	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	903.5	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	919.5	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	928.7	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	937.4	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	956.8	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	961.3	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	964.6	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	968.3	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	968.7	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)