

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331860-840

Luminaire Tested: **S122RDIW-S1005D1240U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331860-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7862.3 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28				
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	29	25				
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19				
7	58	47	39	33	54	43	36	32	37	31	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14				
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.0
10°-20°	439.5	5.6
20°-30°	617.2	7.9
30°-40°	673.0	8.6
40°-50°	618.8	7.9
50°-60°	486.0	6.2
60°-70°	316.9	4.0
70°-80°	163.4	2.1
80°-90°	48.6	0.6
90°-100°	98.3	1.3
100°-110°	305.4	3.9
110°-120°	522.0	6.6
120°-130°	686.4	8.7
130°-140°	770.4	9.8
140°-150°	755.4	9.6
150°-160°	633.6	8.1
160°-170°	420.3	5.3
170°-180°	146.9	1.9
0°-30°	1216.8	15.5
0°-40°	1889.8	24.0
0°-60°	2994.7	38.1
0°-90°	3523.5	44.8
90°-120°	925.7	11.8
90°-150°	3138.0	39.9
90°-180°	4339.0	55.2
0°-180°	7862.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	1	18	46	43	44	6
95°	68	81	84	84	81	78
105°	282	285	288	291	291	297
115°	524	531	529	528	524	518
125°	762	773	770	766	765	681
135°	986	1000	1003	1002	998	761
145°	1197	1206	1214	1215	1210	747
155°	1368	1372	1376	1382	1379	630
165°	1489	1488	1488	1496	1490	420
175°	1549	1545	1542	1551	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	20.1	18.6	17.1	15.6	14.0	13.9	15.2	16.5	17.8	19.1	18.7
90°	1.3	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2
92.5°	23.3	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7
95°	68.1	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8
97.5°	124.4	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9
100°	166.3	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7
102.5°	210.3	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9
105°	281.6	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6
107.5°	353.3	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3
110°	399.4	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.7	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8
115°	523.8	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8
117.5°	597.6	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1
120°	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8
122.5°	691.9	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4
125°	762.0	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1
127.5°	830.4	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6
130°	873.4	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2
132.5°	921.6	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7
135°	986.0	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7
137.5°	1053.8	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8
140°	1094.7	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0
142.5°	1136.6	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1
145°	1196.8	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2
147.5°	1250.5	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4
150°	1287.2	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1
152.5°	1319.7	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9
155°	1368.4	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7
157.5°	1410.0	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9
160°	1435.1	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8
162.5°	1458.1	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0
165°	1488.8	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6
167.5°	1514.5	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4
170°	1528.1	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9
172.5°	1537.5	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4
175°	1549.0	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6
177.5°	1553.8	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	18.3	17.9	17.5	17.4	17.4	17.5	17.5	17.6
90°	44.6	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	41.9	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.1	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.2	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.5	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331860-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	455.0	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.5	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	599.4	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.8	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	768.2	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	838.6	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.7	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	933.4	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.5	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.5	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.3	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.5	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.0	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1379.2	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1419.0	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1442.6	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1464.0	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1491.6	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1514.4	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1526.9	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1536.4	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1546.6	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)