

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331863-840

Luminaire Tested: **S122RDIW-S1005D1440U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331863-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9339.1 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18				
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	1.7
10°-20°	439.5	4.7
20°-30°	617.2	6.6
30°-40°	673.0	7.2
40°-50°	618.8	6.6
50°-60°	486.0	5.2
60°-70°	316.9	3.4
70°-80°	163.4	1.7
80°-90°	47.3	0.5
90°-100°	66.2	0.7
100°-110°	242.8	2.6
110°-120°	649.0	6.9
120°-130°	1071.4	11.5
130°-140°	1139.4	12.2
140°-150°	1059.0	11.3
150°-160°	851.5	9.1
160°-170°	548.7	5.9
170°-180°	188.9	2.0
0°-30°	1216.8	13.0
0°-40°	1889.8	20.2
0°-60°	2994.7	32.1
0°-90°	3522.2	37.7
90°-120°	958.1	10.3
90°-150°	4227.9	45.3
90°-180°	5817.0	62.3
0°-180°	9339.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	1	17	29	36	39	7
95°	93	49	56	63	62	114
105°	437	456	88	103	109	467
115°	826	851	886	252	118	813
125°	1168	1187	1214	1223	1228	1041
135°	1445	1467	1481	1494	1492	1116
145°	1676	1676	1699	1708	1702	1048
155°	1846	1834	1850	1857	1847	850
165°	1945	1937	1940	1949	1940	549
175°	1989	1980	1982	1991	1978	189
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	20.1	18.6	17.1	15.6	14.1	13.6	14.1	14.6	15.1	15.7	15.7
90°	1.4	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3
92.5°	29.0	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1
95°	93.3	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6
97.5°	185.3	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2
100°	254.2	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4
102.5°	330.0	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5
105°	436.7	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1
107.5°	558.2	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1
110°	636.3	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	709.8	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6
115°	825.9	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4
117.5°	929.6	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8
120°	1005.4	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6
122.5°	1069.8	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9
125°	1167.7	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9
127.5°	1256.5	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8
130°	1312.7	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0
132.5°	1370.2	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6
135°	1444.9	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0
137.5°	1520.5	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3
140°	1569.8	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0
142.5°	1611.2	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2
145°	1676.2	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3
147.5°	1732.7	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0
150°	1769.5	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3
152.5°	1800.5	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0
155°	1845.6	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8
157.5°	1881.0	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3
160°	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5
162.5°	1920.0	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1
165°	1944.7	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7
167.5°	1963.1	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8
170°	1973.5	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9
172.5°	1980.3	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8
175°	1989.2	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3
177.5°	1990.6	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	15.8	15.8	15.9	16.0	16.1	16.2	16.3	16.5
90°	31.9	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	34.9	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	59.2	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	77.6	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	86.9	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	90.8	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	94.6	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	115.5	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	187.5	155.6	123.7	108.4	109.7	110.9	112.2	113.5



TEST NUMBER: P331863-840

CATALOG NUMBER: S122RDIW-S1005D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.1	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	590.7	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	910.1	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1060.5	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1125.2	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1218.1	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1304.0	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1358.6	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1411.5	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1487.1	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1557.4	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1602.9	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1644.9	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1703.5	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1754.7	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1786.2	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1814.9	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1853.7	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1886.4	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1905.4	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1923.2	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1963.0	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1972.2	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1979.0	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1986.5	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1987.3	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)