

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331781

Luminaire Tested: **S122RDIW-S290D1440U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331781
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6894.7 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	25	25	25	16				
1	91	86	83	80	79	76	73	71	57	55	53	39	38	37	23	22	22	14				
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	20	19	19	12				
3	75	67	60	55	66	59	53	49	44	41	38	31	29	27	18	17	16	11				
4	69	59	52	46	60	52	46	41	39	35	32	28	25	23	16	15	14	10				
5	63	53	45	40	55	47	40	36	35	31	28	25	22	20	15	14	12	9				
6	58	47	40	34	51	42	35	31	32	27	24	22	20	18	14	12	11	8				
7	54	42	35	30	47	38	31	27	29	24	21	20	18	16	12	11	10	7				
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	11	10	9	6				
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	9	8	6				
10	43	32	25	21	38	28	23	19	22	18	15	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	0.9
10°-20°	172.7	2.5
20°-30°	222.5	3.2
30°-40°	211.5	3.1
40°-50°	181.1	2.6
50°-60°	137.9	2.0
60°-70°	87.2	1.3
70°-80°	43.5	0.6
80°-90°	16.2	0.2
90°-100°	65.6	1.0
100°-110°	240.4	3.5
110°-120°	642.7	9.3
120°-130°	1060.9	15.4
130°-140°	1128.3	16.4
140°-150°	1048.7	15.2
150°-160°	843.1	12.2
160°-170°	543.3	7.9
170°-180°	187.0	2.7
0°-30°	457.2	6.6
0°-40°	668.6	9.7
0°-60°	987.7	14.3
0°-90°	1134.6	16.5
90°-120°	948.7	13.8
90°-150°	4186.6	60.7
90°-180°	5760.0	83.5
0°-180°	6894.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	10
90°	38	1	38	1	38	17
95°	61	92	61	92	61	57
105°	108	432	108	432	108	112
115°	117	818	117	818	117	292
125°	1216	1156	1216	1156	1216	1052
135°	1478	1431	1478	1431	1478	1139
145°	1685	1660	1685	1660	1685	1054
155°	1829	1828	1829	1828	1829	844
165°	1921	1926	1921	1926	1921	542
175°	1958	1970	1958	1970	1958	187
180°	1966	1966	1966	1966	1966	



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	10.6	10.6	10.5	10.4	10.3	10.0	9.7	9.6	9.1	9.0	8.3
90°	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6	30.0	28.4	25.9
92.5°	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6	33.8	33.0	31.7
95°	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6	57.0	55.5	53.3
97.5°	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8	75.5	74.2	69.1
100°	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1	83.6	81.1	75.7
102.5°	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9	86.6	83.3	128.3
105°	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7	90.2	86.8	173.0
107.5°	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4	117.9	121.5	224.9
110°	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7	217.3	248.9	340.2



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2	512.5	627.8	650.3
115°	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9	731.2	877.5	869.6
117.5°	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2	936.6	972.0	966.5
120°	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1	1046.3	1042.5	1036.8
122.5°	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2	1111.9	1109.6	1103.4
125°	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2	1204.0	1201.8	1195.8
127.5°	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3	1288.1	1284.9	1280.4
130°	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3	1341.8	1338.3	1334.8
132.5°	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7	1394.8	1391.8	1388.3
135°	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6	1469.5	1466.3	1463.5
137.5°	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2	1539.1	1536.0	1532.8
140°	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2	1584.4	1581.5	1578.1
142.5°	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8	1626.2	1623.6	1619.6
145°	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9	1684.7	1682.5	1677.1
147.5°	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6	1735.9	1734.3	1729.0
150°	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8	1766.9	1765.0	1759.9
152.5°	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2	1795.3	1793.4	1788.6
155°	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6	1833.7	1831.8	1828.1
157.5°	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0	1865.9	1863.7	1861.0
160°	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8	1884.9	1883.0	1881.1
162.5°	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4	1902.3	1900.1	1898.5
165°	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4	1920.5
167.5°	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8	1941.6	1939.4	1938.5
170°	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9	1950.7	1948.5	1947.8
172.5°	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7	1957.5	1955.3	1954.7
175°	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1	1964.9	1962.7	1962.1
177.5°	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9	1966.2	1964.4	1964.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	7.8	7.4	6.9	6.2	5.6	5.1	5.3	5.6	5.5	5.7	6.0
90°	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4	4.9	8.4	11.9
92.5°	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7	28.4	28.1	27.8
95°	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4	82.0	71.6	61.2
97.5°	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5	154.1	124.7	95.3
100°	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7	208.4	165.1	121.8
102.5°	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8	317.7	308.5	299.3
105°	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4	441.8	451.3	460.8
107.5°	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7	560.3	568.0	575.6
110°	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1	636.7	643.3	650.0



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9	708.7	714.6	720.5
115°	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8	823.2	828.5	833.9
117.5°	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5	926.5	932.5	938.5
120°	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6	1000.3	1005.0	1009.8
122.5°	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3	1064.3	1069.3	1074.3
125°	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3	1160.4	1164.5	1168.6
127.5°	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2	1248.7	1253.3	1257.8
130°	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9	1305.0	1310.0	1315.1
132.5°	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8	1361.1	1365.4	1369.7
135°	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8	1435.8	1440.9	1445.9
137.5°	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6	1509.1	1512.7	1516.2
140°	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5	1557.0	1559.6	1562.1
142.5°	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5	1597.7	1600.0	1602.3
145°	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8	1659.4	1659.1	1658.8
147.5°	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8	1714.6	1713.4	1712.2
150°	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2	1750.0	1747.8	1745.6
152.5°	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9	1780.5	1778.0	1775.5
155°	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6	1824.7	1821.9	1819.0
157.5°	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6	1860.2	1857.8	1855.4
160°	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1881.1	1879.3	1877.4
162.5°	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2	1899.4	1897.5	1895.6
165°	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7	1923.8	1921.9	1920.0
167.5°	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9	1942.0	1940.1	1938.2
170°	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2	1952.3	1950.4	1948.5
172.5°	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0	1959.1	1957.2	1955.3
175°	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8	1967.6	1965.4	1963.2
177.5°	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2	1969.5	1967.7	1965.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	6.5	6.9	7.1	7.6	8.1	8.4	8.7	8.9	9.2	9.5	9.5
90°	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6	33.2	34.8	35.9
92.5°	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6	35.5	36.3	36.9
95°	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6	60.2	61.8	62.4
97.5°	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8	78.0	79.3	80.1
100°	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1	88.7	91.2	92.8
102.5°	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9	93.2	96.5	98.6
105°	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7	97.2	100.7	103.0
107.5°	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4	110.8	107.3	106.2
110°	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7	154.1	122.5	107.3



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2	281.9	166.6	109.4
115°	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9	438.5	292.2	207.6
117.5°	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2	865.8	830.4	775.3
120°	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1	1053.9	1057.7	1038.2
122.5°	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2	1116.5	1118.7	1115.7
125°	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2	1208.4	1210.6	1212.2
127.5°	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3	1294.5	1297.7	1299.5
130°	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3	1348.8	1352.2	1353.8
132.5°	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7	1400.7	1403.7	1405.0
135°	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6	1475.8	1479.0	1480.2
137.5°	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2	1545.3	1548.4	1549.4
140°	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2	1590.1	1592.9	1593.5
142.5°	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8	1631.4	1634.0	1634.5
145°	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9	1689.1	1691.4	1691.7
147.5°	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6	1739.2	1740.9	1741.0
150°	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8	1770.7	1772.6	1772.7
152.5°	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2	1799.1	1801.0	1800.9
155°	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6	1837.5	1839.4	1839.1
157.5°	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0	1870.1	1872.3	1872.1
160°	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8	1888.7	1890.6	1890.5
162.5°	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4	1906.6	1908.7	1908.4
165°	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3
167.5°	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8	1946.0	1948.2	1947.9
170°	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9	1955.1	1957.3	1957.0
172.5°	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7	1961.9	1964.1	1963.8
175°	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1	1969.3	1971.5	1971.1
177.5°	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9	1969.7	1971.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	9.7	9.6	9.9	9.9	9.9	9.6	9.7	9.5	9.5	9.2	8.9
90°	36.5	37.1	37.8	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6
92.5°	37.3	37.6	38.0	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6
95°	62.1	61.8	61.5	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6
97.5°	80.5	80.9	81.3	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8
100°	93.4	94.0	94.7	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1
102.5°	99.5	100.3	101.2	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9
105°	104.3	105.6	106.8	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7
107.5°	107.4	108.7	110.0	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4
110°	108.6	109.8	111.1	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	110.5	111.5	112.5	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2
115°	184.9	162.1	139.4	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9
117.5°	700.5	625.7	550.9	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2
120°	995.6	952.9	910.2	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1
122.5°	1107.4	1099.2	1090.9	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2
125°	1213.2	1214.1	1215.1	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2
127.5°	1299.6	1299.8	1300.0	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3
130°	1353.5	1353.2	1352.9	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3
132.5°	1404.7	1404.4	1404.1	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7
135°	1479.6	1479.0	1478.3	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6
137.5°	1548.3	1547.3	1546.2	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2
140°	1592.0	1590.4	1588.8	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2
142.5°	1632.9	1631.3	1629.8	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8
145°	1690.1	1688.5	1686.9	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9
147.5°	1739.7	1738.4	1737.0	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6
150°	1771.2	1769.6	1768.0	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8
152.5°	1798.8	1796.8	1794.7	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2
155°	1836.6	1834.1	1831.5	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6
157.5°	1869.7	1867.2	1864.7	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0
160°	1888.3	1886.0	1883.8	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8
162.5°	1905.7	1903.0	1900.3	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4
165°	1928.1	1925.9	1923.7	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9
167.5°	1945.1	1942.2	1939.4	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8
170°	1954.2	1951.3	1948.5	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9
172.5°	1961.0	1958.1	1955.3	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7
175°	1967.9	1964.7	1961.6	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1
177.5°	1968.9	1966.7	1964.4	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	8.7	8.4	8.1	7.6	7.1	6.9	6.5	6.0	5.7	5.5	5.6
90°	30.0	28.4	25.9	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4
92.5°	33.8	33.0	31.7	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7
95°	57.0	55.5	53.3	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4
97.5°	75.5	74.2	69.1	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5
100°	83.6	81.1	75.7	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7
102.5°	86.6	83.3	128.3	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8
105°	90.2	86.8	173.0	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4
107.5°	117.9	121.5	224.9	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7
110°	217.3	248.9	340.2	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	512.5	627.8	650.3	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9
115°	731.2	877.5	869.6	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8
117.5°	936.6	972.0	966.5	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5
120°	1046.3	1042.5	1036.8	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6
122.5°	1111.9	1109.6	1103.4	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3
125°	1204.0	1201.8	1195.8	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3
127.5°	1288.1	1284.9	1280.4	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2
130°	1341.8	1338.3	1334.8	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9
132.5°	1394.8	1391.8	1388.3	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8
135°	1469.5	1466.3	1463.5	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8
137.5°	1539.1	1536.0	1532.8	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6
140°	1584.4	1581.5	1578.1	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5
142.5°	1626.2	1623.6	1619.6	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5
145°	1684.7	1682.5	1677.1	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8
147.5°	1735.9	1734.3	1729.0	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8
150°	1766.9	1765.0	1759.9	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2
152.5°	1795.3	1793.4	1788.6	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9
155°	1833.7	1831.8	1828.1	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6
157.5°	1865.9	1863.7	1861.0	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6
160°	1884.9	1883.0	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0
162.5°	1902.3	1900.1	1898.5	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2
165°	1923.7	1921.4	1920.5	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7
167.5°	1941.6	1939.4	1938.5	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9
170°	1950.7	1948.5	1947.8	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2
172.5°	1957.5	1955.3	1954.7	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0
175°	1964.9	1962.7	1962.1	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8
177.5°	1966.2	1964.4	1964.1	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	5.3	5.1	5.6	6.2	6.9	7.4	7.8	8.3	9.0	9.1	9.6
90°	4.9	8.4	11.9	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6
92.5°	28.4	28.1	27.8	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6
95°	82.0	71.6	61.2	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6
97.5°	154.1	124.7	95.3	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8
100°	208.4	165.1	121.8	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1
102.5°	317.7	308.5	299.3	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9
105°	441.8	451.3	460.8	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7
107.5°	560.3	568.0	575.6	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4
110°	636.7	643.3	650.0	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	708.7	714.6	720.5	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2
115°	823.2	828.5	833.9	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9
117.5°	926.5	932.5	938.5	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2
120°	1000.3	1005.0	1009.8	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1
122.5°	1064.3	1069.3	1074.3	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2
125°	1160.4	1164.5	1168.6	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2
127.5°	1248.7	1253.3	1257.8	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3
130°	1305.0	1310.0	1315.1	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3
132.5°	1361.1	1365.4	1369.7	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7
135°	1435.8	1440.9	1445.9	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6
137.5°	1509.1	1512.7	1516.2	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2
140°	1557.0	1559.6	1562.1	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2
142.5°	1597.7	1600.0	1602.3	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8
145°	1659.4	1659.1	1658.8	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9
147.5°	1714.6	1713.4	1712.2	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6
150°	1750.0	1747.8	1745.6	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8
152.5°	1780.5	1778.0	1775.5	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2
155°	1824.7	1821.9	1819.0	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6
157.5°	1860.2	1857.8	1855.4	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0
160°	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8
162.5°	1899.4	1897.5	1895.6	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4
165°	1923.8	1921.9	1920.0	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9
167.5°	1942.0	1940.1	1938.2	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8
170°	1952.3	1950.4	1948.5	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9
172.5°	1959.1	1957.2	1955.3	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7
175°	1967.6	1965.4	1963.2	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1
177.5°	1969.5	1967.7	1965.9	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	9.7	10.0	10.3	10.4	10.5	10.6	10.6
90°	33.2	34.8	35.9	36.5	37.1	37.8	38.4
92.5°	35.5	36.3	36.9	37.3	37.6	38.0	38.4
95°	60.2	61.8	62.4	62.1	61.8	61.5	61.2
97.5°	78.0	79.3	80.1	80.5	80.9	81.3	81.6
100°	88.7	91.2	92.8	93.4	94.0	94.7	95.3
102.5°	93.2	96.5	98.6	99.5	100.3	101.2	102.1
105°	97.2	100.7	103.0	104.3	105.6	106.8	108.1
107.5°	110.8	107.3	106.2	107.4	108.7	110.0	111.2
110°	154.1	122.5	107.3	108.6	109.8	111.1	112.4



TEST NUMBER: P331781

CATALOG NUMBER: S122RDIW-S290D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	281.9	166.6	109.4	110.5	111.5	112.5	113.5
115°	438.5	292.2	207.6	184.9	162.1	139.4	116.6
117.5°	865.8	830.4	775.3	700.5	625.7	550.9	476.2
120°	1053.9	1057.7	1038.2	995.6	952.9	910.2	867.6
122.5°	1116.5	1118.7	1115.7	1107.4	1099.2	1090.9	1082.6
125°	1208.4	1210.6	1212.2	1213.2	1214.1	1215.1	1216.0
127.5°	1294.5	1297.7	1299.5	1299.6	1299.8	1300.0	1300.2
130°	1348.8	1352.2	1353.8	1353.5	1353.2	1352.9	1352.5
132.5°	1400.7	1403.7	1405.0	1404.7	1404.4	1404.1	1403.7
135°	1475.8	1479.0	1480.2	1479.6	1479.0	1478.3	1477.7
137.5°	1545.3	1548.4	1549.4	1548.3	1547.3	1546.2	1545.1
140°	1590.1	1592.9	1593.5	1592.0	1590.4	1588.8	1587.2
142.5°	1631.4	1634.0	1634.5	1632.9	1631.3	1629.8	1628.2
145°	1689.1	1691.4	1691.7	1690.1	1688.5	1686.9	1685.4
147.5°	1739.2	1740.9	1741.0	1739.7	1738.4	1737.0	1735.7
150°	1770.7	1772.6	1772.7	1771.2	1769.6	1768.0	1766.4
152.5°	1799.1	1801.0	1800.9	1798.8	1796.8	1794.7	1792.6
155°	1837.5	1839.4	1839.1	1836.6	1834.1	1831.5	1829.0
157.5°	1870.1	1872.3	1872.1	1869.7	1867.2	1864.7	1862.3
160°	1888.7	1890.6	1890.5	1888.3	1886.0	1883.8	1881.6
162.5°	1906.6	1908.7	1908.4	1905.7	1903.0	1900.3	1897.6
165°	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4
167.5°	1946.0	1948.2	1947.9	1945.1	1942.2	1939.4	1936.5
170°	1955.1	1957.3	1957.0	1954.2	1951.3	1948.5	1945.6
172.5°	1961.9	1964.1	1963.8	1961.0	1958.1	1955.3	1952.4
175°	1969.3	1971.5	1971.1	1967.9	1964.7	1961.6	1958.4
177.5°	1969.7	1971.5	1971.2	1968.9	1966.7	1964.4	1962.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5

(END OF REPORT)