

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331845-840

Luminaire Tested: **S122RDIW-S1005D435U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331845-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.7 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	103	99	95	92	97	94	91	88	84	82	79	75	73	71	67	65	64	60
2	95	88	82	77	89	83	78	74	75	71	68	67	64	61	60	58	56	52
3	87	78	71	66	82	74	68	63	67	62	58	60	57	53	54	51	49	46
4	81	70	63	57	76	67	60	55	61	55	51	55	50	47	49	46	43	40
5	75	63	56	50	70	60	53	48	55	49	45	50	45	42	45	41	38	36
6	69	58	50	44	65	55	48	43	50	44	40	46	41	37	41	38	35	32
7	64	53	45	39	61	50	43	38	46	40	36	42	37	34	38	34	31	29
8	60	48	41	35	57	46	39	34	42	37	32	39	34	31	36	32	29	26
9	56	44	37	32	53	43	36	31	39	34	30	36	31	28	33	29	26	24
10	53	41	34	29	50	40	33	29	37	31	27	34	29	26	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35960	35960	35960	35960
5°	40161	36185	32083	36185
10°	44558	35931	27811	35931
15°	46748	35405	21912	35405
20°	40527	34625	18962	34625
25°	26580	33556	16930	33556
30°	17890	32261	15321	32261
35°	14491	30628	13819	30628
40°	12886	28854	12787	28854
45°	11663	26772	11415	26772
50°	10613	24707	10575	24707
55°	9979	22415	9847	22415
60°	8344	20315	8247	20315
65°	7037	18449	7981	18449
70°	6500	16475	7530	16475
75°	6089	14336	6949	14336
80°	5616	11799	6192	11799
85°	5169	9318	5446	9318



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.1	3.8
10°-20°	588.3	10.5
20°-30°	758.1	13.5
30°-40°	720.4	12.9
40°-50°	617.1	11.0
50°-60°	470.0	8.4
60°-70°	297.1	5.3
70°-80°	148.4	2.6
80°-90°	40.1	0.7
90°-100°	19.9	0.4
100°-110°	73.0	1.3
110°-120°	195.0	3.5
120°-130°	322.0	5.8
130°-140°	342.4	6.1
140°-150°	318.3	5.7
150°-160°	255.9	4.6
160°-170°	164.9	2.9
170°-180°	56.8	1.0
0°-30°	1557.5	27.8
0°-40°	2277.9	40.7
0°-60°	3365.0	60.1
0°-90°	3850.6	68.8
90°-120°	287.9	5.1
90°-150°	1270.6	22.7
90°-180°	1748.0	31.2
0°-180°	5598.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2227	2227	2227	2227	2227	
5°	2478	2233	1980	2233	2478	245
15°	2797	2118	1311	2118	2797	754
25°	1492	1884	950	1884	1492	708
35°	735	1554	701	1554	735	470
45°	511	1172	500	1172	511	395
55°	354	796	350	796	354	311
65°	184	483	209	483	184	187
75°	98	230	111	230	98	103
85°	28	50	29	50	28	30
90°	12	0	12	0	12	6
95°	19	28	19	28	19	17
105°	33	131	33	131	33	34
115°	35	248	35	248	35	89
125°	369	351	369	351	369	319
135°	448	434	448	434	448	346
145°	512	504	512	504	512	320
155°	555	555	555	555	555	256
165°	583	584	583	584	583	165
175°	594	598	594	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2317.5	2319.5	2321.3	2316.9	2316.9	2313.2	2305.2	2299.0	2281.7	2279.2	2279.2
5°	2477.9	2476.4	2479.4	2469.4	2455.5	2452.4	2437.7	2418.3	2398.2	2375.8	2371.2
7.5°	2637.4	2635.0	2628.8	2627.2	2616.5	2593.0	2569.4	2544.2	2510.7	2478.1	2461.6
10°	2717.8	2743.4	2727.8	2700.8	2706.2	2669.9	2650.5	2617.3	2589.4	2540.6	2529.8
12.5°	2797.0	2807.1	2802.2	2786.8	2779.9	2754.6	2728.5	2699.6	2648.2	2604.3	2566.3
15°	2796.7	2811.5	2815.3	2810.7	2814.6	2813.0	2799.0	2775.1	2730.2	2682.2	2640.4
17.5°	2590.3	2600.5	2625.9	2643.0	2664.7	2710.6	2733.1	2742.0	2735.3	2708.0	2678.5
20°	2358.7	2341.7	2412.9	2449.3	2480.2	2557.6	2624.1	2649.7	2690.7	2690.0	2682.2
22.5°	2030.6	2034.7	2102.1	2145.4	2235.7	2313.1	2388.9	2485.1	2564.5	2616.9	2647.6
25°	1492.0	1521.5	1588.7	1647.6	1748.2	1892.1	2022.9	2174.5	2317.7	2430.7	2538.3
27.5°	1120.5	1122.8	1176.1	1230.4	1290.2	1408.2	1572.8	1753.9	1958.0	2126.5	2320.2
30°	959.6	954.9	977.3	1010.7	1061.8	1153.1	1276.9	1454.9	1658.4	1912.2	2138.2
32.5°	845.7	846.0	862.8	887.5	929.9	991.5	1076.3	1220.8	1413.2	1662.7	1927.7
35°	735.2	734.4	746.8	764.6	782.3	821.8	879.9	955.7	1088.0	1321.0	1591.9
37.5°	655.9	659.3	665.4	676.5	696.2	718.1	753.0	803.9	898.2	1035.9	1263.5
40°	611.4	612.9	621.4	630.7	642.3	659.3	687.9	729.0	797.9	907.8	1074.1
42.5°	570.5	572.1	578.0	586.7	595.9	612.9	636.6	672.1	727.9	813.6	950.9
45°	510.8	510.8	516.1	520.1	530.1	545.5	564.9	594.3	633.0	696.5	787.8
47.5°	454.7	454.8	458.5	465.1	471.4	483.5	502.5	526.5	554.7	603.8	681.8
50°	422.5	423.3	425.7	431.0	434.9	445.8	460.5	481.3	510.8	548.7	613.7
52.5°	396.6	396.1	399.0	401.3	403.9	411.7	422.7	441.1	467.4	500.4	554.2
55°	354.5	351.3	356.0	359.8	362.1	365.3	371.4	383.0	405.5	433.3	473.6
57.5°	301.8	300.5	303.9	307.4	314.7	323.1	328.3	335.7	347.3	367.3	407.2
60°	258.4	258.4	265.4	267.7	276.3	287.1	297.9	304.2	315.8	328.9	358.3
62.5°	220.0	220.8	224.0	226.3	231.1	244.4	259.5	273.2	284.2	296.7	316.2
65°	184.2	185.7	185.7	187.2	190.4	193.5	199.7	210.5	229.8	247.6	262.4
67.5°	156.3	156.8	157.2	158.8	159.6	163.0	165.4	170.3	174.7	191.6	209.8
70°	137.7	140.1	139.3	140.9	141.6	143.2	146.2	148.6	155.5	159.5	170.3
72.5°	120.4	122.1	122.0	122.9	124.9	125.2	127.6	130.0	134.5	137.7	143.6
75°	97.6	96.7	97.6	99.1	99.9	100.6	100.6	103.7	106.0	109.1	113.0
77.5°	75.2	76.0	75.8	76.0	76.1	77.6	77.4	78.8	81.1	82.6	84.5
80°	60.4	61.1	60.4	61.1	61.9	62.7	61.9	62.7	65.0	66.6	66.6
82.5°	46.8	46.9	47.4	47.6	47.7	47.9	48.9	49.1	50.8	50.5	51.1
85°	27.9	27.1	27.1	27.1	27.9	28.7	27.9	27.9	28.7	28.7	28.7
87.5°	12.2	12.8	12.8	12.7	12.7	12.6	12.5	13.0	12.3	12.8	12.1
90°	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6	9.1	8.6	7.9
92.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5	10.3	10.0	9.6
95°	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8	17.3	16.9	16.2
97.5°	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3	22.9	22.5	21.0
100°	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2	25.3	24.6	22.9
102.5°	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3	26.3	25.2	39.0
105°	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5	27.4	26.4	52.5
107.5°	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7	35.7	36.9	68.3
110°	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4	65.9	75.5	103.2



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6	155.5	190.6	197.3
115°	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5	221.9	266.3	263.9
117.5°	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5	284.3	295.0	293.4
120°	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7	317.5	316.4	314.7
122.5°	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1	337.5	336.8	334.9
125°	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1	365.4	364.8	362.9
127.5°	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9	390.9	389.9	388.6
130°	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3	407.2	406.2	405.2
132.5°	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2	423.3	422.4	421.3
135°	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0	446.0	445.0	444.1
137.5°	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1	467.1	466.2	465.1
140°	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7	480.8	480.0	478.9
142.5°	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3	493.5	492.7	491.5
145°	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0	511.3	510.6	509.0
147.5°	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4	526.8	526.3	524.7
150°	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8	536.2	535.6	534.1
152.5°	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4	544.8	544.3	542.8
155°	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1	556.5	555.9	554.8
157.5°	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9	566.2	565.6	564.8
160°	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6	572.1	571.5	570.9
162.5°	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9	577.3	576.6	576.1
165°	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1	582.9
167.5°	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0	589.3	588.5	588.3
170°	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7	592.0	591.4	591.2
172.5°	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7	594.1	593.4	593.2
175°	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0	596.3	595.6	595.4
177.5°	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2	596.7	596.1	596.1
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2280.5	2275.4	2271.2	2260.0	2254.4	2242.0	2240.2	2239.6	2223.5	2208.0	2203.6
5°	2358.7	2346.3	2327.8	2306.1	2283.7	2260.5	2245.0	2232.6	2201.6	2172.2	2155.3
7.5°	2437.7	2411.1	2379.0	2338.0	2303.8	2265.4	2237.0	2211.4	2167.5	2125.4	2097.0
10°	2496.5	2453.2	2410.5	2354.1	2310.0	2266.6	2226.4	2191.6	2142.0	2086.4	2046.9
12.5°	2533.0	2485.4	2426.7	2371.5	2314.3	2259.3	2205.3	2160.6	2102.4	2044.9	1998.0
15°	2582.4	2531.3	2460.1	2381.2	2307.6	2235.7	2173.8	2118.1	2042.3	1973.4	1916.1
17.5°	2622.8	2552.5	2476.1	2384.8	2299.7	2208.2	2128.5	2057.3	1972.9	1889.8	1822.3
20°	2635.7	2566.2	2477.9	2386.6	2286.0	2178.5	2092.5	2015.2	1924.6	1834.0	1756.7
22.5°	2627.8	2573.5	2475.5	2366.2	2263.1	2150.6	2053.6	1963.8	1863.3	1770.9	1681.1
25°	2573.1	2554.6	2461.6	2342.5	2224.8	2094.1	1981.9	1883.6	1769.1	1670.0	1572.5
27.5°	2445.7	2485.8	2428.2	2301.3	2170.5	2030.3	1904.2	1792.3	1673.4	1562.0	1464.8
30°	2323.2	2415.2	2390.5	2272.8	2126.6	1988.8	1847.2	1730.4	1603.5	1488.9	1393.0
32.5°	2155.4	2307.5	2331.7	2233.2	2082.0	1930.7	1782.2	1666.0	1533.5	1412.8	1319.3
35°	1888.2	2115.8	2220.2	2157.6	2005.9	1842.6	1689.3	1553.9	1420.8	1301.6	1208.8
37.5°	1569.5	1879.5	2053.6	2058.0	1918.7	1749.0	1582.1	1447.6	1311.4	1194.4	1094.0
40°	1362.8	1698.6	1925.4	1975.7	1858.1	1674.7	1505.9	1369.0	1235.9	1121.4	1006.0
42.5°	1177.1	1511.7	1790.4	1877.8	1784.4	1602.3	1432.9	1289.7	1160.3	1052.0	934.2
45°	951.9	1244.4	1551.6	1707.9	1656.1	1487.3	1308.6	1172.5	1050.9	957.3	844.2
47.5°	802.9	1009.2	1306.5	1517.8	1516.9	1362.9	1187.1	1056.6	943.9	856.2	764.8
50°	718.1	897.7	1149.2	1389.1	1409.2	1280.0	1112.8	983.6	878.4	786.3	712.8
52.5°	642.0	789.9	1016.1	1246.1	1303.3	1191.4	1029.3	909.9	807.8	723.1	660.1
55°	542.5	657.0	828.8	1043.9	1130.6	1051.7	907.8	796.3	713.5	642.3	588.1
57.5°	458.9	544.8	682.7	855.9	956.8	907.2	788.4	697.9	627.0	562.6	519.9
60°	406.3	476.7	593.6	738.3	849.7	814.9	713.5	629.1	568.8	513.1	472.8
62.5°	356.8	417.3	517.5	634.9	737.0	722.7	639.9	569.1	516.1	465.4	431.3
65°	287.1	331.2	409.4	501.5	583.5	590.5	530.9	482.9	435.7	395.5	365.3
67.5°	228.6	257.4	312.5	390.0	451.5	473.4	437.1	400.4	362.9	331.8	305.7
70°	192.7	215.9	256.1	318.8	375.4	398.5	377.7	349.0	316.5	290.9	268.5
72.5°	156.1	178.7	208.4	254.5	302.9	328.0	320.7	300.1	273.8	252.6	231.4
75°	117.6	124.6	144.7	175.7	213.6	235.3	240.7	229.8	208.9	192.7	180.3
77.5°	86.9	91.2	100.8	117.0	141.8	161.1	169.1	167.7	153.4	143.9	132.3
80°	69.7	72.0	76.6	83.6	102.2	121.5	126.9	126.9	116.8	113.0	101.4
82.5°	52.9	54.6	57.5	61.3	70.0	86.8	92.9	94.1	87.8	82.6	73.5
85°	30.2	29.4	31.0	33.3	34.8	39.5	48.8	50.3	48.8	42.5	40.2
87.5°	11.9	12.4	12.2	11.4	11.8	12.3	15.1	18.1	15.8	14.1	13.1
90°	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7	8.6	8.5	8.4
95°	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1	24.8	21.7	18.6
97.5°	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6	46.8	37.9	28.9
100°	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4	63.2	50.1	37.0
102.5°	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2	96.4	93.6	90.9
105°	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2	134.1	136.9	139.9
107.5°	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7	170.1	172.4	174.7
110°	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2	193.2	195.2	197.2



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3	215.1	216.9	218.6
115°	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2	249.8	251.5	253.1
117.5°	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3	281.1	283.0	284.8
120°	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2	303.6	305.0	306.5
122.5°	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4	323.0	324.5	326.0
125°	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9	352.1	353.5	354.7
127.5°	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6	379.0	380.3	381.7
130°	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6	396.1	397.6	399.1
132.5°	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8	413.0	414.3	415.7
135°	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2	435.8	437.3	438.8
137.5°	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0	458.0	459.1	460.2
140°	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8	472.5	473.3	474.0
142.5°	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2	484.9	485.5	486.3
145°	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7	503.6	503.5	503.4
147.5°	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7	520.4	520.0	519.7
150°	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8	531.1	530.4	529.8
152.5°	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1	540.4	539.6	538.9
155°	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6	553.8	552.9	552.1
157.5°	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2	564.5	563.8	563.1
160°	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	570.9	570.4	569.8
162.5°	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0	576.4	575.8	575.3
165°	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4	583.9	583.3	582.7
167.5°	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0	589.4	588.9	588.2
170°	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1	592.5	591.9	591.4
172.5°	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1	594.6	594.0	593.4
175°	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8	597.1	596.4	595.8
177.5°	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2	597.7	597.1	596.6
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2195.6	2191.3	2183.2	2170.8	2163.4	2150.4	2141.7	2146.7	2148.0	2146.7	2145.5
5°	2136.7	2120.4	2098.0	2076.3	2056.2	2034.5	2022.2	2016.7	2005.9	1999.6	1996.6
7.5°	2065.3	2037.3	2005.6	1967.8	1935.7	1902.2	1885.0	1876.4	1854.3	1842.3	1831.7
10°	2012.1	1967.9	1936.2	1886.7	1856.5	1812.4	1782.2	1783.0	1752.8	1735.8	1723.4
12.5°	1953.3	1904.8	1852.0	1807.5	1765.5	1730.1	1693.6	1679.0	1647.0	1630.5	1597.1
15°	1855.7	1799.3	1743.5	1683.1	1640.6	1585.7	1533.1	1468.8	1416.9	1372.1	1359.7
17.5°	1749.3	1679.3	1623.5	1552.6	1479.7	1387.3	1326.3	1289.0	1257.7	1234.1	1216.4
20°	1676.2	1605.0	1545.4	1438.7	1340.3	1277.7	1232.7	1204.2	1171.6	1146.1	1132.2
22.5°	1599.4	1525.1	1443.9	1324.7	1248.1	1197.8	1157.8	1124.9	1102.9	1083.0	1070.3
25°	1490.5	1409.2	1275.4	1193.3	1131.4	1078.7	1050.9	1030.8	1007.5	980.5	968.2
27.5°	1375.3	1246.1	1149.9	1088.9	1029.9	995.6	970.6	940.6	919.8	907.6	894.7
30°	1289.3	1160.0	1085.0	1018.4	976.6	938.7	909.3	892.3	872.1	851.2	842.7
32.5°	1193.3	1090.0	1018.1	962.7	920.3	888.0	864.7	837.2	822.6	809.8	791.9
35°	1074.1	995.9	930.2	885.3	845.1	818.8	791.6	775.4	749.1	738.3	731.3
37.5°	973.2	905.4	856.4	809.0	777.1	748.0	731.4	705.6	694.2	679.1	664.5
40°	916.3	849.7	802.5	763.8	728.2	706.5	685.6	664.8	647.7	640.8	623.0
42.5°	858.1	803.9	756.7	714.3	690.4	667.5	641.1	625.7	608.1	596.8	585.8
45°	777.7	729.7	689.5	654.7	628.3	604.4	587.3	561.8	551.8	529.4	520.1
47.5°	707.2	662.6	624.2	591.1	565.4	549.8	524.8	504.8	488.8	475.0	463.1
50°	657.0	619.9	582.7	553.3	530.1	507.7	482.1	472.0	447.3	440.3	433.3
52.5°	611.2	575.9	541.9	513.1	489.9	468.1	445.6	432.4	415.8	408.8	403.6
55°	547.1	513.1	480.6	455.0	431.8	409.4	395.5	379.2	371.4	366.1	359.8
57.5°	482.7	452.1	427.2	401.3	378.0	360.1	344.1	334.3	326.3	319.1	311.7
60°	441.9	412.4	390.0	366.1	342.0	327.3	315.0	303.4	294.1	283.3	280.1
62.5°	398.5	372.8	352.2	328.9	308.0	294.6	282.8	271.8	260.6	244.9	240.5
65°	338.9	318.8	297.2	277.8	259.2	246.1	229.0	216.7	212.1	210.5	209.7
67.5°	285.1	266.1	247.5	227.6	210.8	198.5	190.0	188.0	184.8	183.9	181.7
70°	249.2	231.4	212.8	194.2	178.0	175.7	172.6	169.5	165.6	164.1	162.5
72.5°	217.0	198.5	180.0	165.1	158.1	155.2	152.2	149.1	146.4	144.9	143.9
75°	166.4	149.4	136.9	131.6	127.6	125.3	120.7	118.4	116.8	114.5	113.7
77.5°	119.8	110.2	104.5	101.1	97.0	94.5	91.9	89.6	88.0	87.5	86.2
80°	91.3	86.6	82.8	78.2	76.6	73.5	72.7	70.4	71.2	68.9	68.9
82.5°	70.9	65.0	61.8	59.6	58.1	55.5	54.8	53.7	53.8	52.1	52.1
85°	36.4	34.8	33.3	31.7	31.7	29.4	30.2	29.4	29.4	27.9	27.1
87.5°	12.7	12.2	11.2	11.3	11.5	11.0	11.1	10.6	10.7	10.8	10.2
90°	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6	10.1	10.5	10.9
92.5°	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5	10.8	11.0	11.2
95°	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8	18.3	18.8	19.0
97.5°	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3	23.7	24.0	24.3
100°	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2	26.9	27.7	28.2
102.5°	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3	28.3	29.3	29.9
105°	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5	29.5	30.6	31.3
107.5°	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7	33.6	32.5	32.2
110°	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4	46.8	37.2	32.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6	85.5	50.6	33.2
115°	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5	133.1	88.7	63.0
117.5°	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5	262.8	252.0	235.3
120°	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7	319.8	321.0	315.1
122.5°	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1	338.8	339.5	338.6
125°	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1	366.8	367.4	367.9
127.5°	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9	392.8	393.8	394.4
130°	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3	409.3	410.4	410.9
132.5°	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2	425.1	426.0	426.4
135°	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0	447.9	448.9	449.2
137.5°	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1	469.0	469.9	470.2
140°	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7	482.6	483.4	483.6
142.5°	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3	495.1	495.9	496.0
145°	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0	512.6	513.3	513.4
147.5°	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4	527.9	528.4	528.4
150°	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8	537.3	538.0	538.1
152.5°	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4	546.0	546.6	546.5
155°	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1	557.6	558.3	558.2
157.5°	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9	567.5	568.3	568.2
160°	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6	573.2	573.8	573.7
162.5°	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9	578.7	579.3	579.2
165°	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5	585.1	585.8	585.8
167.5°	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0	590.6	591.3	591.2
170°	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7	593.4	594.0	593.9
172.5°	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7	595.4	596.1	596.0
175°	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0	597.6	598.3	598.2
177.5°	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2	597.7	598.3	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2138.7	2139.9	2138.1	2139.3	2138.1	2139.9	2138.7	2145.5	2146.7	2148.0	2146.7
5°	1992.7	1983.4	1981.9	1979.5	1981.9	1983.4	1992.7	1996.6	1999.6	2005.9	2016.7
7.5°	1818.5	1817.1	1813.2	1807.8	1813.2	1817.1	1818.5	1831.7	1842.3	1854.3	1876.4
10°	1706.4	1702.5	1701.7	1696.3	1701.7	1702.5	1706.4	1723.4	1735.8	1752.8	1783.0
12.5°	1575.1	1550.2	1547.6	1534.1	1547.6	1550.2	1575.1	1597.1	1630.5	1647.0	1679.0
15°	1341.1	1336.5	1321.0	1310.9	1321.0	1336.5	1341.1	1359.7	1372.1	1416.9	1468.8
17.5°	1207.4	1192.2	1187.4	1185.3	1187.4	1192.2	1207.4	1216.4	1234.1	1257.7	1289.0
20°	1121.4	1107.4	1105.1	1103.6	1105.1	1107.4	1121.4	1132.2	1146.1	1171.6	1204.2
22.5°	1061.9	1047.3	1041.3	1036.6	1041.3	1047.3	1061.9	1070.3	1083.0	1102.9	1124.9
25°	960.4	954.9	951.9	950.3	951.9	954.9	960.4	968.2	980.5	1007.5	1030.8
27.5°	881.0	869.1	866.8	862.7	866.8	869.1	881.0	894.7	907.6	919.8	940.6
30°	835.8	831.9	826.5	821.8	826.5	831.9	835.8	842.7	851.2	872.1	892.3
32.5°	782.5	779.3	774.5	772.3	774.5	779.3	782.5	791.9	809.8	822.6	837.2
35°	723.6	712.8	708.1	701.1	708.1	712.8	723.6	731.3	738.3	749.1	775.4
37.5°	661.2	655.5	648.9	651.3	648.9	655.5	661.2	664.5	679.1	694.2	705.6
40°	612.9	609.0	607.5	606.7	607.5	609.0	612.9	623.0	640.8	647.7	664.8
42.5°	574.5	563.8	559.8	559.7	559.8	563.8	574.5	585.8	596.8	608.1	625.7
45°	516.1	506.1	499.2	499.9	499.2	506.1	516.1	520.1	529.4	551.8	561.8
47.5°	456.5	456.2	451.8	453.1	451.8	456.2	456.5	463.1	475.0	488.8	504.8
50°	428.0	423.3	420.2	421.0	420.2	423.3	428.0	433.3	440.3	447.3	472.0
52.5°	400.7	396.7	394.3	397.5	394.3	396.7	400.7	403.6	408.8	415.8	432.4
55°	356.0	351.3	350.5	349.8	350.5	351.3	356.0	359.8	366.1	371.4	379.2
57.5°	306.0	302.9	298.2	296.2	298.2	302.9	306.0	311.7	319.1	326.3	334.3
60°	270.0	263.9	256.1	255.4	256.1	263.9	270.0	280.1	283.3	294.1	303.4
62.5°	237.2	236.0	234.5	234.3	234.5	236.0	237.2	240.5	244.9	260.6	271.8
65°	208.1	207.4	208.1	208.9	208.1	207.4	208.1	209.7	210.5	212.1	216.7
67.5°	181.4	180.0	178.6	179.3	178.6	180.0	181.4	181.7	183.9	184.8	188.0
70°	161.0	160.2	159.5	159.5	159.5	160.2	161.0	162.5	164.1	165.6	169.5
72.5°	141.2	141.0	140.3	139.6	140.3	141.0	141.2	143.9	144.9	146.4	149.1
75°	113.0	111.4	111.4	111.4	111.4	111.4	113.0	113.7	114.5	116.8	118.4
77.5°	86.0	85.2	84.5	83.9	84.5	85.2	86.0	86.2	87.5	88.0	89.6
80°	68.1	67.4	66.6	66.6	66.6	67.4	68.1	68.9	68.9	71.2	70.4
82.5°	52.0	51.2	51.1	50.5	51.1	51.2	52.0	52.1	52.1	53.8	53.7
85°	27.9	28.7	27.9	29.4	27.9	28.7	27.9	27.1	27.9	29.4	29.4
87.5°	10.3	9.7	10.3	9.8	10.3	9.7	10.3	10.2	10.8	10.7	10.6
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6
92.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5
95°	18.9	18.8	18.7	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8
97.5°	24.4	24.5	24.6	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3
100°	28.4	28.6	28.7	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2
102.5°	30.2	30.5	30.7	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3
105°	31.6	32.0	32.4	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5
107.5°	32.6	33.0	33.3	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7
110°	32.9	33.3	33.7	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6
115°	56.1	49.2	42.3	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5
117.5°	212.6	189.9	167.2	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5
120°	302.2	289.2	276.2	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7
122.5°	336.1	333.6	331.0	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1
125°	368.2	368.5	368.8	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1
127.5°	394.5	394.5	394.6	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9
130°	410.8	410.7	410.6	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3
132.5°	426.3	426.2	426.2	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2
135°	449.1	448.9	448.7	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0
137.5°	469.9	469.6	469.3	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1
140°	483.1	482.6	482.2	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7
142.5°	495.5	495.1	494.6	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3
145°	512.9	512.4	512.0	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0
147.5°	528.0	527.6	527.1	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4
150°	537.6	537.0	536.5	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8
152.5°	545.9	545.3	544.6	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4
155°	557.3	556.6	555.8	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1
157.5°	567.4	566.6	565.9	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9
160°	573.1	572.4	571.7	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6
162.5°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9
165°	585.1	584.5	583.8	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5
167.5°	590.3	589.5	588.5	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0
170°	593.1	592.2	591.4	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7
172.5°	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7
175°	597.2	596.3	595.3	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0
177.5°	597.5	596.8	596.1	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2141.7	2150.4	2163.4	2170.8	2183.2	2191.3	2195.6	2203.6	2208.0	2223.5	2239.6
5°	2022.2	2034.5	2056.2	2076.3	2098.0	2120.4	2136.7	2155.3	2172.2	2201.6	2232.6
7.5°	1885.0	1902.2	1935.7	1967.8	2005.6	2037.3	2065.3	2097.0	2125.4	2167.5	2211.4
10°	1782.2	1812.4	1856.5	1886.7	1936.2	1967.9	2012.1	2046.9	2086.4	2142.0	2191.6
12.5°	1693.6	1730.1	1765.5	1807.5	1852.0	1904.8	1953.3	1998.0	2044.9	2102.4	2160.6
15°	1533.1	1585.7	1640.6	1683.1	1743.5	1799.3	1855.7	1916.1	1973.4	2042.3	2118.1
17.5°	1326.3	1387.3	1479.7	1552.6	1623.5	1679.3	1749.3	1822.3	1889.8	1972.9	2057.3
20°	1232.7	1277.7	1340.3	1438.7	1545.4	1605.0	1676.2	1756.7	1834.0	1924.6	2015.2
22.5°	1157.8	1197.8	1248.1	1324.7	1443.9	1525.1	1599.4	1681.1	1770.9	1863.3	1963.8
25°	1050.9	1078.7	1131.4	1193.3	1275.4	1409.2	1490.5	1572.5	1670.0	1769.1	1883.6
27.5°	970.6	995.6	1029.9	1088.9	1149.9	1246.1	1375.3	1464.8	1562.0	1673.4	1792.3
30°	909.3	938.7	976.6	1018.4	1085.0	1160.0	1289.3	1393.0	1488.9	1603.5	1730.4
32.5°	864.7	888.0	920.3	962.7	1018.1	1090.0	1193.3	1319.3	1412.8	1533.5	1666.0
35°	791.6	818.8	845.1	885.3	930.2	995.9	1074.1	1208.8	1301.6	1420.8	1553.9
37.5°	731.4	748.0	777.1	809.0	856.4	905.4	973.2	1094.0	1194.4	1311.4	1447.6
40°	685.6	706.5	728.2	763.8	802.5	849.7	916.3	1006.0	1121.4	1235.9	1369.0
42.5°	641.1	667.5	690.4	714.3	756.7	803.9	858.1	934.2	1052.0	1160.3	1289.7
45°	587.3	604.4	628.3	654.7	689.5	729.7	777.7	844.2	957.3	1050.9	1172.5
47.5°	524.8	549.8	565.4	591.1	624.2	662.6	707.2	764.8	856.2	943.9	1056.6
50°	482.1	507.7	530.1	553.3	582.7	619.9	657.0	712.8	786.3	878.4	983.6
52.5°	445.6	468.1	489.9	513.1	541.9	575.9	611.2	660.1	723.1	807.8	909.9
55°	395.5	409.4	431.8	455.0	480.6	513.1	547.1	588.1	642.3	713.5	796.3
57.5°	344.1	360.1	378.0	401.3	427.2	452.1	482.7	519.9	562.6	627.0	697.9
60°	315.0	327.3	342.0	366.1	390.0	412.4	441.9	472.8	513.1	568.8	629.1
62.5°	282.8	294.6	308.0	328.9	352.2	372.8	398.5	431.3	465.4	516.1	569.1
65°	229.0	246.1	259.2	277.8	297.2	318.8	338.9	365.3	395.5	435.7	482.9
67.5°	190.0	198.5	210.8	227.6	247.5	266.1	285.1	305.7	331.8	362.9	400.4
70°	172.6	175.7	178.0	194.2	212.8	231.4	249.2	268.5	290.9	316.5	349.0
72.5°	152.2	155.2	158.1	165.1	180.0	198.5	217.0	231.4	252.6	273.8	300.1
75°	120.7	125.3	127.6	131.6	136.9	149.4	166.4	180.3	192.7	208.9	229.8
77.5°	91.9	94.5	97.0	101.1	104.5	110.2	119.8	132.3	143.9	153.4	167.7
80°	72.7	73.5	76.6	78.2	82.8	86.6	91.3	101.4	113.0	116.8	126.9
82.5°	54.8	55.5	58.1	59.6	61.8	65.0	70.9	73.5	82.6	87.8	94.1
85°	30.2	29.4	31.7	31.7	33.3	34.8	36.4	40.2	42.5	48.8	50.3
87.5°	11.1	11.0	11.5	11.3	11.2	12.2	12.7	13.1	14.1	15.8	18.1
90°	9.1	8.6	7.9	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4
92.5°	10.3	10.0	9.6	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7
95°	17.3	16.9	16.2	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1
97.5°	22.9	22.5	21.0	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6
100°	25.3	24.6	22.9	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4
102.5°	26.3	25.2	39.0	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2
105°	27.4	26.4	52.5	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2
107.5°	35.7	36.9	68.3	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7
110°	65.9	75.5	103.2	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	155.5	190.6	197.3	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3
115°	221.9	266.3	263.9	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2
117.5°	284.3	295.0	293.4	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3
120°	317.5	316.4	314.7	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2
122.5°	337.5	336.8	334.9	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4
125°	365.4	364.8	362.9	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9
127.5°	390.9	389.9	388.6	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6
130°	407.2	406.2	405.2	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6
132.5°	423.3	422.4	421.3	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8
135°	446.0	445.0	444.1	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2
137.5°	467.1	466.2	465.1	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0
140°	480.8	480.0	478.9	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8
142.5°	493.5	492.7	491.5	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2
145°	511.3	510.6	509.0	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7
147.5°	526.8	526.3	524.7	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7
150°	536.2	535.6	534.1	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8
152.5°	544.8	544.3	542.8	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1
155°	556.5	555.9	554.8	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6
157.5°	566.2	565.6	564.8	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2
160°	572.1	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5
162.5°	577.3	576.6	576.1	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0
165°	583.8	583.1	582.9	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4
167.5°	589.3	588.5	588.3	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0
170°	592.0	591.4	591.2	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1
172.5°	594.1	593.4	593.2	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1
175°	596.3	595.6	595.4	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8
177.5°	596.7	596.1	596.1	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2242.0	2254.4	2260.0	2271.2	2275.4	2280.5	2279.2	2279.2	2281.7	2299.0
5°	2245.0	2260.5	2283.7	2306.1	2327.8	2346.3	2358.7	2371.2	2375.8	2398.2	2418.3
7.5°	2237.0	2265.4	2303.8	2338.0	2379.0	2411.1	2437.7	2461.6	2478.1	2510.7	2544.2
10°	2226.4	2266.6	2310.0	2354.1	2410.5	2453.2	2496.5	2529.8	2540.6	2589.4	2617.3
12.5°	2205.3	2259.3	2314.3	2371.5	2426.7	2485.4	2533.0	2566.3	2604.3	2648.2	2699.6
15°	2173.8	2235.7	2307.6	2381.2	2460.1	2531.3	2582.4	2640.4	2682.2	2730.2	2775.1
17.5°	2128.5	2208.2	2299.7	2384.8	2476.1	2552.5	2622.8	2678.5	2708.0	2735.3	2742.0
20°	2092.5	2178.5	2286.0	2386.6	2477.9	2566.2	2635.7	2682.2	2690.0	2690.7	2649.7
22.5°	2053.6	2150.6	2263.1	2366.2	2475.5	2573.5	2627.8	2647.6	2616.9	2564.5	2485.1
25°	1981.9	2094.1	2224.8	2342.5	2461.6	2554.6	2573.1	2538.3	2430.7	2317.7	2174.5
27.5°	1904.2	2030.3	2170.5	2301.3	2428.2	2485.8	2445.7	2320.2	2126.5	1958.0	1753.9
30°	1847.2	1988.8	2126.6	2272.8	2390.5	2415.2	2323.2	2138.2	1912.2	1658.4	1454.9
32.5°	1782.2	1930.7	2082.0	2233.2	2331.7	2307.5	2155.4	1927.7	1662.7	1413.2	1220.8
35°	1689.3	1842.6	2005.9	2157.6	2220.2	2115.8	1888.2	1591.9	1321.0	1088.0	955.7
37.5°	1582.1	1749.0	1918.7	2058.0	2053.6	1879.5	1569.5	1263.5	1035.9	898.2	803.9
40°	1505.9	1674.7	1858.1	1975.7	1925.4	1698.6	1362.8	1074.1	907.8	797.9	729.0
42.5°	1432.9	1602.3	1784.4	1877.8	1790.4	1511.7	1177.1	950.9	813.6	727.9	672.1
45°	1308.6	1487.3	1656.1	1707.9	1551.6	1244.4	951.9	787.8	696.5	633.0	594.3
47.5°	1187.1	1362.9	1516.9	1517.8	1306.5	1009.2	802.9	681.8	603.8	554.7	526.5
50°	1112.8	1280.0	1409.2	1389.1	1149.2	897.7	718.1	613.7	548.7	510.8	481.3
52.5°	1029.3	1191.4	1303.3	1246.1	1016.1	789.9	642.0	554.2	500.4	467.4	441.1
55°	907.8	1051.7	1130.6	1043.9	828.8	657.0	542.5	473.6	433.3	405.5	383.0
57.5°	788.4	907.2	956.8	855.9	682.7	544.8	458.9	407.2	367.3	347.3	335.7
60°	713.5	814.9	849.7	738.3	593.6	476.7	406.3	358.3	328.9	315.8	304.2
62.5°	639.9	722.7	737.0	634.9	517.5	417.3	356.8	316.2	296.7	284.2	273.2
65°	530.9	590.5	583.5	501.5	409.4	331.2	287.1	262.4	247.6	229.8	210.5
67.5°	437.1	473.4	451.5	390.0	312.5	257.4	228.6	209.8	191.6	174.7	170.3
70°	377.7	398.5	375.4	318.8	256.1	215.9	192.7	170.3	159.5	155.5	148.6
72.5°	320.7	328.0	302.9	254.5	208.4	178.7	156.1	143.6	137.7	134.5	130.0
75°	240.7	235.3	213.6	175.7	144.7	124.6	117.6	113.0	109.1	106.0	103.7
77.5°	169.1	161.1	141.8	117.0	100.8	91.2	86.9	84.5	82.6	81.1	78.8
80°	126.9	121.5	102.2	83.6	76.6	72.0	69.7	66.6	66.6	65.0	62.7
82.5°	92.9	86.8	70.0	61.3	57.5	54.6	52.9	51.1	50.5	50.8	49.1
85°	48.8	39.5	34.8	33.3	31.0	29.4	30.2	28.7	28.7	28.7	27.9
87.5°	15.1	12.3	11.8	11.4	12.2	12.4	11.9	12.1	12.8	12.3	13.0
90°	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6
92.5°	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5
95°	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8
97.5°	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3
100°	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2
102.5°	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3
105°	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5
107.5°	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7
110°	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6
115°	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5
117.5°	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5
120°	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7
122.5°	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1
125°	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1
127.5°	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9
130°	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3
132.5°	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2
135°	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0
137.5°	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1
140°	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7
142.5°	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3
145°	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0
147.5°	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4
150°	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8
152.5°	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4
155°	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1
157.5°	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9
160°	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6
162.5°	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9
165°	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5
167.5°	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0
170°	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7
172.5°	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7
175°	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0
177.5°	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2305.2	2313.2	2316.9	2316.9	2321.3	2319.5	2317.5
5°	2437.7	2452.4	2455.5	2469.4	2479.4	2476.4	2477.9
7.5°	2569.4	2593.0	2616.5	2627.2	2628.8	2635.0	2637.4
10°	2650.5	2669.9	2706.2	2700.8	2727.8	2743.4	2717.8
12.5°	2728.5	2754.6	2779.9	2786.8	2802.2	2807.1	2797.0
15°	2799.0	2813.0	2814.6	2810.7	2815.3	2811.5	2796.7
17.5°	2733.1	2710.6	2664.7	2643.0	2625.9	2600.5	2590.3
20°	2624.1	2557.6	2480.2	2449.3	2412.9	2341.7	2358.7
22.5°	2388.9	2313.1	2235.7	2145.4	2102.1	2034.7	2030.6
25°	2022.9	1892.1	1748.2	1647.6	1588.7	1521.5	1492.0
27.5°	1572.8	1408.2	1290.2	1230.4	1176.1	1122.8	1120.5
30°	1276.9	1153.1	1061.8	1010.7	977.3	954.9	959.6
32.5°	1076.3	991.5	929.9	887.5	862.8	846.0	845.7
35°	879.9	821.8	782.3	764.6	746.8	734.4	735.2
37.5°	753.0	718.1	696.2	676.5	665.4	659.3	655.9
40°	687.9	659.3	642.3	630.7	621.4	612.9	611.4
42.5°	636.6	612.9	595.9	586.7	578.0	572.1	570.5
45°	564.9	545.5	530.1	520.1	516.1	510.8	510.8
47.5°	502.5	483.5	471.4	465.1	458.5	454.8	454.7
50°	460.5	445.8	434.9	431.0	425.7	423.3	422.5
52.5°	422.7	411.7	403.9	401.3	399.0	396.1	396.6
55°	371.4	365.3	362.1	359.8	356.0	351.3	354.5
57.5°	328.3	323.1	314.7	307.4	303.9	300.5	301.8
60°	297.9	287.1	276.3	267.7	265.4	258.4	258.4
62.5°	259.5	244.4	231.1	226.3	224.0	220.8	220.0
65°	199.7	193.5	190.4	187.2	185.7	185.7	184.2
67.5°	165.4	163.0	159.6	158.8	157.2	156.8	156.3
70°	146.2	143.2	141.6	140.9	139.3	140.1	137.7
72.5°	127.6	125.2	124.9	122.9	122.0	122.1	120.4
75°	100.6	100.6	99.9	99.1	97.6	96.7	97.6
77.5°	77.4	77.6	76.1	76.0	75.8	76.0	75.2
80°	61.9	62.7	61.9	61.1	60.4	61.1	60.4
82.5°	48.9	47.9	47.7	47.6	47.4	46.9	46.8
85°	27.9	28.7	27.9	27.1	27.1	27.1	27.9
87.5°	12.5	12.6	12.7	12.7	12.8	12.8	12.2
90°	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331845-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)