

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331803-840

Luminaire Tested: **S122RDIW-S485D1440U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331803-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7535.9 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	34	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	39	34	31	29	22	21	20	14
4	70	60	53	47	62	54	47	42	41	37	34	30	27	25	20	18	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13	10
7	55	43	35	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	17	19	16	13	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.0
10°-20°	214.2	2.8
20°-30°	300.8	4.0
30°-40°	328.0	4.4
40°-50°	301.6	4.0
50°-60°	236.8	3.1
60°-70°	154.4	2.0
70°-80°	79.6	1.1
80°-90°	25.5	0.3
90°-100°	66.2	0.9
100°-110°	242.8	3.2
110°-120°	649.0	8.6
120°-130°	1071.4	14.2
130°-140°	1139.4	15.1
140°-150°	1059.0	14.1
150°-160°	851.5	11.3
160°-170°	548.7	7.3
170°-180°	188.9	2.5
0°-30°	593.0	7.9
0°-40°	921.0	12.2
0°-60°	1459.4	19.4
0°-90°	1719.0	22.8
90°-120°	958.1	12.7
90°-150°	4227.9	56.1
90°-180°	5817.0	77.2
0°-180°	7535.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	17	29	36	39	6
95°	93	49	56	63	62	114
105°	437	456	88	103	109	467
115°	826	851	886	252	118	813
125°	1168	1187	1214	1223	1228	1041
135°	1445	1467	1481	1494	1492	1116
145°	1676	1676	1699	1708	1702	1048
155°	1846	1834	1850	1857	1847	850
165°	1945	1937	1940	1949	1940	549
175°	1989	1980	1982	1991	1978	189
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.6	9.2	8.8	8.5	8.5	9.1	9.6	10.1	10.6	10.8
90°	1.4	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3
92.5°	29.0	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1
95°	93.3	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6
97.5°	185.3	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2
100°	254.2	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4
102.5°	330.0	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5
105°	436.7	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1
107.5°	558.2	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1
110°	636.3	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	709.8	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6
115°	825.9	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4
117.5°	929.6	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8
120°	1005.4	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6
122.5°	1069.8	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9
125°	1167.7	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9
127.5°	1256.5	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8
130°	1312.7	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0
132.5°	1370.2	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6
135°	1444.9	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0
137.5°	1520.5	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3
140°	1569.8	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0
142.5°	1611.2	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2
145°	1676.2	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3
147.5°	1732.7	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0
150°	1769.5	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3
152.5°	1800.5	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0
155°	1845.6	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8
157.5°	1881.0	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3
160°	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5
162.5°	1920.0	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1
165°	1944.7	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7
167.5°	1963.1	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8
170°	1973.5	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9
172.5°	1980.3	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8
175°	1989.2	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3
177.5°	1990.6	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	10.9	11.1	11.3	11.5	11.6	11.7	11.8	12.0
90°	31.9	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	34.9	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	59.2	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	77.6	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	86.9	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	90.8	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	94.6	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	115.5	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	187.5	155.6	123.7	108.4	109.7	110.9	112.2	113.5



TEST NUMBER: P331803-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.1	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	590.7	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	910.1	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1060.5	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1125.2	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1218.1	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1304.0	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1358.6	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1411.5	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1487.1	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1557.4	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1602.9	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1644.9	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1703.5	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1754.7	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1786.2	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1814.9	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1853.7	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1886.4	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1905.4	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1923.2	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1963.0	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1972.2	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1979.0	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1986.5	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1987.3	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)