

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331768

Luminaire Tested: **S122RDIW-S290D435U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331768
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D435U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2535.8 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																												
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35																												
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	30																												
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26																												
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23																												
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20																												
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18																												
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	18	16																												
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14																												
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																												
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.9
10°-20°	129.0	5.1
20°-30°	181.2	7.1
30°-40°	197.6	7.8
40°-50°	181.6	7.2
50°-60°	142.7	5.6
60°-70°	93.0	3.7
70°-80°	48.0	1.9
80°-90°	14.6	0.6
90°-100°	34.0	1.3
100°-110°	105.7	4.2
110°-120°	180.6	7.1
120°-130°	237.5	9.4
130°-140°	266.6	10.5
140°-150°	261.4	10.3
150°-160°	219.2	8.6
160°-170°	145.4	5.7
170°-180°	50.8	2.0
0°-30°	357.2	14.1
0°-40°	554.7	21.9
0°-60°	879.0	34.7
0°-90°	1034.6	40.8
90°-120°	320.3	12.6
90°-150°	1085.7	42.8
90°-180°	1501.0	59.2
0°-180°	2535.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	0	6	16	15	15	2
95°	24	28	29	29	28	27
105°	97	99	100	101	101	103
115°	181	184	183	182	181	179
125°	264	267	266	265	265	236
135°	341	346	347	346	345	263
145°	414	417	420	420	419	259
155°	473	475	476	478	477	218
165°	515	515	515	518	516	145
175°	536	535	534	537	534	51
180°	537	537	537	537	537	



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	5.9	5.5	5.1	4.7	4.3	4.3	4.7	5.2	5.6	6.1	6.0
90°	0.5	1.7	2.9	4.1	5.3	7.0	9.2	11.4	13.6	15.9	15.7
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.4	13.9	14.4	14.4
95°	23.6	24.6	25.6	26.6	27.6	28.2	28.4	28.6	28.8	29.0	29.0
97.5°	43.0	43.9	44.8	45.7	46.6	47.2	47.6	48.0	48.4	48.7	48.7
100°	57.5	58.3	59.1	60.0	60.8	61.3	61.6	61.9	62.2	62.5	62.5
102.5°	72.8	73.4	74.0	74.7	75.3	75.9	76.2	76.6	77.0	77.4	77.5
105°	97.4	97.7	98.0	98.3	98.6	98.9	99.1	99.3	99.5	99.7	99.9
107.5°	122.2	122.7	123.1	123.6	124.0	124.2	124.2	124.2	124.2	124.2	124.3
110°	138.2	138.8	139.4	140.0	140.6	140.9	140.9	140.9	140.9	140.9	140.9



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.6	156.2	156.8	157.4	158.0	158.3	158.2	158.1	158.0	157.9	157.7
115°	181.2	181.8	182.4	183.0	183.6	183.8	183.6	183.4	183.2	183.0	182.9
117.5°	206.8	207.6	208.4	209.2	210.0	210.1	209.6	209.0	208.4	207.9	207.6
120°	223.8	224.6	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8	223.8
122.5°	239.4	240.4	241.3	242.3	243.3	243.5	242.9	242.3	241.8	241.2	241.0
125°	263.7	264.6	265.5	266.4	267.3	267.6	267.3	267.0	266.7	266.4	266.1
127.5°	287.3	288.5	289.6	290.8	291.9	292.3	292.0	291.6	291.2	290.9	290.5
130°	302.2	303.5	304.8	306.1	307.4	308.0	307.8	307.6	307.4	307.2	307.0
132.5°	318.9	319.9	321.0	322.1	323.1	323.7	323.7	323.8	323.8	323.8	323.4
135°	341.2	342.3	343.4	344.5	345.6	346.2	346.4	346.6	346.8	347.0	346.9
137.5°	364.6	365.5	366.4	367.3	368.2	368.8	369.1	369.4	369.6	369.9	369.8
140°	378.8	379.7	380.6	381.5	382.4	383.1	383.6	384.1	384.6	385.1	385.1
142.5°	393.3	394.2	395.1	396.0	396.9	397.5	397.8	398.2	398.5	398.9	399.0
145°	414.1	414.8	415.5	416.2	416.9	417.6	418.2	418.8	419.4	420.0	420.1
147.5°	432.7	433.5	434.4	435.2	436.1	436.7	437.1	437.5	437.9	438.3	438.5
150°	445.4	446.0	446.6	447.2	447.8	448.3	448.7	449.1	449.5	449.9	450.2
152.5°	456.6	457.2	457.8	458.4	459.0	459.6	460.0	460.5	461.0	461.5	461.9
155°	473.4	473.7	474.0	474.4	474.7	475.0	475.3	475.6	475.9	476.2	476.7
157.5°	487.9	488.1	488.3	488.5	488.7	488.8	489.0	489.2	489.4	489.6	490.3
160°	496.6	496.8	497.0	497.2	497.4	497.5	497.6	497.7	497.8	497.9	498.5
162.5°	504.5	504.6	504.6	504.6	504.7	504.8	504.9	505.0	505.1	505.2	505.8
165°	515.1	515.0	514.9	514.8	514.7	514.7	514.7	514.7	514.7	514.7	515.4
167.5°	524.0	523.7	523.4	523.1	522.8	522.6	522.6	522.6	522.6	522.6	523.3
170°	528.7	528.4	528.1	527.8	527.5	527.3	527.2	527.1	527.0	526.9	527.6
172.5°	532.0	531.7	531.4	531.1	530.8	530.6	530.5	530.4	530.3	530.2	530.9
175°	536.0	535.7	535.4	535.1	534.8	534.5	534.3	534.1	533.9	533.7	534.4
177.5°	537.6	537.4	537.1	536.9	536.6	536.4	536.3	536.1	535.9	535.8	536.3
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	5.8	5.7	5.6	5.5	5.6	5.6	5.6	5.6
90°	15.5	15.3	15.1	15.0	15.1	15.2	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.6	14.7	14.7
95°	29.0	29.0	29.0	28.9	28.7	28.5	28.3	28.1
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7
100°	62.5	62.5	62.5	62.5	62.4	62.3	62.2	62.1
102.5°	77.5	77.6	77.7	77.7	77.6	77.5	77.4	77.3
105°	100.1	100.3	100.5	100.6	100.6	100.6	100.6	100.6
107.5°	124.4	124.5	124.6	124.4	123.9	123.4	123.0	122.5
110°	140.9	140.9	140.9	140.7	140.4	140.1	139.8	139.5



TEST NUMBER: P331768

CATALOG NUMBER: S122RDIW-S290D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	157.2	157.0	156.7	156.5	156.3	156.1	155.9
115°	182.8	182.7	182.6	182.4	182.1	181.8	181.5	181.2
117.5°	207.4	207.1	206.9	206.6	206.3	206.0	205.7	205.4
120°	223.8	223.8	223.8	223.7	223.4	223.1	222.8	222.5
122.5°	240.7	240.5	240.2	240.0	239.8	239.6	239.3	239.1
125°	265.8	265.5	265.2	265.0	264.9	264.8	264.7	264.6
127.5°	290.1	289.8	289.4	289.1	288.7	288.4	288.1	287.8
130°	306.8	306.6	306.4	306.1	305.7	305.3	304.9	304.5
132.5°	323.0	322.5	322.1	321.7	321.4	321.0	320.7	320.4
135°	346.8	346.7	346.6	346.4	346.1	345.8	345.5	345.2
137.5°	369.7	369.6	369.6	369.3	368.9	368.5	368.1	367.7
140°	385.1	385.1	385.1	384.9	384.5	384.1	383.7	383.3
142.5°	399.0	399.1	399.2	399.0	398.6	398.2	397.8	397.4
145°	420.2	420.3	420.4	420.2	419.8	419.4	419.0	418.6
147.5°	438.7	439.0	439.2	439.1	438.7	438.3	437.9	437.6
150°	450.5	450.8	451.1	451.1	450.8	450.5	450.2	449.9
152.5°	462.2	462.6	463.0	463.0	462.6	462.2	461.9	461.5
155°	477.2	477.7	478.2	478.3	478.0	477.7	477.4	477.1
157.5°	490.9	491.6	492.3	492.4	491.9	491.4	491.0	490.5
160°	499.1	499.7	500.3	500.4	500.0	499.6	499.2	498.8
162.5°	506.5	507.2	507.9	508.0	507.5	507.0	506.5	506.1
165°	516.1	516.8	517.5	517.6	517.1	516.6	516.1	515.6
167.5°	524.0	524.7	525.4	525.5	524.9	524.4	523.9	523.4
170°	528.3	529.0	529.7	529.8	529.2	528.6	528.0	527.4
172.5°	531.6	532.3	533.0	533.0	532.4	531.8	531.2	530.6
175°	535.1	535.8	536.5	536.6	536.0	535.4	534.8	534.2
177.5°	536.8	537.2	537.7	537.7	537.2	536.8	536.3	535.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9

(END OF REPORT)