

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331804-840

Luminaire Tested: **S122RDIW-S485D1440U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331804-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D1440U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6765.8 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.2
10°-20°	214.2	3.2
20°-30°	300.8	4.4
30°-40°	328.0	4.8
40°-50°	301.6	4.5
50°-60°	236.8	3.5
60°-70°	154.4	2.3
70°-80°	79.6	1.2
80°-90°	27.8	0.4
90°-100°	114.3	1.7
100°-110°	355.0	5.2
110°-120°	606.9	9.0
120°-130°	798.1	11.8
130°-140°	895.8	13.2
140°-150°	878.3	13.0
150°-160°	736.7	10.9
160°-170°	488.6	7.2
170°-180°	170.8	2.5
0°-30°	593.0	8.8
0°-40°	921.0	13.6
0°-60°	1459.4	21.6
0°-90°	1721.3	25.4
90°-120°	1076.2	15.9
90°-150°	3648.4	53.9
90°-180°	5045.0	74.6
0°-180°	6765.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	2	21	53	50	52	5
95°	79	94	98	97	94	91
105°	327	332	335	338	338	346
115°	609	617	615	613	609	602
125°	886	899	895	891	889	791
135°	1146	1162	1166	1165	1160	885
145°	1392	1402	1411	1412	1407	869
155°	1591	1596	1600	1607	1603	732
165°	1731	1730	1730	1739	1732	488
175°	1801	1797	1793	1803	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	10.0	9.7	9.4	9.2	8.9	9.5	11.0	12.5	14.0	15.5	15.2
90°	1.5	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6
92.5°	27.1	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6
95°	79.2	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5
97.5°	144.6	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8
100°	193.4	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1
102.5°	244.5	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3
105°	327.3	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6
107.5°	410.7	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7
110°	464.3	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	522.8	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9
115°	608.9	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7
117.5°	694.9	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7
120°	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0
122.5°	804.5	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7
125°	886.1	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1
127.5°	965.5	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1
130°	1015.4	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6
132.5°	1071.5	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7
135°	1146.4	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9
137.5°	1225.3	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6
140°	1272.7	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0
142.5°	1321.5	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6
145°	1391.5	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6
147.5°	1453.9	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6
150°	1496.5	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8
152.5°	1534.3	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1
155°	1590.9	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7
157.5°	1639.3	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4
160°	1668.6	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2
162.5°	1695.4	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8
165°	1731.0	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8
167.5°	1760.8	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4
170°	1776.7	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9
172.5°	1787.7	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9
175°	1801.0	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8
177.5°	1806.5	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	14.9	14.6	14.4	14.3	14.3	14.4	14.5	14.5
90°	51.9	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.7	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.5	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	336.3	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.0	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	473.5	472.9	471.9	470.9	469.9	468.9





TEST NUMBER: P331804-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	529.1	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.4	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.9	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.9	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	893.1	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	974.9	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.9	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1085.3	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.5	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.3	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1340.9	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.0	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1474.3	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1603.5	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1649.7	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1677.2	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1702.1	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1734.2	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1760.7	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1775.3	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1786.2	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1798.2	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)